



The Maintenance Guide 2007

Standard Products - Consumables
Advice & Spare Parts - Tools & Software - Services

Instrument Express



Our efficiency serves yours

■ **Order status**
Tel.: 0161 286 5113
We take care of your order and help you in case of a mistake.

■ **Helpdesk / After sales**
Tel.: 0161 286 5113
We give you advice on the installation and the commissioning of your equipment, and also help you to select the right spare part.

By calling this number you also obtain all the information you need on our range of services.

■ **Calibration department**
Tel.: 0161 286 5000
We can help you with our calibration services (on-site calibration, factory and express factory calibration)

■ **Training department**
Tel.: 0161 286 5000
For information on our training programmes.

■ **Download area**
www.fr.endress.com
Click "Download" to access all the Endress+Hauser technical documentation and to get all the latest free versions of Endress+Hauser software.

Instruments International

Endress+Hauser GmbH+Co. KG
Instruments International
P.O. Box 2222
79574 Weil am Rhein
Germany
Tel. +49 7621 975 02
Fax +49 7621 975 345
<http://www.endress.com>
info@ii.endress.com

09.03/MMC



Need spare parts, electrodes, tools, advice or services?



Standard products, consumables and spares ultra-fast delivery!

It's simple, fast and reliable!

Contents



Trends in maintenance

The true original	4
A good night's sleep at last	6
Ready for the international market	8
Hygienic on-site calibration	10



Standard products

Conductive limit detection	12
Capacitive limit detection	13
Level limit switch for liquids	14
Level limit switch for solids	16
Float switch	17
Pressure measurement	18
Flow switch	20
Temperature measurement	21
Contactors, galvanic separator	26
Indicators	27
Recorder	30
Overvoltage protection	31



Consumables

What's new?	34
Electrode Selection Guide	35
Standard electrodes and cables	37
IP68 TOP electrodes and cables	38
ISFET electrodes	39
Compact electrodes	39
New electrodes with Variopol plug-in head	40
New Memosens technology	41
Consumables for dissolved Cl ₂ & O ₂	42
Buffer solutions	43
Stamolys service kits & reagents	44
STIP Analysers service kits & reagents	46
Paper & pens for recorders	48

Instrument-Express allows a consistent stock cost reduction - even for your most critical devices - by ensuring a short delivery time of these products.

NOTE: Availability and prices are valid for maximum three pieces per order. Please contact us before ordering larger quantities.

It's easy to place your order:

1. Specify your order number as well as all details required for delivery and invoicing.
2. In case of ordering spare parts, don't forget to mention your equipment's order code and serial number.
3. Choose your payment method:
 - By cheque with order
 - Payment within 30 days of receipt of invoice (Account holders only)
 - By credit card

4. Choose the lead time that suits you best:

- 24 Hour Service on request
Guaranteed Overnight Delivery for all orders placed before 4 pm - Please add £ 12.50
- 48 Hour Standard Service
Unless differently specified, your order is shipped the next working day to arrive within 48 hours (free postage and packaging throughout the UK)
Your Order Form is filled? Just fax it off!

Conditions of sale
Endres + Hauser's Instrument Express Conditions of sale apply. See page 101. Such conditions are considered to be valid without your written acceptance.

Guarantee
All Instrument Express products are guaranteed for 12 months from date of despatch. This guarantees parts and labour for work carried out in our Service Workshop.

Guaranteed!

Constant availability of Instrument Express products

All our products are carefully selected and we are committed to keeping them available.

Immediate processing of your order

You can order by telephone, fax or e-mail. Your order can be received 24 hours a day and is processed the same day.

Guaranteed Lead Time

Your order is delivered to you within 48 hours. For urgent orders of maximum 3 pieces, our '24 hour service' offers you the guarantee of next-day delivery throughout the UK.

No Quibble Guarantee

Our range of products is renowned for its quality and we are certain that you will be entirely satisfied with them. Please contact us immediately, should any fault be detected or if you made a mistake when placing your order. We will exchange or take your products back without further discussion, provided they are returned in original condition, within 15 days.