



A0038974

- 1 With lagging and cap nut, female thread, available in $G\frac{1}{2}$ " and $G\frac{3}{4}$ ", $\varnothing D = 9 \text{ mm (0.35 in)}$ or 12 mm (0.47 in)
- 2 With lagging, G- or M-thread version
- 3 With lagging, NPT-thread version
- 4 Without lagging, terminal head process connection, M- or G-thread version
- 5 Without lagging, terminal head process connection, NPT-thread version