# Technical Information Proline Promass F 100

Coriolis flowmeter



# The flowmeter with premium accuracy, robustness and an ultra-compact transmitter

# Application

Measuring principle operates independently of physical fluid properties such as viscosity or density

#### Device properties

- Mass flow: measured error ±0.05 % (PremiumCal)
- Pressure rating of sensor housing up to 40 bar (580 psi)
- Nominal diameter: DN 8 to 250 (<sup>3</sup>/<sub>8</sub> to 10")
- Robust, ultra-compact transmitter housing
- Highest degree of protection: IP69
- Local display available

# Your benefits

- Highest process safety immune to fluctuating and harsh environments
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no inlet/outlet run needs
- Space-saving transmitter full functionality on smallest footprint
- Time-saving local operation without additional software and hardware integrated web server
- Integrated verification Heartbeat Technology



# Table of contents

About this document	<b>4</b> 4
Function and material design	-
Function and system design	5
Measuring principle	
Measuring system	. 6 7
Equipment architecture	-
Safety	/
Input	8
Measured variable	. 8
Measuring range	. 8
Operable flow range	9
Output	9
Output signal	9
Signal on alarm	11
Ex connection data	12
Low flow cut off	13
Protocol-specific data	13
D	22
Power supply	23
Terminal assignment	23
Pin assignment, device plug	30
Supply voltage	32
Power consumption	33
Current consumption	33
Power supply failure	33
Electrical connection	34
Potential equalization	39
Terminals	39
Cable entries	39
Cable specification	39
Doutour on an about stariation	41
Performance characteristics	
reference operating conditions	41
Maximum measured error	41 43
Repeatability	
Response time	43
Influence of ambient temperature	43
Influence of medium temperature	43
Influence of medium pressure	44 44
Design fundamentals	44
Installation	45
	<b>4</b> 5
Mounting location	45 46
Orientation	40 47
Special mounting instructions	47 48
Installing the Safety Barrier Promass 100	40
Environment	49
Ambient temperature range	49
Storage temperature	49
Climate class	49
Degree of protection	49
Vibration resistance	49
	77

Shock resistance	49 49 49 49
Process . Medium temperature range . Density . Pressure-temperature curves . Secondary containment . Rupture disk . Flow limit . Pressure loss . System pressure . Thermal insulation . Heating . Vibrations .	50 50 55
Mechanical construction	87 88
Operability	<b>90</b> 90 91 91 93
Certificates and approvals	95 96 96 96
Ordering information	98
Application packages	<b>98</b> 98 99 99
Accessories	<b>99</b> 99 100 101

Supplementary documentation	101
Standard documentation	101
Supplementary device-dependent documentation	102

Registered trademarks ..... 102

# About this document

# Symbols used

# Electrical symbols

Symbol	Meaning
	Direct current
$\sim$	Alternating current
8	Direct current and alternating current
<u>+</u>	<b>Ground connection</b> A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective Earth (PE) A terminal which must be connected to ground prior to establishing any other connections.
	<ul><li>The ground terminals are situated inside and outside the device:</li><li>Inner ground terminal: Connects the protectiv earth to the mains supply.</li><li>Outer ground terminal: Connects the device to the plant grounding system.</li></ul>

# Symbols for certain types of information

Symbol	Meaning
	<b>Permitted</b> Procedures, processes or actions that are permitted.
	<b>Preferred</b> Procedures, processes or actions that are preferred.
×	<b>Forbidden</b> Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
<u></u>	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.


#### Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections
EX	Hazardous area
X	Safe area (non-hazardous area)
≈➡	Flow direction

# Function and system design

Measuring principle	The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.
	$F_c = 2 \cdot \Delta m (v \cdot \omega)$
	$F_c = Coriolis force$
	$\Delta m = moving mass$
	$\omega = rotational velocity$
	v = radial velocity in rotating or oscillating system
	The amplitude of the Coriolis force depends on the moving mass $\Delta m$ , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity $\omega$ , the sensor uses oscillation.
	In the sensor, two parallel measuring tubes containing flowing fluid oscillate in antiphase, acting like a tuning fork. The Coriolis forces produced at the measuring tubes cause a phase shift in the tube oscillations (see illustration): • At zero flow (when the fluid is at a standstill) the two tubes oscillate in phase (1).

- At zero flow (when the fluid is at a standstill) the two tubes oscillate in phase (1).
- Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).



The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is ensured by the antiphase oscillation of the two measuring tubes. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

#### **Density measurement**

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.

# Volume measurement

Together with the measured mass flow, this is used to calculate the volume flow.

#### **Temperature measurement**


The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.

#### Measuring system


The device consists of a transmitter and a sensor. If a device with Modbus RS485 intrinsically safe is ordered, the Safety Barrier Promass 100 is part of the scope of supply and must be implemented to operate the device.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.


#### Transmitter




#### Sensor



#### Safety Barrier Promass 100



#### Equipment architecture



- Possibilities for integrating measuring devices into a system
- 1 Control system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 PROFINET
- 5 Modbus RS485
- 6 4-20 mA HART, pulse/frequency/switch output
- 7 Safety Barrier Promass 100
- 8 Modbus RS485 intrinsically safe
- 9 Non-hazardous area
- 10 Non-hazardous area and Zone 2/Div. 2
- 11 Hazardous area and Zone 1/Div. 1

Safety

#### IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

# Input

### Measured variable

# Direct measured variables

- Mass flow
- Density
- Temperature

# Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

# Measuring range

# Measuring ranges for liquids

DN		Measuring range full scale values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$	
[mm]	[in]	[kg/h]	[lb/min]
8	3⁄8	0 to 2 000	0 to 73.50
15	1/2	0 to 6 500	0 to 238.9
25	1	0 to 18000	0 to 661.5
40	11/2	0 to 45 000	0 to 1654
50	2	0 to 70000	0 to 2 573
80	3	0 to 180 000	0 to 6615
100	4	0 to 350 000	0 to 12860
150	6	0 to 800 000	0 to 29 400
250	10	0 to 2 200 000	0 to 80850

# Measuring ranges for gases

The full scale values depend on the density of the gas and can be calculated with the formula below:  $\dot{m}_{max(G)} = \dot{m}_{max(F)} \cdot \rho_G$ : x

m <sub>max(G)</sub>	Maximum full scale value for gas [kg/h]
m <sub>max(F)</sub>	Maximum full scale value for liquid [kg/h]
$\dot{m}_{max(G)} < \dot{m}_{max(F)}$	$\dot{m}_{max(G)}$ can never be greater than $\dot{m}_{max(F)}$
βG	Gas density in [kg/m³] at operating conditions
х	Constant dependent on nominal diameter

DN		x
[mm]	[in]	[kg/m³]
8	3/8	60
15	1⁄2	80
25	1	90
40	1½	90
50	2	90
80	3	110
100	4	130

DN		x
[mm]	[in]	[kg/m <sup>3</sup> ]
150	6	200
250	10	200

To calculate the measuring range, use the Applicator sizing tool  $\rightarrow \square$  100

#### Calculation example for gas

- Sensor: Promass F, DN 50
- Gas: Air with a density of 60.3 kg/m<sup>3</sup> (at 20 °C and 50 bar)
- Measuring range (liquid): 70000 kg/h
- $x = 90 \text{ kg/m}^3$  (for Promass F, DN 50)

Maximum possible full scale value:

 $\dot{m}_{max(G)} = \dot{m}_{max(F)} \cdot \rho_{G}$ : x = 70000 kg/h · 60.3 kg/m<sup>3</sup> : 90 kg/m<sup>3</sup> = 46900 kg/h

#### Recommended measuring range

"Flow limit" section  $\rightarrow \square 56$ 

Operable flow range

#### Over 1000 : 1.

Flow rates above the preset full scale value do not override the electronics unit, with the result that the totalizer values are registered correctly.

# Output

Output signal

#### HART current output

Current output	4-20 mA HART (active)
Maximum output values	<ul> <li>DC 24 V (no flow)</li> <li>22.5 mA</li> </ul>
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Adjustable: 0.07 to 999 s
Assignable measured variables	<ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>

#### Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	<ul> <li>DC 30 V</li> <li>25 mA</li> </ul>
Voltage drop	For 25 mA: ≤ DC 2 V
Pulse output	
Pulse width	Adjustable: 0.05 to 2 000 ms

Maximum pulse rate	10 000 Impulse/s
Pulse value	Adjustable
Assignable measured variables	<ul><li>Mass flow</li><li>Volume flow</li><li>Corrected volume flow</li></ul>
Frequency output	
Output frequency	Adjustable: 0 to 10 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	<ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	<ul> <li>Off</li> <li>On</li> <li>Diagnostic behavior</li> <li>Limit value <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>Totalizer 1-3</li> </ul> </li> <li>Flow direction monitoring</li> <li>Status <ul> <li>Partially filled pipe detection</li> <li>Low flow cut off</li> </ul> </li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>

# PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud

### Modbus RS485

Physical interface	In accordance with EIA/TIA-485-A standard
Terminating resistor	<ul> <li>For device version used in non-hazardous areas or Zone 2/Div. 2: integrated and can be activated via DIP switches on the transmitter electronics module</li> <li>For device version used in intrinsically safe areas: integrated and can be activated via DIP switches on the Safety Barrier Promass 100</li> </ul>

#### EtherNet/IP

Standards	In accordance with IEEE 802.3

# PROFINET

Standards In accordance with IEEE 802.3	
---	--

# Signal on alarm

Depending on the interface, failure information is displayed as follows:

# Current output 4 to 20 mA

4 to 20 mA

Failure mode	Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Freely definable value between: 3.59 to 22.5 mA Actual value Last valid value
--------------	---

#### Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from: • Actual value • No pulses
Frequency output	
Failure mode	Choose from: • Actual value • 0 Hz • Defined value: 0 to 12 500 Hz
Switch output	
Failure mode	Choose from: • Current status • Open • Closed

#### PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

# Modbus RS485

Failure mode	Choose from:
	<ul><li>NaN value instead of current value</li><li>Last valid value</li></ul>

### EtherNet/IP

iput Assembly
put Assembly

#### PROFINET

Device diagnostics	According to "Application Layer protocol for decentralized periphery", Version 2.3
--------------------	--

#### Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.

Status signal as per NAMUR recommendation NE 107

#### Interface/protocol

- Via digital communication:
  - HART protocol
  - PROFIBUS DP
  - Modbus RS485
- EtherNet/IP
- PROFINET
- Via service interface CDI-RJ45 service interface

Plain text display	With information on cause and remedial measures
--------------------	---

Additional information on remote operation  $\rightarrow \cong 91$ 

#### Web server

Plain text display	With information on cause and remedial measures
--------------------	---

#### Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes	
	The following information is displayed depending on the device version: <ul> <li>Supply voltage active</li> </ul>	
	<ul> <li>Supply voltage active</li> <li>Data transmission active</li> </ul>	
	<ul> <li>Device alarm/error has occurred</li> </ul>	
	<ul> <li>EtherNet/IP network available</li> </ul>	
	<ul> <li>EtherNet/IP connection established</li> </ul>	
	<ul> <li>PROFINET network available</li> </ul>	
	<ul> <li>PROFINET connection established</li> </ul>	
	<ul> <li>PROFINET blinking feature</li> </ul>	

#### Ex connection data

These values only apply for the following device version: Order code for "Output", option M "Modbus RS485", for use in intrinsically safe areas

#### Safety Barrier Promass 100

Safety-related values

Terminal numbers			
Supply voltage		Signal tra	nsmission
2 (L-)	1 (L+)	26 (A) 27 (B)	
U <sub>nom</sub> = DC 24 V U <sub>max</sub> = AC 260 V		U <sub>nom</sub> = U <sub>max</sub> = A	DC 5 V .C 260 V

#### Intrinsically safe values

Terminal numbers			
Supply voltage		Signal transmission	
20 (L-)	20 (L-) 10 (L+)		72 (B)
$\begin{split} U_{o} &= 16.24 \text{ V} \\ I_{o} &= 623 \text{ mA} \\ P_{o} &= 2.45 \text{ W} \\ \end{split}$ With IIC <sup>1)</sup> : $L_{o} &= 92.8 \ \mu\text{H}, \ C_{o} &= 0.433 \ \mu\text{F}, \ L_{o}/R_{o} &= 14.6 \ \mu\text{H}/\Omega \\ \end{aligned}$ With IIB: $L_{o} &= 372 \ \mu\text{H}, \ C_{o} &= 2.57 \ \mu\text{F}, \ L_{o}/R_{o} &= 58.3 \ \mu\text{H}/\Omega \end{split}$			
For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device			

1) The gas group depends on the sensor and nominal diameter ff.

#### Transmitter

Intrinsically safe values

Order code for	Terminal numbers			
"Approval"	Supply voltage		Signal transmission	
	20 (L-)	10 (L+)	62 (A)	72 (B)
<ul> <li>Option BM: ATEX II2G + IECEX Z1 Ex ia, II2D Ex tb</li> <li>Option BO: ATEX II1/2G + IECEX Z0/Z1 Ex ia, II2D</li> <li>Option BQ: ATEX II1/2G + IECEX Z0/Z1 Ex ia</li> <li>Option BU: ATEX II2G + IECEX Z1 Ex ia</li> <li>Option C2: CSA C/US IS Cl. I, II, III Div. 1</li> <li>Option 85: ATEX II2G + IECEX Z1 Ex ia + CSA C/US IS Cl. I, II, III Div. 1</li> </ul>		$\begin{array}{c} U_{i} = 1 i \\ I_{i} = 62 \\ P_{i} = 2 \\ L_{i} = 0 \\ C_{i} = 0 \end{array}$	23 mA .45 W 0 μH	
For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device				

Low flow cut off

The switch points for low flow cut off are user-selectable.

Protocol-specific data

# HART

Manufacturer ID	0x11
Device type ID	0x4A
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable) <ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> </ul>
	Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1 Totalizer 2 Totalizer 3 The range of options increases if the measuring device has one or more application packages.
	<ul> <li>Heartbeat Technology application package</li> <li>Additional measured variables are available with the Heartbeat Technology application package:</li> <li>Carrier pipe temperature</li> <li>Oscillation amplitude 0</li> </ul>
Device variables	Read out the device variables: HART command 9The device variables are permanently assigned.A maximum of 8 device variables can be transmitted:• 0 = mass flow• 1 = volume flow• 2 = corrected volume flow• 3 = density• 4 = reference density• 5 = temperature• 6 = totalizer 1• 7 = totalizer 2• 8 = totalizer 3• 13 = target mass flow• 14 = carrier mass flow
	<ul> <li>14 currentiation</li> <li>15 = concentration</li> </ul>

# PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1561
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org

Output values	Analog input 1 to 8 <ul> <li>Mass flow</li> </ul>
(from measuring device to	<ul> <li>Mass flow</li> <li>Volume flow</li> </ul>
automation system)	<ul> <li>Corrected volume flow</li> </ul>
	<ul> <li>Target mass flow</li> </ul>
	<ul> <li>Carrier mass flow</li> </ul>
	<ul><li>Density</li></ul>
	<ul> <li>Reference density</li> </ul>
	<ul> <li>Concentration</li> </ul>
	<ul> <li>Temperature</li> </ul>
	<ul> <li>Carrier pipe temperature</li> </ul>
	Electronic temperature
	<ul> <li>Oscillation frequency</li> </ul>
	<ul> <li>Oscillation amplitude</li> </ul>
	<ul> <li>Frequency fluctuation</li> </ul>
	<ul> <li>Oscillation damping</li> </ul>
	<ul> <li>Tube damping fluctuation</li> </ul>
	<ul> <li>Signal asymmetry</li> </ul>
	<ul> <li>Exciter current</li> </ul>
	Digital input 1 to 2
	<ul> <li>Partially filled pipe detection</li> </ul>
	<ul> <li>Low flow cut off</li> </ul>
	Totalizer 1 to 3
	<ul> <li>Mass flow</li> </ul>
	<ul> <li>Volume flow</li> </ul>
	<ul> <li>Corrected volume flow</li> </ul>
Input values	Analog output 1 to 3 (fixed assignment)
(from automation system to	<ul> <li>Pressure</li> </ul>
measuring device)	<ul><li>Temperature</li></ul>
incusaring acvice,	<ul> <li>Reference density</li> </ul>
	Digital output 1 to 3 (fixed assignment)
	<ul> <li>Digital output 1: switch positive zero return on/off</li> </ul>
	<ul> <li>Digital output 2: perform zero point adjustment</li> </ul>
	<ul> <li>Digital output 3: switch switch output on/off</li> </ul>
	Totalizer 1 to 3
	<ul> <li>Totalize</li> </ul>
	<ul> <li>Reset and hold</li> </ul>
	<ul> <li>Preset and hold</li> </ul>
	<ul> <li>Stop</li> </ul>
	<ul> <li>Operating mode configuration:</li> </ul>
	– Net flow total
	<ul> <li>Forward flow total</li> </ul>
	<ul> <li>Reverse flow total</li> </ul>
Supported functions	Identification & Maintenance
••	Simplest device identification on the part of the control system and
	nameplate
	<ul> <li>PROFIBUS upload/download</li> </ul>
	Reading and writing parameters is up to ten times faster with PROFIBUS
	upload/download
	<ul> <li>Condensed status</li> </ul>
	Simplest and self-explanatory diagnostic information by categorizing
	diagnostic messages that occur
Configuration of the device	<ul> <li>DIP switches on the I/O electronics module</li> </ul>
address	<ul> <li>Via operating tools (e.g. FieldCare)</li> </ul>
address	<ul> <li>via operating tools (e.g. FieldCare)</li> </ul>

#### Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0

Function codes	<ul> <li>03: Read holding register</li> <li>04: Read input register</li> <li>06: Write single registers</li> <li>08: Diagnostics</li> <li>16: Write multiple registers</li> <li>23: Read/write multiple registers</li> </ul>	
Broadcast messages	<ul> <li>Supported by the following function codes:</li> <li>06: Write single registers</li> <li>16: Write multiple registers</li> <li>23: Read/write multiple registers</li> </ul>	
Supported baud rate	<ul> <li>1 200 BAUD</li> <li>2 400 BAUD</li> <li>4 800 BAUD</li> <li>9 600 BAUD</li> <li>19 200 BAUD</li> <li>38 400 BAUD</li> <li>57 600 BAUD</li> <li>115 200 BAUD</li> </ul>	
Data transfer mode	<ul><li>ASCII</li><li>RTU</li></ul>	
Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information, see "Description of device parameters" documentation	

#### EtherNet/IP

Protocol	<ul> <li>The CIP Networks Library Volume 1: Common Industrial Protocol</li> <li>The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP</li> </ul>
Communication type	<ul><li>10Base-T</li><li>100Base-TX</li></ul>
Device profile	Generic device (product type: 0x2B)
Manufacturer ID	0x49E
Device type ID	0x104A
Baud rates	Automatic $^{10}\!\!\gamma_{100}$ Mbit with half-duplex and full-duplex detection
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported CIP connections	Max. 3 connections
Explicit connections	Max. 6 connections
I/O connections	Max. 6 connections (scanner)
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module for IP addressing</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>Electronic Data Sheet (EDS) integrated in the measuring device</li> </ul>
Configuration of the EtherNet interface	<ul> <li>Speed: 10 MBit, 100 MBit, auto (factory setting)</li> <li>Duplex: half-duplex, full-duplex, auto (factory setting)</li> </ul>
Configuration of the device address	<ul> <li>DIP switches on the electronics module for IP addressing (last octet)</li> <li>DHCP</li> <li>Manufacturer-specific software (FieldCare)</li> <li>Add-on Profile Level 3 for Rockwell Automation control systems</li> <li>Web browser</li> <li>EtherNet/IP tools, e.g. RSLinx (Rockwell Automation)</li> </ul>
Device Level Ring (DLR)	No

זמת	1			
RPI	5 ms to 10 s (factory setting: 20 ms)			
Exclusive Owner Multicast		Instance	Size [byte]	
	Instance configuration:	0x68	398	
	$O \rightarrow T$ configuration:	0x66	64	
	$T \rightarrow O$ configuration:	0x64	44	
Exclusive Owner Multicast		Instance	Size [byte]	
	Instance configuration:	0x69	-	
	$0 \rightarrow T$ configuration:	0x66	64	
	$T \rightarrow O$ configuration:	0x64	44	
Input only Multicast		Instance	Size [byte]	
	Instance configuration:	0x68	398	
	$O \rightarrow T$ configuration:	0xC7	-	
	$T \rightarrow O$ configuration:	0x64	44	
Input only Multicast		Instance	Size [byte]	
	Instance configuration:	0x69	-	
	$O \rightarrow T$ configuration:	0xC7	-	
	$T \rightarrow O$ configuration:	0x64	44	
	<ul><li>Temperature</li><li>Totalizer 1</li></ul>			
	<ul><li>Totalizer 2</li><li>Totalizer 3</li></ul>			
Configurable Input				
Configurable Input RPI		20 ms)		
	Totalizer 3	20 ms) Instance	Size [byte]	
RPI	Totalizer 3		Size [byte] 398	
RPI	Totalizer 3     5 ms to 10 s (factory setting: 2	Instance		
RPI	Totalizer 3      5 ms to 10 s (factory setting: 2      Instance configuration:	Instance 0x68	398	
RPI	Totalizer 3      5 ms to 10 s (factory setting: 2      Instance configuration:     O → T configuration:	Instance 0x68 0x66	398 64 88	
RPI Exclusive Owner Multicast	Totalizer 3      5 ms to 10 s (factory setting: 2      Instance configuration:     O → T configuration:	Instance 0x68 0x66 0x65	398 64 88	
RPI Exclusive Owner Multicast	Totalizer 3      5 ms to 10 s (factory setting: 2      Instance configuration:     O → T configuration:     T → O configuration:	Instance 0x68 0x66 0x65 Instance	398 64 88	
RPI Exclusive Owner Multicast	Totalizer 3      5 ms to 10 s (factory setting: 2      Instance configuration:     O → T configuration:     T → O configuration:     Instance configuration:	Instance 0x68 0x66 0x65 Instance 0x69	398 64 88 Size [byte] -	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	• Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration: T $\rightarrow O$ configuration: Instance configuration: $O \rightarrow T$ configuration: $O \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66	398 64 88 Size [byte] - 64 88	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	• Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: $O \rightarrow T$ configuration: T $\rightarrow O$ configuration: Instance configuration: $O \rightarrow T$ configuration: $O \rightarrow T$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65	398 64 88 Size [byte] - 64 88	
RPI Exclusive Owner Multicast	• Totalizer 35 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration:Instance configuration: $0 \rightarrow T$ configuration: $1$ $1$ $0 \rightarrow T$ configuration: $1$ $0 \rightarrow T$ configuration: $1$ $0 \rightarrow T$ configuration: $1 \rightarrow 0$ configuration: $1 \rightarrow 0$ configuration: $1 \rightarrow 0$ configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance	398 64 88 Size [byte] - 64 88 Size [byte]	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	<ul> <li>Totalizer 3</li> <li>5 ms to 10 s (factory setting: 2</li> <li>Instance configuration:</li> <li>O → T configuration:</li> <li>T → O configuration:</li> <li>O → T configuration:</li> <li>T → O configuration:</li> <li>T → O configuration:</li> <li>Instance configuration:</li> <li>Instance configuration:</li> <li>Instance configuration:</li> </ul>	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance 0x68	398 64 88 Size [byte] - 64 88 Size [byte]	
RPI Exclusive Owner Multicast Exclusive Owner Multicast	• Totalizer 35 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration:Instance configuration: $0 \rightarrow T$ configuration: $1$ $1$ $0 \rightarrow T$ configuration: $1 \rightarrow 0$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration:	Instance           0x68           0x66           0x65           Instance           0x69           0x65           0x65           0x66           0x65           0x65           0x65           0x65           0x65           0x65           0x65           0x67	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88	
RPI Exclusive Owner Multicast Exclusive Owner Multicast Input only Multicast	• Totalizer 35 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration:Instance configuration: $0 \rightarrow T$ configuration: $1$ $1$ $0 \rightarrow T$ configuration: $1 \rightarrow 0$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration: $0 \rightarrow T$ configuration:	Instance           0x68           0x66           0x65           Instance           0x66           0x65           Instance           0x65           0x65           0x65           0x65           0x65           0x65           0x68           0x67           0x65	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88	
RPI Exclusive Owner Multicast Exclusive Owner Multicast Input only Multicast	• Totalizer 35 ms to 10 s (factory setting: 2Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration:Instance configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration: $0 \rightarrow T$ configuration: $T \rightarrow 0$ configuration:	Instance           0x68           0x66           0x65           Instance           0x69           0x65           0x65           0x65           0x65           0x65           0x65           0x65           Instance           0x65           Instance           0x68           0x65           0x65	64 88 Size [byte] - 64 88 Size [byte] 398 -	

Configurable Input Assembly	<ul> <li>Current device diagnostics</li> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Density</li> <li>Reference density</li> <li>Temperature</li> <li>Totalizer 1</li> <li>Totalizer 2</li> <li>Totalizer 3</li> <li>The range of options increases if the measuring device has one or more application packages.</li> </ul>
Fix Output	
Output Assembly	<ul> <li>Activation of reset totalizers 1-3</li> <li>Activation of pressure compensation</li> <li>Activation of reference density compensation</li> <li>Activation of temperature compensation</li> <li>Reset totalizers 1-3</li> <li>External pressure value</li> <li>Pressure unit</li> <li>External reference density</li> <li>Reference density unit</li> <li>External temperature</li> <li>Temperature unit</li> </ul>
Configuration	
Configuration Assembly	Only the most common configurations are listed below.         Software write protection         Mass flow unit         Mass unit         Volume flow unit         Volume unit         Corrected volume flow unit         Corrected volume unit         Density unit         Reference density unit         Temperature unit         Pressure unit         Length         Totalizer 1-3:         Assignment         Unit         Operating mode         Failsafe mode

# PROFINET

Protocol	"Application layer protocol for decentral device periphery and distributed automation", version 2.3
Conformity class	В
Communication type	100 MBit/s
Device profile	Application interface identifier 0xF600 Generic device
Manufacturer ID	0x11
Device type ID	0x844A
Device description files (GSD, DTM)	Information and files under: • www.endress.com On the product page for the device: Documents/Software → Device drivers • www.profibus.org
Baud rates	Automatic 100 Mbit/s with full-duplex detection

Cycle times	From 8 ms
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported connections	<ul> <li>1 x AR (Application Relation)</li> <li>1 x Input CR (Communication Relation)</li> <li>1 x Output CR (Communication Relation)</li> <li>1 x Alarm CR (Communication Relation)</li> </ul>
Configuration options for measuring device	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>Manufacturer-specific software (FieldCare, DeviceCare)</li> <li>Web browser</li> <li>Device master file (GSD), can be read out via the integrated Web server of the measuring device</li> </ul>
Configuration of the device name	<ul> <li>DIP switches on the electronics module, for device name assignment (last part)</li> <li>DCP protocol</li> </ul>
Output values (from measuring device to automation system)	Analog Input module (slot 1 to 14)Mass flowVolume flowCorrected volume flowTarget mass flowCarrier mass flowDensityReference densityConcentrationTemperatureCarrier pipe temperatureElectronic temperatureOscillation frequencyOscillation amplitudeFrequency fluctuationOscillation dampingTube damping fluctuationSignal asymmetryExciter current
	Discrete Input module (slot 1 to 14) <ul> <li>Empty pipe detection</li> <li>Low flow cut off</li> </ul> <li>Diagnostics Input module (slot 1 to 14) <ul> <li>Last diagnostics</li> <li>Current diagnosis</li> </ul> </li> <li>Totalizer 1 to 3 (slot 15 to 17)</li>
	<ul> <li>Mass flow</li> <li>Volume flow</li> <li>Corrected volume flow</li> <li>Heartbeat Verification module (fixed assignment)</li> </ul>
	Verification status (slot 23) The range of options increases if the measuring device has one or more application packages.

<b>Input values</b> (from automation system to measuring device)	<ul> <li>Analog Output module (fixed assignment)</li> <li>External pressure (slot 18)</li> <li>External temperature (slot 19)</li> <li>External reference density (slot 20)</li> <li>Discrete Output module (fixed assignment)</li> <li>Activate/deactivate positive zero return (slot 21)</li> <li>Perform zero point adjustment (slot 22)</li> </ul>
	Totalizer 1 to 3 (slot 15 to 17)  Totalize  Reset and hold  Preset and hold  Stop  Operating mode configuration:  Net flow total  Forward flow total  Reverse flow total
	Heartbeat Verification module (fixed assignment) Start verification (slot 23)
	The range of options increases if the measuring device has one or more application packages.
Supported functions	<ul> <li>Identification &amp; Maintenance Simple device identification via: <ul> <li>Control system</li> <li>Nameplate</li> </ul> </li> <li>Measured value status The process variables are communicated with a measured value status</li> <li>Blinking feature via the local display for simple device identification and assignment</li> </ul>

# Administration of software options

Input/output value	Process variable	Category	Slot	
Output value	Mass flow	Process variable	1 to 14	
	Volume flow			
	Corrected volume flow			
	Density			
	Reference density			
	Temperature			
	Electronic temperature			
	Oscillation frequency			
	Frequency fluctuation			
	Oscillation damping			
	Oscillation frequency			
	Signal asymmetry			
	Exciter current			
	Empty pipe detection			
	Low flow cut off			
	Current device diagnostics			
	Previous device diagnostics			
Output value	Target mass flow	Concentration <sup>1)</sup>	1 to 14	
	Carrier mass flow			
	Concentration			
Output value	Carrier pipe temperature	Heartbeat <sup>2)</sup>	1 to 14	

Input/output value	Process variable	Category	Slot
	Oscillation damping 1		
	Oscillation frequency 1		
	Oscillation amplitude 0		
	Oscillation amplitude 1		
	Frequency fluctuation 1		
	Tube damping fluctuation 1		
	Exciter current 1		
Input value	External density	Process monitoring	18
	External temperature		19
	External reference density		20
	Flow override		21
	Zero point adjustment		22
	Status verification	Heartbeat Verification <sup>2)</sup>	23

Only available with the "Concentration" application package. Only available with the "Heartbeat" application package. 1) 2)


Startup configuration (NSU)	If startup configuration is enabled, the configuration of the most important device parameters is taken from the automation system and used.
(1450)	
	The following configuration is taken from the automation system: <ul> <li>Management</li> </ul>
	- Software revision
	- Write protection
	<ul> <li>System units</li> </ul>
	- Mass flow
	- Mass
	- Volume flow
	- Volume
	<ul> <li>Corrected volume flow</li> </ul>
	<ul> <li>Corrected volume</li> </ul>
	– Density
	<ul> <li>Reference density</li> </ul>
	– Temperature
	- Pressure
	<ul> <li>Concentration application package</li> </ul>
	<ul> <li>Coefficients A0 to A4</li> </ul>
	<ul> <li>Coefficients B1 to B3</li> </ul>
	<ul> <li>Sensor adjustment</li> </ul>
	<ul> <li>Process parameter</li> </ul>
	<ul> <li>Damping (flow, density, temperature)</li> </ul>
	– Flow override
	Low flow cut off
	<ul> <li>Assign process variable</li> </ul>
	- Switch-on/switch-off point
	<ul> <li>Pressure shock suppression</li> </ul>
	<ul> <li>Empty pipe detection</li> </ul>
	<ul> <li>Assign process variable</li> <li>Limit unluce</li> </ul>
	- Limit values
	<ul> <li>Response time</li> <li>Max. damping</li> </ul>
	<ul> <li>Corrected volume flow calculation</li> </ul>
	<ul> <li>External reference density</li> </ul>
	<ul> <li>Fixed reference density</li> </ul>
	<ul> <li>Reference temperature</li> </ul>
	<ul> <li>Linear expansion coefficient</li> </ul>
	<ul> <li>Square expansion coefficient</li> </ul>
	<ul> <li>Measuring mode</li> </ul>
	– Medium
	– Gas type
	<ul> <li>Reference sound velocity</li> </ul>
	<ul> <li>Temperature coefficient sound velocity</li> </ul>
	<ul> <li>External compensation</li> </ul>
	- Pressure compensation
	- Pressure value
	<ul> <li>External pressure</li> </ul>
	<ul> <li>Diagnostic settings</li> </ul>
	<ul> <li>Diagnostic behavior for diverse diagnostic information</li> </ul>

# Startup configuration

# Power supply

Terminal assignment

Overview: housing version and connection versions



- *A Housing version: compact, aluminum coated*
- *B* Housing version: compact, hygienic, stainless
- C Housing version: ultra-compact, hygienic, stainless
- 1 Connection version: 4-20 mA HART, pulse/frequency/switch output
- 1.1 Signal transmission: pulse/frequency/switch output
- 1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage
- 2 Connection version: Modbus RS485
- 2.1 Signal transmission
- 2.2 Supply voltage
- 3 Connection versions: EtherNet/IP and PROFINET
- 3.1 Signal transmission
- 3.2 Supply voltage
- 4 Connection version: PROFIBUS DP
- 4.1 Signal transmission
- 4.2 Supply voltage

#### Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output

Order code for "Output", option  ${\boldsymbol{B}}$ 


Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Onden ee de	Connection methods available		Dessible entions for order order	
Order code "Housing"	Outputs	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option D: thread NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>	
Options A, B	Device plugs → 🗎 31	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT <sup>1</sup>/<sub>2</sub>"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Options A, B, C	Device plugs → 🗎 31	Device plugs $\rightarrow {31}$	Option <b>Q</b> : 2 x plug M12x1	

Option  $\boldsymbol{A}\!\!:\! \text{compact, coated aluminum}$ 

- Option **B**: compact, hygienic, stainless

• Option **C** ultra-compact, hygienic, stainless



₽ 2 Terminal assignment 4-20 mA HART with pulse/frequency/switch output

- 1 Power supply: DC 24 V
- 2
- Output 1: 4-20 mA HART (active) Output 2: pulse/frequency/switch output (passive) 3

	Terminal number					
Order code "Output"	Power supply		Output 1		Output 2	
	2 (L-)	1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)
Option <b>B</b>	DC 24 V		4-20 mA HART (active)		Pulse/frequ output (	,
Order code for "Output": Option <b>B</b> : 4-20 mA HART with pulse/frequency/switch output						

PROFIBUS DP connection version

For use in the non-hazardous area and Zone 2/Div. 2

Order code for "Output", option  $\boldsymbol{L}$ 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.


Onden es de	Connection me	thods available	
Order code "Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option D: thread NPT <sup>1</sup>/<sub>2</sub>"</li> </ul>
Options A, B	Device plug connectors → 🗎 31	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>
Options A, B, C	Device plug connectors → 🗎 31	Device plug connectors → 🗎 31	Option <b>Q</b> : 2 x plug M12x1

Order code for "Housing":

• Option A: compact, coated aluminum

• Option **B**: compact, hygienic, stainless

• Option **C** ultra-compact, hygienic, stainless



- 🛃 3 PROFIBUS DP terminal assignment
- Power supply: DC 24 V PROFIBUS DP 1
- 2

	Terminal number				
Order code	Power supply		Output		
"Output"	2 (L-)	1 (L+)	26 (RxD/TxD-P)	27 (RxD/TxD- N)	
Option L	DC 2	24 V	В	А	
Order code for "Output": Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/Div. 2					

Modbus RS485 connection version

For use in the non-hazardous area and Zone 2/Div. 2

# Order code for "Output", option ${\boldsymbol{M}}$


Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Orden ee de	Connection me	thods available	Describle antices for order or de
Order code "Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>
Options A, B	Device plugs → 🗎 31	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT <sup>1</sup>/<sub>2</sub>"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G <sup>1</sup>/<sub>2</sub>"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>
Options A, B, C	Device plugs → 🖺 31	Device plugs → 🖺 31	Option <b>Q</b> : 2 x plug M12x1
Order code for "Hou	sina".		

Order code for "Housing":

- Option  $\boldsymbol{A}{:}$  compact, coated aluminum

Option B: compact, hygienic, stainless
Option C: ultra-compact, hygienic, stainless



€ 4 Modbus RS485 terminal assignment, connection version for use in non-hazardous areas and Zone 2/Div. 2

Power supply: DC 24 V 1

Modbus RS485 2

	Terminal number					
Order code "Output"	Power supply		Output			
Catpat	1 (L+)	2 (L-)	26 (B)	27 (A)		
Option <b>M</b>	DC 24 V		Modbus	s RS485		
Order code for "Output":						

Option M: Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2

Modbus RS485 connection version

For use in the intrinsically safe area. Connection via Safety Barrier Promass 100.

Order code for "Output", option **M** 

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Onden se de	Connection me	thods available	Dessible entires for order as de	
Order code "Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Terminals	Terminals	<ul> <li>Option A: coupling M20x1</li> <li>Option B: thread M20x1</li> <li>Option C: thread G ½"</li> <li>Option D: thread NPT ½"</li> </ul>	
A, B, C	Device plugs → 🗎 31		Option I: plug M12x1	
Order code for "Hou		∃ J1		

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option **B**: compact, hygienic, stainless
- Option **C** ultra-compact, hygienic, stainless




Image: Source State S

- 1 Intrinsically safe power supply
- 2 Modbus RS485

Order code "Output"	10 (L+)	20 (L-)	62 (B)	72 (A)
Option <b>M</b>	Intrinsically safe supply voltage		Modbus RS485	intrinsically safe
Order code for "Output":				

Option M: Modbus RS485, for use in the intrinsically safe area (connection via Safety Barrier Promass 100)


#### EtherNet/IP connection version

#### Order code for "Output", option N

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code	Connection me	thods available	Describle entions for order so de
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Device plug connectors → 🗎 32	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>
Options A, B, C	Device plug connectors → 🗎 32	Device plug connectors → 🗎 32	Option <b>Q</b> : 2 x plug M12x1
Order code for "Hou	sing":	1	

- Option A: compact, coated aluminum
  Option B: compact, hygienic, stainless
- Option **C** ultra-compact, hygienic, stainless



፼ 6 EtherNet/IP terminal assignment

Power supply: DC 24 V 1

EtherNet/IP 2

	Terminal number				
Order code "Output"	Power supply		Output		
	2 (L-)	1 (L+)	Device plug M12x1		
Option N	DC 24 V		EtherNet/IP		
Order code for "Output": Option <b>N</b> : EtherNet/IP					

#### PROFINET connection version

Order code for "Output", option **R** 


Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Outen este	Connection me	thods available	Dessible entions for order and	
Order code "Housing"	Output	Power supply	Possible options for order code "Electrical connection"	
Options A, B	Device plug connectors → 🖺 30	Terminals	<ul> <li>Option L: plug M12x1 + thread NPT ½"</li> <li>Option N: plug M12x1 + coupling M20</li> <li>Option P: plug M12x1 + thread G ½"</li> <li>Option U: plug M12x1 + thread M20</li> </ul>	
Options A, B, C	Device plug connectors → 🗎 30	Device plug connectors → 🗎 30	Option <b>Q</b> : 2 x plug M12x1	

Order code for "Housing":

Option A: compact, coated aluminum
Option B: compact, hygienic, stainless


• Option **C** ultra-compact, hygienic, stainless



- 7 PROFINET terminal assignment
- Power supply: DC 24 V 1
- 2 PROFINET

	Terminal number				
Order code "Output"	Power supply		Output		
	2 (L-)	1 (L+)	Device plug M12x1		
Option R	DC 24 V		PROFINET		
Order code for "Output": Option <b>R</b> : PROFINET					

#### Safety Barrier Promass 100



- EtherNet/IP  $\rightarrow$   $\cong$  28
- PROFINET → 🗎 29

# Supply voltage

For all connection versions except MODBUS RS485 intrinsically safe (device side)

P Device plug MODBUS RS485 intrinsically safe with supply voltage → 🗎 31


2	Pin	Assignment		
	1	L+	DC 24 V	
	2		Not assigned	
	3		Not assigned	
5	4	L-	DC 24 V	
4 A0029042	5		Grounding/shielding	
	Cod	ling	Plug/socket	
	I	Ą	Plug	

The following is recommended as a socket:

- Binder, series 763, part no. 79 3440 35 05
- Alternatively: Phoenix part no. 1669767 SAC-5P-M12MS
  - With the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
     With the order code for "Output", option N: EtherNet/IP
- When using the device in a hazardous location: Use a suitably certified socket.

#### 4-20 mA HART with pulse/frequency/switch output

Device plug for signal transmission (device side)



 Recommended plug: Binder, series 763, part no. 79 3439 12 05 **i** 


• When using the device in a hazardous location, use a suitably certified plug.

#### PROFIBUS DP

-

For use in the non-hazardous area and Zone 2/Div. 2.

Device plug for signal transmission (device side)



**i** 

Recommended plug: Binder, series 763, part no. 79 4449 20 05When using the device in a hazardous location, use a suitably certified plug.


#### MODBUS RS485

Device plug for signal transmission with supply voltage (device side), MODBUS RS485 (intrinsically safe)

2	Pin		Assignment
	1	L+	Supply voltage, intrinsically safe
	2	А	Modbus RS485 intrinsically safe
	3	В	Moubus K3405 Intrinsically safe
5	4	L-	Supply voltage, intrinsically safe
4 A0029042	5		Grounding/shielding
	Cod	ling	Plug/socket
	А		Plug

Recommended socket: Binder, series 763, part no. 79 3439 12 05
 When using the device in a hazardous location: Use a suitably certified socket.

Device plug for signal transmission (device side), MODBUS RS485 (not intrinsically safe) For use in the non-hazardous area and Zone 2/Div. 2.



• Recommended plug: Binder, series 763, part no. 79 4449 20 05

• When using the device in a hazardous location, use a suitably certified plug.

#### EtherNet/IP

Device plug for signal transmission (device side)


2	Pin		Assignment
$\sim$	1	+	Тх
	2	+	Rx
	3	-	Тх
	4	-	Rx
4 A0016812	Coding		Plug/socket
	D		Socket

Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

#### PROFINET

Device plug for signal transmission (device side)



Recommended plug:

- Binder, series 763, part no. 99 3729 810 04
- Phoenix, part no. 1543223 SACC-M12MSD-4Q
- When using the device in a hazardous location, use a suitably certified plug.

Supply voltage

The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV).

#### Transmitter

For device version with communication type:

- HART, PROFIBUS DP, EtherNet/IP: DC 20 to 30 V
- Modbus RS485, device version:
  - For use in the non-hazardous area and Zone 2/Div. 2: DC 20 to 30 V
  - For use in the intrinsically safe area: power supply via Safety Barrier Promass 100

#### Promass 100 safety barrier

DC 20 to 30 V

Transmitter

#### Power consumption

Order code for "Output"	Maximum Power consumption
Option <b>B</b> : 4-20 mA HART with pulse/frequency/switch output	3.5 W
Option L: PROFIBUS DP	3.5 W
Option <b>M</b> Modbus RS485, for use in non-hazardous areas and Zone 2/ Div. 2	3.5 W
Option <b>M</b> : Modbus RS485, for use in intrinsically safe areas	2.45 W
Option N: EtherNet/IP	3.5 W
Option R: PROFINET	3.5 W

Promass 100 safety barrier

Order code for "Output"		Maximum Power consumption	
	Option ${\bf M}$ : Modbus RS485, for use in intrinsically safe areas	4.8 W	

#### **Current consumption**

#### Transmitter

Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option <b>B</b> : 4-20mA HART, pul./freq./switch output	145 mA	18 A (< 0.125 ms)
Option L: PROFIBUS DP	145 mA	18 A (< 0.125 ms)
Option <b>M</b> Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2	90 mA	10 A (< 0.8 ms)
Option <b>M</b> : Modbus RS485, for use in intrinsically safe areas	145 mA	16 A (< 0.4 ms)
Option <b>N</b> : EtherNet/IP	145 mA	18 A (< 0.125 ms)
Option R: PROFINET	145 mA	18 A (< 0.125 ms)

#### Promass 100 safety barrier


Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option $\mathbf{M}$ : Modbus RS485, for use in intrinsically safe areas	230 mA	10 A (< 0.8 ms)

#### Power supply failure

Depending on the device version, the configuration is retained in the device memoryor in the pluggable data memory (HistoROM DAT).

# **Electrical connection**

### Connecting the transmitter



- A Housing version: compact, aluminum coated
- B Housing version: compact hygienic, stainless
- 1 Cable entry or device plug for signal transmission
- 2 Cable entry or device plug for supply voltage
- C Housing version: ultra-compact, hygienic, stainless, M12 device plug
- 3 Device plug for signal transmission
- 4 Device plug for supply voltage


• Terminal assignment  $\rightarrow \cong 23$ 

Pin assignment, device plug→ 🖺 30

In the case of device versions with a connector, the transmitter housing does not need to be opened to connect the signal cable or power supply cable.


#### **Connection examples**

Current output 4 to 20 mA HART



Connection example for 4 to 20 mA HART current output (active)


- 1 Automation system with current input (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 🗎 39
- 3 Connection for HART operating devices  $\rightarrow \square 91$
- 4 Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load
- 5 Analog display unit: observe maximum load
- 6 Transmitter



■ 10 Connection example for 4 to 20 mA HART current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications  $\rightarrow \cong 39$
- 4 Analog display unit: observe maximum load
- 5 Transmitter


#### Pulse/frequency output



11 Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values  $\rightarrow \square 9$


#### Switch output



■ 12 Connection example for switch output (passive)

- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply 3 Transmitter: 0
- 3 Transmitter: Observe input values

PROFIBUS DP




I3 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Transmitter

If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

Modbus RS485


Modbus RS485, non-hazardous area and Zone 2/Div. 2



■ 14 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications → 🗎 39
- 3 Distribution box
- 4 Transmitter


Modbus RS485 intrinsically safe



🛃 15 Connection example for Modbus RS485 intrinsically safe

- 1 Control system (e.g. PLC)
- Cable shield, observe cable specifications
- 2 3 Safety Barrier Promass 100
- 4 Observe cable specifications
- 5 6 Non-hazardous area
- Non-hazardous area and Zone 2/Div. 2
- 7 Intrinsically safe area
- 8 Transmitter


#### EtherNet/IP




 16 Connection example for EtherNet/IP

- 1 Control system (e.g. PLC)
- 2 3 Ethernet switch
- Observe cable specifications
- 4 Device plug
- 5 Transmitter


#### PROFINET





- Control system (e.g. PLC) 1
- 2 3
- Ethernet switch Observe cable specifications
- 4 Device plug
- 5 Transmitter

#### HART input



🛃 18 Connection example for HART input (burst mode) via current output (active)

- 1 Cable shield, observe cable specifications
- Resistor for HART communication ( $\geq 250 \Omega$ ): observe maximum load 2
- 3 Connection for HART operating devices Analog display unit
- 4
- 5 Transmitter
- 6 Sensor for external measured variable

	$\begin{bmatrix} 1 & 2 & 3 & 4 & 5 \\ & 4 & 20 \text{ mA} \\ & 4 & 20 \text{ mA} \\ & & & & & & & & & & & & \\ & & & & & $				
	<ul> <li>In Connection example for HART input (master mode) via current output (active)</li> <li>Automation system with current input (e.g. PLC). Prerequisite: automation system with HART version 6, HART commands 113 and 114 can be processed.</li> <li>Cable shield, observe cable specifications</li> <li>Resistor for HART communication (≥ 250 Ω): observe maximum load</li> <li>Connection for HART operating devices</li> <li>Analog display unit</li> <li>Transmitter</li> <li>Sensor for external measured variable</li> </ul>				
Potential equalization	Requirements				
	No special measures for potential equalization are required.				
	<ul> <li>Please consider the following to ensure correct measurement:</li> <li>Same electrical potential for the fluid and sensor</li> <li>Company-internal grounding concepts</li> <li>For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA).</li> </ul>				
Terminals	<b>Transmitter</b> Spring terminals for wire cross-sections0.5 to 2.5 mm <sup>2</sup> (20 to 14 AWG)				
	<b>Promass 100 safety barrier</b> Plug-in screw terminals for wire cross-sections0.5 to 2.5 mm <sup>2</sup> (20 to 14 AWG)				
Cable entries	<ul> <li>Cable gland: M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in)</li> <li>Thread for cable entry: <ul> <li>M20</li> <li>G ½"</li> <li>NPT ½"</li> </ul> </li> </ul>				
Cable specification	Permitted temperature range				
	<ul><li>The installation guidelines that apply in the country of installation must be observed.</li><li>The cables must be suitable for the minimum and maximum temperatures to be expected.</li></ul>				
	<ul> <li>The cables must be suitable for the minimum and maximum temperatures to be expected.</li> </ul>				
	<ul> <li>The cables must be suitable for the minimum and maximum temperatures to be expected.</li> <li>Power supply cable</li> </ul>				
	Power supply cable				
	Power supply cable Standard installation cable is sufficient. Signal cable				
	<b>Power supply cable</b> Standard installation cable is sufficient.				
	Power supply cable Standard installation cable is sufficient. Signal cable Current output 4 to 20 mA HART				

#### PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz
Cable capacitance	< 30 pF/m
Wire cross-section	> 0.34 mm <sup>2</sup> (22 AWG)
Cable type	Twisted pairs
Loop resistance	<110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

#### Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 $\Omega$ at a measuring frequency of 3 to 20 MHz
Cable capacitance	< 30 pF/m
Wire cross-section	> 0.34 mm <sup>2</sup> (22 AWG)
Cable type	Twisted pairs
Loop resistance	<110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.

#### EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.

For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization

#### PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.

For more information on planning and installing PROFINET networks, see: "PROFINET Cabling and Interconnection Technology", Guideline for PROFINET

#### Connecting cable between Safety Barrier Promass 100 and measuring device

51	Shielded twisted-pair cable with 2x2 wires. When grounding the cable shield, observe the grounding concept of the plant.
Maximum cable resistance	2.5 Ω, one side



Comply with the maximum cable resistance specifications to ensure the operational reliability of the measuring device.

The maximum cable length for individual wire cross-sections is specified in the table below. Observe the maximum capacitance and inductance per unit length of the cable and connection values for hazardous areas .

Wire cross-section		Maximum cable length		
[mm <sup>2</sup> ]	[mm <sup>2</sup> ] [AWG]		[ft]	
0.5	20	70	230	
0.75	18	100	328	
1.0	17	100	328	
1.5	16	200	656	
2.5	14	300	984	

## **Performance characteristics**

reference operating conditions	<ul> <li>Error limits based on ISO 11631</li> <li>Water with +15 to +45 °C (+59 to +113 °F) at2 to 6 bar (29 to 87 psi)</li> <li>Specifications as per calibration protocol</li> <li>Accuracy based on accredited calibration rigs that are traced to ISO 17025.</li> </ul>				
	To obtain measured errors, us	e the Applicator sizing tool $\rightarrow$	₿ 100		
Maximum measured error	o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$ ;	T = medium temperature			
	Base accuracy				
	Design fundamentals $\rightarrow \cong 44$				
	Mass flow and volume flow (liquids)				
	$\pm 0.05$ % o.r. (PremiumCal; order code for "Calibration flow", option D, for mass flow) $\pm 0.10$ % o.r.				
	Mass flow (gases)				
	±0.35 % o.r.				
	Density (liquids)				
	Under reference operating conditions	Standard density calibration <sup>1)</sup>	Wide-range Density specification <sup>2) 3)</sup>		
	[g/cm³]	[g/cm <sup>3</sup> ]	[g/cm <sup>3</sup> ]		
	±0.0005	±0.01	±0.001		

a) and range for special density calibration. 0 to 2 g/cm , +5 to +60 C (+41 to +1/6 F)
 a) order code for "Application package", option EE "Special density" only in combination with the order code for "Measuring tube mat., wetted surface", option BB, BF, HA, SA

Temperature

±0.5 °C ± 0.005 · T °C (±0.9 °F ± 0.003 · (T – 32) °F)

### Zero point stability

D	N	Zero poin	t stability
[mm]	[in]	[kg/h]	[lb/min]
8	3/8	0.030	0.001
15	1/2	0.200	0.007
25	1	0.540	0.019
40	1½	2.25	0.083
50	2	3.50	0.129
80	3	9.0	0.330
100	4	14.0	0.514
150	6	32.0	1.17
250	10	88.0	3.23

### Flow values

Flow values as turndown parameter depending on nominal diameter.

#### SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
8	2 000	200	100	40	20	4
15	6 5 0 0	650	325	130	65	13
25	18000	1800	900	360	180	36
40	45 000	4 500	2250	900	450	90
50	70000	7000	3 500	1400	700	140
80	180000	18000	9000	3 600	1800	360
100	350000	35000	17 500	7 000	3 500	700
150	800000	80000	40000	16000	8000	1600
250	2 200 000	220000	110000	44000	22000	4400

#### US units


DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
3/8	73.50	7.350	3.675	1.470	0.735	0.147
1/2	238.9	23.89	11.95	4.778	2.389	0.478
1	661.5	66.15	33.08	13.23	6.615	1.323
1½	1654	165.4	82.70	33.08	16.54	3.308
2	2 5 7 3	257.3	128.7	51.46	25.73	5.146
3	6615	661.5	330.8	132.3	66.15	13.23
4	12860	1286	643.0	257.2	128.6	25.72
6	29400	2940	1470	588	294	58.80
10	80850	8085	4043	1617	808.5	161.7

Accuracy of outputs

	can be ignored for fi	must be factored into the measured error if analog outputs are used, but eldbus outputs (e.g. Modbus RS485, EtherNet/IP). owing base accuracy specifications.			
	Current output				
	Accuracy	Max. ±5 µA			
	Pulse/frequency output				
	o.r. = of reading				
	Accuracy	Max. ±50 ppm o.r. (over the entire ambient temperature range)			
Repeatability	o.r. = of reading; 1 g/cm <sup>3</sup>	= 1 kg/l; T = medium temperature			
	Base repeatability				
	Design fundamental	s → 🗎 44			
	Mass flow and volume flo	w (liquids)			
	±0.025 % o.r. (PremiumC ±0.05 % o.r.	al, for mass flow)			
	Mass flow (gases)				
	±0.25 % o.r.				
	Density (liquids)				
	±0.00025 g/cm <sup>3</sup>				
	Temperature				
	±0.25 °C ± 0.0025 · T °C (±0.45 °F ± 0.0015 · (T−32) °F)				
Response time	The response time depend	ds on the configuration (damping).			
Influence of ambient	Current output				
temperature	o.r. = of reading				
	Temperature coefficient	Max. ±0.005 % o.r./°C			
	Pulse/frequency output				
	Temperature coefficient	No additional effect. Included in accuracy.			
Influence of medium	Mass flow and volume fl	ow			
temperature	o.f.s. = of full scale value				
	When there is a difference between the temperature for zero point adjustment and the process temperature, the additional measured error of the sensor is typically $\pm 0.0002 \%$ o.f.s./°C ( $\pm 0.0001 \%$ o.f.s./°F).				
	The effect is reduced if ze	ro point adjustment is performed at process temperature.			
	temperature, the typical n	e between the density calibration temperature and the process neasured error of the sensor is 000025 g/cm <sup>3</sup> /°F). Field density calibration is possible.			

#### Wide-range density specification (special density calibration)

If the process temperature is outside the valid range ( $\rightarrow \square 41$ ) the measured error is ±0.00005 g/cm<sup>3</sup> /°C (±0.000025 g/cm<sup>3</sup> /°F)



MeasValue = measured value; ZeroPoint = zero point stability


Calculation of the maximum measured error as a function of the flow rate

Flow rate	Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	± BaseAccu
< ZeroPoint BaseAccu · 100	$\pm \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$

Calculation of the maximum repeatability as a function of the flow rate

Flow rate	Maximum repeatability in % o.r.	
$\geq \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$	± BaseRepeat	A0021340
AOC	1335	
$< \frac{\frac{1}{2} \cdot \text{ZeroPoint}}{\text{BaseRepeat}} \cdot 100$	$\pm \frac{1}{2} \cdot \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$	
AOC	1336	A0021337

#### Example for maximum measured error




*E* Maximum measured error in % o.r. (example with PremiumCal)

*Q* Flow rate in % of maximum full scale value

## Installation

No special measures such as supports etc. are necessary. External forces are absorbed by the construction of the device.

#### Mounting location




To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

#### Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



20 Installation in a down pipe (e.g. for batching applications)

1 Supply tank

- 2 Sensor
- 3 Orifice plate, pipe restriction
- 4 Valve
- 5 Batching tank

D	N	Ø orifice plate,	pipe restriction
[mm]	[in]	[mm]	[in]
8	<sup>3</sup> / <sub>8</sub>	6	0.24
15	1/2	10	0.40
25	1	14	0.55
40	11/2	22	0.87
50	2	28	1.10
80	3	50	1.97
100	4	65	2.60
150	6	90	3.54
250	10	150	5.91

Orientation


The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).


	Orientatio	n	Recommendation	
A	Vertical orientation			
В	Horizontal orientation, transmitter at top	A0015589	$ \overrightarrow{\mathbf{V}}^{1)} $ Exceptions: $ \overrightarrow{\mathbf{P}} \ \ 21, \ \overrightarrow{\mathbf{P}} \ \ 47 $	

	Orientatio	Recommendation	
С	Horizontal orientation, transmitter at bottom		$\mathbf{\nabla}^{(2)}$ Exceptions: $\rightarrow \mathbf{E}$ 21, $\mathbf{E}$ 47
D	Horizontal orientation, transmitter at side	A0015590	×

- 1) Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.
- 2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

If a sensor is installed horizontally with a curved measuring tube, match the position of the sensor to the fluid properties.





1 Rupture disk label

2 Rupture disk with 1/2" NPT internal thread with 1" width across flat

3 Transport protection

For information on the dimensions: see the "Mechanical construction -> Accessories" section

#### Zero point adjustment

All measuring devices are calibrated in accordance with state-of-the-art technology. Calibration takes place under reference conditions  $\rightarrow \textcircled{B} 41$ . Therefore, a zero point adjustment in the field is generally not required.

Experience shows that zero point adjustment is advisable only in special cases:

- To achieve maximum measuring accuracy even with low flow rates.
- Under extreme process or operating conditions (e.g. very high process temperatures or very high-viscosity fluids).




Image: Minimum distance between additional Safety Barrier Promass 100 or other modules. Engineering unit mm (in)

Ambient temperature range	Measuring device	<ul> <li>-40 to +60 °C (-40 to +140 °F)</li> <li>Order code for "Test, certificate", option JM:</li> <li>-50 to +60 °C (-58 to +140 °F)</li> </ul>					
	Safety Barrier Promass 100	-40 to +60 °C (-40 to +140 °F)					
	<ul> <li>If operating outdoors: Avoid direct sunlight, particularly in warm climatic regions.</li> </ul>						
Storage temperature		rably at +20 °C (+68 °F) (standard version)					
	–50 to +80 °C (–58 to +176 °F) (Orde	r code for " <i>l'est, certificate</i> ", option JM)					
Climate class	DIN EN 60068-2-38 (test Z/AD)						
Degree of protection	<ul> <li>Transmitter and sensor</li> <li>As standard: IP66/67, type 4X encl</li> <li>With the order code for "Sensor opt</li> <li>When housing is open: IP20, type 1</li> <li>Display module: IP20, type 1 enclose</li> </ul>	ions", option <b>CM</b> : IP69 can also be ordered . enclosure					
	Safety Barrier Promass 100 IP20						
Vibration resistance	<ul> <li>Oscillation, sinusoidal, following IE</li> <li>2 to 8.4 Hz, 3.5 mm peak</li> <li>8.4 to 2 000 Hz, 1 g peak</li> <li>Oscillation, broadband noise follow</li> <li>10 to 200 Hz, 0.003 g<sup>2</sup>/Hz</li> <li>200 to 2 000 Hz, 0.001 g<sup>2</sup>/Hz</li> <li>Total: 1.54 g rms</li> </ul>						
Shock resistance	Shock, half-sine according to IEC 600 6 ms 30 g	68-2-27					
Shock resistance	Shock due to rough handling followin	g IEC 60068-2-31					
Interior cleaning	<ul> <li>Cleaning in place (CIP)</li> <li>Sterilization in place (SIP)</li> <li>Options</li> <li>Oil- and grease-free version for wet Order code for "Service", option HA</li> <li>Oil- and grease-free version for wet declaration Order code for "Service", option HB</li> </ul>	tted parts, without declaration tted parts as per IEC/TR 60877-2.0 and BOC 50000810-4, with					
Electromagnetic compatibility (EMC)	Volume 2, IEC 61784 The following applies for PROFI	P: JR Recommendation 21 (NE 21) JR Recommendation 21 (NE 21) ndustry as per EN 55011 (Class A) Complies with emission limits for industry as per EN 50170 BUS DP: If baud rates > 1.5 MBaud, an EMC cable entry must be ontinue as far as the terminal wherever possible.					


## Environment

## Process

#### Medium temperature range

Standard version	–50 to +150 °C (–58 to +302 °F)	Order code for "Measuring tube mat., wetted surface", option <b>HA</b> , <b>SA</b> , <b>SB</b> , <b>SC</b>
Extended temperature version	–50 to +240 °C (–58 to +464 °F)	Order code for "Measuring tube mat., wetted surface", option <b>SD</b> , <b>SE, SF, TH</b>

#### Dependency of ambient temperature on medium temperature



*■ 23 Exemplary representation, values in the table below.* 

- *T<sub>a</sub> Ambient temperature*
- $T_m$  Medium temperature
- A Maximum permitted medium temperature  $T_m$  at  $T_{a max} = 60 \degree C$  (140 °F); higher medium temperatures  $T_m$  require a reduced ambient temperature  $T_a$
- *B* Maximum permitted ambient temperature  $T_a$  for the maximum specified medium temperature  $T_m$  of the sensor

Values for devices used in the hazardous area: Separate Ex documentation (XA) for the device .


	Not insulated			Insulated					
	A		В		A		В		
Version	Ta	T <sub>m</sub>	Ta	T <sub>m</sub>	Ta	T <sub>m</sub>	Ta	T <sub>m</sub>	
Standard version	60 °C (140 °F)	150 ℃ (302 ℉)	-	-	60 °C (140 °F)	110 °C (230 °F)	55 ℃ (131 °F)	150 °C (302 °F)	
Extended temperature version	60 °C (140 °F)	170 ℃ (338 °F)	55 ℃ (131 ℉)	240 °C (464 °F)	60 °C (140 °F)	110 °C (230 °F)	50 ℃ (122 ℉)	240 °C (464 °F)	

#### Density


#### 0 to 5000 kg/m $^3$ (0 to 312 lb/cf)

Pressure-temperature curves


The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.




Flange according to EN 1092-1 (DIN 2501)




🗷 24 With flange material 1.4404 (F316/F316L), Alloy C22






With flange material 1.4404 (F316/F316L)




■ 26 With flange material Alloy C22

#### Flange JIS B2220




🖻 27 With flange material 1.4404 (F316/F316L), Alloy C22



#### Flange DIN 11864-2 Form A


■ 28 With connection material 1.4404 (316/316L)

#### Lap joint flange according to EN 1092-1 (DIN 2501)




29 With flange material 1.4301 (F304); wetted parts Alloy C22






🗷 30 With flange material 1.4301 (F304); wetted parts Alloy C22

#### Lap joint flange JIS B2220





☑ 31 With flange material 1.4301 (F304); wetted parts Alloy C22

#### Thread DIN 11851





DIN 11851 allows for applications up to +140  $^{\circ}$ C (+284  $^{\circ}$ F) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.






☑ 33 With connection material 1.4404 (316/316L)





■ 34 With connection material 1.4404 (316/316L)


#### Thread SMS 1145



■ 35 With connection material 1.4404 (316/316L)


SMS 1145 allows for applications up to 16 bar (232 psi) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

#### VCO



■ 36 With connection material 1.4404 (316/316L)

#### Tri-Clamp



The clamp connections are suitable up to a maximum pressure of 16 bar (232 psi). Please observe the operating limits of the clamp and seal used as they can be over 16 bar (232 psi). The clamp and seal are not included in the scope of supply.

 Secondary containment
 For the Standard version with the temperature range -50 to +150 °C (-58 to +302 °F), the sensor housing is filled with dry nitrogen gas and protects the electronics and mechanics inside.

 For all other temperature versions the sensor housing is filled with dry inert gas.

 The following secondary containment pressure ratings/burst pressures are only valid for standard devices and/or devices equipped with closed purge connections (never opened/as delivered).

 If a device fitted with purge connections (order code for "Sensor option", option CH "Purge connection") is connected to the purge system, the maximum nominal pressure is determined by the

purge system itself or by the device, depending on which component has the lower nominal pressure classification.

If the device is fitted with a rupture disk (order code for "Sensor option", option **CA** "Rupture disk"), the rupture disk trigger pressure is decisive for the maximum nominal pressure  $\rightarrow \cong 56$ .

The secondary containment burst pressure refers to a typical internal pressure achieved prior to mechanical failure of the secondary containment as determined during type testing. The corresponding type test declaration can be ordered with the device (order code for "Additional approval", option **LN** "Type test containment").

D	N	pressur	a safety factor	Secondary containment burst pressure		
[mm]	[in]	[bar]	[psi]	[bar]	[psi]	
8	3/8	40	580	255	3698	
15	1/2	40	580	200	2 900	
25	1	40	580	280	4060	
40	1½	40	580	180	2610	
50	2	40	580	195	2828	
80	3	25	362	105	1522	
100	4	16	232	85	1232	
150	6	16	232	80	1160	
250	10	10	145	57	826	

If a measuring tube fails (e.g. due to process characteristics like corrosive or abrasive fluids), the fluid will be contained by the secondary containment.

If there is a need to drain the leaking medium into a discharge device, the sensor should be fitted with a rupture disk. Connect the discharge to the additional threaded connection  $\rightarrow \square$  77.

If the sensor is to be purged with gas (gas detection), it should be equipped with purge connections.

Do not open the purge connections unless the containment can be filled immediately with a dry, inert gas. Use only low pressure to purge. Maximum pressure: 5 bar (72.5 psi).

In case of a tube failure, the pressure level inside the secondary containment will rise according to the operating process pressure. If the user judges that the secondary containment pressure rating/ burst pressure does not provide an adequate safety margin, the device can be fitted with a rupture disk. This prevents excessively high pressure from forming inside the secondary containment. Therefore, the use of a rupture disk is strongly recommended in applications involving high gas pressures, and particularly in applications in which the process pressure is greater than 2/3 of the secondary containment burst pressure.

For information on the dimensions: see the "Mechanical construction" section

Rupture diskTo increase the level of safety, a device version with a rupture disk with a trigger pressure of<br/>10 to 15 bar (145 to 217.5 psi)can be used (order code for "Sensor option", option CA "rupture disk").<br/>Rupture disks cannot be combined with the separately available heating jacket .<br/>Special mounting instructions: → 🗎 47<br/>For information on the dimensions: → 🗎 77

Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.

For an overview of the full scale values for the measuring range, see the "Measuring range" section  $\rightarrow \cong 8$ 

	<ul> <li>The minimum recommended full scale value is approx. 1/20 of the maximum full scale value</li> <li>In most applications, 20 to 50 % of the maximum full scale value can be considered ideal</li> <li>A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity &lt; 1 m/s (&lt; 3 ft/s).</li> <li>For gas measurement the following rules apply: <ul> <li>The flow velocity in the measuring tubes should not exceed half the sound velocity (0.5 Mach).</li> <li>The maximum mass flow depends on the density of the gas: formula → 🗎 8</li> </ul> </li> <li>To calculate the flow limit, use the Applicator sizing tool → 🖺 100</li> </ul>
Pressure loss	To calculate the pressure loss, use the <i>Applicator</i> sizing tool $\rightarrow \cong 100$
	Promass F with reduced pressure loss: order code for "Sensor option", option <b>CE</b> "reduced pressure loss"
System pressure	It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.
	<ul><li>For this reason, the following mounting locations are recommended:</li><li>At the lowest point in a vertical pipe</li><li>Downstream from pumps (no danger of vacuum)</li></ul>
Thermal insulation	A0028777 In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.
	<ul> <li>The following device versions are recommended for versions with thermal insulation:</li> <li>Version with extended neck for insulation:</li> <li>Order code for "Sensor option", option CG with an extended neck length of 105 mm (4.13 in).</li> <li>Extended temperature version:</li> <li>Order code for "Measuring tube material", option SD, SE, SF or TH with an extended neck length of 105 mm (4.13 in).</li> </ul>
	<ul> <li>NOTICE</li> <li>Electronics overheating on account of thermal insulation!</li> <li>Recommended orientation: horizontal orientation, transmitter housing pointing downwards.</li> <li>Do not insulate the transmitter housing .</li> <li>Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F)</li> <li>Thermal insulation with extended neck free: the insulation is omitted around the extended neck. We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat.</li> </ul>

■ 37 Thermal insulation with extended neck free

Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

#### Heating options

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam
- Via heating jackets



#### NOTICE


#### Danger of overheating when heating

- ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- Ensure that convection takes place on a sufficiently large scale at the transmitter neck.
- Ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations

The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

## Mechanical construction



Order code for "Housing", option A "Compact, aluminum, coated"

DN	<sup>1)</sup> A	<sup>1)</sup> B	С	D	E <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	148	94	54	75	185	260	136	5.35	4)	70
15	148	94	54	75	185	260	136	8.30	4)	70
25	148	94	54	75	185	260	136	12.0	4)	70
40	148	94	54	105	189.5	294.5	136	17.6	4)	79
50	148	94	54	141	199.5	340.5	136	26.0	4)	99
80	148	94	54	200	219.5	419.5	136	40.5	4)	139
100	148	94	54	254	238	492	136	51.2	4)	176
150	148	94	54	378	259	637	136	68.9	4)	218
250	148	94	54	548	302.5	850.5	136	102.3	4)	305

1) Depending on the cable gland used: values up to + 30 mm

2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH: values +70 mm

3) If using a display, order code for "Display; operation", option B: values +28 mm

4) Depending on respective process connection →

DN	<sup>1)</sup> A	<sup>1)</sup> B	С	D	E <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
8	137	78	59	75	180	255	134	5.35	4)	70
15	137	78	59	75	180	255	134	8.30	4)	70
25	137	78	59	75	180	255	134	12.0	4)	70
40	137	78	59	105	184.5	289.5	134	17.6	4)	79
50	137	78	59	141	194.5	335.5	134	26.0	4)	99
80	137	78	59	200	214.5	414.5	134	40.5	4)	139
100	137	78	59	254	233	487	134	51.2	4)	176

Order code for "Housing", option B "Compact hygienic, stainless"

DN	<sup>1)</sup> A	<sup>1)</sup> B	С	D	E <sup>2)3)</sup>	F <sup>2)3)</sup>	G	K	L	М
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]
150	137	78	59	378	254	632	134	68.9	4)	218
250	137	78	59	548	297.5	845.5	134	102.3	4)	305

1) Depending on the cable gland used: values up to + 30 mm

2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH: values +70 mm

3) If using a display, order code for "Display; operation", option B: values +28 mm

4) Depending on respective process connection  $\rightarrow \triangleq 61$ 

DN	<sup>1)</sup> A	<sup>1)</sup> B	С	D	F <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
8	124	68	56	75	180	255	112	5.35	4)	70
15	124	68	56	75	180	255	112	8.30	4)	70
25	124	68	56	75	180	255	112	12.0	4)	70
40	124	68	56	105	184.5	289.5	112	17.6	4)	79
50	124	68	56	141	194.5	335.5	112	26.0	4)	99
80	124	68	56	200	214.5	414.5	112	40.5	4)	139
100	124	68	56	254	233	487	112	51.2	4)	176
150	124	68	56	378	254	632	112	68.9	4)	218
250	124	68	56	548	297.5	845.5	112	102.3	4)	305
			•		•					

Order code for "Housing", option C "Ultra-compact hygienic, stainless"

1) Depending on the cable gland used: values up to + 30 mm


2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH: values +70 mm

3) If using a display, order code for "Display; operation", option B: values +14 mm

4) Depending on respective process connection  $\rightarrow \bigoplus 61$ 

#### Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



Length tolerance for dimension L in mm: ■ DN ≤ 100: +1.5 / -2.0 ■ DN ≥ 125: +3.5

Flange according to EN 1092-1 (DIN 2501): PN16 1.4404 (F316/F316L): order code for "Process connection", option D1S Alloy C22: order code for "Process connection", option D1C

Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN16 1.4404 (F316/F316L): order code for "Process connection", option D5S Alloy C22: order code for "Process connection", option D5C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
100	220	180	8ר18	20	107.1	1 127/1 400 <sup>1)</sup>
150	285	240	8 × Ø22	22	159.3	1 3 3 0 / 1 7 0 0 <sup>1)</sup>
250	405	355	12 × Ø26	26	260.4	1775
Surface roug	hness (flange)	: EN 1092-1 F	orm B1 (DIN 2526	Form C), Ra 3	.2 to 12.5 µm	

Installation length in accordance with NAMUR recommendation NE 132 optionally available (order code 1) for "Process connection", option D1N or D5N (with groove))

1.4404 (	1.4404 (F316/F316L												
DN [mm]	reduction to DN [mm]	Order code for "Process connection", option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
100	80	DHS	220	180	8ר18	20	107.1	874					
150	100	DJS	285	240	8 × Ø 22	22	159.3	1167					
200	150	DLS	340	295	12 × Ø 22	24	206.5	1461					
Surface ro	oughness (flang	e): EN 1092-1 Form	B1 (DIN 2	526 Form	C), Ra 3.2 to 12	.5 µm							

## Flange according to EN 1092-1 (DIN 2501): PN16 with reduction in nominal diameter

J),

Alloy C22: order code for "Process connection", option D2C Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 40 1.4404 (F316/F316L): order code for "Process connection", option D6S Alloy C22: order code for "Process connection", option D6C										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
8 <sup>1)</sup>	95	65	$4 \times Ø14$	16	17.3	370/510 <sup>2)</sup>				
15	95	65	4 × Ø14	16	17.3	404/510 <sup>2)</sup>				
25	115	85	4 × Ø14	18	28.5	440/600 <sup>2)</sup>				
40	150	110	4 × Ø18	18	43.1	550				
50	165	125	4 × Ø18	20	54.5	715				
80	200	160	8 × Ø18	24	82.5	840/915 <sup>2)</sup>				
100	235	190	8 × Ø22	24	107.1	1 1 2 7				
150	300	250	8 × Ø26	28	159.3	1370				
250	450	385	12 × Ø33	38	258.8	1845				

1)

DN 8 with DN 15 flanges as standard Installation length in accordance with NAMUR recommendation NE 132 optionally available (order code for "Process connection", option D2N or D6N (with groove)) 2)

Flange according to EN 1092-1 (DIN 2501): PN 40 (with DN 25 flanges) 1.4404 (F316/F316L): order code for "Process connection", option R2S										
DNABCDEL[mm][mm][mm][mm][mm][mm]										
8	115	85	4ר14	18	28.5	440				
15 115 85 4ר14 18 28.5 440										
Surface roughr	iess (flange): EN	1092-1 Form H	31 (DIN 2526 Form	n C), Ra 3.2 to 12	2.5 µm					

# Flange according to EN 1092-1 (DIN 2501): PN 40 with reduction in nominal diameter

1.4404 (I	F316/F316L)							
DN [mm]	reduction to DN [mm]	Order code for "Process connection", option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50	40	DFS	165	125	4 × Ø 18	20	54.5	555
80	50	DGS	200	160	8 × Ø 18	24	82.5	840
100	80	DIS	235	190	8 × Ø 22	24	107.1	874
150	100	DKS	300	250	8 × Ø 26	28	159.3	1167
200	150	DMS	375	320	12 × Ø 30	34	206.5	1461
Surface ro	oughness (flang	e): EN 1092-1 Form	B1 (DIN 2	526 Form	C), Ra 3.2 to 12	.5 µm		

#### Flange according to EN 1092-1 (DIN 2501): PN 63

1.4404 (F316/F316L): order code for "Process connection", option D3S Alloy C22: order code for "Process connection", option D3C

#### Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 63 1.4404 (F316/F316L): order code for "Process connection", option D7S Alloy C22: order code for "Process connection", option D7C

,	· · · · · · <b>,</b> · · · · · ·	,	<b>F</b>			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
50	180	135	4 × Ø22	26	54.5	724
80	215	170	8 × Ø22	28	81.7	875
100	250	200	8 × Ø26	30	106.3	1127
150	345	280	8 × Ø33	36	157.1	1410
250	470	400	12 × Ø36	46	255.4	1885

Surface roughness (flange):

EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5  $\mu m$  EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2  $\mu m$ 

#### Flange according to EN 1092-1 (DIN 2501): PN 100

1.4404 (F316/F316L): order code for "Process connection", option D4S Alloy C22: order code for "Process connection", option D4C

Flange with groove according to EN 1092-1 Form D (DIN 2512N): PN 100 1.4404 (F316/F316L): order code for "Process connection", option D8S Alloy C22: order code for "Process connection", option D8C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 <sup>1)</sup>	105	75	4ר14	20	17.3	400
15	105	75	4 × Ø14	20	17.3	420
25	140	100	4 × Ø18	24	28.5	470
40	170	125	4 × Ø22	26	42.5	590
50	195	145	4 × Ø26	28	53.9	740
80	230	180	8 × Ø26	32	80.9	885
100	265	210	8 × Ø30	36	104.3	1127
150	355	290	12 × Ø33	44	154.0	1450
Surface rough	2000 (flango): EN	1 1002-1 Eorm	D1 /DIN 2526 Earm	$E$ $P_2 \cap Q \neq Q^2$	2	

Surface roughness (flange): EN 1092-1 Form B2 (DIN 2526 Form E), Ra 0.8 to 3.2  $\mu m$ 

1) DN 8 with DN 15 flanges as standard

1.4404 (F316	Flange according to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC											
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]						
8 <sup>1)</sup>	90	60.3	4 × Ø15.7	11.2	15.7	370						
15	90	60.3	4 × Ø15.7	11.2	15.7	404						
25	110	79.4	4 × Ø15.7	14.2	26.7	440						
40	125	98.4	4 × Ø15.7	17.5	40.9	550						
50	150	120.7	4 × Ø19.1	19.1	52.6	715						
80	190	152.4	4 × Ø19.1	23.9	78.0	840						
100	230	190.5	8 × Ø19.1	23.9	102.4	1127						
150	280	241.3	8 × Ø22.4	25.4	154.2	1398						

Flange according to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC										
DN         A         B         C         D         E         L           [mm]         [mm]         [mm]         [mm]         [mm]         [mm]										
250 405 362 12ר25.4 30.2 254.5 1832										
Surface rough	ness (flange): F	Ra 3.2 to 6.3 µn	n							

1) DN 8 with DN 15 flanges as standard

#### Flange according to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L) DN reduction Order code for Α В С D Ε L [mm] to DN [mm] [mm] "Process [mm] [mm] [mm] [mm] [mm] connection", option

40	AHS	150	120.7	4 × Ø 19.1	19.1	52.6	550
50	AJS	190	152.4	4 × Ø 19.1	23.9	78.0	720
80	ALS	230	190.5	8 × Ø 19.1	23.9	102.4	874
100	ANS	280	241.3	8 × Ø 22.4	25.4	154.2	1167
150	APS	345	298.5	8 × Ø 22.4	29	202.7	1461
	50 80 100	50         AJS           80         ALS           100         ANS	50         AJS         190           80         ALS         230           100         ANS         280	50         AJS         190         152.4           80         ALS         230         190.5           100         ANS         280         241.3	50         AJS         190         152.4         4ר19.1           80         ALS         230         190.5         8ר19.1           100         ANS         280         241.3         8ר22.4	50         AJS         190         152.4         4 × Ø 19.1         23.9           80         ALS         230         190.5         8 × Ø 19.1         23.9           100         ANS         280         241.3         8 × Ø 22.4         25.4	50     AJS     190     152.4     4 × Ø 19.1     23.9     78.0       80     ALS     230     190.5     8 × Ø 19.1     23.9     102.4       100     ANS     280     241.3     8 × Ø 22.4     25.4     154.2

Surface roughness (flange): Ra 3.2 to 6.3  $\mu m$ 

#### Flange according to ASME B16.5: Class 300

**1.4404 (F316/F316L):** order code for "Process connection", option ABS

Alloy C22: order code for "Process connection", option ABC

,	· · · · · · · · · · · · · · · · · · ·		, - <u>r</u>												
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]									
8 <sup>1)</sup>	95	66.7	4 × Ø15.7	14.2	15.7	370									
15	95	66.7	4 × Ø15.7	14.2	15.7	404									
25	125	88.9	4 × Ø19.1	17.5	26.7	440									
40	155	114.3	4 × Ø22.3	20.6	40.9	550									
50	165	127	8 × Ø19.1	22.3	52.6	715									
80	210	168.3	8 × Ø22.3	28.4	78.0	840									
100	255	200	8 × Ø22.3	31.7	102.4	1127									
150	320	269.9	12 × Ø22.3	36.5	154.2	1417									
250	445	387.4	16 × Ø28.4	47.4	254.5	1863									
Surface rough	ness (flange): F	Ra 3.2 to 6.3 μn	n	1	1	1									

1) DN 8 with DN 15 flanges as standard

5	Flange according to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)											
DN [mm]	reduction to DN [mm]	Order code for "Process connection", option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
50	40	AIS	165	127	8 × Ø 19.1	22.3	52.6	615				
80	50	AKS	210	168.3	8 × Ø 22.3	28.4	78.0	732				
100	80	AMS	255	200	8 × Ø 22.3	31.7	102.4	894				

5	Flange according to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)									
DN [mm]	reduction to DN [mm]	Order code for "Process connection", option	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]		
150	100	AOS	320	269.9	12 × Ø 22.3	36.5	154.2	1 187		
200	150	AQS	380	330.2	12 × Ø 25.4	41.7	202.7	1461		
Surface ro	oughness (flang	e): Ra 3.2 to 6.3 µm								

Surface roughness (flange): Ra 3.2 to 6.3  $\mu$ m

#### Flange according to ASME B16.5: Class 600

1.4404 (F316/F316L): order code for "Process connection", option ACS

Alloy C22: order code for "Process connection", option ACC

	,		, 1			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 <sup>1)</sup>	95	66.7	4 × Ø15.7	20.6	13.9	400
15	95	66.7	4 × Ø15.7	20.6	13.9	420
25	125	88.9	4 × Ø19.1	23.9	24.3	490
40	155	114.3	4 × Ø22.3	28.7	38.1	600
50	165	127	8 × Ø19.1	31.8	49.2	742
80	210	168.3	8 × Ø22.3	38.2	73.7	900
100	275	215.9	8 × Ø25.4	48.4	97.3	1157
150	355	292.1	12 × Ø28.4	47.8	154.2	1467
250	510	431.8	16 × Ø35.1	69.9	254.5	1946
Surface rough	ness (flange): F	Ra 3.2 to 6.3 un	n	1	1	

Surface roughness (flange): Ra 3.2 to 6.3 µm

1) DN 8 with DN 15 flanges as standard

#### Flange JIS B2220: 10K

**1.4404 (F316/F316L):** order code for "Process connection", option NDS Alloy C22: order code for "Process connection", option NDC

		contraction	, option 1120			
DN [mm]			C [mm]	D [mm]	E [mm]	L [mm]
50	155	120	4 × Ø19	16	50	715
80	185	150	8 × Ø19	18	80	832
100	210	175	8 × Ø19	18	100	1127
150	280	240	8 × Ø23	22	150	1354
250	400	355	12 × Ø25	24	250	1775
Surface rough	ness (flange): R	a 3.2 to 6.3 µm		•	•	

Surface roughness (fiange). Ra 5.2 to 6.5 p

#### Flange JIS B2220: 20K

**1.4404 (F316/F316L):** order code for "Process connection", option **NES Alloy C22:** order code for "Process connection", option **NEC** 

5	· · · · · ·		· •			
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 <sup>1)</sup>	95	70	4 × Ø15	14	15	370
15	95	70	4 × Ø15	14	15	404
25	125	90	4 × Ø19	16	25	440
40	140	105	4 × Ø19	18	40	550

#### Flange JIS B2220: 20K 1.4404 (F316/F316L): order code for "Process connection", option NES Alloy C22: order code for "Process connection", option NEC С DN Α В D Ε L [mm] [mm] [mm] [mm] [mm] [mm] [mm] 50 155 120 8ר19 18 50 715 80 200 160 8 × Ø23 22 80 832 225 24 100 1127 100 185 8 × Ø23 150 305 260 12 × Ø25 28 150 1386 250 430 380 12 × Ø27 34 250 1845 Surface roughness (flange): Ra 1.6 to 3.2 µm

1) DN 8 with DN 15 flanges as standard

#### Flange JIS B2220: 40K

<b>1.4404 (F316/F316L):</b> order code for "Process connection", option NGS
Alloy C22: order code for "Process connection", option NGC

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8 <sup>1)</sup>	115	80	4 × Ø19	20	15	400
15	115	80	4 × Ø19	20	15	425
25	130	95	4 × Ø19	22	25	485
40	160	120	4 × Ø23	24	38	600
50	165	130	8 × Ø19	26	50	760
80	210	170	8 × Ø23	32	75	890
100	250	205	8 × Ø25	36	100	1167
150	355	295	12 × Ø33	44	150	1498
Surface rough	ness (flange): Ra	a 1.6 to 3.2 µm				

1) DN 8 with DN 15 flanges as standard


#### Flange JIS B2220: 63K

**1.4404 (F316/F316L):** order code for "Process connection", option NHS Alloy C22: order code for "Process connection", option NHC

Anoy Czz. order code for Process connection, option NAC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
8 <sup>1)</sup>	120	85	4 × Ø19	23	12	420				
15	120	85	4 × Ø19	23	12	440				
25	140	100	4 × Ø23	27	22	494				
40	175	130	4 × Ø25	32	35	620				
50	185	145	8 × Ø23	34	48	775				
80	230	185	8 × Ø25	40	73	915				
100	270	220	8 × Ø27	44	98	1167				
150	365	305	12 × Ø33	54	146	1528				
Surface roughr	ness (flange): Ra	a 1.6 to 3.2 μm								

1) DN 8 with DN 15 flanges as standard

Fixed flange DIN 11864-2



Detail X: Asymmetrical process connection; the part shown in blue is provided by the supplier. 🛃 38

Length tolerance for dimension L in mm: +1.5 / -2.0


Flange DIN11864-2 Form A, for pipe according to DIN11866 series A, flat with notch
1.4404 (316/316L)
Order code for "Process connection" ontion KCS

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
8	54	37	4 × Ø9	10	10	387				
15	59	42	4 × Ø9	10	16	418				
25	70	53	4 × Ø9	10	26	454				
40	82	65	4 × Ø9	10	38	560				
50	94	77	4 × Ø9	10	50	720				
80	133	112	8ר11	12	81	900				
100	159	137	8ר11	14	100	1127				

3A-version available: order code for "Additional approval", option LP in conjunction with

 $Ra \le 0.8 \ \mu\text{m}$ : order code for "Measuring tube material", option SB, SE or  $Ra \le 0.4 \ \mu\text{m}$ : order code for "Measuring tube material", option SC, SF

Lap joint flange EN 1092-1, ASME B16.5, JIS B2220





Length tolerance for dimension L in mm: +1.5 / -2.0

1.4301 (F	Lap joint flange according to EN 1092-1 Form D: PN 40 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option DAC									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L <sub>diff</sub> <sup>1)</sup> [mm]		
8 <sup>2)</sup>	95	65	4ר14	14.5	45	17.3	370	0		
15	95	65	4ר14	14.5	45	17.3	404	0		
25	115	85	4ר14	16.5	68	28.5	444	+4		
40	150	110	4 × Ø 18	21	88	43.1	560	+10		
50	165	125	4 × Ø 18	23	102	54.5	719	+4		
80	200	160	8 × Ø 18	29	138	82.5	848	+8		
100	235	190	8 × Ø 22	34	162	107.1	1131	+4		
Surface rou	Ighness (fla:	nge): Ra 3.2	to 12.5 µm							

1) Difference to installation length of the welding neck flange (order code for "Process connection", option D2C)

2) DN 8 with DN 15 flanges as standard

1.4301 (F3	Lap joint flange according to ASME B16.5: Class 150 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option ADC									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L <sub>diff</sub> <sup>1)</sup> [mm]		
8 <sup>2)</sup>	90	60.3	4 × Ø 15.7	15	35.1	15.7	370	0		
15	90	60.3	4 × Ø 15.7	15	35.1	15.7	404	0		
25	110	79.4	4 × Ø 15.7	16	50.8	26.7	440	0		
40	125	98.4	4 × Ø 15.7	15.9	73.2	40.9	550	0		
50	150	120.7	4 × Ø 19.1	19	91.9	52.6	715	0		
80	190	152.4	4 × Ø 19.1	22.3	127.0	78.0	840	0		

Lap joint flange according to ASME B16.5: Class 150 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option ADC									
DN         A         B         C         D         E         F         L         L <sub>diff</sub> <sup>1)</sup> [mm]         [mm]         [mm]         [mm]         [mm]         [mm]         [mm]         [mm]									
100	230	190.5	8 × Ø 19.1	26	157.2	102.4	1127	0	
Surface rou	Surface roughness (flange): Ra 3.2 to 12.5 µm								

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

2) DN 8 with DN 15 flanges as standard

### Lap joint flange according to ASME B16.5: Class 300

1.4301 (F304), wetted parts Alloy C22

Oraer coae	Oraer coae for Process connection, option AEC							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L <sub>diff</sub> <sup>1)</sup> [mm]
8 <sup>2)</sup>	95	66.7	4 × Ø 15.7	16.5	35.1	15.7	376	+6
15	95	66.7	4 × Ø 15.7	16.5	35.1	15.7	406	+2
25	125	88.9	4 × Ø 19.1	21.0	50.8	26.7	450	+10
40	155	114.3	4 × Ø 22.3	23.0	73.2	40.9	564	+14
50	165	127	8 × Ø 19.1	25.5	91.9	52.6	717	+2
80	210	168.3	8 × Ø 22.3	31.0	127.0	78.0	852.6	+12.6
100	255	200	8 × Ø 22.3	32.0	157.2	102.4	1139	+12
Surface rea	Jahnoss (fla	$(\mathbf{p}_{\alpha}) \cdot \mathbf{p}_{\alpha} \geq 2$	to 12 5 um					

Surface roughness (flange): Ra 3.2 to 12.5 µm

Difference to installation length of the welding neck flange (order code for "Process connection", option 1) ABC)

2) DN 8 with DN 15 flanges as standard

## Lap joint flange according to ASME B16.5: Class 600 **1.4301 (F304)**, wetted parts Alloy C22 Order code for "Process connection", option AFC

Order code	order code for Process connection, option APC							
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L <sub>diff</sub> <sup>1)</sup> [mm]
8 <sup>2)</sup>	95	66.7	4 × Ø 15.7	17.0	35.1	13.9	400	0
15	95	66.7	4 × Ø 15.7	17.0	35.1	13.9	420	0
25	125	88.9	4 × Ø 19.1	21.5	50.8	24.3	490	0
40	155	114.3	4 × Ø 22.3	25.0	73.2	38.1	600	0
50	165	127	8 × Ø 19.1	28.0	91.9	49.2	742	0
80	210	168.3	8 × Ø 22.3	35.0	127.0	73.7	900	0
100	275	215.9	8 × Ø 25.4	44.0	157.2	97.3	1167	+10
Surface rou	ughness (fla	nge): Ra 3.2	to 12.5 µm					

1) Difference to installation length of the welding neck flange (order code for "Process connection", option ACC)

2) DN 8 with DN 15 flanges as standard


	for "Process c	, - I	1		1	1		1
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L <sub>diff</sub> <sup>1</sup> [mm]
8 <sup>2)</sup>	95	70	4 × Ø 15	14	51	15	370	0
15	95	70	4 × Ø 15	14	51	15	404	0
25	125	90	4 × Ø 19	18.5	67	25	440	0
40	140	105	4 × Ø 19	18.5	81	40	550	0
50	155	120	8ר19	23	96	50	715	0
80	200	160	8 × Ø 23	29	132	80	844	+12
100	225	185	8ר23	29	160	100	1127	0

Difference to installation length of the welding neck flange (order code for "Process connection", option 1) NEC) DN 8 with DN 15 flanges as standard

2)

#### **Clamp** connections

Tri-Clamp



Length tolerance for dimension L in mm: +1.5 / -2.0

Tri-Clamp (½"), for pipe according to DIN 11866 series C         1.4404 (316/316L)         Order code for "Process connection", option FDW					
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]	
8	1/2	25.0	9.5	367	
15	1/2	25.0	9.5	398	
3-A version available	order code for "Additio	nal approval" option L	<b>P</b> in conjunction with		

3-A version available: order code for "Additional approval", option  $\ensuremath{\mathbf{LP}}$  in conjunction with

 $Ra \le 0.8 \ \mu\text{m}$ : order code for "Measuring tube material", option SB, SE or

 $Ra \leq 0.4~\mu m$ : order code for "Measuring tube material", option SC, SF

# Tri-Clamp ( $\geq$ 1"), for pipe according to DIN 11866 series C 1.4404 (316/316L)

Order code for "Process connection", option FTS

DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]
8	1	50.4	22.1	367
15	1	50.4	22.1	398
25	1	50.4	22.1	434
40	11/2	50.4	34.8	560
50	2	63.9	47.5	720
80	3	90.9	72.9	900
100	4	118.9	97.4	1127


3-A version available: order code for "Additional approval", option LP in conjunction with

 $\text{Ra} \leq 0.8~\mu\text{m}$ : order code for "Measuring tube material", option SB, SE or

 $Ra \leq 0.4~\mu m$ : order code for "Measuring tube material", option SC, SF

#### Threaded couplings

Thread DIN 11851, DIN11864-1, SMS 1145





Length tolerance for dimension L in mm: +1.5 / -2.0

<b>Thread DIN 11851, for p</b> <b>1.4404 (316/316L)</b> Order code for "Process co	<pre>pipe according to DIN11866, seri nnection", option FMW</pre>	es A	
DN [mm]	A [in]	B [mm]	L [mm]
8	Rd 34 × <sup>1</sup> / <sub>8</sub>	16	367
15	Rd 34 × <sup>1</sup> / <sub>8</sub>	16	398
25	Rd 52 × <sup>1</sup> ⁄ <sub>6</sub>	26	434
40	Rd 65 × ¼	38	560
50	Rd 78 × <sup>1</sup> / <sub>6</sub>	50	720
80	Rd 110 × ¼	81	900
100	Rd 130 × ¼	100	1127
3-A version available: or	ler code for "Additional approval"	option <b>LP</b> in conjunction wi	th

3-A version available: order code for "Additional approval", option  ${\bf LP}$  in conjunction with  $Ra \leq 0.8~\mu m$ : order code for "Measuring tube material", option SB, SE

	onnection", option <b>FLW</b>		
DN [mm]	A [in]	B [mm]	L [mm]
8	Rd 28 × $\frac{1}{8}$	10	367
15	Rd 34 × $\frac{1}{8}$	16	398
25	Rd 52 × <sup>1</sup> / <sub>8</sub>	26	434
40	Rd 65 × $\frac{1}{6}$	38	560
50	Rd 78 × ¼	50	720
80	Rd 110 × ¼	81	900
100	Rd 130 × ¼	100	1 1 2 7

3-A version available: order code for "Additional approval", option **LP** in conjunction with Ra  $\leq$  0.8  $\mu$ m: order code for "Measuring tube material", option **SB**, **SE** or


 $Ra \le 0.4 \ \mu m$ : order code for "Measuring tube material", option SC, SF

Order code for "Process co	nnection", option SCS	1.4404 (316/316L) Order code for "Process connection", option SCS								
DN [mm]	A [in]	B [mm]	L [mm]							
8	Rd 40 × <sup>1</sup> ⁄ <sub>6</sub>	22.6	367							
15	Rd 40 × <sup>1</sup> ⁄ <sub>6</sub>	22.6	398							
25	Rd 40 × <sup>1</sup> ⁄ <sub>6</sub>	22.6	434							
40	Rd 60 × <sup>1</sup> / <sub>6</sub>	35.6	560							
50	Rd 70 × <sup>1</sup> / <sub>6</sub>	48.6	720							
80	Rd 98 × <sup>1</sup> ⁄ <sub>6</sub>	72.9	900							
100	Rd 132 × 1/ <sub>6</sub>	97.6	1 1 2 7							

Ra  $\leq$  0.8 µm: order code for "Measuring tube material", option SB, SE

### Thread ISO 2853

i




Length tolerance for dimension L in mm: +1.5 / -2.0

Thread ISO 2853, for pipe according to ISO 2037 1.4404 (316/316L) Order code for "Process connection", option JSF								
DN [mm]	A <sup>1)</sup> [mm]	B [mm]	L [mm]					
8	37.13	22.6	367					
15	37.13	22.6	398					
25	37.13	22.6	434					
40	52.68	35.6	560					
50	64.16	48.6	720					
80	91.19	72.9	900					
100	118.21	97.6	1127					
3-A version available: orde	r code for "Additional approva	l", option <b>LP</b> in conjunction v	vith					

3-A version available: order code for "Additional approval", option LP in conjunction with Ra  $\leq 0.8~\mu m$ : order code for "Measuring tube material", option SB, SE or Ra  $\leq 0.4~\mu m$ : order code for "Measuring tube material", option SC, SF

1) Max. thread diameter as per ISO 2853 annex A

VCO




Length tolerance for dimension L in mm: +1.5 / -2.0

8-VCO-4 (½") 1.4404 (316/316L) Order code for "Process connection", option CVS									
DN [mm]									
8 AF 1 10.2 390									

<b>12-VCO-4 (¾")</b> <b>1.4404 (316/316L)</b> Order code for "Process connection", option CWS									
DN [mm]									
15	AF 1½	15.7	430						

# Safety Barrier Promass 100


- Top-hat rail EN 60715: TH 35 x 7.5 TH 35 x 15



A	В	C D [mm] [mm]				
[mm]	[mm] [mm]		[mm]			
108	114.5	99	22.5			

#### Accessories

#### Rupture disk/purge connections




#### 🛃 39

- 1 Connection nipple for purge connections: order code for "Sensor options", option CH "Purge connection"
- 2 Connection nipple with rupture disk: order code for "Sensor option", option CA "Rupture disk"

DN	A	L
[mm]	[mm]	[mm]
8	62	216
15	62	220
25	62	260
40	67	310
50	79	452
80	101	560
100	120	684
150	141	880
250	182	380

# **Dimensions in US units**

**Compact version** 



Order code for "Housing", option A "Compact, aluminum, coated"

DN	A 1)	B 1)	С	D	F <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	5.83	3.70	2.13	2.95	7.28	10.24	5.35	0.211	4)	2.76
1/2	5.83	3.70	2.13	2.95	7.28	10.24	5.35	0.33	4)	2.76
1	5.83	3.70	2.13	2.95	7.28	10.24	5.35	0.47	4)	2.76
11/2	5.83	3.70	2.13	4.13	7.46	11.59	5.35	0.69	4)	3.11
2	5.83	3.70	2.13	5.55	7.85	13.41	5.35	1.02	4)	3.90
3	5.83	3.70	2.13	7.87	8.64	16.52	5.35	1.59	4)	5.47
4	5.83	3.70	2.13	10	9.37	19.37	5.35	2.02	4)	6.93
6	5.83	3.70	2.13	14.88	10.2	25.08	5.35	2.71	4)	8.58
10	5.83	3.70	2.13	21.57	11.91	33.48	5.35	4.03	4)	12.01

Depending on the cable gland used: values up to + 1.18 in 1)

With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, 2) SF, TH: values +2.76 in

If using a display, order code for "Display; operation", option B: values +1.1 in Depending on respective process connection  $\rightarrow \cong 80$ 3)

4)

DN	A 1)	В	С	D	F <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	5.39	3.07	2.32	2.95	7.09	10.04	5.28	0.211	4)	2.76
1/2	5.39	3.07	2.32	2.95	7.09	10.04	5.28	0.33	4)	2.76
1	5.39	3.07	2.32	2.95	7.09	10.04	5.28	0.47	4)	2.76
1½	5.39	3.07	2.32	4.13	7.26	11.4	5.28	0.69	4)	3.11
2	5.39	3.07	2.32	5.55	7.66	13.21	5.28	1.02	4)	3.90
3	5.39	3.07	2.32	7.87	8.44	16.32	5.28	1.59	4)	5.47
4	5.39	3.07	2.32	10	9.17	19.17	5.28	2.02	4)	6.93

Order code for "Housing", option B "Compact hygienic, stainless"

DN	A <sup>1)</sup>	В	С	D	F <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
6	5.39	3.07	2.32	14.88	10	24.88	5.28	2.71	4)	8.58
10	5.39	3.07	2.32	21.57	11.71	33.29	5.28	4.03	4)	12.01

1) Depending on the cable gland used: values up to +1.18 in

 With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH: values +2.76 in

3) If using a display, order code for "Display; operation", option B: values +1.1 in

4) Depending on respective process connection  $\rightarrow \textcircled{B} 80$ 

Order code	for "Housing".	option C "Ultra-c	ompact hygieni	c. stainless"

DN	A <sup>1)</sup>	В	С	D	F <sup>2)3)</sup>	F <sup>2)3)</sup>	G	К	L	М
[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]
3/8	4.88	2.68	2.20	2.95	7.09	10.04	4.41	0.21	4)	2.76
1/2	4.88	2.68	2.20	2.95	7.09	10.04	4.41	0.33	4)	2.76
1	4.88	2.68	2.20	2.95	7.09	10.04	4.41	0.47	4)	2.76
11/2	4.88	2.68	2.20	4.13	7.26	11.4	4.41	0.69	4)	3.11
2	4.88	2.68	2.20	5.55	7.66	13.21	4.41	1.02	4)	3.90
3	4.88	2.68	2.20	7.87	8.44	16.32	4.41	1.59	4)	5.47
4	4.88	2.68	2.20	10	9.17	19.17	4.41	2.02	4)	6.93
6	4.88	2.68	2.20	14.88	10	24.88	4.41	2.71	4)	8.58
10	4.88	2.68	2.20	21.57	11.71	33.29	4.41	4.03	4)	12.01

1) Depending on the cable gland used: values up to +1.18 in


2) With order code for "Sensor option", option CG or order code for "Measuring tube material", option SD, SE, SF, TH: values +2.76 in

3) If using a display, order code for "Display; operation", option B: values +1.1 in

4) Depending on respective process connection  $\rightarrow \cong 80$ 

### Flange connections

Fixed flange ASME B16.5



Length tolerance for dimension L in inch: •  $DN \le 4^{"}$ : +0.06 / -0.08 ň

- DN ≥ 5": +0.14

Flange according to ASME B16.5: Class 150 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC

Alloy CZZ. 0	iuei coue joi 1100		prion AC		Andy C22. Order code for Trocess connection, option Arc										
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]									
3/8 1)	3.54	2.37	4 × Ø 0.62	0.44	0.62	14.57									
1/2	3.54	2.37	4 × Ø0.62	0.44	0.62	15.91									
1	4.33	3.13	4 × Ø0.62	0.56	1.05	17.32									
11/2	4.92	3.87	4 × Ø0.62	0.69	1.61	21.65									
2	5.91	4.75	4 × Ø0.75	0.75	2.07	28.15									
3	7.48	6.00	4 × Ø0.75	0.94	3.07	33.07									
4	9.06	7.50	8 × Ø0.75	0.94	4.03	44.37									
6	11.02	9.50	8 × Ø0.88	1	6.07	55.04									
10	15.94	14.25	12 × Ø1.0	1.19	10.02	72.13									
Surface roug	Surface roughness (flange): Ra 125 to 250 µin														

1) DN  $^3\!\!/_8$  with DN  $^1\!\!/_2$  flanges as standard

5	Flange according to ASME B16.5: Class 150 with reduction in nominal diameter 1.4404 (F316/F316L)									
DN [in]	reduction to DN [in]	Order code for "Process connection", option	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]		
2	1½	AHS	5.91	4.75	4 × Ø 0.75	0.75	2.07	21.65		
3	2	AJS	7.48	6	4 × Ø 0.75	0.94	3.07	28.35		
4	3	ALS	9.06	7.5	8 × Ø 0.75	0.94	4.03	34.41		
6	4	ANS	11.02	9.5	8 × Ø 0.88	1	6.07	45.94		
8	6	APS	13.58	11.75	8 × Ø 0.88	1.14	7.98	57.52		
Surface ro	Surface roughness (flange): Ra 125 to 250 μin									

# Flange according to ASME B16.5: Class 300

1.4404 (F316/F316L): order code for "Process connection", option ABS

Alloy C22:	order code for "P	rocess connectio	on", option <b>ABC</b>			
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
3/8 1)	3.74	2.63	4 × Ø0.62	0.56	0.62	14.57
1/2	3.74	2.63	4 × Ø0.62	0.56	0.62	15.91
1	4.92	3.50	4 × Ø0.75	0.69	1.05	17.32
11/2	6.10	4.50	4 × Ø0.88	0.81	1.61	21.65
2	6.50	5.00	8 × Ø0.75	0.88	2.07	28.15
3	8.27	6.63	8 × Ø0.88	1.12	3.07	33.07
4	10.04	7.87	8 × Ø0.88	1.25	4.03	44.37
6	12.6	10.63	12 × Ø0.88	1.44	6.07	55.79
10	17.52	15.25	16 × Ø1.12	1.87	10.02	73.35
Surface rou	ghness (flange):	Ra 125 to 250	uin			

Surface roughness (flange): Ra 125 to 250 µin

1) DN  $\frac{3}{8}$ " with DN  $\frac{1}{2}$ " flanges as standard

# Flange according to ASME B16.5: Class 300 with reduction in nominal diameter 1.4404 (F316/F316L)

1.1101 ()	1 ) 10/1 ) 10L)							
DN [in]	reduction to DN [in]	Order code for "Process connection", option	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
2	11/2	AIS	6.5	5	8 × Ø 0.75	0.88	2.07	24.21
3	2	AKS	8.27	6.63	8 × Ø 0.88	1.12	3.07	28.82
4	3	AMS	10.04	7.87	8 × Ø 0.88	1.25	4.03	35.2
6	4	AOS	12.6	10.63	12 × Ø 0.88	1.44	6.07	46.73
8	6	AQS	14.96	13	12 × Ø 1	1.64	7.98	57.52
Surfacer	oughness (flang	α)· Ba 125 to 250 μi	n					

Surface roughness (flange): Ra 125 to 250 µin

#### Flange according to ASME B16.5: Class 600


1.4404 (F316/F316L): order code for "Process connection", option ACS

Alloy C22: order code for "Process connection", option ACC

Alloy C22.	oraer coue jor i		ni, option ACC			
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
3/8 1)	3.74	2.63	4 × Ø0.62	0.81	0.55	15.75
1/2	3.74	2.63	4 × Ø0.62	0.81	0.55	16.54
1	4.92	3.50	4 × Ø0.75	0.94	0.96	19.29
11/2	6.10	4.50	4 × Ø0.88	1.13	1.5	23.62
2	6.50	5.00	8 × Ø0.75	1.25	1.94	29.21
3	8.27	6.63	8 × Ø0.88	1.5	2.9	35.43
4	10.83	8.50	8ר1.00	1.91	3.83	45.55
6	13.98	11.50	12 × Ø1.12	1.88	6.07	57.76
10	20.08	17.00	16 × Ø1.38	2.75	10.02	76.61
Surface rou	ghness (flange):	: Ra 125 to 250	μin			

1) DN  $^3\!\!/_8$  with DN  $^1\!\!/_2$  flanges as standard

# Lap joint flange ASME B16.5





Length tolerance for dimension L in inch: +0.06 / -0.08

1.4301 (F	Lap joint flange according to ASME B16.5: Class 150 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option ADC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L <sub>diff</sub> <sup>1)</sup> [in]		
3/8 2)	3.54	2.37	4 × Ø 0.62	0.59	1.38	0.62	14.57	0		
1/2	3.54	2.37	4 × Ø 0.62	0.59	1.38	0.62	15.91	0		
1	4.33	3.13	4 × Ø 0.62	0.63	2	1.05	17.32	0		
1½	4.92	3.87	4 × Ø 0.62	0.63	2.88	1.61	21.65	0		
2	5.91	4.75	4 × Ø 0.75	0.75	3.62	2.07	28.15	0		
3	7.48	6.00	4 × Ø 0.75	0.88	5	3.07	33.07	0		
4	9.06	7.50	8 × Ø 0.75	1.02	6.19	4.03	44.37	0		
Surface rou	ughness (fla:	nge): Ra 125	5 to 492 µin							

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC) DN  $^{3}\!\!\!/_{8}$  with DN  $^{4}\!\!\!/_{2}$  flanges as standard

2)

1.4301 (F	Lap joint flange according to ASME B16.5: Class 300 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AEC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L <sub>diff</sub> <sup>1)</sup> [in]		
<sup>3</sup> /8 <sup>2)</sup>	3.74	2.63	4 × Ø 0.62	0.65	1.38	0.62	14.8	+0.23		
1/2	3.74	2.63	4 × Ø 0.62	0.65	1.38	0.62	15.98	+0.07		
1	4.92	3.50	4 × Ø 0.75	0.83	2	1.05	17.72	+0.40		
1½	6.10	4.50	4 × Ø 0.88	0.91	2.88	1.61	22.2	+0.55		
2	6.50	5.00	8 × Ø 0.75	1	3.62	2.07	28.23	+0.08		
3	8.27	6.63	8 × Ø 0.88	1.22	5	3.07	33.57	+0.50		

1.4301 (F	Lap joint flange according to ASME B16.5: Class 300 1.4301 (F304), wetted parts Alloy C22 Order code for "Process connection", option AEC								
$ \begin{array}{c c c c c c c c c c c c c c c c c c c $									
4	10.04	7.87	8 × Ø 0.88	1.26	6.19	4.03	44.84	+0.47	
Surface rou	Surface roughness (flange): Ra 125 to 492 µin								

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

2) DN  $\frac{3}{8}$  with DN  $\frac{1}{2}$  flanges as standard

.4301 (F304), wetted parts Alloy C22 Irder code for "Process connection", option AFC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L <sub>diff</sub> <sup>1</sup> [in]	
<sup>3</sup> /8 <sup>2)</sup>	3.74	2.63	4 × Ø 0.62	0.67	1.38	0.55	15.75	0	
1/2	3.74	2.63	4 × Ø 0.62	0.67	1.38	0.55	16.54	0	
1	4.92	3.50	4 × Ø 0.75	0.85	2	0.96	19.29	0	
11/2	6.10	4.50	4 × Ø 0.88	0.98	2.88	1.5	23.62	0	
2	6.50	5.00	8 × Ø 0.75	1.1	3.62	1.94	29.21	0	
3	8.27	6.63	8 × Ø 0.88	1.38	5	2.9	35.43	0	
4	10.83	8.50	8ר1	1.73	6.19	3.83	45.94	+0.39	


Surface roughness (flange): Ra 125 to 492 µin

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

2) DN  $\frac{3}{8}$  with DN  $\frac{1}{2}$  flanges as standard

#### **Clamp connections**

Tri-Clamp





Length tolerance for dimension L in inch: +0.06 / -0.08

Tri-Clamp (½"), DIN 11866 series C         1.4404 (316/316L)         Order code for "Process connection", option FDW								
DN [in]	Clamp [in]	A [in]	B [in]	L [in]				
3⁄8	1/2	0.98	0.37	14.4				
1/2	1/2	0.98	0.37	15.7				
3-A version available	e: order code for "Additior	al approval", option <b>LF</b>	in conjunction with					


 $Ra \le 32 \ \mu in:$  order code for "Measuring tube material", option SB, SE or  $Ra \le 16 \ \mu in:$  order code for "Measuring tube material", option SC, SF

der code for "Process connection", option <b>FTS</b>								
DN [in]	Clamp [in]	A [in]	B [in]	L [in]				
3/8	1	1.98	0.87	14.4				
1/2	1	1.98	0.87	15.7				
1	1	1.98	0.87	17.1				
11/2	11/2	1.98	1.37	22.0				
2	2	2.52	1.87	28.3				
3	3	3.58	2.87	35.4				
4	4	4.68	3.83	44.4				

 $Ra \le 32 \ \mu$ in: order code for "Measuring tube material", option SB, SE or  $Ra \le 16 \ \mu$ in: order code for "Measuring tube material", option SC, SF

# Threaded couplings

Thread SMS 1145




Length tolerance for dimension L in inch: +0.06 / -0.08

Thread SMS 1145         1.4404 (316/316L)         Order code for "Process connection", option SCS									
DN [in]	A [in]	B [in]	L [in]						
3/8	Rd 40 × 1/ <sub>6</sub>	0.89	14.45						
1/2	Rd 40 × 1/ <sub>6</sub>	0.89	15.67						
1	Rd 40 × 1/ <sub>6</sub>	0.89	17.09						
11/2	Rd 60 × 1/ <sub>6</sub>	1.4	22.05						
2	Rd 70 × 1/ <sub>6</sub>	1.91	28.35						
3	Rd 98 × $\frac{1}{6}$	2.87	35.43						
4	Rd 132 × 1/ <sub>6</sub>	3.84	44.37						

3-A version available: order code for "Additional approval", option **LP** in conjunction with Ra  $\leq$  32 µin: order code for "Measuring tube material", option **SB**, **SE** 

VCO





Length tolerance for dimension L in inch: +0.06 / -0.08


8-VCO-4 (½") 1.4404 (316/316L) Order code for "Process cor								
DN [in]	A [in]	B [in]	L [in]					
3/8	AF 1	0.4	15.35					

<b>12-VCO-4 (¾")</b> <b>1.4404 (316/316L)</b> Order code for "Process co	onnection", option <b>CWS</b>		
DN [in]	A [in]	B [in]	L [in]
1/2	AF 1½	0.62	16.93

# Safety Barrier Promass 100

Top-hat rail EN 60715: • TH 35 x 7.5


- TH 35 x 15



А	В	С	D
[in]	[in]	[in]	[in]
4.25	4.51	3.9	0.89

#### Accessories

#### Rupture disk/purge connections



Connection nipple for purge connections: order code for "Sensor options", option CH "Purge connection" 1 Connection nipple with rupture disk: order code for "Sensor option", option CA "Rupture disk" 2

DN	A	L
[in]	[in]	[in]
3/8	2.44	8.50
1/2	2.44	8.66
1	2.44	10.24
1½	2.64	12.20
2	3.11	17.78
3	3.98	22.0
4	4.72	27.0
6	5.55	34.6
10	7.17	14.96

# Weight

All values (weight exclusive of packaging material) refer to devices with EN/DIN PN 40 flanges. Weight specifications including transmitter: order code for "Housing", option A "Compact, aluminum coated".

Different values due to different transmitter versions:

#### Weight in SI units

DN [mm]	Weight [kg]
8	9
15	10
25	12
40	17
50	28
80	53
100	94

DN [mm]	Weight [kg]
150	152
250	398

# Weight in US units

DN [in]	Weight [lbs]
3/8	20
1/2	22
1	26
1½	37
2	62
3	117
4	207
6	335
10	878

#### Safety Barrier Promass 100


49 g (1.73 ounce)

#### Materials

#### Transmitter housing

- Order code for "Housing", option **A** "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Order code for "Housing", option **B** "Compact, hygienic, stainless":
  - Hygienic version, stainless steel 1.4301 (304)
  - Optional: order code for "Sensor feature", option CC
    - Hygienic version, for maximum corrosion resistance: stainless steel 1.4404 (316L)
- Order code for "Housing", option **C** "Ultra-compact, hygienic, stainless":
  - Hygienic version, stainless steel 1.4301 (304)
  - Optional: order code for "Sensor feature", option CC
  - Hygienic version, for maximum corrosion resistance: stainless steel 1.4404 (316L)
- Window material for optional local display ( $\Rightarrow \square 91$ ):
  - For order code for "Housing", option  $\boldsymbol{A}:$  glass
  - For order code for "Housing", option **B** and **C**: plastic

### Cable entries/cable glands



☑ 40 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with internal thread  $G \frac{1}{2}$  or NPT  $\frac{1}{2}$

Order code for "Housing", option A "Compact, aluminum, coated"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	
Adapter for cable entry with internal thread G $\frac{1}{2}$	Nickel-plated brass
Adapter for cable entry with internal thread NPT ½"	

#### Order code for "Housing", option B "Compact hygienic, stainless"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread G $\frac{1}{2}$ "	
Adapter for cable entry with internal thread NPT $\frac{1}{2}$ "	

#### Device plug

Electrical connection	Material
Plug M12x1	<ul> <li>Socket: Stainless steel, 1.4404 (316L)</li> <li>Contact housing: Polyamide</li> <li>Contacts: Gold-plated brass</li> </ul>

#### Sensor housing

The material of the sensor housing depends on the option selected in the order code for "Measuring tube mat., wetted surface".

Order code for "Measuring tube mat., wetted surface"	Material
Option HA, SA, SD, TH	<ul><li>Acid and alkali-resistant outer surface</li><li>Stainless steel 1.4301 (304)</li></ul>
	With order code for "Sensor option", option CC "316L Sensor housing": stainless steel, 1.4404 (316L)
Option SB, SC, SE, SF	<ul><li>Acid and alkali-resistant outer surface</li><li>Stainless steel 1.4301 (304)</li></ul>

### Measuring tubes

- DN 8 to 100 (3/8...4"): stainless steel, 1.4539 (904L); Manifold: stainless steel, 1.4404 (316/316L)
- DN 150 (6"), DN 250 (10"): stainless steel, 1.4404 (316/316L); Manifold: stainless steel, 1.4404 (316/316L)
- DN 8 to 250 (3/8 to 10"): Alloy C22, 2.4602 (UNS N06022); Manifold: Alloy C22, 2.4602 (UNS N06022)

#### **Process connections**

- Flanges according to EN 1092-1 (DIN2501) / according to ASME B 16.5 / as per JIS B2220:
  - Stainless steel, 1.4404 (F316/F316L)
  - Alloy C22, 2.4602 (UNS N06022)
  - Lap joint flanges: stainless steel, 1.4301 (F304); wetted parts Alloy C22
- All other process connections: Stainless steel, 1.4404 (316/316L)
- Available process connections  $\rightarrow \cong 90$

#### Seals

Welded process connections without internal seals

### Safety Barrier Promass 100

Housing: Polyamide

Process connections	<ul> <li>Fixed flange connections: <ul> <li>EN 1092-1 (DIN 2501) flange</li> <li>EN 1092-1 (DIN 2512N) flange</li> <li>Namur lengths in accordance with NE 132</li> <li>ASME B16.5 flange</li> <li>JIS B2220 flange</li> <li>DIN 11864-2 Form A flange, DIN 11866 series A, flange with notch</li> </ul> </li> <li>Clamp connections: <ul> <li>Tri-Clamp (OD tubes), DIN 11866 series C</li> </ul> </li> <li>Thread: <ul> <li>DIN 11851 thread, DIN 11866 series A</li> <li>SMS 1145 thread</li> <li>ISO 2853 thread, ISO 2037</li> <li>DIN 11864-1 Form A thread, DIN 11866 series A</li> </ul> </li> <li>VCO connections: <ul> <li>8-VCO-4</li> <li>12-VCO-4</li> </ul> </li> </ul>
	Process connection materials
Surface roughness	All data relate to parts in contact with fluid. The following surface roughness quality can be ordered. • Not polished • Ra <sub>max</sub> = 0.8 µm (32 µin)

Ra<sub>max</sub> = 0.4 μm (16 μin)

# Operability

Operating concept	Operator-oriented menu structure for user-specific tasks <ul> <li>Commissioning</li> <li>Operation</li> <li>Diagnostics</li> <li>Expert level</li> </ul>
	<ul> <li>Quick and safe commissioning</li> <li>Individual menus for applications</li> <li>Menu guidance with brief explanations of the individual parameter functions</li> </ul>

### **Reliable operation**

- Operation in the following languages:
  - Via "FieldCare", "DeviceCare" operating tool:
    - English, German, French, Spanish, Italian, Chinese, Japanese
  - Via integrated Web browser(only available for device versions with HART, PROFIBUS DP, PROFINET and EtherNet/IP):

English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean

- Uniform operating philosophy applied to operating tools and Web browser
- If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure.

For devices with Modbus RS485, the data recovery function is implemented without the plug-in memory (HistoROM DAT).

#### Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the operating tools and web browser
- Diverse simulation options
- Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment

#### Local display

A local display is only available for device versions with the following communication protocols: HART, PROFIBUS-DP, PROFINET, EtherNet/IP

The local display is only available with the following device order code: Order code for "Display; operation", option **B**: 4-line; illuminated, via communication

#### **Display element**

- 4-line liquid crystal display with 16 characters per line.
- White background lighting; switches to red in event of device errors.
- Format for displaying measured variables and status variables can be individually configured.
- Permitted ambient temperature for the display: –20 to +60  $^\circ$ C (–4 to +140  $^\circ$ F). The readability of
  - the display may be impaired at temperatures outside the temperature range.

#### **Remote operation**

# Via HART protocol

This communication interface is available in device versions with a HART output.





Image: Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 VIATOR Bluetooth modem with connecting cable
- 7 Transmitter

#### Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




42 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

#### Via EtherNet/IP network

This communication interface is available in device versions with EtherNet/IP.

Star topology




43 Options for remote operation via EtherNet/IP network: star topology

- 1 Automation system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Custom Add-On Profile for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare) with COM DTM "CDI Communication TCP/IP"
- 4 Ethernet switch
- 5 Measuring device

#### Via PROFINET network

This communication interface is available in device versions with PROFINET.

#### Star topology



44 Options for remote operation via PROFINET network: star topology

- 1 Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or computer with operating tool (e.g. FieldCare, DeviceCare, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 3 Switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device


#### Service interface

#### Via service interface (CDI-RJ45)

This communication interface is present in the following device version:

- Order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option L: PROFIBUS DP
- Order code for "Output", option **N**: EtherNet/IP
- Order code for "Output", option R: PROFINET


#### HART



🗷 45 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output

- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
   Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with
- "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


#### PROFIBUS DP



☑ 46 Connection for order code for "Output", option L: PROFIBUS DP

- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


#### EtherNet/IP



47 Connection for order code for "Output", option N: EtherNet/IP

- 1 Service interface (CDI -RJ45) and EtherNet/IP interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### PROFINET




48 Connection for order code for "Output", option R: PROFINET

- 1 Service interface (CDI -RJ45) and PROFINET interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

#### Via service interface (CDI)

This communication interface is present in the following device version: Order code for "Output", option **M**: Modbus RS485

Modbus RS485



- 1 Service interface (CDI) of measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

# **Certificates and approvals**

CE mark	The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-Tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

#### Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

#### ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

#### Ex ia

Category (ATEX)	Type of protection
II1/2G	Ex ia IIC T6T1 Ga/Gb or Ex ia IIB T6T1 Ga/Gb
II2G	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb
II1/2G, II2D	Ex ia IIC T6T1 Ga/Gb or Ex ia IIB T6T1 Ga/Gb Ex tb IIIC Txx °C Db
II2G, II2D	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb Ex tb IIIC Txx °C Db

#### Ex nA

Category (ATEX)	Type of protection
II3G	Ex nA IIC T6T1 Gc or Ex nA IIC T5-T1 Gc

#### <sub>C</sub>CSA<sub>US</sub>

Currently, the following versions for use in hazardous areas are available:

IS (Ex i)

	<ul> <li>Class I Division 1 Groups ABCD</li> <li>Class II Division 1 Groups EFG and Class III</li> </ul>		
	NI (Ex nA) Class I Division 2 Groups ABCD		
Sanitary compatibility	<ul> <li>3-A approval Only devices with the order code for "Additional approval", option LP "3A" have 3-A approval.</li> <li>EHEDG-tested Only devices with the order code for "Additional approval", option LT "EHEDG" have been tested and meet the requirements of the EHEDG. To meet the requirements for EHEDG certification, the device must be used with process connections in accordance with the EHEDG position paper entitled "Easy Cleanable Pipe Couplings and Process Connections" (www.ehedg.org).</li> </ul>		

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

**Certification PROFIBUS** 

HART certification

### **PROFIBUS** interface

HART interface

The measuring device is certified and registered by the PNO (PROFIBUS User Organization Organization). The measuring system meets all the requirements of the following specifications: • Certified in accordance with PROFIBUS PA Profile 3.02

• The device can also be operated with certified devices of other manufacturers (interoperability)

PROFINET interface			
<ul> <li>The measuring device is certified and registered by the PNO (PROFIBUS User Organization Organization). The measuring system meets all the requirements of the following specifications:</li> <li>Certified according to: <ul> <li>Test specification for PROFINET devices</li> <li>PROFINET Security Level 1 - Netload Class</li> </ul> </li> <li>The device can also be operated with certified devices of other manufacturers (interoperability)</li> </ul>			
The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications: • Certified in accordance with the ODVA Conformance Test • EtherNet/IP Performance Test • EtherNet/IP PlugFest compliance • The device can also be operated with certified devices of other manufacturers (interoperability)			
The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out.			
The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary.			
<ul> <li>With the identification PED/G1/x (x = category) on the sensor nameplate, Endress+Hauser confirms conformity with the "Essential Safety Requirements" specified in Appendix I of the Pressure Equipment Directive 2014/68/EU.</li> <li>Devices bearing this marking (PED) are suitable for the following types of medium: <ul> <li>Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to0.5 bar (7.3 psi)</li> <li>Unstable gases</li> </ul> </li> <li>Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Article 4 paragraph 3 of the Pressure Equipment Directive 2014/68/EU. The range of application is indicated in tables 6 to 9 in Annex 1 of the Pressure Equipment Directive 2014/68/EU.</li> </ul>			
<ul> <li>EN 60529 Degrees of protection provided by enclosures (IP code)</li> <li>IEC/EN 60068-2-6 Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal).</li> <li>IEC/EN 60068-2-31 Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices.</li> <li>EN 61010-1 Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements</li> <li>IEC/EN 61326 Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).</li> <li>NAMUR NE 21 Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment</li> <li>NAMUR NE 32 Data retention in the event of a power failure in field and control instruments with microprocessors</li> <li>NAMUR NE 43 Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.</li> <li>NAMUR NE 53 Software of field devices and signal-processing devices with digital electronics</li> <li>NAMUR NE 80 The application of the pressure equipment directive to process control devices</li> <li>NAMUR NE 105 Specifications for integrating fieldbus devices in engineering tools for field devices</li> </ul>			

- NAMUR NE 131
  - Requirements for field devices for standard applications
- NAMUR NE 132
   Coriolis mass meter
- NACE MR0103
- Materials resistant to sulfide stress cracking in corrosive petroleum refining environments.
- NACE MR0175/ISO 15156-1 Materials for use in H2S-containing Environments in Oil and Gas Production.

# **Ordering information**

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
   -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
   Open product page -> The "Configure" button to the right of the product image opens the Product
   Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com
- Product Configurator the tool for individual product configuration
- Up-to-the-minute configuration data
  - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
  - Automatic verification of exclusion criteria
  - Automatic creation of the order code and its breakdown in PDF or Excel output format
  - Ability to order directly in the Endress+Hauser Online Shop

# **Application packages**

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Detailed information on the application packages: Special Documentation for the device  $\rightarrow \square 102$ 

Heartbeat Technology	Package	Description
	Heartbeat Verification +Monitoring	<ul> <li>Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications.</li></ul>
		<ul> <li>Extension of calibration intervals according to operator's risk assessment.</li> <li>Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to: <ul> <li>Draw conclusions - using these data and other information - about the impact process influences (such as corrosion, abrasion, buildup etc.) have on the measuring performance over time. <li>Schedule servicing in time.</li> <li>Monitor the process or product quality, e.g. gas pockets.</li> </li></ul></li></ul>

Concentration	Package	Description
	Concentration	Calculation and outputting of fluid concentrations
		<ul> <li>The measured density is converted to the concentration of a substance of a binary mixture using the "Concentration" application package:</li> <li>Choice of predefined fluids (e.g. various sugar solutions, acids, alkalis, salts, ethanol etc.)</li> <li>Common or user-defined units ("Brix, "Plato, % mass, % volume, mol/l etc.) for standard applications.</li> <li>Concentration calculation from user-defined tables.</li> <li>The measured values are output via the digital and analog outputs of the device.</li> </ul>

Special density	Package	Description
	Special density	Many applications use density as a key measured value for monitoring quality or controlling processes. The device measures the density of the fluid as standard and makes this value available to the control system. The "Special Density" application package offers high-precision density measurement over a wide density and temperature range particularly for applications subject to varying process conditions.

# Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

#### Device-specific accessories For the sensor

Accessories	Description
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor. Water, water vapor and other non-corrosive liquids are permitted for use as fluids. If using oil as a heating medium, please consult with Endress+Hauser. Heating jackets cannot be used with sensors fitted with a rupture disk. If set of the se

Communication-specific accessories	Accessories	Description
	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop.
		For details, see the "Technical Information" document TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.
		For details, see "Technical Information" TI00429F and Operating Instructions BA00371F
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity.
		For details, see Operating Instructions BA00061S

Fieldgate FXA320	Gateway for the remote monitoring of connected 4 to 20 mA measuring devices via a Web browser.	
	For details, see "Technical Information" TI00025S and Operating Instructions BA00053S	
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser.	
	For details, see "Technical Information" TI00025S and Operating Instructions BA00051S	
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in non-hazardous areas.	
	For details, see Operating Instructions BA01202S	
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in the non-hazardous area and in the hazardous area.	
	For details, see Operating Instructions BA01202S	

Service-specific accessories	Accessories	Description
	Applicator	<ul> <li>Software for selecting and sizing Endress+Hauser measuring devices:</li> <li>Choice of measuring devices for industrial requirements</li> <li>Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy.</li> <li>Graphic illustration of the calculation results</li> <li>Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project.</li> <li>Applicator is available:</li> <li>Via the Internet: https://wapps.endress.com/applicator</li> </ul>
		<ul> <li>As a downloadable DVD for local PC installation.</li> </ul>
	W@M	<ul> <li>W@M Life Cycle Management</li> <li>Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle.</li> <li>W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime.</li> <li>Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, visit</li> <li>www.endress.com/lifecyclemanagement</li> </ul>
	FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.
		For details, see Operating Instructions BA00027S and BA00059S
	DeviceCare	Tool for connecting and configuring Endress+Hauser field devices.
		For details, see Innovation brochure IN01047S
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see "Technical Information" TI00405C

# System components

Accessories	Description	
Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.	
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R	
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the medium temperature.	
	For details, see "Fields of Activity", FA00006T	

# Supplementary documentation

For an overview of the scope of the associated Technical Documentation, refer to the following: • The *W@M Device Viewer* (www.endress.com/deviceviewer): Enter serial number from

- nameplate
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

#### Standard documentation

#### Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline Promass F	KA01261D

#### Transmitter Brief Operating Instructions

Measuring device	Documentation code
Proline Promass 100	KA01334D KA01333D KA01335D KA01332D KA01336D

#### **Technical Information**

Measuring device	Documentation code
Proline Promass F 100	TI01034D

#### **Description of Device Parameters**

Measuring device	Documentation code
Proline Promass 100	GP01033D
Proline Promass 100	GP01034D
Proline Promass 100	GP01035D
Proline Promass 100	GP01036D
Proline Promass 100	GP01037D

#### Supplementary devicedependent documentation

#### Safety Instructions

Content	Documentation code
ATEX/IECEx Ex i	XA00159D
ATEX/IECEx Ex nA	XA01029D
cCSAus IS	XA00160D
INMETRO Ex i	XA01219D
INMETRO Ex nA	XA01220D
NEPSI Ex i	XA01249D
NEPSI Ex nA	XA01262D

### **Special Documentation**

Content	Documentation code
Information on the Pressure Equipment Directive	SD00142D
Modbus RS485 Register Information	SD00154D
Concentration measurement	SD01152D
Concentration measurement	SD01503D
Heartbeat Technology	SD01153D
Heartbeat Technology	SD01493D
Web server	SD01820D
Web server	SD01821D
Web server	SD01822D
Web server	SD01823D

### Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory .

# **Registered trademarks**

### HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

#### **PROFIBUS®**

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

# Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

# EtherNet/IP™

Trademark of ODVA, Inc.

# **PROFINET**®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

#### Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

#### TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

www.addresses.endress.com

