

Technical Information

RMS621

Energy Manager Steam and Heat Computer for Industrial Energy Calculation of Steam and Water



Applications

- Energy management
- Chemical industry
- Heating and air conditioning
- Pharmaceutical industry
- Food and beverage
- Plant and panel manufacture

Features and benefits

• Calculation of the following applications:

Steam mass, steam heat quantity, net steam quantity, steam-heat differential, water heat quantity, waterheat differential

- Simultaneous calculation of up to three applications per device
- Real time clock
- Log book function for error messages and parameter changes with date and time
- Presettable allocation of the inputs/outputs to each application
- Configuration and operation using a serial interface and ReadWin[®] 2000 PC software
- Modular expansion using plug-in cards
- Large back-lit LC display with color change in the event of an error

- Quick and safe configuration with application-guided operation (Quick Setup)
- Online help function on all parameters optional
- Calculation as per IAPWS-IF 97
- Meets standards EN 1434-1, 2, 5 and 6 and OIML R75
- Bi-directional flow applications or energy measurement is possible
- Split-range flow measurements
- Averaging of several input signals
- Flow compensation due to improved differential pressure procedure
- UL recognized component to UL 3111-1





Function and system design

Measuring principle

Up to three different applications per device can be processed simultaneously. Two separate counters are available for each application, each of them is resettable.

Connection of measured variables 0/4 to 20 mA, PFM or pulse for sensors such as flow (differential pressure probes, vortex, turbine, orifice plate, among others) or pressure. When measuring temperatures, Pt100, Pt500 and Pt1000 in a 3- or 4-wire system can be connected as a 4 to 20 mA signal directly or using temperature transmitters (e.g. TMT181). A separate transmitter power supply is installed for each analog or pulse input. The available outputs are signal types 0/4 to 20 mA, pulse, digital and relay. The number of inputs, outputs, relays and transmitter power supplies contained in the basic device can be individually extended over a maximum of three plug-in cards.

In applications with overheated steam, the process is monitored for saturated steam or wet steam. If the saturated steam curve is reached, this can be output as an alarm value. The summation of the calculated values is not interrupted when process limits (e.g. saturated steam curve) are exceeded or below set values. The most recently valid values are registered in the event memory when they leave or return to the valid process limits.

Steam mass

Calculation of the mass flow in a steam line from the process variables for flow, pressure and temperature. In saturated steam operation, the mass flow is calculated from two input variables (pressure-compensated or temperature-compensated).

Steam heat quantity

Calculation of the mass flow and its quantity of heat (energy) in a steam line from the process variables for flow, pressure and temperature. Saturated steam operation is possible, calculation is the same as for steam mass.



Calculation of the steam mass flow and steam heat quantity from the input variables for flow (Q), pressure (p) and temperature (T)

Steam - heat - differential

Calculation of the quantity of heat emitted or absorbed in a steam application using temperature differential measurement from the process variables for flow, pressure and two temperature values. Balancing a steam generation process (phase transition: water \rightarrow steam) or a steam heating process (phase transition: steam \rightarrow water) is possible.

Net steam quantity

Calculation of the quantity of heat that can be extracted from a steam mass flow until it condenses to water. Process variables: flow, pressure, temperature. For saturated steam, the calculation is made from two input variables.



Calculation of the steam-heat differential and net steam quantity from the input variables for flow (Q), pressure (p) and the temperature differential $(T_1 - T_2)$

Water heat quantity

Calculation of the quantity of heat in a water flow from the process variables for flow and temperature.

Water-heat differential

Calculation of the quantity of heat that is emitted or absorbed by a water flow in a heating or cooling system. The quantity of heat is calculated from the process variable for flow and the differential from the feed and return temperature. Bidirectional energy calculations, such as the calculating systems with changing flow direction (charging/discharging the heat accumulator) are also possible.



Calculation of the water heat quantity and water-heat differential from the input variables for flow (Q) and the temperature differential ($T_1 - T_2$)

Measuring system

The analog input variables are digitized, the pulse and PFM signals recorded using period length/frequency measurement and processed further in the arithmetic unit controlled by the microcontroller. The energy values are calculated in accordance with the highly precise equations of the international industry standard IAPWS-IF97, which makes the calculation quicker and more precise. This guarantees maximum precision and high calculating speed in all temperature ranges. The internal real time clock with power reserve is used to integrate the flow values. Both the input variables and the results can be transferred via the outputs. When a differential pressure signal is used, the sensor data is recalculated over the entire working range of the flow sensors. Configuration of the inputs, outputs, alarm values, the display as well as commissioning and maintenance of the device can be performed via 8 soft keys with the back-lit dot matrix display, or using the RS232 interface with the ReadWin[®] 2000 PC software or using an external display and operating unit. A menu-guided quick setup is available on request for the initial start-up. Online help makes on-site operation easier. The color change of the background lighting visualizes alarm value violations or faults. A function expansion of the device by means of expansion cards can be made at any time.

Input

Measured variable

Current, PFM, pulse, temperature

Input signals

Flow, differential pressure, pressure, temperature

Measuring range

Measured variable	Input		
Current	 0/4 to 20 mA +10% overreach Max. input current 150 mA Input impedance < 10 Ω Accuracy 0.1% of full scale value Temperature drift 0.04% / 1 K (1.8 °F) ambient temperature change Signal attenuation low-pass filter 1st order, filter constants 0 to 99 s configurable Resolution 13 Bit Fault recognition 3.6 mA or 21 mA limit as per NAMUR NE 43* 		
PFM	 Frequency range when using an input on the mainboard (Slot A): 0.25 Hz to 12.5 kHz Frequency range when using an input on an extension board (Slot B, C, D): 0.01 Hz to 12.5 kHz Signal level 2 to 7 mA low; 13 to 19 mA high Measurement method: period length/frequency measurement Accuracy 0.01% of measured value Temperature drift 0.1% / 10 K (18 °F) ambient temperature change 		
Pulse	 Frequency range when using an input on the mainboard (Slot A): 0.25 Hz to 12.5 kHz Frequency range when using an input on an extension board (Slot B, C, D): 0.01 Hz to 12.5 kHz Signal level 2 to 7 mA low; 13 to 19 mA high with approx. 1.3 kΩ dropping resistor at max. 24 V voltage level 		
Temperature	Resistance thermometer (RTD) according to IEC 751 ($\alpha = 0.00385$):		
	Designation	Measuring range	Accuracy (4-wire connection)
	Pt100	-200 to 800 °C (-328 to 1472 °F)	0.03% of full-scale value
	Pt500	-200 to 250 °C (-328 to 482 °F)	0.1% of full-scale value
	Pt1000	-200 to 250 °C (-328 to 482 °F)	0.08% of full-scale value
	 Type of conne Measuring cut Resolution 16 Temperature of 	ection: 3– or 4-wire system rrent 500 μA Bit drift 0.01% / 10 K (18 °F) ambient tempe	rature change

Number:

- 2 x 0/4 to 20 mA/PFM/Pulse
- 2 x Pt100/500/1000 (in basic device)

Maximum number:

• 10 (depends on number and kind of plug-in cards)

* Breakdown information to NAMUR NE 43

Breakdown information is created when the measuring information is invalid or not present anymore and gives a complete listing of all errors occuring in the measuring system.

		Signal (mA)
Under ranging	Standard	3.8
Over ranging	Standard	20.5
Sensor break; sensor short circuit low	To NAMUR NE 43	≤ 3.6
Sensor break; sensor short circuit high	To NAMUR NE 43	≥ 21.0

Galvanic isolation

The inputs are galvanically isolated between the individual expansion cards and the basic device (see also 'galvanic isolation' in section "Output").

Output

Basic device:

Output signal

Current, pulse, transmitter power supply and switching output

Galvanic isolation

Connection, terminals	Power supply (L/N)	Input 1/2 0/4 to 20 mA/PFM/ pulse (10/11) or (110/11)	Input 1/2 TPS (82/81) or (83/81)	Input 1/2 temperature (1/5/6/2) or (3/7/8/4)	Output 1/2 0 to 20 mA/ pulse (132/131) or (134/ 133)	Interface RS232/485 housing front or (102/101)	TPS external (92/91)
Power supply		2.3 kV	2.3 kV	2.3 kV	2.3 kV	2.3 kV	2.3 kV
Input 1/2 0/4 to 20 mA/ PFM/pulse	2.3 kV			500 V	500 V	500 V	500 V
Input 1/2 TPS	2.3 kV			500 V	500 V	500 V	500 V
Input 1/2 temperature	2.3 kV	500 V	500 V		500 V	500 V	500 V
Output 1/2 0 to 20 mA/ pulse	2.3 kV	500 V	500 V	500 V	500 V	500 V	500 V
Interface RS232/RS485	2.3 kV	500 V	500 V	500 V	500 V	500 V	500 V
TPS external	2.3 kV	500 V	500 V	500 V	500 V	500 V	

Note!

The specified insulation voltage is the AC testing voltage $U_{eff.}$, which is applied between the connections. Basis for assessment: IEC 61010-1, protection class II, overvoltage category II

Current - pulse output variable

Current	 0/4 to 20 mA +10% overreach, invertible Max. loop current 22 mA (short-circuit current) Max. load 750 Ω at 20 mA Accuracy 0.1% of full-scale value Temperature drift: 0.1% / 10 K (18 °F) ambient temperature change Output ripple < 10 mV at 500 Ω for frequencies < 50 kHz Resolution 13 Bit Error signals 3.6 mA or 21 mA limit configurable as per NAMUR NE43 (see current inputs, page 4)
Pulse	Basic device: Frequency range to 12.5 kHz Voltage level 0 to 1 V low, 24 V high ±15% Min. load 1 kΩ Max. pulse width 0.04 to 1000 ms
	Expansion cards (digital passive, open collector): • Frequency range to 12.5 kHz • $I_{max.} = 200 \text{ mA}$ • $U_{max.} = 24 \text{ V} \pm 15\%$ • $U_{low/max.} = 1.3 \text{ V}$ at 200 mA • Max. pulse width 0.04 to 1000 ms

Number	Number: • 2 x 0/4 to 20 mA/Pulse (in basic device)
	 Maximum number: 8 x 0/4 to 20 mA/Pulse (depends on the number of plug-in cards) 6 x digital passive (depends on the number of plug-in cards)
Signal sources	All available multifunctional inputs (current, PFM or pulse inputs) and results can be freely allocated to the outputs.

Switching output

Function	Limit relay switches in these operating modes: minimum, maximum safety, gradient, alarm, saturated steam alarm, frequency/pulse, device error
Switch behavior	Binary, switches when the alarm value is reached (potential-free NO contact)
Relay switching capacity	Max. 250 V AC, 3 A / 30 V DC, 3 A
	Note! When using relays on expansion cards, a mixture of low voltage and extra-low voltage is not permitted.
Switching frequency	Max. 5 Hz
Switching threshold	Programmable (wet steam alarm is preset to 2 °C (35.6 °F) at the factory)
Hysteresis	0 to 99%
Signal source	All available inputs and calculated variables can be allocated freely to the switching outputs.
Number	1 (in basic device) Max. number: 7 (depends on number and kind of plug-in cards)
Number of output states	100,000
Scan rate	250 ms

Transmitter power supply and external power supply

- Transmitter power supply (TPS), terminals 81/82 or 81/83 (optional universal expansion cards 181/182 or 181/183): Supply voltage 24 V DC \pm 15% Impedance < 345 Ω Maximum output current 22 mA (for U_{out} > 16 V) Maximum current 30 mA, short-circuit proof HART[®] communication is not accounted for Number 2 (in basic device) Maximum number: 5 (depends on number and kind of plug-in cards)
 - Additional power supply (e.g. external display), Terminals 91/92: Supply voltage 24 V DC \pm 5% Maximum current 80 mA, short-circuit proof Number 1 Source resistance < 10 Ω

Power supply

Electrical connection (wiring diagrams)



RMS621 terminal assignment - basic device + expansion cards (optional)

Supply voltage	 Low voltage power unit: 90 to 250 V AC 50/60 Hz Extra-low voltage power unit: 20 to 36 V DC or 20 to 28 V AC 50/60 Hz
Power consumption	8 to 26 VA (dependent on the expansion stage)

Connection data interface	RS232	
	 Connection: 3.5 mm (0.14 in) jack plug on front panel Transmission protocol: ReadWin[®] 2000 Transmission rate: max. 57,600 Baud 	
	RS-485	
	 Connection: plug-in terminals 101/102 (in basic device) Transmission protocol: (serial: ReadWin[®] 2000; parallel: open standard) Transmission rate: max. 57,600 Baud 	
	Optional: additional RS-485 interface	
	 Connection: plug-in terminals 103/104 Transmission protocol and transmission rate same as standard RS-485 interface 	

Performance characteristics

Reference operating conditions	 Power supply 230 V AC ± 10%; 50 Hz ± 0.5 Hz Warm-up period > 30 min
	 Ambient temperature 25 °C ± 5 K (77 °F ± 9 °F) Humidity 39% ± 10% relative humidity

Arithmetic unit	Medium	Variable	Range	
		Temperature measuring range	0 to 374 °C (32 to 705.2 °F)	
		Maximum Temperature differential range ΔT	0 to 374 °C (0 to 673.2 °F)	
		Water	Error limit for ΔT	3 to 20 K (5.4 to 36 °F) $<$ 2.0% of measured value 20 to 250 K (36 to 450 °F) $<$ 0.3% of measured value
		Arithmetic unit accuracy class	as per EN 1434-1 / OIML R75 (< 1.5%)	
			Measurement and calculation interval	500 ms
		Temperature measuring range	0 to 800 °C (32 to 1472 °F)	
	Steam	Pressure measuring range	0 to 1000 bar (0 to 14,500 psi)	
		Measurement and calculation interval	500 ms	

Installation conditions

Installation instructions	Mounting location
	In the cabinet on DIN rail IEC 60715 TH 35
	Caution! When using extension cards, venting with an air current of at least 0.5 m/s is necessary.
	Orientation
	no restrictions

Environmental conditions

-20 to 60 °C (-4 to 140 °F)
-30 to 70 °C (-22 to 158 °F)
as per IEC 60 654-1 Class B2 / EN 1434 Class 'C'
As per IEC 61010-1: Environment < 2000 m (6560 ft) above sea level
 Basic device: NEMA 1 (IP 20) External display: NEMA 4X (IP 65)
NAMUR NE 21
This recommendation is an uniform and practical way of determining whether the devices used in laboratory and process control are immune to interference with an objective to increase its functional safety.
Interference emission
IEC 61326 (EN 61326 Class A)
Interference immunity
 Power failure: 20 ms, no influence Starting current limitation: I_{max}/I_n ≤ 50% (T50% ≤ 50 ms) Electromagnetic fields: 10 V/m as per IEC 61000-4-3 Conducted HF: 0.15 to 80 MHz, 10 V as per IEC 61000-4-3 Electrostatic discharge: 6 kV contact, indirect as per IEC 61000-4-2 Burst (power supply): 2 kV as per IEC 61000-4-4 Burst (signal): 1 kV/2 kV as per IEC 61000-4-4 Surge (AC power supply): 1 kV/2 kV as per IEC 61000-4-5 Surge (signal):500 V/1 kV as per IEC 61000-4-5

Mechanical construction

Design, dimensions



Housing for DIN rail as per IEC 60751 TH35; dimensions in mm (inch)



Unit upgrade with expansion cards (optional or available as accessories)

- Slots A and E equipped in the basic device
 Slots B, C and D can be upgraded with expansion cards

Weight	 Basic device: 500 g (1.1 lb) in maximum configuration with expansion cards Remote control unit: 300 g (0.7 lb)
Material	Housing: polycarbonate plastic, UL 94V0
TerminalsCoded, pluggable screw terminals; Clamping area 1.5 mm² (16 AWG) solid, 1.0 mm² (maximum 18 AWG) flexible with wire end ferrule (applies to all connections).	

Human interface

Display elements

Display (optional):

160 x 80 Dot-matrix LCD with blue background lighting Color changes to red in the event of an error (adjustable)

- LED status display: Operation: 1 x green (2 mm; 0.079 in) Fault message: 1 x red (2 mm; 0.079 in)
- External display and operating unit (optional or as accessory):

A display and operating unit can also be connected to the energy manager in the panel mounted housing, dimensions (WxHxT) 144 mm (5.7 in) x 72 mm (2.84 in) x 43 mm (1.7 in). The connection to the integrated RS485 interface is made using the connecting cable, l = 3 m (10 ft), which is included in the accessories set. Parallel operation of the external display unit with a device-internal display in the RMS621 is possible.



External display and operating unit for panel mounting (optional or available as accessory); dimensions in mm (inches)



External display and operating unit in the panel mounted housing

Operating elements	Eight front-panel soft keys interact with the display (function of the keys is shown in the display).
Remote operation	RS232 interface (3.5 mm (0.14 in) jack plug on front panel): configuration via PC with ReadWin [®] 2000 PC operating software.
Real time clock	 Deviation: 2.6 min per year Power reserve: 14 days

Mathematical functions	Continuous calculation of dimensions, standard volumes, density, enthalpy, quantity of heat via IAWPS-IF97.						
	Note! How the IAPWS standards relate to the ASME Steam Tables The "ASME Steam Tables" many people are familar with, is a book first published in 1967, with accompanyingsoftware in later editions. The thermodynamic properties in the 1967 ASME Steam Tables book were calculated from a formulation for industrial use known as IFC-67, which was developed and adopted as a standard by the international organization that later became IAPWS. The ASME Steam Tables was just one ofmany books produced from this international standard; several other countries and organizations have issuedbooks based on IFC-67.						
	However, the IFC-67 formulation is now officially obsolete, having been replaced in late 1997 by a new for- mulation known as IAPWS-IF97. IAPWS-IF97 is now the international standard for calculations in the steampower industry. As a result, the ASME has produced a replacement for the 1967 book, titled ASME Internati-onal Steam Tables for Industrial Use. This book has tables based on the new IAPWS-IF97 formulation.						

CE-approval	The device meets the legal requirements of the EC directives. Endress+Hauser confirms that the device has been successfully tested by applying the CE mark.
Other standards and guidelines	 NAMUR NE21, NE43 Standardization association for measurement and control in chemical and pharmaceutical industries. IAWPS-IF 97 International applicable and recognized calculation standard (since 1997) for steam and water. Issued by the International Association for the Properties of Water and Steam (IAPWS). OIML R75 International construction regulation and test specification for water energy managers from the Organisation Internationale de Métrologie Légale. EN 1434-1, 2, 5 and 6 ISO 5167 Flow measurement of fluids with throttle devices
UL approval	Recognized component to UL 3111-1.

Certificates and approvals

Ordering information

Product structure	RMS621 Steam- and heat computer For calculating steam mass, heat and differential between water/steam. Calculation formula to IAPWS-IF 97; Standard input: 2 x 0/4 to 20 mA/PFM/Pulse, 2 x Pt100/500/1000; Standard output: 2 x 0/4 to 20 mA/PEM/Pulse, 1 x relay (closing cont.), 1 x transmitter power supply													
		Operation												
		1	Softv	ware	Read	lWin	® 200)0, w	/o b	outt	on			
		2	Alph	anur	neric	disp	lay, b	utton	18					
		3	Rem	ote,	RS48	5, pa	inel n	iount	ting 7	72 in a	x 144 mm			
		4	Kein	ote, .	ZXK	.340.	so, panel mounting / 2 x 144 mm							
			Pov	ver	supp	ply		0.44.0						
			1 2	90 t 20 t	o 25(o 36	0 V A V D(AC, 50 C / 20	C, 50/60Hz / 20 to 28 V AC, 50/60Hz						
				Slo	t B									
		B Input: 2 x 0/4 to 20 mA/PFM/Pulse + 2 x loop power supply												
			b Input: $2 \times 0/4$ to $20 \text{ mA/Pruse} + 2 \times 100p$ power supply Output: $2 \times 0/4$ to $20 \text{ mA/Pulse} 2 \times \text{digital}, 2 \times \text{relays SPST}$ C Input: $2 \times \text{Pt100/500/1000}$ Output: $2 \times 0/4$ to $20 \text{ mA/Pulse}, 2 \times \text{digital}, 2 \times \text{relays SPST}$											
		Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST									v i use, 2 x uigildi, 2 x ieldys ofol			
					Slo A	t C	11000	1						
		A Not used B Input: 2 x 0/4 to 20 mA/PFM/Pulse + 2 x loop power supply Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST									mA/PFM/Pulse + 2 x loop power supply			
											0 mA/Pulse, 2 x digital, 2 x relays SPST			
					C Input: 2 x Pt100/500/1000 Output: 2 x 0/4 to 20 mA/Pulse 2 x digital 2 x relays SPST									
		1				Sla	+ D		,	-				
				A Not used										
						В	B Input: 2 x 0/4 to 20 mA/PFM/Pulse + 2 x loop power supply							
		C Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST Input: 2 x Pt100/500/1000 Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST								4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST				
										4 to 20 mA/Pulse, 2 x digital, 2 x relays SPST				
		User Mode												
		1 Basic version									on			
		2 1 x application, pre-installed Operation Language												
								an						
								2	En	iglis	sh			
							3 French 4 Italian							
				5 Czech							h			
		6 American							ican					
				7 Polish										
							n sh							
						1	1	1						
										om 	1 x RS232 + 1 x RS485			
									2		1 x RS232 + 1 x RS485 + cable + software ReadWin [®] 2000			
									3		1 x RS232 + ext. PROFIBUS-DP slave module			
									4		1 x RS232 + cable + ext. PROFIBUS-DP slave module + software ReadWin [®] 2000			
									5		1X K5232/1X M-BUS + 1X K5485 1x R5232/1X M-BUS + 1x R5485 + cable + software PoadWin® 2000			
									A		1x RS232 + 1x RS485 + 1x ModBus			
									В		1x RS232 + 1x RS485 + 1x ModBus + cable + software Readwin			
											Additional Option			
											1 Basic version			
											Works calib. certif., 5-pointDIN rail installation kit			
	RMS621-										$\leftarrow \text{Order code (complete)}$			

Product structure selection aid

The following table contains an overview of the order codes for the expansion cards with the possible applications in a RMS621 energy manager:

Applications in one unit	Number of input	Order code (expansion cards)	
1 x saturated steam mass	1 x Pulse flow 1 x 4 to 20 mA pressure		
1 x steam mass	1 x 4 to 20 mA flow 1 x 4 to 20 mA pressure 1 x Pt100 temperature	RMS621-xxAAAxxxx	
1 x steam heat differencial	1 x 4 to 20 mA flow 1 x 4 to 20 mA pressure 2 x Pt100 temperature		
2 x saturated steam mass	2 x Pulse flow 2 x 4 to 20 mA pressure	RMS621-xxBAAxxxx	
1 x steam mass 1 x steam heat quantity	2 x PFM flow 2 x 4 to 20 mA pressure 2 x Pt500 temperature		
1 x saturated steam mass 1 x water heat quantity	2 x Pulse flow 1 x 4 to 20 mA pressure 2 x Pt100 temperature		
2 x water heat quantity	DMS621 wrCAAwww		
1 x water heat quantity 1 x water heat differencial	2 x 4 to 20 mA flow 4 x Pt100 temperature	1 KIVIƏUZ I-XXUAAXXXX	
3 x saturated steam mass	3 x Pulse flow 3 x 4 to 20 mA pressure	RMS621-xxBBAxxxx	
1 x steam heat quantity 1 x water heat differencial	1 x PFM flow 1 x Pulse flow 1 x 4 to 20 mA pressure 3 x Pt100 temperature	RMS621-xxBCAxxxx	
1 x steam heat differencial 1 x water heat differencial	2 x PFM flow 1 x 4 to 20 mA pressure 4 x Pt100 temperature		
1 x steam mass 1 x net steam quantity 1 x water heat quantity	3 x PFM flow 2 x 4 to 20 mA pressure 4 x Pt100 temperature	- RMS621-xxBBCxxxx	
3 x steam mass	3 x 4 to 20 mA flow 3 x 4 to 20 mA pressure 3 x Pt500 temperature		
1 x steam mass 2 x water heat differencial	3 x PFM flow 1 x 4 to 20 mA pressure 5 x Pt100 temperature	RMS621-xxBCCxxxx	
3 x water heat differencial	3 x Pulse flow 6 x Pt100 temperature		

Accessories

	 PC configuration software ReadWin[®] 2000 and serial configu (0.14 in) stereo type jack plug. Order No.: RMS621A-VK External display and operating unit in the panel mounted hour (5.7 x 2.84 x 1.7 inches) Order No.: RMS621A-AA NEMA 4 (IP 66) protective housing for field mounting DIN ra Order No.: 52010132 PROFIBUS Interface Order No.: RMS621A-P1 	configuration software ReadWin [®] 2000 and serial configuration cable with 3.5 mm 4 in) stereo type jack plug. er No.: RMS621A-VK ernal display and operating unit in the panel mounted housing 144 x 72 x 43 mm x 2.84 x 1.7 inches) er No.: RMS621A-AA MA 4 (IP 66) protective housing for field mounting DIN rail instrumentation er No.: 52010132 DFIBUS Interface er No.: RMS621A-P1					
Expansion cards	A function expansion of the device by means of max. 3 extension cards (universal and/or temperature cards) is possible.						
	Extension card temperature Input: 2 x Pt100/500/1000 Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays	Order No.: RMS621A-TA					
	Extension card universal Input: 2 x $0/4$ to 20 mA/PFM/Pulse with transmitter power supply	Order No.: RMS621A-UA					

Documentation

Output: 2 x 0/4 to 20 mA/Pulse, 2 x digital, 2 x relays

Operating manual 'Energy Manager RMS621' (BA255R/09)
Technical information "PROline Prowirl 72 flowmeter" (TI070D/06)

Instruments International

Endress+Hauser Instruments International AG Kaegenstrasse 2 4153 Reinach Switzerland

Tel. +41 61 715 81 00 Fax +41 61 715 25 00 www.endress.com info@ii.endress.com

