Technical Information **Proline Promass P 100**

Coriolis flowmeter



Specialist for life sciences with an ultra-compact transmitter

Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Designed for applications under sterile conditions in the life sciences industry

Device properties

- ASME BPE, 3-A, EHEDG compliant & low delta-ferrite
- Electropolished measuring tube in 1.4435 (316L)
- Fast recovery from CIP/SIP
- Robust, ultra-compact transmitter housing
- Highest degree of protection: IP69K
- Local display available

Your benefits

- Highest process quality fully compliant with industry requirements
- Fewer process measuring points multivariable measurement (flow, density, temperature)
- Space-saving installation no inlet/outlet run needs
- Space-saving transmitter full functionality on smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification Heartbeat Technology™



Table of contents

Document information		Degree of protection	
For all or and a street dealers	_	Shock resistance	51
Function and system design		Interior cleaning	51
Measuring principle		Electromagnetic compatibility (EMC)	51
Measuring system		F	
Equipment architecture		D.	-1
Safety	. 7	Process	51
		Medium temperature range	
Input	Ω	Density	51
Measured variable		Pressure-temperature ratings	51
		Secondary containment pressure rating	55
Measuring range		Flow limit	55
Operable flow range		Pressure loss	55
Input signal	. 8	System pressure	55
		Thermal insulation	56
Output	9	Heating	57
Output signal		Vibrations	57
Signal on alarm		vioracions) /
Ex connection data	12		
		Mechanical construction	58
Low flow cut off	13	Dimensions in SI units	58
Galvanic isolation	13	Dimensions in US units	78
Protocol-specific data	13	Weight	86
		Materials	
Power supply	23	Process connections	
Terminal assignment		Surface roughness	88
Pin assignment, device plug		Surface roughness vivient vivient vivient vivient	00
Supply voltage	32		
Power consumption		Operability	
Current consumption		Operating concept	
	33	Local display	89
Power supply failure	34	Remote operation	89
Electrical connection		Service interface	91
Potential equalization	39		
Terminals	39	Contificates and approvals	94
Cable entries	39	Certificates and approvals	
Cable specification	39	CE mark	
		C-Tick symbol	
Performance characteristics	41	Ex approval	94
Reference operating conditions		Sanitary compatibility	95
Maximum measured error		HART certification	
	42	Certification PROFIBUS	95
Repeatability		Certification PROFINET	95
Response time	43	EtherNet/IP certification	95
Influence of ambient temperature	43	Modbus RS485 certification	95
Influence of medium temperature		Pressure Equipment Directive	95
Influence of medium pressure	44	Other standards and guidelines	96
Design fundamentals	44	J	
			~~
Installation	45	Ordering information	96
Mounting location			
Orientation	46	Application packages	96
Inlet and outlet runs	46	Heartbeat Technology	97
Special mounting instructions	46	Concentration	
Mounting Safety Barrier Promass 100		Gomeenitiation)
Miduliting Safety Darrier Fromass 100	40		
			97
Environment	48	Device-specific accessories	97
Ambient temperature range	48	Communication-specific accessories	98
Storage temperature	50	Service-specific accessories	98
Climate class	50	System components	99
	- 1	•	

2

Supplementary documentation	99
Standard documentation	. 99
Supplementary device-dependent documentation	100
Registered trademarks	100

Document information

$Symbols\ used$

Electrical symbols

Symbol	Meaning	Symbol	Meaning
	Direct current	~	Alternating current
≂	Direct current and alternating current	≐	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective ground connection A terminal which must be connected to ground prior to establishing any other connections.	\$	Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice.

Symbols for certain types of information

Symbol	Meaning
\checkmark	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
X	Forbidden Procedures, processes or actions that are forbidden.
i	Tip Indicates additional information.
[i	Reference to documentation
A	Reference to page
	Reference to graphic
	Visual inspection

Symbols in graphics

Symbol	Meaning	Symbol	Meaning
1, 2, 3,	Item numbers	1. , 2. , 3	Series of steps
A, B, C,	Views	A-A, B-B, C-C,	Sections
EX	Hazardous area	×	Safe area (non-hazardous area)
≈ →	Flow direction		

Function and system design

Measuring principle

The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.

 $F_c = 2 \cdot \Delta m (v \cdot \omega)$

 F_c = Coriolis force

 $\Delta m = moving mass$


 $\omega = rotational velocity$

v = radial velocity in rotating or oscillating system

The amplitude of the Coriolis force depends on the moving mass Δm , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity ω , the sensor uses oscillation.

In the sensor, an oscillation is produced in the measuring tube. The Coriolis forces produced at the measuring tube cause a phase shift in the tube oscillations (see illustration):

- If there is zero flow (i.e. when the fluid stands still), the oscillation measured at points A and B has the same phase (no phase difference).
- Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).



A0016772

The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. System balance is created by exciting an eccentrically arranged swinging mass to antiphase oscillation. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

Density measurement

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.

Volume measurement

Together with the measured mass flow, this is used to calculate the volume flow.

Temperature measurement

The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.


Measuring system

The device consists of a transmitter and a sensor. If a device with Modbus RS485 intrinsically safe is ordered, the Safety Barrier Promass 100 is part of the scope of supply and must be implemented to operate the device.

The device is available as a compact version:

The transmitter and sensor form a mechanical unit.

Transmitter



Device versions and materials:

- Compact, aluminum coated: Aluminum, AlSi10Mg, coated
- Compact, hygienic, stainless:
 Hygienic version, stainless steel 1.4301 (304)
- Ultra-compact, hygienic, stainless: Hygienic version, stainless steel 1.4301 (304)


Configuration:

- Via operating tools (e.g. FieldCare)
- Additionally for device version with local display:
 Via Web browser (e.g. Microsoft Internet Explorer)
- Also for device version with 4-20 mA HART, pulse/frequency/switch output:

Via Web browser (e.g. Microsoft Internet Explorer)


- Also for device version with EtherNet/IP output:
 - Via Web browser (e.g. Microsoft Internet Explorer)
 - Via Add-on Profile Level 3 for automation system from Rockwell Automation
 - Via Electronic Data Sheet (EDS)
- Also for device version with PROFINET output:
- Via Web browser (e.g. Microsoft Internet Explorer)
- Via device master file (GSD)

Sensor




- For use in sterile applications in heavily regulated industries
- Nominal diameter range: DN 8 to 50 (3/8 to 2")
- Materials:
 - Sensor: stainless steel, 1.4301 (304)
- Measuring tubes: stainless steel, 1.4435 (316L)
- Process connections: stainless steel, 1.4435 (316L); 1.4404 (316/316L)
- Surface quality: Ra_{max} 0.76 μm (30 μin) Ra_{max} 0.38 μm (15 μin) (electropolished)
- Delta ferrite <1%

Safety Barrier Promass 100



- Dual-channel safety barrier for installation in non-hazardous locations or zone 2/div. 2:
 - Channel 1: DC 24 V power supply
 - Channel 2: Modbus RS485
- In addition to current, voltage and power limitation, it offers galvanic isolation of circuits for explosion protection.
- Easy top-hat rail mounting (DIN 35 mm) for installation in control cabinets

Equipment architecture



 $\blacksquare \ 1$ Possibilities for integrating measuring devices into a system

- 1 Automation system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 Modbus RS485
- 5 4-20 mA HART, pulse/frequency/switch output
- 6 Safety Barrier Promass 100
- 7 Modbus RS485 intrinsically safe
- 8 Non-hazardous area
- 9 Non-hazardous area and Zone 2/Div. 2
- 1.0 Intrinsically safe area and Zone 1/Div. 1

Safety

IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

Input

Measured variable

Direct measured variables

- Mass flow
- Density
- Temperature

Calculated measured variables

- Volume flow
- Corrected volume flow
- Reference density

Measuring range

Measuring ranges for liquids

DN		Measuring range full scale values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$	
[mm]	[in]	[kg/h]	[lb/min]
8	3/8	0 to 2 000	0 to 73.50
15	1/2	0 to 6 500	0 to 238.9
25	1	0 to 18 000	0 to 661.5
40	1½	0 to 45 000	0 to 1654
50	2	0 to 70 000	0 to 2 573

Recommended measuring range

Operable flow range

Over 1000:1.

Flow rates above the preset full scale value are not overridden by the electronics unit, with the result that the totalizer values are registered correctly.

Input signal

External measured values

To increase the accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write different measured values to the measuring device:

- Operating pressure to increase accuracy (Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.q. Cerabar M or Cerabar S)
- Medium temperature to increase accuracy (e.g. iTEMP)
- Reference density for calculating the corrected volume flow for gases
- Various pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section → 🗎 99

It is recommended to read in external measured values to calculate the following measured variables:

- Mass flow
- Corrected volume flow

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Digital communication

The measured values can be written from the automation system to the measuring via:

- PROFIBUS DP
- Modbus RS485
- EtherNet/IP
- PROFINET

Output

Output signal

Current output

Current output	4-20 mA HART (active)
Maximum output values	DC 24 V (no flow)22.5 mA
Load	0 to 700 Ω
Resolution	0.38 μΑ
Damping	Adjustable: 0.07 to 999 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature The range of options increases if the measuring device has one or more application packages.

Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	■ DC 30 V ■ 25 mA
Voltage drop	For 25 mA: ≤ DC 2 V
Pulse output	
Pulse width	Adjustable: 0.05 to 2 000 ms
Maximum pulse rate	10 000 Impulse/s
Pulse value	Adjustable
Assignable measured variables	Mass flowVolume flowCorrected volume flow
Frequency output	
Output frequency	Adjustable: 0 to 10 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature The range of options increases if the measuring device has one or more application packages.
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s

Number of switching cycles	Unlimited
Assignable functions	■ Off ■ On ■ Diagnostic behavior ■ Limit value ■ Mass flow ■ Volume flow ■ Corrected volume flow ■ Density ■ Reference density ■ Temperature ■ Totalizer 1-3 ■ Flow direction monitoring ■ Status ■ Partially filled pipe detection ■ Low flow cut off The range of options increases if the measuring device has one or more application packages.

PROFIBUS DP

Signal encoding	NRZ code
Data transfer	9.6 kBaud12 MBaud

Modbus RS485

Physical interface	In accordance with EIA/TIA-485-A standard
Terminating resistor	 For device version used in non-hazardous areas or Zone 2/Div. 2: integrated and can be activated via DIP switches on the transmitter electronics module For device version used in intrinsically safe areas: integrated and can be activated via DIP switches on the Safety Barrier Promass 100

EtherNet/IP

Standards In accordance with IEEE 802.3	
---	--

PROFINET

Standards	In accordance with IEEE 802.3
-----------	-------------------------------

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

4-20 mA

 Min. value: 3.59 mA Max. value: 22.5 mA Freely definable value between: 3.59 to 22.5 mA Actual value Last valid value 	Failure mode	 Freely definable value between: 3.59 to 22.5 mA Actual value
---	--------------	---

HART

Device diagnostics	Device condition can be read out via HART Command 48
Device diagnostics	Device condition can be read out via 11 livi command 40

Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from: Actual value No pulses
Frequency output	
Failure mode	Choose from: Actual value O Hz Defined value: 0 to 12 500 Hz
Switch output	
Failure mode	Choose from: Current status Open Closed

PROFIBUS DP

Status and alarm	Diagnostics in accordance with PROFIBUS PA Profile 3.02
messages	

Modbus RS485

Failure mode	Choose from:
	NaN value instead of current value
	■ Last valid value

EtherNet/IP

Device diagnostics	Device condition can be read out in Input Assembly

PROFINET

1	In accordance with "Application Layer protocol for decentral device periphery and
	distributed automation", version 2.3

Local display

Plain text display	With information on cause and remedial measures
Backlight	Red backlighting indicates a device error.



Status signal as per NAMUR recommendation NE 107

Operating tool

- Via digital communication:
 - HART protocol
 - PROFIBUS DP
 - Modbus RS485
 - EtherNet/IP
 - PROFINET
- Via service interface
- Via Web server

Plain text display	With information on cause and remedial measures
--------------------	---

i

Additional information on remote operation $\rightarrow~\equiv~89$

Web browser

Plain text display	With information on cause and remedial measures
--------------------	---

Light emitting diodes (LED)

Status information	Status indicated by various light emitting diodes
	The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred EtherNet/IP network available EtherNet/IP connection established PROFINET network available PROFINET onnection established PROFINET blinking feature

Ex connection data

These values only apply for the following device version:

Order code for "Output", option M "Modbus RS485", for use in intrinsically safe areas

Safety Barrier Promass 100

Safety-related values

Terminal numbers			
Supply voltage		Signal tra	nsmission
2 (L-)	1 (L+)	26 (A) 27 (B)	
U _{nom} = DC 24 V U _{max} = AC 260 V		$U_{nom} = U_{max} = A$	DC 5 V AC 260 V

Intrinsically safe values

Terminal numbers			
Supply voltage Signal transmission		nsmission	
20 (L-) 10 (L+) 62 (A)		72 (B)	
	$\begin{array}{c} U_o = 16.24 \ V \\ I_o = 623 \ mA \\ P_o = 2.45 \ W \\ With \ IIC \ ^{1)} : L_o = 92.8 \ \mu H, \ C_o = 0.433 \ \mu F, \ L_o/R_o = 14.6 \ \mu H/\Omega \\ With \ IIB \ ^{1)} : L_o = 372 \ \mu H, \ C_o = 2.57 \ \mu F, \ L_o/R_o = 58.3 \ \mu H/\Omega \end{array}$		
For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device			

1) The gas group depends on the sensor and nominal diameter.

12

Transmitter

Intrinsically safe values

Order code for	Terminal numbers			
"Approval"	Supply voltage		Signal transmission	
	20 (L-)	10 (L+)	62 (A)	72 (B)
 Option BM: ATEX II2G + IECEx Z1 Ex ia, II2D Ex tb Option BO: ATEX II1/2G + IECEx Z0/Z1 Ex ia, II2D Option BQ: ATEX II1/2G + IECEx Z0/Z1 Ex ia Option BU: ATEX II2G + IECEx Z1 Ex ia Option C2: CSA C/US IS Cl. I, II, III Div. 1 Option 85: ATEX II2G + IECEx Z1 Ex ia + CSA C/US IS Cl. I, II, III Div. 1 		$I_i = 62$ $P_i = 2$ $L_i =$	6.24 V 23 mA .45 W 0 µH 6 nF	

For an overview and for information on the interdependencies between the gas group - sensor - nominal diameter, see the "Safety Instructions" (XA) document for the measuring device

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The following connections are galvanically isolated from each other:

- Outputs
- Power supply

Protocol-specific data

HART

Manufacturer ID	0x11
Device type ID	0x4A
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	Min. 250 Ω

Dynamic variables	Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables.
	Measured variables for PV (primary dynamic variable) Mass flow Volume flow Corrected volume flow Density Reference density Temperature Measured variables for SV, TV, QV (secondary, tertiary and quaternary dynamic variable) Mass flow Volume flow
	 Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1 Totalizer 2 Totalizer 3
	The range of options increases if the measuring device has one or more application packages.
	Heartbeat Technology Application Package Additional measured variables are available with the Heartbeat Technology application package: Carrier pipe temperature Oscillation amplitude 0
Device variables	Read out the device variables: HART command 9 The device variables are permanently assigned.
	A maximum of 8 device variables can be transmitted: • 0 = mass flow • 1 = volume flow • 2 = corrected volume flow • 3 = density • 4 = reference density • 5 = temperature • 6 = totalizer 1 • 7 = totalizer 2 • 8 = totalizer 3 • 13 = target mass flow • 14 = carrier mass flow • 15 = concentration

PROFIBUS DP

Manufacturer ID	0x11
Ident number	0x1561
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: ■ www.endress.com On the product page for the device: Documents/Software → Device drivers ■ www.profibus.org

Output values	Analog input 1 to 0
Output values (from measuring device to	Analog input 1 to 8 Mass flow
automation system)	Volume flow
automation system,	Corrected volume flow
	Target mass flow
	 Carrier mass flow
	Density
	Reference density
	 Concentration
	■ Temperature
	Carrier pipe temperature
	Electronic temperature
	Oscillation frequency Oscillation annulist declaration and the second
	Oscillation amplitude Frequency fluctuation
	Frequency fluctuationOscillation damping
	Tube damping fluctuation
	Signal asymmetry
	• Exciter current
	Digital input 1 to 2 Partially filled pipe detection
	Low flow cut off
	Totalizer 1 to 3
	Mass flow Volume flow
	Corrected volume flow
	- Corrected volume now
Input values	Analog output 1 to 3 (fixed assignment)
(from automation system to	• Pressure
measuring device)	TemperatureReference density
	Digital output 1 to 3 (fixed assignment)
	Digital output 1: switch positive zero return on/off Digital output 2: parform and point adjustment
	Digital output 2: perform zero point adjustment Digital output 3: gwitch gwitch output on off
	Digital output 3: switch switch output on/off
	Totalizer 1 to 3
	Totalize
	Reset and holdPreset and hold
	Stop
	Operating mode configuration:
	- Net flow total
	- Forward flow total
	- Reverse flow total
Supported functions	Identification & Maintenance
Supported fulletions	Simplest device identification on the part of the control system and
	nameplate
	■ PROFIBUS upload/download
	Reading and writing parameters is up to ten times faster with PROFIBUS
	upload/download
	 Condensed status
	Simplest and self-explanatory diagnostic information by categorizing
	diagnostic messages that occur
Configuration of the device	DIP switches on the I/O electronics module
address	 Via operating tools (e.g. FieldCare)

Modbus RS485

Protocol	Modbus Applications Protocol Specification V1.1
Device type	Slave
Slave address range	1 to 247
Broadcast address range	0

Function codes	 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers
Broadcast messages	Supported by the following function codes: O6: Write single registers 16: Write multiple registers 23: Read/write multiple registers
Supported baud rate	 1200 BAUD 2400 BAUD 4800 BAUD 9600 BAUD 19200 BAUD 38400 BAUD 57600 BAUD 115200 BAUD
Data transfer mode	■ ASCII ■ RTU
Data access	Each device parameter can be accessed via Modbus RS485. For Modbus register information

EtherNet/IP

Protocol	 The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP 	
Communication type	■ 10Base-T ■ 100Base-TX	
Device profile	Generic device (product type: 0x2B)	
Manufacturer ID	0x49E	
Device type ID	0x104A	
Baud rates	Automatic ¹⁰ / ₁₀₀ Mbit with half-duplex and full-duplex detection	
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs	
Supported CIP connections	Max. 3 connections	
Explicit connections	Max. 6 connections	
I/O connections	Max. 6 connections (scanner)	
Configuration options for measuring device	 DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device 	
Configuration of the EtherNet interface	 Speed: 10 MBit, 100 MBit, auto (factory setting) Duplex: half-duplex, full-duplex, auto (factory setting) 	
Configuration of the device address	 DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation) 	
Device Level Ring (DLR)	No	

Fix Input			
RPI	5 ms to 10 s (factory setting: 2	20 ms)	
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0x66	64
	$T \rightarrow O$ configuration:	0x64	44
Exclusive Owner Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0x66	64
	$T \rightarrow O$ configuration:	0x64	44
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x68	398
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x64	44
Input only Multicast		Instance	Size [byte]
	Instance configuration:	0x69	-
	$O \rightarrow T$ configuration:	0xC7	-
	$T \rightarrow O$ configuration:	0x64	44
	Corrected volume flowDensityReference density		
Configurable Input	TemperatureTotalizer 1Totalizer 2Totalizer 3		
Configurable Input	TemperatureTotalizer 1Totalizer 2	20 ms)	
	TemperatureTotalizer 1Totalizer 2Totalizer 3	20 ms) Instance	Size [byte]
RPI	TemperatureTotalizer 1Totalizer 2Totalizer 3	·	Size [byte]
RPI	 Temperature Totalizer 1 Totalizer 2 Totalizer 3 5 ms to 10 s (factory setting: 2	Instance	
RPI	Temperature Totalizer 1 Totalizer 2 Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration:	Instance 0x68	398
RPI	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration:	Instance 0x68 0x66	398 64
RPI Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration:	0x68 0x66 0x65	398 64 88
RPI Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration:	Ox68 Ox66 Ox65 Instance	398 64 88
RPI Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: Instance configuration:	0x68 0x66 0x65 Instance 0x69	398 64 88 Size [byte]
RPI Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: O → T configuration: O → T configuration:	0x68 0x66 0x65 Instance 0x69 0x66	398 64 88 Size [byte] - 64
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: O → T configuration: O → T configuration:	0x68 0x66 0x65 Instance 0x69 0x66 0x65	398 64 88 Size [byte] - 64 88
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: O → T configuration: T → O configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance	398 64 88 Size [byte] - 64 88 Size [byte]
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: O → T configuration: T → O configuration: Instance configuration: T → O configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance 0x68	398 64 88 Size [byte] - 64 88 Size [byte] 398
RPI Exclusive Owner Multicast Exclusive Owner Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration:	Instance 0x68 0x66 0x65 Instance 0x69 0x66 0x65 Instance 0x68 0xC7	398 64 88 Size [byte] - 64 88 Size [byte] 398 -
RPI Exclusive Owner Multicast Exclusive Owner Multicast Input only Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88
RPI Exclusive Owner Multicast Exclusive Owner Multicast Input only Multicast	■ Temperature ■ Totalizer 1 ■ Totalizer 2 ■ Totalizer 3 5 ms to 10 s (factory setting: 2 Instance configuration: O → T configuration: T → O configuration: O → T configuration: T → O configuration: T → O configuration: T → O configuration: T → O configuration: O → T configuration: T → O configuration:	Instance	398 64 88 Size [byte] - 64 88 Size [byte] 398 - 88

Configurable Input Assembly	 Current device diagnostics Mass flow Volume flow
	 Corrected volume flow
	DensityReference density
	TemperatureTotalizer 1
	■ Totalizer 1 ■ Totalizer 2
	• Totalizer 3
	The range of options increases if the measuring device has one or more application packages.
Fix Output	
Output Assembly	• Activation of reset totalizers 1-3
	Activation of pressure compensationActivation of reference density compensation
	 Activation of reference density compensation
	Reset totalizers 1-3
	External pressure valuePressure unit
	External reference density
	 Reference density unit
	External temperature
	Temperature unit
Configuration	
Configuration Assembly	Only the most common configurations are listed below.
	Software write protection
	Mass flow unitMass unit
	Volume flow unit
	 Volume unit
	Corrected volume flow unit
	Corrected volume unitDensity unit
	Reference density unit
	Temperature unit
	Pressure unit
	LengthTotalizer 1-3:
	- Assignment
	- Unit
	- Measuring mode
	Failsafe mode■ Alarm delay
	- Alami delay

PROFINET

Protocol	"Application layer protocol for decentral device periphery and distributed automation", version 2.3
Conformity class	В
Communication type	100 MBit/s
Device profile	Application interface identifier 0xF600 Generic device
Manufacturer ID	0x11
Device type ID	0x844A
Device description files (GSD, DTM)	Information and files under: ■ www.endress.com On the product page for the device: Documents/Software → Device drivers ■ www.profibus.org
Baud rates	Automatic 100 Mbit/s with full-duplex detection

Cycle times	From 8 ms
Polarity	Auto-polarity for automatic correction of crossed TxD and RxD pairs
Supported connections	 1 x AR (Application Relation) 1 x Input CR (Communication Relation) 1 x Output CR (Communication Relation) 1 x Alarm CR (Communication Relation)
Configuration options for measuring device	 DIP switches on the electronics module, for device name assignment (last part) Manufacturer-specific software (FieldCare, DeviceCare) Web browser Device master file (GSD), can be read out via the integrated Web server of the measuring device
Configuration of the device name	 DIP switches on the electronics module, for device name assignment (last part) DCP protocol
Output values (from measuring device to automation system)	Analog Input module (slot 1 to 14) Mass flow Volume flow Corrected volume flow Carrier mass flow Density Reference density Concentration Temperature Carrier pipe temperature Electronic temperature Oscillation frequency Oscillation amplitude Frequency fluctuation Oscillation damping Tube damping fluctuation Signal asymmetry Exciter current
	Discrete Input module (slot 1 to 14) Empty pipe detection Low flow cut off Diagnostics Input module (slot 1 to 14) Last diagnostics Current diagnosis
	Totalizer 1 to 3 (slot 15 to 17) Mass flow Volume flow Corrected volume flow
	Heartbeat Verification module (fixed assignment) Verification status (slot 23) The range of options increases if the measuring device has one or more application packages.

Input values (from automation system to measuring device)	Analog Output module (fixed assignment) External pressure (slot 18) External temperature (slot 19) External reference density (slot 20) Discrete Output module (fixed assignment) Activate/deactivate positive zero return (slot 21) Perform zero point adjustment (slot 22)
	Totalizer 1 to 3 (slot 15 to 17) Totalize Reset and hold Preset and hold Stop Operating mode configuration: Net flow total Forward flow total Reverse flow total
	Heartbeat Verification module (fixed assignment) Start verification (slot 23) The range of options increases if the measuring device has one or more application packages.
Supported functions	 Identification & Maintenance Simple device identification via: Control system Nameplate Measured value status The process variables are communicated with a measured value status Blinking feature via the onsite display for simple device identification and assignment

Administration of software options

Input/output value	Process variable	Category	Slot
Output value	Mass flow	Process variable	114
	Volume flow		
	Corrected volume flow		
	Density		
	Reference density		
	Temperature		
	Electronic temperature		
	Oscillation frequency		
	Frequency fluctuation		
	Oscillation damping		
	Oscillation frequency		
	Signal asymmetry		
	Exciter current		
	Empty pipe detection		
	Low flow cut off		
	Current device diagnostics		
	Previous device diagnostics		
Output value	Target mass flow	Concentration 1)	114
	Carrier mass flow		
	Concentration		
Output value	Carrier pipe temperature	Heartbeat ²⁾	114

20

Input/output value	Process variable	Category	Slot
	Oscillation damping 1		
	Oscillation frequency 1		
	Oscillation amplitude 0		
	Oscillation amplitude 1		
	Frequency fluctuation 1		
	Tube damping fluctuation 1		
	Exciter current 1		
Input value	External density	Process monitoring	18
	External temperature		19
	External reference density		20
	Flow override		21
	Zero point adjustment		22
	Verification status	Heartbeat Verification 2)	23

- Only available with the "Concentration" application package. Only available with the "Heartbeat" application package. 1) 2)

Startup configuration

Startup configuration (NSU)

If startup configuration is enabled, the configuration of the most important device parameters is taken from the automation system and used.


The following configuration is taken from the automation system:

- Management
 - Software revision
 - Write protection
- System units
 - Mass flow
 - Mass
 - Volume flow
 - Volume
 - Corrected volume flow
 - Corrected volume
 - Density
 - Reference density
 - Temperature
 - Pressure
- Concentration application package
 - Coefficients A0 to A4
 - Coefficients B1 to B3
- Sensor adjustment
- Process param.
 - Damping (flow, density, temperature)
 - Flow override
- Low flow cut off
 - Assign process variable
 - Switch-on/switch-off point
 - Pressure shock suppression
- Empty pipe detection
 - Assign process variable
 - Limit values
 - Response time
 - Max. damping
- Corrected volume flow calculation
 - External reference density
 - Fixed reference density
 - Reference temperature
 - Linear expansion coefficient
 - Square expansion coefficient
- Measuring mode
 - Medium
 - Gas type
 - Reference sound velocity
- Temperature coefficient sound velocity
- External compensation
 - Pressure compensation
 - Pressure value
- External pressure
- Diagnostic settings
- Diagnostic behavior for diverse diagnostic information

Power supply

Terminal assignment

Overview: housing version and connection versions



A001677

- A Housing version: compact, aluminum coated
- B Housing version: compact, hygienic, stainless
- C Housing version: ultra-compact, hygienic, stainless
- 1 Connection version: 4-20 mA HART, pulse/frequency/switch output
- 1.1 Signal transmission: pulse/frequency/switch output
- 1.2 Signal transmission: 4-20 mA HART
- 1.3 Supply voltage
- 2 Connection version: Modbus RS485
- 2.1 Signal transmission
- 2.2 Supply voltage
- 3 Connection versions: EtherNet/IP and PROFINET
- 3.1 Signal transmission
- 3.2 Supply voltage
- 4 Connection version: PROFIBUS DP
- 4.1 Signal transmission
- 4.2 Supply voltage

Transmitter

Connection version 4-20 mA HART with pulse/frequency/switch output


Order code for "Output", option ${\bf B}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection methods available		Describle entions for order sode
"Housing"	Outputs	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½"
Options A, B	Device plugs → 🖺 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option **B**: compact, hygienic, stainless
- Option **C** ultra-compact, hygienic, stainless



A001688

- 2 Terminal assignment 4-20 mA HART with pulse/frequency/switch output
- 1 Power supply: DC 24 V
- 2 Output 1: 4-20 mA HART (active)
- 3 Output 2: pulse/frequency/switch output (passive)

	Terminal number					
Order code for "Output"	Power	supply	Outp	out 1	Outp	out 2
	2 (L-)	1 (L+)	27 (-)	26 (+)	25 (-)	24 (+)
Option B	DC 24 V		4-20 mA HART (active)		Pulse/frequency/switch output (passive)	

Order code for "Output":

Option **B**: 4-20 mA HART with pulse/frequency/switch output

PROFIBUS DP connection version

For use in the non-hazardous area and Zone 2/Div. 2.


Order code for "Output", option ${\bf L}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Possible options for order code
"Housing"	Output	Power supply	"Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½"
Options A, B	Device plugs → 🖺 30	Terminals	■ Option L: plug M12x1 + thread NPT ½" ■ Option N: plug M12x1 + coupling M20 ■ Option P: plug M12x1 + thread G ½" ■ Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1

Order code for "Housing":

- $\, \bullet \,$ Option A: compact, coated aluminum
- Option B: compact, hygienic, stainless
 Option C ultra-compact, hygienic, stainless



- PROFIBUS DP terminal assignment
- Power supply: DC 24 V
- PROFIBUS DP

	Terminal number			
Order code for	Power supply		Output	
"Output"	2 (L-)	1 (L+)	26 (RxD/TxD-P)	27 (RxD/TxD- N)
Option L	DC 24 V		В	A

Order code for "Output":

Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/div. 2

Modbus RS485 connection version

For use in the non-hazardous area and Zone 2/Div. 2.


Order code for "Output", option \boldsymbol{M}

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection methods available		Describle entions for order sode
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½"
Options A, B	Device plugs → 🖺 30	Terminals	■ Option L: plug M12x1 + thread NPT ½" ■ Option N: plug M12x1 + coupling M20 ■ Option P: plug M12x1 + thread G ½" ■ Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1

Order code for "Housing":

- $\, \bullet \,$ Option A: compact, coated aluminum
- Option B: compact, hygienic, stainless
 Option C ultra-compact, hygienic, stainless



- € 4 Modbus RS485 terminal assignment, connection version for use in non-hazardous areas and Zone 2/Div.
- Power supply: DC 24 V
- Modbus RS485

	Terminal number			
Order code for "Output"	Power supply		Output	
Output	2 (L-)	1 (L+)	27 (B)	26 (A)
Option M	DC 24 V		Modbus	s RS485

Order code for "Output":

Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2

26

Modbus RS485 connection version

For use in the intrinsically safe area. Connection via Safety Barrier Promass 100.


Order code for "Output", option ${\bf M}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Descible entions for order sode
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Terminals	Terminals	 Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½"
A, B, C	Device plugs → 30		Option I: plug M12x1

Order code for "Housing":

- Option A: compact, coated aluminum
- lacktriangledown Option **B**: compact, hygienic, stainless
- Option C ultra-compact, hygienic, stainless



A0017053

- Modbus RS485 terminal assignment, connection version for use in intrinsically safe areas (connection via Safety Barrier Promass 100)
- 1 Intrinsically safe power supply
- 2 Modbus RS485

Order code for "Output"	20 (L-)	10 (L+)	72 (B)	62 (A)
Option M	Intrinsically safe supply voltage		Modbus RS485	intrinsically safe

Order code for "Output":

Option \mathbf{M} : Modbus RS485, for use in intrinsically safe areas (connection via Safety Barrier Promass 100)

EtherNet/IP connection version


Order code for "Output", option ${\bf N}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Possible options for order code	
"Housing"	Output	Power supply	"Electrical connection"	
Options A, B	Device plugs → 🖺 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20 	
Options A, B, C	Device plugs → 🖺 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1	

Order code for "Housing":

- Option **A**: compact, coated aluminum
- Option B: compact, hygienic, stainless
 Option C ultra-compact, hygienic, stainless



№ 6 EtherNet/IP terminal assignment

- Power supply: DC 24 V
- EtherNet/IP

	Terminal number			
Order code for "Output"	Power supply 2 (L-) 1 (L+)		Output	
2			Device plug M12x1	
Option N	DC 24 V		EtherNet/IP	
Order code for "Output": Option N : EtherNet/IP				

PROFINET connection version


Order code for "Output", option ${\bf R}$

Depending on the housing version, the transmitters can be ordered with terminals or device plugs.

Order code for	Connection me	thods available	Descible entions for order sode
"Housing"	Output	Power supply	Possible options for order code "Electrical connection"
Options A, B	Device plugs → 🖺 30	Terminals	 Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20
Options A, B, C	Device plugs → 🖺 30	Device plugs → 🖺 30	Option Q : 2 x plug M12x1

Order code for "Housing":


- Option **A**: compact, coated aluminum
- Option B: compact, hygienic, stainless
 Option C ultra-compact, hygienic, stainless



- **₽** 7 PROFINET terminal assignment
- Power supply: DC 24 V
- PROFINET

	Terminal number			
Order code for "Output"	Power supply		Output	
	2 (L-)	1 (L+)	Device plug M12x1	
Option R	DC 24 V		PROFINET	
Order code for "Output": Option R : PROFINET				

Safety Barrier Promass 100



- 8 Safety Barrier Promass 100 with terminals
- 1 Non-hazardous area and Zone 2/Div. 2
- 2 Intrinsically safe area

Pin assignment, device plug


Order codes for the M12x1 connectors, see the "Order code for **electrical connection**" column:

- PROFIBUS DP→ 🖺 25
- Modbus RS485 → 🖺 26
- EtherNet/IP → 🗎 28
- PROFINET → 🗎 29

Supply voltage

For all connection versions except MODBUS RS485 intrinsically safe (device side)

P Device plug MODBUS RS485 intrinsically safe with supply voltage → 🖺 31




- The following is recommended as a socket:
 - Binder, series 763, part no. 79 3440 35 05
 - Alternatively: Phoenix part no. 1669767 SAC-5P-M12MS
 - With the order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
 - With the order code for "Output", option ${\bf N}$: EtherNet/IP
 - When using the device in a hazardous location: Use a suitably certified socket.

30

4-20 mA HART with pulse/frequency/switch output

Device plug for signal transmission (device side)




- Recommended plug: Binder, series 763, part no. 79 3439 12 05
- When using the device in a hazardous location, use a suitably certified plug.

PROFIBUS DP



For use in the non-hazardous area and Zone $2/\text{Div.}\ 2$.

Device plug for signal transmission (device side)






- Recommended plug: Binder, series 763, part no. 79 4449 20 05
 When using the device in a hazardous location, use a suitably certified plug.

MODBUS RS485

Device plug for signal transmission with supply voltage (device side), MODBUS RS485 (intrinsically safe)



- Recommended socket: Binder, series 763, part no. 79 3439 12 05
 When using the device in a hazardous location: Use a suitably certified socket.

Device plug for signal transmission (device side), MODBUS RS485 (not intrinsically safe)

For use in the non-hazardous area and Zone 2/Div. 2.

2	Pin		Assignment
	1		Not assigned
$1 \longrightarrow 0 \longrightarrow 3$	2	А	Modbus RS485
	3		Not assigned
5	4	В	Modbus RS485
4 A0016811	5		Grounding/shielding
	Cod	ling	Plug/socket
	Ι	3	Socket

Recommended plug: Binder, series 763, part no. 79 4449 20 05

• When using the device in a hazardous location, use a suitably certified plug.

EtherNet/IP

Device plug for signal transmission (device side)

2	Pin		Assignment
	1	+	Tx
1 3	2	+	Rx
	3	-	Tx
	4	-	Rx
4 A0016812	Cod	ling	Plug/socket
	I)	Socket

Recommended plug:

Binder, series 763, part no. 99 3729 810 04

• Phoenix, part no. 1543223 SACC-M12MSD-4Q

 $\, \bullet \,$ When using the device in a hazardous location, use a suitably certified plug.

PROFINET

Device plug for signal transmission (device side)

2	Pin		Assignment
	1	+	TD +
$1 \longrightarrow 3$	2	+	RD +
	3	-	TD -
	4	-	RD -
4 A0016812	Cod	ing	Plug/socket
	I)	Socket

Recommended plug:

Binder, series 763, part no. 99 3729 810 04

■ Phoenix, part no. 1543223 SACC-M12MSD-4Q

• When using the device in a hazardous location, use a suitably certified plug.

Supply voltage

The power unit must be tested to ensure it meets safety requirements (e.g. PELV, SELV).

Transmitter

For device version with communication type:

- HART, PROFIBUS DP, EtherNet/IP: DC 20 to 30 V
- Modbus RS485, device version:
 - For use in the non-hazardous area and Zone 2/Div. 2: DC 20 to 30 V
 - For use in the intrinsically safe area: power supply via Safety Barrier Promass 100

Safety Barrier Promass 100

DC 20 to 30 V

Power consumption

Transmitter

Order code for "Output"	Maximum Power consumption
Option B : 4-20 mA HART with pulse/frequency/switch output	3.5 W
Option L: PROFIBUS DP	3.5 W
Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2	3.5 W
Option M : Modbus RS485, for use in intrinsically safe areas	2.45 W
Option N: EtherNet/IP	3.5 W
Option R: PROFINET	3.5 W

Safety Barrier Promass 100

Order code for "Output"	Maximum Power consumption
Option M : Modbus RS485, for use in intrinsically safe areas	4.8 W

Current consumption

Transmitter

Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option B : 4-20mA HART, pul./freq./switch output	145 mA	18 A (< 0.125 ms)
Option L : PROFIBUS DP	145 mA	18 A (< 0.125 ms)
Option M Modbus RS485, for use in non-hazardous areas and Zone 2/Div. 2	90 mA	10 A (< 0.8 ms)
Option ${\bf M}$: Modbus RS485, for use in intrinsically safe areas	145 mA	16 A (< 0.4 ms)
Option N : EtherNet/IP	145 mA	18 A (< 0.125 ms)
Option R: PROFINET	145 mA	18 A (< 0.125 ms)

Safety Barrier Promass 100


Order code for "Output"	Maximum Current consumption	Maximum switch-on current
Option M : Modbus RS485, for use in intrinsically safe areas	230 mA	10 A (< 0.8 ms)

Power supply failure

- Totalizers stop at the last value measured.
- Depending on the device version, the configuration is retained in the device memory or in the plug-in memory (HistoROM DAT).
- Configuration is retained in the plug-in memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Electrical connection

Connecting the transmitter




A001692

- A Housing version: compact, aluminum coated
- *B* Housing version: compact hygienic, stainless
- 1 Cable entry or device plug for signal transmission
- 2 Cable entry or device plug for supply voltage
- C Housing version: ultra-compact, hygienic, stainless, M12 device plug
- 3 Device plug for signal transmission
- 4 Device plug for supply voltage
- i
 - Terminal assignment → 🗎 23
- In the case of device versions with a connector, the transmitter housing does not need to be opened to connect the signal cable or power supply cable.

Connection examples


Current output 4-20 mA HART



A001680


- 9 Connection example for 4-20 mA HART current output (active)
- 1 Automation system with current input (e.g. PLC)
- 2 Cable shield, observe cable specifications
- 3 Connection for HART operating devices
- 4 Resistor for HART communication ($\geq 250~\Omega$): observe maximum load
- 5 Analog display unit: observe maximum load
- 6 Transmitter

Pulse/frequency output



- 10 Connection example for pulse/frequency output (passive)
- Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply3 Transmitter: c


Switch output



A00168

- 11 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply3 Transmitter: c
- 3 Transmitter: observe input values


PROFIBUS DP



- 12 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2
- Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- Transmitter 3
- If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.


Modbus RS485

Modbus RS485, non-hazardous area and Zone 2/Div. 2



- **■** 13 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2
- Control system (e.g. PLC)
- Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 3 Distribution box
- Transmitter


Modbus RS485 intrinsically safe



 ${\it Connection\ example\ for\ Modbus\ RS485\ intrinsically\ safe}$

- 1
- Control system (e.g. PLC) Cable shield, observe cable specifications
- 3 Safety Barrier Promass 100
- 4 5 Observe cable specifications
- Non-hazardous area
- 6 Non-hazardous area and Zone 2/Div. 2
- Intrinsically safe area
- 8 Transmitter


EtherNet/IP



■ 15 Connection example for EtherNet/IP

- Control system (e.g. PLC)
- Ethernet switch 2
- 3 Observe cable specifications
- 4 Device plug
- Transmitter


PROFINET



■ 16 Connecting cable for PROFINET

- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications
- 4 Connector
- Transmitter

HART input




A0019828

■ 17 Connection example for HART input (burst mode) via current output (active)

- Cable shield, observe cable specifications
- Resistor for HART communication ($\geq 250 \Omega$): observe maximum load 2
- 3 Connection for HART operating devices Analog display unit
- 4
- 5 Transmitter
- $Sensor\ for\ external\ measured\ variable$

38



■ 18 Connection example for HART input (master mode) via current output (active)

- 1 Automation system with current input (e.g. PLC).Prerequisite: automation system with HART version 6, HART commands 113 and 114 can be processed.
- 2 Cable shield, observe cable specifications
- Resistor for HART communication ($\geq 250 \Omega$): observe maximum load
- 4 Connection for HART operating devices
- 5 Analog display unit
- 6 Transmitter
- 7 Sensor for external measured variable


Potential equalization

Requirements

No special measures for potential equalization are required.

Please consider the following to ensure correct measurement:

- Same electrical potential for the fluid and sensor
- Company-internal grounding concepts



Terminals

Transmitter

Spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)

Safety Barrier Promass 100

Plug-in screw terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)

Cable entries

- Cable gland: M20 \times 1.5 with cable ϕ 6 to 12 mm (0.24 to 0.47 in)
- Thread for cable entry:
 - NPT ½"
 - G ½"
 - M20

Cable specification

Permitted temperature range

- -40 °C (-40 °F) to +80 °C (+176 °F)
- Minimum requirement: cable temperature range ≥ ambient temperature +20 K

Power supply cable

Standard installation cable is sufficient.

Signal cable

Current output

For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant.

Pulse/frequency/switch output

Standard installation cable is sufficient.

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	<30 pF/m
Wire cross-section	>0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.


Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

Cable type	A
Characteristic impedance	135 to 165 Ω at a measuring frequency of 3 to 20 MHz
Cable capacitance	<30 pF/m
Wire cross-section	>0.34 mm ² (22 AWG)
Cable type	Twisted pairs
Loop resistance	≤110 Ω/km
Signal damping	Max. 9 dB over the entire length of the cable cross-section
Shield	Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant.


EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.



PROFINET

Standard IEC 61156-6 specifies CAT 5 as the minimum category for a cable used for PROFINET. CAT 5e and CAT 6 are recommended.



Connecting cable between Safety Barrier Promass 100 and measuring device

Cable type	Shielded twisted-pair cable with 2x2 wires. When grounding the cable shield, observe the grounding concept of the plant.
Maximum cable resistance	2.5Ω , one side

Comply with the maximum cable resistance specifications to ensure the operational reliability of the measuring device.

The maximum cable length for individual wire cross-sections is specified in the table below. Observe the maximum capacitance and inductance per unit length of the cable and connection values for hazardous areas .

Wire cross-section		Maximum cable length	
[mm ²]	[AWG]	[m]	[ft]
0.5	20	70	230
0.75	18	100	328
1.0	17	100	328
1.5	16	200	656
2.5	14	300	984

Performance characteristics


Reference operating conditions

- Error limits based on ISO 11631
- Water with +15 to +45 °C (+59 to +113 °F) at 2 to 6 bar (29 to 87 psi)
- Specifications as per calibration protocol
- Accuracy based on accredited calibration rigs that are traced to ISO 17025.

Maximum measured error

o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature

Base accuracy



Mass flow and volume flow (liquids)

±0.10 % o.r.

Density (liquids)

Under reference operating conditions		Standard density calibration ¹⁾		Wide-range density specification ^{2) 3)}	
[g/cm³]	[lbs/in³]	[g/cm³]	[lbs/in³]	[g/cm³]	[lbs/in³]
±0.0005	±0.00097	±0.01	±0.019	±0.002	±0.0039

- 1) Valid over the entire temperature and density range
- Valid range for special density calibration: 0 to 2 g/cm³, +5 to +80 $^{\circ}$ C (+41 to +176 $^{\circ}$ F)
- 3) Order code for "Application package", option EF "Special density and concentration"

Temperature

 $\pm 0.5 \,^{\circ}\text{C} \pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.9 \,^{\circ}\text{F} \pm 0.003 \cdot (\text{T} - 32) \,^{\circ}\text{F})$

Zero point stability

DN		Zero poin	t stability
[mm]	[in]	[kg/h]	[lb/min]
8	³ / ₈	0.20	0.007
15	1/2	0.65	0.024
25	1	1.80	0.066

DN		Zero poin	t stability
[mm]	[in]	[kg/h]	[lb/min]
40	1½	4.50	0.165
50	2	7.0	0.257

Flow values

Flow values as turndown parameter depending on nominal diameter.

SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
8	2 000	200	100	40	20	4
15	6500	650	325	130	65	13
25	18000	1800	900	360	180	36
40	45 000	4500	2 250	900	450	90
50	70 000	7 000	3 500	1400	700	140

US units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
3/8	73.50	7.350	3.675	1.470	0.735	0.147
1/2	238.9	23.89	11.95	4.778	2.389	0.478
1	661.5	66.15	33.08	13.23	6.615	1.323
1½	1654	165.4	82.70	33.08	16.54	3.308
2	2 5 7 3	257.3	128.7	51.46	25.73	5.146

Accuracy of outputs



In the case of analog outputs, the output accuracy must also be considered for the measured error; in contrast, this need not be considered in the case of fieldbus outputs (e.g. Modbus RS485, EtherNet/IP).

The outputs have the following base accuracy specifications.

Current output

Accuracy	Max. ±5 μA

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ±50 ppm o.r. (across the entire ambient temperature range)
----------	---

Repeatability

o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature

Base repeatability

Mass flow and volume flow (liquids)

±0.05 % o.r.



Design fundamentals → 🖺 44

Density (liquids)

 $\pm 0.00025 \text{ g/cm}^3$

Temperature

 $\pm 0.2\bar{5}$ °C $\pm 0.0025 \cdot$ T °C (± 0.45 °F $\pm 0.0015 \cdot$ (T-32) °F)

Response time

The response time depends on the configuration (damping).

Influence of ambient temperature

Current output

o.r. = of reading

Temperature coefficient	Max. ±0.005% o.r./°C
-------------------------	----------------------

Pulse/frequency output

Temperature coefficient	No additional effect. Included in accuracy.
-------------------------	---

Influence of medium temperature

Mass flow and volume flow


When there is a difference between the temperature for zero point adjustment and the process temperature, the typical measured error of the sensor is ± 0.0002 % of the full scale value/°C (± 0.0001 % of the full scale value/°F).

Density

When there is a difference between the density calibration temperature and the process temperature, the typical measured error of the sensor is ± 0.0001 g/cm³/°C (± 0.00005 g/cm³/°F). Field density calibration is possible.

Wide-range density specification (special density calibration)

If the process temperature is outside the valid range (\Rightarrow \cong 41) the measured error is ± 0.0001 g/cm³ /°C (± 0.00005 g/cm³ /°F)



- 1 Field density calibration, for example at +20 $^{\circ}$ C (+68 $^{\circ}$ F)
- 2 Special density calibration

Temperature

 $\pm 0.005 \cdot \text{T} \,^{\circ}\text{C} \, (\pm 0.005 \cdot (\text{T} - 32) \,^{\circ}\text{F})$

Influence of medium pressure

The table below shows the effect on accuracy of mass flow due to a difference between calibration pressure and process pressure.

o.r. = of reading

DN		[% o.r./bar]	[% o.r./psi]		
[mm]	[in]				
8	3/8	-0.002	-0.0001		
15	1/2	-0.006	-0.0004		
25	1	-0.005	-0.0003		
40	1½	-0.007	-0.0005		
50	2	-0.006	-0.0004		

Design fundamentals

o.r. = of reading, o.f.s. = of full scale value

 $\label{eq:baseAccu} \textit{BaseAccu} = \textit{base accuracy in \% o.r.}, \textit{BaseRepeat} = \textit{base repeatability in \% o.r.}.$

MeasValue = measured value; ZeroPoint = zero point stability


Calculation of the maximum measured error as a function of the flow rate

Flow rate	Maximum measured error in % o.r.
$\geq \frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	± BaseAccu
$<\frac{\text{ZeroPoint}}{\text{BaseAccu}} \cdot 100$	$\pm \frac{\text{ZeroPoint}}{\text{MeasValue}} \cdot 100$

Calculation of the maximum repeatability as a function of the flow rate

Flow rate	Maximum repeatability in % o.r.
$\geq \frac{\frac{1}{2} \cdot ZeroPoint}{BaseRepeat} \cdot 100$	± BaseRepeat
A0021335	N0021.740
$<\frac{\frac{1}{2} \cdot ZeroPoint}{BaseRepeat} \cdot 100$	± ½ · ZeroPoint MeasValue · 100
A0021336	A0021337

Example for max. measured error




E Error: Maximum measured error as % o.r. (example)

Q Flow rate as %

Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.

Mounting location




A0023344

To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



A001559

■ 19 Installation in a down pipe (e.g. for batching applications)

- 1 Supply tank
- 2 Sensor
- 3 Orifice plate, pipe restriction
- 4 Valve
- 5 Batching tank

D	N	Ø orifice plate, pipe restriction		
[mm]	[in]	[mm]	[in]	
8	3/8	6	0.24	
15	1/2	10	0.40	
25	1	14	0.55	
40	11/2	22	0.87	
50	2	28	1.10	


Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

	Orientatio	n	Recommendation
A	Vertical orientation	A0015591	₩ ₩
В	Horizontal orientation, transmitter head up	A0015589	Exceptions: $\rightarrow \square 20, \square 46$
С	Horizontal orientation, transmitter head down	A0015590	Exceptions: $\rightarrow \square 20, \square 46$
D	Horizontal orientation, transmitter head at side	A0015592	V

- Applications with low process temperatures may decrease the ambient temperature. To maintain the minimum ambient temperature for the transmitter, this orientation is recommended.
- 2) Applications with high process temperatures may increase the ambient temperature. To maintain the maximum ambient temperature for the transmitter, this orientation is recommended.

If a sensor is installed horizontally with a curved measuring tube, match the position of the sensor to the fluid properties.



■ 20 Orientation of sensor with curved measuring tube

- 1 Avoid this orientation for fluids with entrained solids: Risk of solids accumulating.
- 2 Avoid this orientation for outgassing fluids: Risk of gas accumulating.

Inlet and outlet runs


No special precautions need to be taken for fittings which create turbulence, such as valves, elbows or T-pieces, as long as no cavitation occurs $\rightarrow \triangleq 55$.

Special mounting instructions

$Complete\ drainability\ guaranteed$

When the sensor is installed in a horizontal line, eccentric clamps can be used to ensure complete drainability. When the system is pitched in a specific direction and at a specific slope, gravity can be used to achieve complete drainability. The sensor must be mounted in the correct position to ensure full drainability in the horizontal position. Markings on the sensor show the correct mounting position to optimize drainability.

46




A0016583

- 1 Eccentric clamp connection
- 2 "This side up" label indicates which side is up
- 3 Slope the device in accordance with the hygiene guidelines. Slope: approx. 2 ° or 35 mm/m (0.42 in/feet)
- 4 Line on the underside indicates the lowest point of the eccentric process connection.
- 5 Transmitter

Securing with mounting clamp in the case of hygiene connections

It is not necessary to provide additional support for the sensor for operational performance purposes. If, however, additional support is required for installation purposes, the following dimensions must be observed.

Use mounting clamp with lining between clamp and measuring instrument.



A0016588


DN		A		В		С	
[mm]	[in]	[mm]	[in]	[mm]	[in]	[mm]	[in]
8	3/8	298	11.73	33	1.3	28	1.1
15	1/2	402	15.83	33	1.3	28	1.1
25	1	542	21.34	33	1.3	38	1.5
40	1 1/2	658	25.91	36.5	1.44	56	2.2
50	2	772	30.39	44.1	1.74	75	2.95

Zero point adjustment

Experience shows that zero point adjustment is advisable only in special cases:

- To achieve maximum measuring accuracy even with low flow rates
- Under extreme process or operating conditions (e.g. very high process temperatures or very high-viscosity fluids).

Mounting Safety Barrier Promass 100



21 Minimum distance between additional Safety Barrier Promass 100 or other modules. Engineering unit mm (in)

Environment

Ambient temperature range

Measuring device	Non-Ex	-40 to +60 °C (-40 to +140 °F)
	Ex na, NI version	-40 to +60 °C (-40 to +140 °F)
	Ex ia, IS version	■ -40 to +60 °C (-40 to +140 °F) ■ -50 to +60 °C (-58 to +140 °F) (order code for "Test, certificate", option JM))
Readability of the local display		-20 to $+60$ °C (-4 to $+140$ °F) The readability of the display may be impaired at temperatures outside the temperature range.
Safety Barrier Pro	nass 100	-40 to +60 °C (-40 to +140 °F)

If operating outdoors:Avoid direct sunlight, particularly in warm climatic regions.

Weather protection covers can be ordered from Endress+Hauser: see "Accessories" section

Temperature tables

In the following tables, the following interdependencies between the maximum medium temperature $T_{\rm m}$ for T6 to T1 and the maximum ambient temperature $T_{\rm a}$ apply when operating the device in hazardous areas.

Ex ia, cCSA_{US} IS

SI units

Order code for "Housing"	T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300 °C]	T1 [450 ℃]
Option A "Compact coated alu"	35	50	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
Option B "Compact hygienic, stainless"	50	-	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
	60	-	-	120	150 ¹⁾	150 ²⁾	150 ²⁾
Option C "Ultra-compact, hygienic, stainless"	35	50	85	120	150 ¹⁾	150 ²⁾	150 ²⁾

Order code for "Housing"	T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 ℃]	T2 [300 °C]	T1 [450 ℃]
	45	-	85	120	150 ¹⁾	150 ²⁾	150 ²⁾
	50	-	-	120	150 ¹⁾	150 ²⁾	150 ²⁾

- The following applies for specified sensors with a maximum medium temperature $T_{\rm m}$ = 205 °C: $T_{\rm m}$ = 170 °C 1)
- 2) The following applies for specified sensors with a maximum medium temperature T_m = 205 °C: T_m

US units

Order code for "Housing"	T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu"	95	122	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
Option B "Compact hygienic, stainless"	122	-	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
	140	-	-	248	302 ¹⁾	302 ²⁾	302 ²⁾
Option C "Ultra-compact, hygienic, stainless"	95	122	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
	113	-	185	248	302 ¹⁾	302 ²⁾	302 ²⁾
	122	-	-	248	302 ¹⁾	302 ²⁾	302 ²⁾

- The following applies for specified sensors with a maximum medium temperature T_m = 401 °F: T_m = 338 °F 1)
- The following applies for specified sensors with a maximum medium temperature T_m = 401 °F: T_m = 401 °F

Ex nA, $_{\text{C}}\text{CSA}_{\text{US}}$ NI

SI units

Order code for "Housing"	T _a [°C]	T6 [85 ℃]	T5 [100 ℃]	T4 [135 ℃]	T3 [200 °C]	T2 [300°C]	T1 [450°C]
Option A "Compact coated alu"	35	50	85	120	150 ¹⁾	150 ²⁾	150
Option B "Compact hygienic, stainless"	50	-	85	120	150	150	150
	60	-	-	120	150	150	150
Option C "Ultra-compact, hygienic, stainless"	50	-	85	120	150	150	150
	60	-	-	120	150	150	150

- The following applies for specified sensors with a maximum medium temperature T_m = 205 °C: T_m = 170 °C The following applies for specified sensors with a maximum medium temperature T_m = 205 °C: T_m = 205 °C 2)

US units

Order code for "Housing"	T _a [°F]	T6 [185 °F]	T5 [212 °F]	T4 [275 °F]	T3 [392 °F]	T2 [572 °F]	T1 [842 °F]
Option A "Compact coated alu"	95	122	185	248	302 ¹⁾	302 ²⁾	302
Option B "Compact hygienic,	122	_	185	248	302	302	302
stainless"	140	-	-	248	302	302	302
Option C "Ultra-compact, hygienic,	122	-	185	248	302	302	302
stainless"	140	-	-	248	302	302	302

- The following applies for specified sensors with a maximum medium temperature T_m = 401 °F: T_m = 338 °F
- 2) The following applies for specified sensors with a maximum medium temperature T_m = 401 $^{\circ}F$: T_m = 401 $^{\circ}F$


Explosion hazards arising from gas and dust

Determining the temperature class and surface temperature with the temperature table

- In the case of gas: Determine the temperature class as a function of the ambient temperature T_a and the medium temperature T_m .
- In the case of dust: Determine the maximum surface temperature as a function of the maximum ambient temperature T_a and the maximum medium temperature T_m .

Example

- Measured maximum ambient temperature: T_{ma} = 47 °C
- Measured maximum medium temperature: $T_{mm} = 108 \, ^{\circ}\text{C}$



A00197

- 22 Procedure for determining the maximum surface temperature
- 1. Select device (optional).
- 2. In the column for the maximum ambient temperature T_a select the temperature that is immediately greater than or equal to the measured maximum ambient temperature T_{ma} that is present.
 - $T_a = 50 \, ^{\circ}$ C. The row showing the maximum medium temperature is determined.
- 3. Select the maximum medium temperature T_m of this row, which is larger or equal to the measured maximum medium temperature T_{mm} .
 - Arr The column with the temperature class for gas is determined: 108 °C ≤ 120°C \rightarrow T4.
- 4. The maximum temperature of the temperature class determined corresponds to the maximum surface temperature for dust: $T4 = 135 \,^{\circ}C$

Storage temperature

-40 to +80 °C (-40 to +176 °F), preferably at +20 °C (+68 °F) (standard version)

-50 to +80 °C (-58 to +176 °F) (Order code for "Test, certificate", option JM)

Climate class

DIN EN 60068-2-38 (test Z/AD)

Degree of protection

Transmitter and sensor

- As standard: IP66/67, type 4X enclosure
- With the order code for "Sensor options", option **CM**: IP69K can also be ordered
- When housing is open: IP20, type 1 enclosure
- Display module: IP20, type 1 enclosure

Safety Barrier Promass 100

IP20

Vibration resistance


Compact version

- Vibration, sinusoidal according to IEC 60068-2-6
 - 2 to 8.4 Hz, 3.5 mm peak
 - 8.4 to 2000 Hz, 1 g peak
- Vibration broad-band random, according to IEC 60068-2-64
 - -10 to 200 Hz, 0.003 q^2/Hz
 - $-200 \text{ to } 2000 \text{ Hz}, 0.001 \text{ g}^2/\text{Hz}$
 - Total: 1.54 g rms

Shock resistance	Compact version Shock, half-sine according to IEC 60068-2-27 6 ms 30 g
Shock resistance	Compact version Rough handling shocks according to IEC 60068-2-31
Interior cleaning	 Cleaning in place (CIP) Sterilization in place (SIP) Cleaning with pigs
	Options Oil- and grease-free version for wetted parts, without inspection certificate Order code for "Service", option HA
Electromagnetic compatibility (EMC)	 Depends on the communication protocol: HART. PROFIBUS DP. Modbus RS485. EtherNet/IP:

compatibility (EMC)

- As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21) - PROFINET: as per IEC/EN 61326
- Complies with emission limits for industry as per EN 55011 (Class A)
- Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784





For details, refer to the Declaration of Conformity.

Process

Medium temperature range

- -50 to +150 °C (-58 to +302 °F)
- -50 to +205 °C (-58 to +401 °F) with extended temperature (order code for "Measuring tube mat." option TD, TG)

Seals

No internal seals


Density

0 to 5000 kg/m^3 (0 to 312 lb/cf)

Pressure-temperature ratings

The following pressure-temperature ratings refer to the entire device and not just the process connection.


Flange according to EN 1092-1 (DIN 2501)



23 € With flange material 1.4404 (F316/F316L).

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG


Flange according to ASME B16.5



€ 24 With flange material 1.4404 (F316/F316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG


Flange JIS B2220



■ 25 With flange material 1.4404 (F316/F316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG


Flange DIN 11864-2 Form A



■ 26 With flange material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG


Neumo BioConnect, BBS flange



■ 27 With flange material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG

Thread DIN 11851




■ 28 With flange material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG

DIN 11851 allows for applications up to +140 °C (+284 °F) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.


Thread DIN 11864-1 Form A



With connection material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG


Thread ISO 2853



■ 30 With connection material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG

Thread SMS 1145




■ 31 With connection material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 °C (+302 to +401 °F) apply only to the order code for "Measuring tube material", option TD, TG

SMS 1145 allows for applications up to 6 bar (87 psi) if suitable sealing materials are used. Please take this into account when selecting seals and counterparts, as these components can limit the pressure and temperature range.

Clamp connections DIN 11864-3 Form A



■ 32 With connection material 1.4435 (316L)

The material load curves for the temperature range +150 to +205 $^{\circ}$ C (+302 to +401 $^{\circ}$ F) apply only to the order code for "Measuring tube material", option TD, TG

Tri-Clamp; clamp connection ISO 2852, DIN 32676, BBS, Neumo BioConnect


The clamp connections are suitable up to a maximum pressure of 16 bar (232 psi). Please observe the operating limits of the clamp and seal used as they can be over 16 bar (232 psi). The clamp and seal are not included in the scope of supply.

Secondary containment pressure rating

The sensor housing is filled with dry nitrogen and protects the electronics and mechanics inside.

The following secondary containment pressure rating is only valid for a fully welded sensor housing and/or a device equipped with closed purge connections (never opened/as delivered).

DN		pressur	containment e rating a a safety factor 4)	Secondary containment burst pressure		
[mm]	[mm] [in]		[psi]	[bar]	[psi]	
8	3/8	25	362	190	2755	
15	1/2	25	362	175	2535	
25	1	25	362	165	2930	
40	1½	25	362	152	2204	
50	2	25	362	103	1493	



With the help of these connections, the fluid collected in the secondary containment can be bled off in the event of tube failure. This is especially important in high-pressure gas applications. These connections can also be used for gas purging (gas detection).

Do not open the purge connections unless the containment can be filled immediately with a dry, inert gas. Use only low gauge pressure to purge. Maximum pressure: 5 bar (72.5 psi).

If a device fitted with purge connections is connected to the purge system, the maximum nominal pressure is determined by the purge system itself or by the device, depending on which component has the lower nominal pressure.

Dimensions: → 🖺 58

Flow limit

Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.



For an overview of the full scale values for the measuring range, see the "Measuring range" section

- The minimum recommended full scale value is approx. 1/20 of the maximum full scale value
- In most applications, 20 to 50 % of the maximum full scale value can be considered ideal
- A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity < 1 m/s (< 3 ft/s).

Pressure loss




To calculate the pressure loss, use the *Applicator* sizing tool $\rightarrow \bigcirc$ 98

System pressure

It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.


For this reason, the following mounting locations are recommended:

- At the lowest point in a vertical pipe
- Downstream from pumps (no danger of vacuum)



Thermal insulation

In the case of some fluids, it is important that the heat radiated from the sensor to the transmitter is kept to a minimum. A wide range of materials can be used for the required insulation.




A00199

- Minimum distance to insulation
- t maximum Insulation thickness

The minimum distance between the transmitter housing and the insulation is 10 mm (0.39 in) so that the transmitter head remains completely exposed.

Maximum recommended insulation thickness



Maximum recommended insulation thickness depending on the temperature of the medium and the ambient temperature

t Insulation thickness


 $T_{\rm m}$ Medium temperature

 $T_{40(104)}$ Maximum recommended insulation thickness at an ambient temperature of $T_a = 40$ °C (104 °F)

 $T_{60(140)}$ Maximum recommended insulation thickness at an ambient temperature of $T_a = 60$ °C (140 °F)

Maximum recommended insulation thickness for the extended temperature range and insulation

For the extended temperature range, version with long extension neck, order code for "Measuring tube material", option TD, TG or extension neck for insulation, order code for "Sensor option", option CG:



Maximum recommended insulation thickness depending on the temperature of the medium and the ambient temperature

t Insulation thickness

 $T_{\rm m}$ Medium temperature

 $T_{40(104)}$ Maximum recommended insulation thickness at an ambient temperature of T_a = 40 °C (104 °F)

 $T_{60(140)}$ Maximum recommended insulation thickness at an ambient temperature of $T_a = 60 \,^{\circ}\text{C}$ (140 $^{\circ}\text{F}$)

NOTICE

Danger of overheating with insulation

► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F)

NOTICE

The insulation can also be thicker than the maximum recommended insulation thickness. Prerequisite:


- ► Ensure that convection takes place on a sufficiently large scale at the transmitter neck.
- ► Ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

Heating options

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam
- Via heating jackets



NOTICE

Danger of overheating when heating

- ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- ► Ensure that convection takes place on a sufficiently large scale at the transmitter neck.
- ► Ensure that a sufficiently large area of the housing support remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations


The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

Mechanical construction

Dimensions in SI units


Compact version

Order code for "Housing", option A "Compact coated aluminum"



DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ^{1) 2)} [mm]	F ^{1) 2)} [mm]	G [mm]	H [mm]	K [mm]	L [mm]
8	136	147.5	93.5	54	191	299	8.31	108	92	3)
15	136	147.5	93.5	54	191	299	12.00	108	92	3)
25	136	147.5	93.5	54	191	312	17.60	121	92	3)
40	136	147.5	93.5	54	231	407	26.00	176	141	3)
50	136	147.5	93.5	54	256	516	38.00	260	168	3)


- If using an extension neck for the extended temperature range, order code for "Sensor option", option CG and order code for "Measuring tube material", option TD, TG: values +70 mm
- If using a display, order code for "Display; Operation", option B: values +28 mm
- 2) 3) Dependent on the particular process connection



Order code for "Housing", option B "Compact hygienic, stainless"

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ^{1) 2)} [mm]	F ^{1) 2)} [mm]	G [mm]	H [mm]	K [mm]	L [mm]
8	133.5	136.8	78	58.8	186	294	8.31	108	92	3)
15	133.5	136.8	78	58.8	186	294	12.00	108	92	3)
25	133.5	136.8	78	58.8	186	307	17.60	121	92	3)
40	133.5	136.8	78	58.8	226	402	26.00	176	141	3)
50	133.5	136.8	78	58.8	251	511	38.00	260	168	3)

- If using an extension neck for the extended temperature range, order code for "Sensor option", option CG 1) and order code for "Measuring tube material", option TD, TG: values +70~mm If using a display, order code for "Display; Operation", option B: values +14~mm
- 3) Dependent on the particular process connection



Order code for "Housing", option C "Ultra-compact hygienic, stainless"


DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E ¹⁾²⁾ [mm]	F ¹⁾²⁾ [mm]	G [mm]	H [mm]	K [mm]	L [mm]
8	111.4	123.6	67.7	55.9	186	294	8.31	108	92	3)
15	111.4	123.6	67.7	55.9	186	294	12.00	108	92	3)
25	111.4	123.6	67.7	55.9	186	307	17.60	121	92	3)
40	111.4	123.6	67.7	55.9	226	402	26.00	176	141	3)
50	111.4	123.6	67.7	55.9	251	511	38.00	260	168	3)

- If using an extension neck for the extended temperature range, order code for "Sensor option", option CG and order code for "Measuring tube material", option TD, TG: values \pm 70 mm 1)
- If using a display, order code for "Display; Operation", option B: values +14 mm Dependent on the particular process connection 2)
- 3)

60

Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



■ 35 Engineering unit mm (in)

Flange according to EN 1092-1 (DIN 2501): PN 40 1.4404 (316/316L) Order code for "Process connection", option D2W										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
8 ¹⁾	95	65	4 × Ø14	17.0	17.3	336				
15	95	65	4 × Ø14	20.0	17.3	440				
25	115	85	4 × Ø14	19.0	28.5	580				
40	150	110	4 × Ø18	21.0	43.1	707				
50	50 165 125 4 × Ø18 25.0 54.5 828									
Surface roughn	iess (flange): EN	1092-1 Form E	31 (DIN 2526 Form	n C), Ra 3.2 to 12	2.5 µm					

1) DN 8 with DN 15 flanges as standard


1.4404 (316/	Flange according to ASME B16.5: Cl 150 1.4404 (316/316L) Order code for "Process connection", option AAW										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8 ¹⁾	90	60.3	4 × Ø15.7	11.2	15.7	336					
15	90	60.3	4 × Ø15.7	11.2	15.7	440					
25	110	79.4	4 × Ø15.7	14.2	26.7	580					
40	125	98.4	4 × Ø15.7	17.5	40.9	707					
50 150 120.7 8 × Ø19.1 19.1 52.6 828											
Surface rough	ness (flange): R	a 3.2 to 6.3 µm	1								

1) DN 8 with DN 15 flanges as standard

1.4404 (316/	Flange JIS B2220: 20K 1.4404 (316/316L) Order code for "Process connection", option NEW										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8 ¹⁾	95	70	4 × Ø15	16.0	15	336					
15	95	70	4 × Ø15	16.0	15	440					
25	125	90	4 × Ø19	17.5	25	580					
40	140	105	4 × Ø19	20.0	40	707					
50 155 120 8 × Ø19 27.5 50 828											
Surface roughr	ness (flange): Ra	3.2 to 6.3 µm									

¹⁾ DN 8 with DN 15 flanges as standard

Fixed flange DIN 11864-2




■ 36 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

1.4435 (316L)	Flange DIN 11864-2 Form A, for pipe according to DIN 11866 series A, flat flange 1.4435 (316L) Order code for "Process connection", option KJW										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8	59.0	42	4 × Ø9	10	16.00	384					
15	59.0	42	4 × Ø9	10	16.00	488					
25	70.0	53	4 × Ø9	10	26.00	626					
40	82.0	65	4 × Ø9	10	38.00	753					
50	94.0	77	4 × Ø9	10	50.00	877					

Ra $_{max}\,0.76~\mu m$: order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

BBS fixed flange



■ 37 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).


BBS flange small (sterile orbital), for pipe according to DIN 11866 series A, female 1.4435 (316L) Order code for "Process connection", option BSK										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
8	59	42	4 × Ø9	10	10.00	384				
15	59	42	4 × Ø9	10	16.00	488				
25	70	53	4 × Ø9	10	26.00	626				
40	82	65	4 × Ø9	10	38.00	753				
50	94	77	4 × Ø9	10	50.00	877				

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG

1.4435 (316L)	BBS flange small (sterile orbital), for pipe according to DIN 11866 series B, female 1.4435 (316L) Order code for "Process connection", option BSL										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
8	59	42	4 × Ø9	10	14.00	384					
15	62	45	4 × Ø9	10	18.10	488					
25	74	57	4 × Ø9	10	29.70	626					
40	88	71	4 × Ø9	10	44.30	753					
50	103	85	4 × Ø9	10	56.30	877					

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Neumo BioConnect fixed flange



₹ 38 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

Neumo BioConnect flange, for pipe according to DIN 11866 series A, flange form R 1.4435 (316L)


Order code for "Process connection", option BSB

oraci code joi 1700cos contection, option 202						
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
8	65	45	4 × Ø9	10	10.00	384
15	75	55	4 × Ø9	10	16.00	488
25	85	65	4 × Ø9	12	26.00	626
40	100	80	4 × Ø9	12	38.00	753
50	110	90	4 × Ø9	14	50.00	877

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Clamp connections

Tri-Clamp



■ 39 Engineering unit mm (in)

Tri-Clamp, for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FHW						
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]		
8	1/2	25.0	9.40	362		
15	3/4	25.0	15.75	466		
25	1 1)	50.4	22.10	606		
40	1½ 1)	50.4	34.80	731		
50 2 ¹⁾ 63.9 47.50 853						
Ra _{max} 0.76 µm: order code for "Measuring tube material", option BB, TD Ra _{max} 0.38 µm electropolished: order code for "Measuring tube material", option BC, TG						

1) The connection complies with the hygienic clamp dimensions as per ASME BPE.

1/2" Tri-Clamp, for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FCW				
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]
15	1/2	25.0	9.40	466
Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG				

3/4" Tri-Clamp, for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FFW				
DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]
8	3/4	25.0	15.75	362
Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG				

1" Tri-Clamp, for pipe according to DIN 11866 series C 1.4435 (316L) $\,$

Order code for "Process connection", option FPW

DN [mm]	Clamp [in]	A [mm]	B [mm]	L [mm]
8	1 1)	50.4	22.10	362
15	1 1)	50.4	22.10	466

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

1) The connection complies with the hygienic clamp dimensions as per ASME BPE.

Tri-Clamp eccentric, for pipe according to DIN 11866 series C 1.4435 (316L)						
DN [mm]	Order code for "Process connection", option	Clamp [in]	A [mm]	B [mm]	L [mm]	
8	FEB	1/2	25.0	9.40	362	
15	FED	3/4	25.0	15.75	466	
25	FEF	1 ¹⁾	50.4	22.10	606	
40	FEH	1½ 1)	50.4	34.80	738	
50	FEK	2 1)	63.9	47.50	860	


Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{\text{max}}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

1) The connection complies with the hygienic clamp dimensions as per ASME BPE.

Clamp connection DIN 32676, ISO 2852



■ 40 Engineering unit mm (in)

Clamp DIN 32676, for pipe according to DIN 11866 series A 1.4435 (316L) Order code for "Process connection", option KPW				
DN [mm]	A [mm]	B [mm]	L [mm]	
8	34.0	16.00	362	
15	34.0	16.00	466	
25	50.5	26.00	606	

Clamp DIN 32676, for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option KPW

DN [mm]	A [mm]	B [mm]	L [mm]
40	50.5	38.00	732
50	64.0	50.00	854

Ra $_{\text{max}}$ 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Clamp ISO 2852, for pipe according to ISO 2037 1.4435 (316L)

Order code for "Process connection", option JSA

DN [mm]	A [mm]	B [mm]	L [mm]
8	50.5	22.6	362
15	50.5	22.6	466
25	50.5	22.6	606
40	50.5	35.6	731
50	64.0	48.6	853

Ra $_{max}$ 0.76 μm order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG

Clamp ISO 2852, for pipe according to DIN11866 series B 1.4435 (316L)


Order code for "Process connection", option JSC

, , , , , , , , , , , , , , , , , , ,						
DN [mm]	A [mm]	B [mm]	L [mm]			
8	34.0	14.00	362			
15	34.0	18.10	466			
25	50.5	29.70	606			
40	64.0	44.30	731			
50	77.5	56.30	853			

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG


Clamp connection DIN 11864-3



₽ 41 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

Clamp DIN 11864-3 Form A, for pipe according to DIN 11866 series A, with notch 1.4435 (316L) Order code for "Process connection", option KLW				
DN [mm]	A [mm]	B [mm]	L [mm]	
8	34.0	16.05	370	
15	34.0	16.05	474	
25	50.5	26.05	614	
40	64.0	38.05	738	
50	77.5	50.05	853	
Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG				

BBS clamp connection



₽ 42 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

BBS Quick Connect (sterile orbital), for pipe according to DIN 11866 series A, female 1.4435 (316L) $\,$

Order code for "Process connection", option BSE

DN [mm]	A [mm]	B [mm]	L [mm]
8	25.0	10.00	362
15	50.5	16.00	466
25	50.5	26.00	606
40	64.0	38.00	732
50	77.5	50.00	854

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

BBS Quick Connect (sterile orbital) for pipe according to DIN11866 series B, female 1.4435 (316L)


Order code for "Process connection", option BSJ

DN [mm]	A [mm]	B [mm]	L [mm]
8	25.0	14.00	362
15	50.5	18.10	466
25	50.5	29.70	606
40	64.0	44.30	738
50	77.5	56.30	860

Ra $_{\text{max}}$ 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{\text{max}}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Neumo BioConnect clamp connection



■ 43 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).


Clamp, Neumo BioConnect, for pipe according to DIN 11866 series A, clamp form R
1.4435 (316L)

Order code for "Process connection", option BSA

DN [mm]	A [mm]	B [mm]	L [mm]
8	25.0	10.00	362
15	25.0	16.00	466
25	50.4	26.00	606
40	64.0	38.00	732
50	77.4	50.00	854

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG

Eccentric clamp connection DIN 32676, ISO 2852



Engineering unit mm (in)

Eccentric clamp DIN 32676, for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option KRW			
DN [mm]	A [mm]	B [mm]	L [mm]
8	34.0	10.00	362
15	34.0	16.00	466
25	50.5	26.00	606
50	64.0	50.00	860

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG

Eccentric clamp ISO 2852, for pipe according to DIN11866 series \ensuremath{B}

Order code for "Process connection", option JEC			
DN [mm]	A [mm]	B [mm]	L [mm]
8	34.0	10.30	362
15	34.0	14.00	466
25	34.0	18.10	606
40	50.5	29.70	738

Eccentric clamp ISO 2852, for pipe according to DIN11866 series B 1.4435 (316L)

Order code for "Process connection", option JEC

DN	A	B	L
[mm]	[mm]	[mm]	[mm]
50	64.0	44.30	853

 $\mbox{Ra}_{\mbox{ max}}$ 0.76 $\mu\mbox{m:}$ order code for "Measuring tube material", option BB, TD

Ra $_{max}\,0.38~\mu m$ electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

Eccentric clamp ISO 2852, for pipe according to DIN11866 series B, for connection to DN15 pipes $1.4435\ (316L)$

Order code for "Process connection", option **JED**


DN	A	B	L
[mm]	[mm]	[mm]	[mm]
25	50.5	18.10	

 Ra_{max} 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

Eccentric clamp connection DIN 11864-3



Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

Eccentric clamp DIN 11864-3 Form A, for pipe according to DIN 11866 series A, with notch 1.4435 (316L) $\,$

Order code for "Process connection", option KNW

DN [mm]	A [mm]	B [mm]	L [mm]
8	34.0	10.00	370
15	34.0	16.00	474
25	50.5	26.00	624
50	77.5	50.00	869


 $Ra_{max} 0.76 \mu m$: order code for "Measuring tube material", option BB, TD

Ra $_{\text{max}}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

72

BBS eccentric clamp connection



€ 46 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

BBS Quick Connect (sterile 1.4435 (316L) Order code for "Process conn	,, , , , , , , , , , , , , , , , , , ,	e according to DIN11866 se	ries A, female
DN [mm]	A [mm]	B [mm]	L [mm]
8	25.0	10.00	362
15	50.5	16.00	466
25	50.5	26.00	606
50	77.5	50.00	860

Ra $_{\text{max}}$ 0.76 μm order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"


BBS Quick Connect (sterile orbital), eccentric, for pipe according to DIN11866 series B, female
1.4435 (316L)
Order code for "Process connection", option BEK

oraci coacjo, rroccos connection, opaon 221				
DN [mm]	A [mm]	B [mm]	L [mm]	
8	25.0	10.30	362	
15	50.5	14.00	466	
25	50.5	18.10	606	
40	50.5	29.70	738	
50	64.0	44.30	860	

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

Neumo BioConnect eccentric clamp connection



Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).


Neumo BioConnect eccentric clamp connection 1.4435 (316L) Order code for "Process connection", option BEA				
DN [mm]	A [mm]	B [mm]	L [mm]	
8	25	10.00	362	
15	25	16.00	466	
25	25	26.00	610	
50	25	50.00	859	

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

Cable glands

Thread DIN 11851, DIN 11864-1, SMS 1145, BBS



€ 48 Engineering unit mm (in)

Thread DIN 11851, for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option KCW

DN [mm]	A [mm]	B [mm]	L [mm]
8	Rd 34 × ⅓	16	362
15	Rd 34 × ¹ ⁄ ₈	16	466
25	Rd 52 × ¹ ⁄ ₆	26	606
40	Rd 65 × 1/ ₆	38	738
50 Rd 78 × ½		50	864

 Ra_{max} 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Thread DIN 11851, Rd 28 × $\frac{1}{8}$ ", for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option KAW

DN [mm]	A [mm]	B [mm]	L [mm]	
8	Rd $28 \times \frac{1}{8}$ "	10.00	362	
15	Rd $28 \times \frac{1}{8}$ "	10.00	466	

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD

 Ra_{max} 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Thread DIN 11864-1 Form A, for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option KGW

oraci code joi i roccos co.	. 1. Occasi contraction, option 125 ii			
DN [mm]	A [mm]	B [mm]	L [mm]	
8	Rd 34 × 1/8"	16	362	
15	Rd 34 × 1/8"	16	466	
25	Rd 52 × 1/6"	26	620	
40	Rd 65 × 1/6"	38	738	
50	50 Rd 78 × ½"		864	

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Thread SMS 1145 1.4435 (316L)

order code for Process connection, option SAW				
DN [mm]	A [mm]	B [mm]	L [mm]	
8	8 Rd 40 × ½"		362	
15	Rd 40 × 1/6"	22.50	466	
25	25 Rd 40 × ½"		606	
40	Rd 60 × 1/6"	35.50	742	
50 Rd 70 × ½"		48.50	864	

Ra $_{max}$ 0.76 μm : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

BBS thread (sterile orbital), for pipe according to DIN 11866 series A 1.4435 (316L)

Order code for "Process connection", option BSC

*	•			
DN A [mm]		B [mm]	L [mm]	
8	M22 ×1.5	10.00	362	
15	M30 × 2	16.00	466	
25	M42 × 2	26.00	606	
40	M52 × 2	38.00	732	
50	M68 × 2	50.00	854	

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG

BBS thread (sterile orbital), for pipe according to DIN 11866 series $\ensuremath{\mathtt{B}}$ 1.4435 (316L)


Order code for "Process connection", option BSD

DN [mm]	A [mm]	B [mm]	L [mm]
8	M26 × 1.5	10.00	362
15	15 M30 × 2		466
25	M42 × 2	26.00	606
40 M56 × 2		38.00	738
50 M68 × 2		50.00	860

Ra $_{\text{max}}$ 0.76 μm order code for "Measuring tube material", option BB, TD

Ra $_{max}$ 0.38 μm electropolished: order code for "Measuring tube material", option BC, TG

Thread ISO 2853



Engineering unit mm (in)

Thread ISO 2853, for pipe according to ISO 2037 1.4435 (316L) Order code for "Process connection", option JSD Α В DN L [mm] [mm] [mm] [mm] 37.13 8 22.60 370 15 37.13 22.60 474 25 37.13 22.60 614 50.65 35.60 742


Thread ISO 2853, for pipe according to ISO 2037 1.4435 (316L) Order code for "Process connection", option JSD				
DN [mm]	L [mm]			
50	64.10	48.60	864	

Ra $_{max}$ 0.76 μ m: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 0.38 μ m electropolished: order code for "Measuring tube material", option BC, TG


Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH



DN	G	A	Н	L
[mm]	[in]	[mm]	[mm]	[mm]
8	½ NPT	25	82	110
15	½ NPT	25	82	204
25	½ NPT	25	82	348




DN	A	В	С
[mm]	[in]	[mm]	[mm]
40	½ NPT	68.15	418
50	½ NPT	81.65	473

Dimensions in US units


Compact version

Order code for "Housing", option A "Compact coated aluminum"



DN [in]	A [in]	B [in]	C [in]	D [in]	E ^{1) 2)} [in]	F ¹⁾²⁾ [in]	G [in]	H [in]	K [in]	L [in]
3/8	5.35	5.81	3.68	2.13	7.52	11.77	0.33	4.25	3.62	3)
1/2	5.35	5.81	3.68	2.13	7.52	11.77	0.47	4.25	3.62	3)
1	5.35	5.81	3.68	2.13	7.52	12.28	0.69	4.76	3.62	3)
1½	5.35	5.81	3.68	2.13	9.09	16.02	1.02	6.93	5.55	3)
2	5.35	5.81	3.68	2.13	10.08	20.31	1.5	10.24	6.61	3)


- If using an extension neck for the extended temperature range, order code for "Sensor option", option CG and order code for "Measuring tube material", option TD, TG: values ± 2.76 in If using a display, order code for "Display; Operation", option B: values ± 1.1 in 1)
- 2) 3) Dependent on the particular process connection



Order code for "Housing", option B "Compact hygienic, stainless"

DN [in]	A [in]	B [in]	C [in]	D [in]	E ^{1) 2)} [in]	F ^{1) 2)} [in]	G [in]	H [in]	K [in]	L [in]
3/8	5.26	5.39	3.07	2.31	7.32	11.57	0.33	4.25	3.62	3)
1/2	5.26	5.39	3.07	2.31	7.32	11.57	0.47	4.25	3.62	3)
1	5.26	5.39	3.07	2.31	7.32	12.09	0.69	4.76	3.62	3)
1½	5.26	5.39	3.07	2.31	8.9	15.83	1.02	6.93	5.55	3)
2	5.26	5.39	3.07	2.31	9.88	20.12	1.5	10.24	6.61	3)

- If using an extension neck for the extended temperature range, order code for "Sensor option", option CG 1) and order code for "Measuring tube material", option TD, TG: values +2.76 in If using a display, order code for "Display; Operation", option B: values +0.55 in
- 3) Dependent on the particular process connection




Order code for "Housing", option C "Ultra-compact hygienic, stainless"

DN [in]	A [in]	B [in]	C [in]	D [in]	E ^{1) 2)} [in]	F ¹⁾²⁾ [in]	G [in]	H [in]	K [in]	L [in]
3/8	4.39	4.87	2.67	2.2	7.32	11.57	0.33	4.25	3.62	3)
1/2	4.39	4.87	2.67	2.2	7.32	11.57	0.47	4.25	3.62	3)
1	4.39	4.87	2.67	2.2	7.32	12.09	0.69	4.76	3.62	3)
11/2	4.39	4.87	2.67	2.2	8.9	15.83	1.02	6.93	5.55	3)
2	4.39	4.87	2.67	2.2	9.88	20.12	1.5	10.24	6.61	3)

- 1) If using an extension neck for the extended temperature range, order code for "Sensor option", option CG and order code for "Measuring tube material", option TD, TG: values ± 2.76 in
- 2) If using a display, order code for "Display; Operation", option B: values +0.55 in
- 3) Dependent on the particular process connection

Flange connections

Fixed flange ASME B16.5




■ 50 Engineering unit mm (in)

1.4404 (31	Flange according to ASME B16.5: Cl 150 1.4404 (316/316L) Order code for "Process connection", option AAW							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]		
3/8 1)	3.54	2.37	4 × Ø0.62	0.44	0.62	13.23		
1/2	3.54	2.37	4 × Ø0.62	0.44	0.62	17.32		
1	4.33	3.13	4 × Ø0.62	0.56	1.05	22.83		
1½	4.92	3.87	4 × Ø0.62	0.69	1.61	27.83		
2 5.91 4.75 4 × Ø0.75 0.75 2.07 32.6								
Surface roug	Surface roughness (flange): Ra 3.2 to 6.3 µm							

1) DN $^3\!/\!_8$ with DN $^1\!/\!_2$ flanges as standard

Neumo BioConnect fixed flange




€ 51 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

1.4435 (316)	Neumo BioConnect flange; for pipe according to DIN 11866 series A, flange form R 1.4435 (316L) Order code for "Process connection", option BSB							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]		
3/8	2.56	1.77	4 × Ø0.35	0.39	0.39	15.12		
1/2	2.95	2.17	4 × Ø0.35	0.39	0.63	19.21		
1	3.35	2.56	4 × Ø0.35	0.47	1.02	24.65		
1½	3.94	3.15	4 × Ø0.35	0.47	1.5	29.65		
2	4.33	3.54	4 × Ø0.35	0.55	1.97	34.53		

Ra $_{max}$ 30 $\mu in:$ order code for "Measuring tube material", option BB, TD Ra $_{max}$ 15 μin electropolished: order code for "Measuring tube material", option BC, TG

Clamp connections

Tri-Clamp



■ 52 Engineering unit mm (in)

Tri-Clamp; for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FHW DN Clamp Α В L [in] [in] [in] [in] [in] 3/8 0.98 0.37 14.25 1/2 1/2 3/4 0.98 0.62 18.35 1 1 1.98 0.87 23.86 11/2 1 ½ 1.98 1.37 28.78 2 2.52 1.87 33.58 Ra $_{\text{max}}$ 30 $\mu\text{in:}$ order code for "Measuring tube material", option BB, TD

1½" Tri-Clamp; for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FCW						
DN Clamp A B L [in] [in] [in] [in]						
1/2 1/2 0.98 0.37 18.35						
Ra max 30 µin: order code for "Measuring tube material", option BB, TD Ra 15 µin electropolished: order code for "Measuring tube material" option BC, TG						

Ra $_{max}$ 15 μ in electropolished: order code for "Measuring tube material", option BC, TG

%" Tri-Clamp; for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FFW						
DN Clamp A B L [in] [in] [in] [in]						
³ / ₈ 3/ ₄ 0.98 0.62 14.25						
111001	Ra max 30 µin: order code for "Measuring tube material", option BB, TD Ra max 15 µin electropolished: order code for "Measuring tube material", option BC, TG					

1" Tri-Clamp; for pipe according to DIN 11866 series C 1.4435 (316L) Order code for "Process connection", option FPW							
DN Clamp A B L [in] [in] [in] [in]							
3/8	1	1.98	0.87	14.25			
1 1.98 0.87 18.35							

 $Ra_{\,max}$ 30 $\mu in:$ order code for "Measuring tube material", option BB, TD


Ra $_{max}$ 15 μ in electropolished: order code for "Measuring tube material", option BC, TG

Tri-Clamp eccer 1.4435 (316L)	Tri-Clamp eccentric; for pipe according to DIN 11866 series C 1.4435 (316L)							
DN [in]	Order code for "Process connection", option	Clamp [in]	A [in]	B [in]	L [in]			
3/8	FEB	1/2	0.98	0.37	14.25			
1/2	FED	3/4	0.98	0.62	18.35			
1	FEF	1	1.98	0.87	23.86			
1½	FEH	1½	1.98	1.37	29.06			
2	FEK	2	2.52	1.87	33.86			

Ra $_{max}$ 30 μin : order code for "Measuring tube material", option BB, TD Ra $_{max}$ 15 μin electropolished: order code for "Measuring tube material", option BC, TG

Additional information on "Eccentric clamps"

Neumo BioConnect clamp connection




■ 53 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

Clamp; Neumo BioConnect, for pipe according to DIN 11866 series A; clamp form R 1.4435 (316L) Order code for "Process connection", option BSA						
DN A B L [in] [in] [in]						
3/8	0.98	0.39	14.25			
1/2	0.98	0.63	18.35			
1	1.98	1.02	23.86			
11/2	2.52	1.5	28.82			

Clamp; Neumo BioConnect, for pipe according to DIN 11866 series A; clamp form R 1.4435 (316L) Order code for "Process connection", option BSA						
DN A B L [in] [in]						
2 3.05 1.97 33.62						
111011	Ra max 30 µin: order code for "Measuring tube material", option BB, TD Ra max 15 µin electropolished: order code for "Measuring tube material", option BC, TG					

Neumo BioConnect eccentric clamp connection




€ 54 Detail X: Asymmetrical process connection; the part shown in gray is provided by the supplier. Engineering unit mm (in).

Neumo BioConnect eccentric clamp connection 1.4435 (316L) Order code for "Process connection", option BEA			
DN [in]	A [in]	B [in]	L [in]
3/8	0.98	0.39	14.25
1/2	0.98	0.63	18.35
1	0.98	1.02	24.02
1	0.98	1.97	43.39

Ra $_{max}$ 30 μ in: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 15 μ in electropolished: order code for "Measuring tube material", option BC, TG Additional information on "Eccentric clamps"

Cable glands

Thread SMS 1145



№ 55 Engineering unit mm (in)


Thread SMS 1145 1.4435 (316L) Order code for "Process connection", option SAW			
DN [in]	A [in]	B [in]	L [in]
3/8	Rd 40 × 1/ ₆	0.89	14.25
1/2	Rd 40 × ¹ ⁄ ₆	0.89	18.35
1	Rd 40 × 1/ ₆	0.89	23.86
1½	Rd 60 × 1/ ₆	1.4	29.21
2	Rd 70 × ½	1.91	34.02

Ra $_{max}$ 30 μ in: order code for "Measuring tube material", option BB, TD Ra $_{max}$ 15 μ in electropolished: order code for "Measuring tube material", option BC, TG


Accessories

Purge connections / secondary containment monitoring

Order code for "Sensor options", option CH



DN	G	A	Н	L
[in]	[in]	[in]	[in]	[in]
3/8	½ NPT	0.98	3.23	4.34
1/2	½ NPT	0.98	3.23	8.04
1	½ NPT	0.98	3.23	13.54



DN	A	В	С
[in]	[in]	[in]	[in]
11/2	½ NPT	2.683	16.46
2	½ NPT	3.215	18.62

Weight Compact version

Weight in SI units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [kg].

DN [mm]	Weight [kg]
8	11
15	13
25	19
40	35
50	58

Weight in US units

All values (weight) refer to devices with EN/DIN PN 40 flanges. Weight information in [lbs].

DN [in]	Weight [lbs]
3/8	24
1/2	29
1	42
1½	77
2	128

Safety Barrier Promass 100


49 g (1.73 ounce)

Materials

Transmitter housing

- Order code for "Housing", option A "Compact, aluminum coated": Aluminum, AlSi10Mq, coated
- Order code for "Housing", option B "Compact, hygienic, stainless": Hygienic version, stainless steel 1.4301 (304)
- Order code for "Housing", option C "Ultra-compact, hygienic, stainless": Hygienic version, stainless steel 1.4301 (304)
- Window material for optional local display (→ 🖺 89):
 - For order code for "Housing", option A: glass
 - For order code for "Housing", option **B** and **C**: plastic

Cable entries/cable glands



A0020640

- 56 Possible cable entries/cable glands
- Cable entry in transmitter housing with internal thread M20 x 1.5
- 2 Cable gland M20 x 1.5
- 3 Adapter for cable entry with internal thread G $\frac{1}{2}$ " or NPT $\frac{1}{2}$ "

Order code for "Housing", option A "Compact, coated aluminum"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Nickel-plated brass
Adapter for cable entry with internal thread G ½"	
Adapter for cable entry with internal thread NPT ½"	

Order code for "Housing", option B "Compact, hygienic, stainless"

The various cable entries are suitable for hazardous and non-hazardous areas.

Cable entry/cable gland	Material
Cable gland M20 × 1.5	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread G ½"	
Adapter for cable entry with internal thread NPT ½"	

Device plug

Electrical connection	Material
Plug M12x1	 Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass

Sensor housing

- Acid and alkali-resistant outer surface
- Stainless steel 1.4301 (304)

Measuring tubes

Stainless steel, 1.4435 (316L)

Process connections

- Flanges according to EN 1092-1 (DIN 2501) / according to ASME B16.5 / according to JIS B2220: Stainless steel, 1.4404 (316/316L)
- All other process connections: Stainless steel, 1.4435 (316L)
- i

Seals


Welded process connections without internal seals

Safety Barrier Promass 100

Housing: Polyamide

Process connections

- Fixed flange connections:
 - EN 1092-1 (DIN 2501) flange
 - EN 1092-1 (DIN 2512N) flange
 - ASME B16.5 flange
 - JIS B2220 flange
 - DIN 11864-2 Form A flange, DIN11866 series A, flat flange
 - BBS small flange (sterile, orbital), DIN11866 series A, grooved flange
 - BBS small flange (sterile, orbital), DIN11866 series B, grooved flange
- Clamp connections
 - Tri-Clamp (OD tubes), DIN 11866 series C
 - DIN 11864-3 Form A Clamp, DIN11866 series A, aseptic liner
 - DIN 32676 clamp, DIN11866 series A
 - ISO 2852 clamp, ISO2037
 - ISO 2852 clamp, DIN11866 series B
 - BBS Quick-Connect (sterile, orbital), DIN11866 series A, female
 - BBS Quick-Connect (sterile, orbital), DIN11866 series B, female
 - Neumo BioConnect Clamp, DIN11866 series A, clamp form R
- Excentric clamp connection:
 - Excen. Tri-Clamp, DIN 11866 series C
 - DIN 11864-3 Form A Clamp, DIN11866 series A, aseptic liner
 - DIN 32676 clamp, DIN11866 series A
 - ISO 2852 clamp, DIN11866 series B
 - BBS Quick-Connect (sterile, orbital), DIN11866 series A, female
 - BBS Quick-Connect (sterile, orbital), DIN11866 series B, female
 - Neumo BioConnect Clamp, DIN11866 series A, clamp form R
- Threaded hygienic connection:
 - DIN 11851 threaded hygienic connection, DIN11866 series A
 - SMS 1145 threaded hygienic connection
 - ISO 2853 threaded hygienic connection, ISO2037
 - DIN 11864-1 Form A threaded hygienic connection, DIN11866 series A
 - BBS threaded adapter (sterile, orbital), DIN11866 series A
 - BBS threaded adapter (sterile, orbital), DIN11866 series B



Surface roughness

All data relate to parts in contact with fluid.

- $Ra_{max} = 0.76 \mu m (30 \mu in)$
- $Ra_{max} = 0.38 \mu m$ (15 μ in) electropolished
- Delta ferrite < 1%

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Quick and safe commissioning

- Individual menus for applications
- Menu quidance with brief explanations of the individual parameter functions

Reliable operation

- Operation in the following languages:
 - Via "FieldCare" operating tool:
 - English, German, French, Spanish, Italian, Chinese, Japanese
 - Via integrated Web browser (only available for device versions with HART, PROFIBUS DP, PROFINET and EtherNet/IP):
 - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech, Swedish, Korean
- Uniform operating philosophy applied to operating tools and Web browser
- If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure.

For devices with Modbus RS485, the data recovery function is implemented without the plug-in memory (HistoROM DAT).

Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the operating tools and Web browser
- Diverse simulation options
- Status indicated by several light emitting diodes (LEDs) on the electronic module in the housing compartment

Local display



A local display is only available for device versions with the following communication protocols: HART, PROFIBUS-DP, PROFINET, EtherNet/IP

The local display is only available with the following device order code: Order code for "Display; Operation", option **B**: 4-line; lit, via communication


Display element

- 4-line liquid crystal display with 16 characters per line.
- White background lighting; switches to red in event of device errors.
- Format for displaying measured variables and status variables can be individually configured.
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F). The readability of the display may be impaired at temperatures outside the temperature range.

Remote operation

Via HART protocol

This communication interface is available in device versions with a HART output.




■ 57 Options for remote operation via HART protocol

- 1 Control system (e.g. PLC)
- 2 Field Communicator 475
- 3 Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- 4 Commubox FXA195 (USB)
- 5 Field Xpert SFX350 or SFX370
- 6 VIATOR Bluetooth modem with connecting cable
- 7 Transmitter

Via PROFIBUS DP network

This communication interface is available in device versions with PROFIBUS DP.




■ 58 Options for remote operation via PROFIBUS DP network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Measuring device

Via Ethernet-based fieldbus

This communication interface is available in device versions with EtherNet/IP.




■ 59 Options for remote operation via Ethernet-based fieldbus

- 1 Control system, e.g. "RSLogix" (Rockwell Automation)
- 2 Workstation for measuring device operation: with Add-on Profile Level 3 for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- 3 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 4 Ethernet switch
- 5 Measuring device

Via PROFINET network

This communication interface is available in device versions with PROFINET.



■ 60 Options for remote operation via PROFINET network

- Automation system, e.g. Simatic S7 (Siemens)
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Switch, e.g. Scalance X204 (Siemens)
- 4 Measuring device

Service interface

Via service interface (CDI-RJ45)


This communication interface is present in the following device version:

- Order code for "Output", option **B**: 4-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option **L**: PROFIBUS DP
- Order code for "Output", option N: EtherNet/IP
- Order code for "Output", option **R**: PROFINET

Endress+Hauser 91

A0026545


HART



A0016926

- 61 Connection for the order code for "Output", option B: 4-20 mA HART, pulse/frequency/switch output
- 1 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug


PROFIBUS DP



A0021270

- 62 Connection for order code for "Output", option L: PROFIBUS DP
- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

EtherNet/IP




A0016040

63 Connection for order code for "Output", option N: EtherNet/IP

- 1 Service interface (CDI -RJ45) and EtherNet/IP interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

PROFINET



A0016940


■ 64 Connection for order code for "Output", option R: PROFINET

- Service interface (CDI -RJ45) and PROFINET interface of the measuring device with access to the integrated Web server
- 2 Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 3 Standard Ethernet connecting cable with RJ45 plug

Via service interface (CDI)

This communication interface is present in the following device version: Order code for "Output", option $\bf M$: Modbus RS485

Modbus RS485



A0016925

- 1 Service interface (CDI) of the measuring device
- 2 Commubox FXA291
- 3 Computer with "FieldCare" operating tool with COM DTM "CDI Communication FXA291"

Certificates and approvals

CE mark

The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

C-Tick symbol

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



The separate Ex documentation (XA) containing all the relevant explosion protection data is available from your Endress+Hauser sales center.

ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

Ex ia

Category (ATEX)	Type of protection
II2G	Ex ia IIC T6T1 Gb
II2G	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb
II1/2G, II2D	Ex ia IIC T6T1 Ga/Gb or Ex ia IIB T6T1 Ga/Gb Ex tb IIIC Txx °C Db
II2G, II2D	Ex ia IIC T6T1 Gb or Ex ia IIB T6T1 Gb Ex tb IIIC Txx °C Db

Ex nA

Category (ATEX)	Type of protection
II3G	Ex nA IIC T6T1 Gc or Ex nA IIC T5-T1 Gc

$_{C}CSA_{US}$

Currently, the following versions for use in hazardous areas are available:

IS (Ex i)

- Class I Division 1 Groups ABCD
- Class II Division 1 Groups EFG and Class III

NI (Ex nA)

Class I Division 2 Groups ABCD

Sanitary compatibility

- 3-A approval
- EHEDG-tested

HART certification

HART interface

The measuring device is certified and registered by the FieldComm Group. The measuring system meets all the requirements of the following specifications:

- Certified according to HART 7
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with PROFIBUS PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

Certification PROFINET

PROFINET interface

The measuring device is certified and registered by the PNO (PROFIBUS User Organization). The measuring system meets all the requirements of the following specifications:

- Certified according to:
 - Test specification for PROFINET devices
 - PROFINET Security Level 1 Net load test
- The device can also be operated with certified devices of other manufacturers (interoperability)

EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

Modbus RS485 certification

The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "MODBUS/TCP Conformance Test Laboratory" of the University of Michigan.

Pressure Equipment Directive

The devices can be ordered with or without a PED approval. If a device with a PED approval is required, this must be explicitly stated in the order. For devices with nominal diameters less than or equal to DN 25 (1"), this is neither possible nor necessary.

- With the PED/G1/x (x = category) marking on the sensor nameplate, Endress+Hauser confirms compliance with the "Essential Safety Requirements" specified in Annex I of the Pressure Equipment Directive 97/23/EC.
- Devices bearing this marking (PED) are suitable for the following types of medium:
 - Media in Group 1 and 2 with a vapor pressure greater than, or smaller and equal to 0.5 bar (7.3 psi)
 - Unstable gases
- Devices not bearing this marking (PED) are designed and manufactured according to good engineering practice. They meet the requirements of Art.3 Section 3 of the Pressure Equipment Directive 97/23/EC. The range of application is indicated in tables 6 to 9 in Annex II of the Pressure Equipment Directive.

Other standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ IEC/EN 60068-2-6

Environmental influences: Test procedure - Test Fc: vibrate (sinusoidal).

■ IEC/EN 60068-2-31

Environmental influences: Test procedure - Test Ec: shocks due to rough handling, primarily for devices.

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use - general requirements

■ IEC/EN 61326

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 80

The application of the pressure equipment directive to process control devices

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

■ NAMUR NE 132

Coriolis mass meter

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration • Up-to-the-minute configuration data

- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.



Detailed information on the application packages:

- Special Documentation for the device
- Special Documentation for the device

Package	Description			
Heartbeat Verification +Monitoring	Heartbeat Monitoring Continuously supplies data, which are characteristic of the measuring principle, to an external condition monitoring system for the purpose of preventive maintenance or process analysis. These data enable the operator to: Draw conclusions - using these data and other information - about the impact process influences (such as corrosion, abrasion, buildup etc.) have on the measuring performance over time. Schedule servicing in time. Monitor the process or product quality, e.g. gas pockets.			
	Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". Functional testing in the installed state without interrupting the process. Traceable verification results on request, including a report. Simple testing process via local operation or other operating interfaces. Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. Extension of calibration intervals according to operator's risk assessment.			

Concentration

Package	Description
Concentration measurement and special density	Calculation and outputting of fluid concentrations Many applications use density as a key measured value for monitoring quality or controlling processes. The device measures the density of the fluid as standard and makes this value available to the control system. The "Special Density" application package offers high-precision density measurement over a wide density and temperature range particularly for applications subject to varying process conditions.
	With the help of the "Concentration Measurement" application package, the measured density is used to calculate other process parameters: Temperature-compensated density (reference density). Percentage mass of the individual substances in a two-phase fluid. (Concentration in %). Fluid concentration is output with special units (Brix, Baumé, API, etc.) for standard applications.
	The measured values are output via the digital and analog outputs of the device.

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the sensor

Accessories	Description
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor. Water, water vapor and other non-corrosive liquids are permitted for use as fluids. If using oil as a heating medium, please consult with Endress+Hauser.
	For details, see Operating Instructions BA00099D

Communication-specific accessories

Accessories	Description			
Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F $ \frac{1}{2} = \frac{1}{2} \left(\frac{1}{2} + \frac{1}{2} \right) \left(\frac{1}{2} + \frac{1}{2} + \frac{1}{2} \right) \left(\frac{1}{2} + \frac{1}$			
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. For details, see the "Technical Information" document TI405C/07			
HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F			
Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S			
Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00053S			
Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00051S			
Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area . For details, see Operating Instructions BA01202S			
Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area . For details, see Operating Instructions BA01202S			

Service-specific accessories

Accessories	Description
Applicator	Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results
	Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project.
	Applicator is available: Via the Internet: https://wapps.endress.com/applicator On CD-ROM for local PC installation.
W@M	Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records.
	W@M is available: Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation.

FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them using the status information, it is also a simple but effective way of checking the status and condition. For details, see Operating Instructions BA00027S and BA00059S	
DeviceCare	Tool for connecting and configuring Endress+Hauser field devices. For details, see Innovation brochure IN01047S	
Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Haus Common Data Interface) and the USB port of a computer or laptop. For details, see "Technical Information" TI00405C	

System components

Accessories	Description			
Memograph M graphic display recorder	The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick.			
	For details, see "Technical Information" TI00133R and Operating Instructions BA00247R			
iTEMP	The temperature transmitters can be used in all applications and are suitable for the measurement of gases, steam and liquids. They can be used to read in the fluid temperature.			
	For details, see "Fields of Activity", FA00006T			

Supplementary documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- The *W@M Device Viewer*: Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions



Brief Operating Instructions containing the most important information for standard commissioning are supplied with the device.

Operating Instructions

	Documentation code				
Measuring device	HART PROFIBUS DP Modbus RS485 EtherNet/IP PROFINET				
Promass P 100	BA01192D	BA01253D	BA01059D	BA01067D	BA01431D

Description of device parameters

	Documentation code				
Measuring device	HART PROFIBUS DP Modbus RS485 EtherNet/IP PROFINET				
Promass 100	GP01033D	GP01034D	GP01035D	GP01036D	GP01037D

Supplementary devicedependent documentation

Safety Instructions

Content	Documentation code
ATEX/IECEx Ex i	XA00159D
ATEX/IECEx Ex nA	XA01029D
cCSAus IS	XA00160D
INMETRO Ex i	XA01219D
INMETRO Ex nA	XA01220D
NEPSI Ex i	XA01249D
NEPSI Ex nA	XA01262D

Special Documentation

Content	Documentation code
Information on the Pressure Equipment Directive	SD00142D
Modbus RS485 Register Information	SD00154D
Concentration Measurement	SD01152D
Heartbeat Technology	SD01153D

Installation Instructions

Contents	Documentation code
Installation Instructions for spare part sets	Specified for each individual accessory

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA $\,$

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

$Modbus^{\otimes}$

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IPTM

Trademark of ODVA, Inc.

PROFINET®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

TRI-CLAMP

Registered trademark of Ladish & Co., Inc., Kenosha, USA

Applicator®, FieldCare®, DeviceCare®, Field Xpert™, HistoROM®, TMB®, Heartbeat Technology™

Registered or registration-pending trademarks of the Endress+Hauser Group



www.addresses.endress.com

