Technical Information **Proline Promass A 200**

Coriolis flowmeter



Flowmeter with genuine two-wire technology for accurate measurement of smallest flow quantities

Application

- Measuring principle operates independently of physical fluid properties such as viscosity or density
- Suitable for applications with the smallest flow quantities in the chemical industry

Device properties

- Nominal diameter: DN 1 to 4 $(\frac{1}{24} \text{ to } \frac{1}{8})$
- Process pressure: up to 430.9 bar (6250 psi)
- Medium temperature up to +205 °C (+401 °F)
- Loop-powered technology
- Robust dual-compartment housing
- Plant safety: worldwide approvals (SIL, Haz. area)

Your benefits

- Space-saving installation compact, lightweight sensor
- Highest product quality self-drainable measuring tube design available in all line sizes
- Optimum process safety resistant to corrosive ambient conditions and internal clogging
- Convenient device wiring separate connection compartment
- Safe operation no need to open the device due to display with touch control, background lighting
- Integrated verification Heartbeat Technology



Table of contents

About this document	4
Symbols used	4
Function and austom design	E
	.)
	· >
Measuring system	. /
Safety	, 7
Input	. 9
Measured variable	
Measuring range	ģ
Operable flow range	10
Input signal	10
Output	10
Output signal	10
Signal on alarm	12
Load	13
Ex connection data	14
Low flow cut off	17
Galvanic isolation	18
Protocol-specific data	18
Dower supply	10
Torminal aggigment	10
Din assignment device plug	20
	20
Device consumption	20
Current consumption	21
	21
Fower supply failure	21
	22
	25
	28
Ierminais	28
Cable entries	28
Cable specification	28 28
5.	
Performance characteristics	29
Reference operating conditions	29
Maximum measured error	29
Repeatability	30
Response time	31
Influence of ambient temperature	31
Influence of medium temperature	31
Influence of medium pressure	32
Design fundamentals	32
Installation	33
Mounting location	33
Orientation	34
Inlet and outlet runs	34
Special mounting instructions	34
Environment	36
Ambient temperature range	26
Storage temperature	26
	50

Climate class	36 37 37 37 37 37 37
Process Medium temperature range Density Pressure-temperature ratings Sensor housing Rupture disk Flow limit Pressure loss System pressure Thermal insulation Heating Vibrations	37 37 37 41 42 42 42 42 42 42 42 43
Mechanical construction Dimensions in SI units Dimensions in US units Weight Materials Process connections Surface roughness Operability Operating concept Languages Local operation Remote operation Service interface	44 44 54 61 61 64 64 64 65 65 66 68
Certificates and approvals CE mark . C-Tick symbol . Functional safety . Ex approval . Sanitary compatibility . Pharmaceutical compatibility . Pharmaceutical compatibility . Functional safety . HART certification . FOUNDATION Fieldbus certification . Certification PROFIBUS . Additional certification . Other standards and guidelines .	68 69 69 70 70 70 70 70 70 70 70 70
Ordering information	72

Accessories Device-specific accessories Communication-specific accessories Service-specific accessories System components .	73 74 75 75
Documentation	76 76 76
Registered trademarks	77

About this document

Symbols used

Electrical symbols

Symbol	Meaning
	Direct current
\sim	Alternating current
\sim	Direct current and alternating current
÷	Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system.
	Protective Earth (PE) A terminal which must be connected to ground prior to establishing any other connections.
	The ground terminals are situated inside and outside the device:Inner ground terminal: Connects the protectiv earth to the mains supply.Outer ground terminal: Connects the device to the plant grounding system.

Communication symbols

Symbol	Meaning
((:-	Wireless Local Area Network (WLAN) Communication via a wireless, local network.

Symbols for certain types of information

Symbol	Meaning
	Permitted Procedures, processes or actions that are permitted.
	Preferred Procedures, processes or actions that are preferred.
×	Forbidden Procedures, processes or actions that are forbidden.
1	Tip Indicates additional information.
Ĩ	Reference to documentation.
	Reference to page.
	Reference to graphic.
	Visual inspection.

Symbols in graphics

Symbol	Meaning
1, 2, 3,	Item numbers
1., 2., 3.,	Series of steps
A, B, C,	Views
A-A, B-B, C-C,	Sections

Symbol	Meaning
EX	Hazardous area
×	Safe area (non-hazardous area)
≈ →	Flow direction

Function and system design

Measuring principle	The measuring principle is based on the controlled generation of Coriolis forces. These forces are always present in a system when both translational and rotational movements are superimposed.
	$F_c = 2 \cdot \Delta m (v \cdot \omega)$
	$F_c =$ Coriolis force
	$\Delta m = moving mass$
	$\omega = rotational velocity$
	v = radial velocity in rotating or oscillating system
	The amplitude of the Coriolis force depends on the moving mass Δm , its velocity v in the system and thus on the mass flow. Instead of a constant rotational velocity ω , the sensor uses oscillation.
	 In the sensor, an oscillation is produced in the measuring tube. The Coriolis forces produced at the measuring tube cause a phase shift in the tube oscillations (see illustration): If there is zero flow (i.e. when the fluid stands still), the oscillation measured at points A and B has the same phase (no phase difference) (1). Mass flow causes deceleration of the oscillation at the inlet of the tubes (2) and acceleration at the outlet (3).

The phase difference (A-B) increases with increasing mass flow. Electrodynamic sensors register the tube oscillations at the inlet and outlet. The measuring principle operates independently of temperature, pressure, viscosity, conductivity and flow profile.

2

Density measurement

1

The measuring tube is continuously excited at its resonance frequency. A change in the mass and thus the density of the oscillating system (comprising measuring tube and fluid) results in a corresponding, automatic adjustment in the oscillation frequency. Resonance frequency is thus a function of medium density. The microprocessor utilizes this relationship to obtain a density signal.

Volume measurement

Together with the measured mass flow, this is used to calculate the volume flow.

3

Temperature measurement The temperature of the measuring tube is determined in order to calculate the compensation factor due to temperature effects. This signal corresponds to the process temperature and is also available as an output signal.

Measuring system

The device consists of a transmitter and a sensor.

The device is available as a compact version: The transmitter and sensor form a mechanical unit.

Transmitter



Sensor



Safety

IT security

Our warranty is valid only if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the settings.

IT security measures, which provide additional protection for the device and associated data transfer, must be implemented by the operators themselves in line with their security standards.

Device-specific IT security

The device offers a range of specific functions to support protective measures on the operator's side. These functions can be configured by the user and guarantee greater in-operation safety if used correctly. An overview of the most important functions is provided in the following section.

Protecting access via hardware write protection

Write access to the device parameters via the local display or operating tool (e.g. FieldCare, DeviceCare) can be disabled via a write protection switch (DIP switch on the motherboard). When hardware write protection is enabled, only read access to the parameters is possible.

Hardware write protection is disabled when the device is delivered.

Protecting access via a password

A password can be used to protect against write access to the device parameters.

This password locks write access to the device parameters via the local display or another operating tool (e.g. FieldCare, DeviceCare) and, in terms of functionality, is equivalent to hardware write protection. If the service interface CDI RJ-45 is used, read access is only possible if the password is entered.

User-specific access code

Write access to the device parameters via the local display or operating tool (e.g. FieldCare, DeviceCare) can be protected by the modifiable, user-specific access code.

Access via fieldbus

Cyclic fieldbus communication (read and write, e.g. measured value transmission) with a higherorder system is not affected by the restrictions mentioned above.

Input

Measured variable	Direct measured variables	
	Mass flowDensityTemperature	
	Calculated measured variables	
	Volume flowCorrected volume flowReference density	
Monguring range	Monouring ranges for liquids	-

Measuring range

Measuring ranges for liquids

DN		Measuring range full scale values $\dot{m}_{min(F)}$ to $\dot{m}_{max(F)}$	
[mm]	[in]	[kg/h]	[lb/min]
1	1/24	0 to 20	0 to 0.735
2	1/12	0 to 100	0 to 3.675
4	1/8	0 to 450	0 to 16.54

Measuring range for gases

The full scale value depends on the density and the sound velocity of the gas used and can be calculated with the formula below:

 $\dot{m}_{max(G)} = minimum (\dot{m}_{max(F)} \cdot \rho_G : x; \rho_G \cdot c_G \cdot \pi/2 \cdot (d_i)^2 \cdot 3600)$

m _{max(G)}	Maximum full scale value for gas [kg/h]
m _{max(F)}	Maximum full scale value for liquid [kg/h]
$\dot{m}_{\max(G)} < \dot{m}_{\max(F)}$	$\dot{m}_{max(G)}$ can never be greater than $\dot{m}_{max(F)}$
ρ _G	Gas density in [kg/m ³] at operating conditions
х	Constant dependent on nominal diameter
c _G	Sound velocity (gas) [m/s]
d _i	Measuring tube internal diameter [m]

DN		x
[mm]	[in]	[kg/m ³]
1	1/24	32
2	1/12	32
4	1/8	32

i

To calculate the measuring range, use the Applicator sizing tool \rightarrow B 75

Calculation example for gas

- Sensor: Promass A, DN 2
- Gas: Air with a density of 11.9 kg/m³ (at 20 °C and 10 bar)
- Measuring range (liquid): 100 kg/h
- $x = 32 \text{ kg/m}^3$ (for Promass A DN 2)

Maximum possible full scale value:

 $\dot{m}_{max(G)} = \dot{\dot{m}}_{max(F)} \cdot \rho_{G}$: x = 100 kg/h \cdot 11.9 kg/m³ : 32 kg/m³ = 37.2 kg/h

	Recommended measuring range
	"Flow limit" section $\rightarrow \bigoplus 42$
Operable flow range	Over 1000 : 1.
	Flow rates above the preset full scale value do not override the electronics unit, with the result that the totalizer values are registered correctly.
Input signal	External measured values
	To increase the accuracy of certain measured variables or to calculate the corrected volume flow for gases, the automation system can continuously write the operating pressure to the measuring device. Endress+Hauser recommends the use of a pressure measuring device for absolute pressure, e.g. Cerabar M or Cerabar S.
	Yarious pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section → 🗎 75
	It is recommended to read in external measured values to calculate the following measured variables: Mass flow Corrected volume flow
	HART protocol
	The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions: HART protocol Burst mode
	Digital communication
	The measured values can be written from the automation system to the measuring via: FOUNDATION Fieldbus PROFIBUS PA

Output

Output signal

Current output

Current output 1	4-20 mA HART (passive)
Current output 2	4-20 mA (passive)
Resolution	< 1 µA
Damping	Adjustable: 0.0 to 999.9 s
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature

Pulse/frequency/switch output

Function	Can be set to pulse, frequency or switch output
Version	Passive, open collector
Maximum input values	 DC 35 V 50 mA
	For information on the Ex connection values $\rightarrow \triangleq 14$

Voltage drop	 For ≤ 2 mA: 2 V For 10 mA: 8 V
Residual current	≤ 0.05 mA
Pulse output	
Pulse width	Adjustable: 5 to 2 000 ms
Maximum pulse rate	100 Impulse/s
Pulse value	Adjustable
Assignable measured variables	Mass flowVolume flowCorrected volume flow
Frequency output	
Output frequency	Adjustable: 0 to 1 000 Hz
Damping	Adjustable: 0 to 999 s
Pulse/pause ratio	1:1
Assignable measured variables	 Mass flow Volume flow Corrected volume flow Density Reference density Temperature
Switch output	
Switching behavior	Binary, conductive or non-conductive
Switching delay	Adjustable: 0 to 100 s
Number of switching cycles	Unlimited
Assignable functions	 Off On Diagnostic behavior Limit value Mass flow Volume flow Corrected volume flow Density Reference density Temperature Totalizer 1-3 Flow direction monitoring Status Partially filled pipe detection Low flow cut off

FOUNDATION Fieldbus

FOUNDATION Fieldbus	H1, IEC 61158-2, galvanically isolated
Data transfer	31.25 kbit/s
Current consumption	18 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

PROFIBUS PA

PROFIBUS PA	In accordance with EN 50170 Volume 2, IEC 61158-2 (MBP), galvanically isolated
Data transmission	31.25 kbit/s

Current consumption	16 mA
Permitted supply voltage	9 to 32 V
Bus connection	With integrated reverse polarity protection

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output 4 to 20 mA

4 to 20 mA

Failure mode	 Choose from: 4 to 20 mA in accordance with NAMUR recommendation NE 43 4 to 20 mA in accordance with US Min. value: 3.59 mA Max. value: 22.5 mA Freely definable value between: 3.59 to 22.5 mA Actual value Last valid value
--------------	---

Pulse/frequency/switch output

Pulse output	
Failure mode	Choose from: • Actual value • No pulses
Frequency output	
Failure mode	Choose from: • Actual value • 0 Hz • Defined value: 0 to 1250 Hz
Switch output	
Failure mode	Choose from: • Current status • Open • Closed

FOUNDATION Fieldbus

Status and alarm messages	Diagnostics in accordance with FF-891
Failure current FDE (Fault Disconnection Electronic)	0 mA

PROFIBUS PA

Status and alarm messages	Diagnostics in accordance with PROFIBUS PA Profile 3.02
Failure current FDE (Fault Disconnection Electronic)	0 mA

Local display

Plain text display	With information on cause and remedial measures
Backlight	Additionally for device version with SD03 local display: red lighting indicates a device error.

Status signal as per NAMUR recommendation NE 107

Interface/protocol

- Via digital communication:
 - HART protocol
 - FOUNDATION Fieldbus
 - PROFIBUS PA
- Via service interface CDI service interface

Plain text display With information on cause and remedial measures	
--	--

Additional information on remote operation $\rightarrow \square 66$

Load for current output: 0 to 500 Ω , depending on the external supply voltage of the power supply unit

Calculation of the maximum load

Depending on the supply voltage of the power supply unit (U_S), the maximum load (R_B) including line resistance must be observed to ensure adequate terminal voltage at the device. In doing so, observe the minimum terminal voltage

- For $U_S = 17.9$ to 18.9 V: $R_B \le (U_S 17.9 \text{ V})$: 0.0036 A
- For $U_S = 18.9$ to 24 V: $R_B \le (U_S 13 \text{ V}): 0.022 \text{ A}$
- For $U_s = 24$ V: $R_B \le 500 \Omega$



- A Operating range for order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/ frequency/switch output" with Ex i and option C "4-20 mA HART + 4-20 mA analog"
- *B* Operating range for order code for "Output", option A "4-20 mA HART"/option B "4-20 mA HART, pulse/ frequency/switch output" with non-Ex and Ex d

Sample calculation

Supply voltage of power supply unit: $U_S = 19 \text{ V}$ Maximum load: $R_B \le (19 \text{ V} - 13 \text{ V})$: 0.022 A = 273 Ω

Load

Ex connection data

Safety-related values

Type of protection Ex d

Order code for "Output"	Output type	Safety-related values	
Option A	4-20mA HART	$U_{nom} = DC 35 V$ $U_{max} = 250 V$	
Option B	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V	
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$	
Option C	4-20mA HART	U _{nom} = DC 30 V	
	4-20mA analog	U _{max} = 250 V	
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$	
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$	
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$	
	Pulse/frequency/switch output		

1) Internal circuit limited by $R_i = 760.5 \ \Omega$

Type of protection Ex ec

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option C	4-20mA HART	U _{nom} = DC 30 V
	4-20mA analog	$U_{max} = 250 V$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$

1) Internal circuit limited by $R_i = 760.5 \Omega$

Type of protection XP

Order code for "Output"	Output type	Safety-related values
Option A	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
Option B	4-20mA HART	U _{nom} = DC 35 V U _{max} = 250 V
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1}$
Option C	4-20mA HART	$U_{nom} = DC 30 V$
	4-20mA analog	$U_{max} = 250 V$
Option E	FOUNDATION Fieldbus	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$
Option G	PROFIBUS PA	$U_{nom} = DC 32 V$ $U_{max} = 250 V$ $P_{max} = 0.88 W$
	Pulse/frequency/switch output	$U_{nom} = DC 35 V$ $U_{max} = 250 V$ $P_{max} = 1 W^{1)}$

1) Internal circuit limited by R_i = 760.5 Ω

Intrinsically safe values

Type of protection Ex ia

Order code for "Output"	Output type	Intrinsically safe valu	ıes
Option A	4-20mA HART	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; nF \end{array}$	
Option B	4-20mA HART	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; nF \end{array}$	
	Pulse/frequency/switch output	$\begin{array}{l} U_i = DC \; 30 \; V \\ I_i = 300 \; mA \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 6 \; nF \end{array}$	
Option C	4-20mA HART	$U_i = DC 30 V$	
	4-20mA analog	$I_i = 300 \text{ mA}$ $P_i = 1 \text{ W}$ $L_i = 0 \mu \text{H}$ $C_i = 30 \text{ nF}$	
Option E	FOUNDATION Fieldbus	$\begin{array}{lll} STANDARD & FIS \\ U_i = 30 \ V & U_i = \\ l_i = 300 \ mA & l_i = \\ P_i = 1.2 \ W & P_i = \\ L_i = 10 \ \mu H & L_i = \\ C_i = 5 \ nF & C_i = \\ \end{array}$	CO = 17.5 V 550 mA = 5.5 W = 10 μH = 5 nF

Order code for "Output"	Output type	Intrinsically safe values	
	Pulse/frequency/switch output	$\begin{array}{l} U_i = 30 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array}$	
Option G	PROFIBUS PA	$\begin{array}{ll} \text{STANDARD} & \text{FISCO} \\ U_i = 30 \ V & U_i = 17.5 \ V \\ l_i = 300 \ \text{mA} & l_i = 550 \ \text{m} \\ P_i = 1.2 \ W & P_i = 5.5 \ W \\ L_i = 10 \ \mu\text{H} & L_i = 10 \ \mu\text{H} \\ C_i = 5 \ \text{nF} & C_i = 5 \ \text{nF} \end{array}$	/ A
	Pulse/frequency/switch output	$\begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array}$	

Type of protection Ex ic

Order code for "Output"	Output type	Intrinsically safe values	
Option A	4-20mA HART	$\begin{array}{l} U_{i} = DC \ 35 \ V \\ I_{i} = n.a. \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 5 \ nF \end{array}$	
Option B	4-20mA HART	$\begin{array}{l} U_i = DC \; 35 \; V \\ I_i = n.a. \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 5 \; nF \end{array}$	
	Pulse/frequency/switch output	$\begin{array}{l} U_i = DC \; 35 \; V \\ I_i = n.a. \\ P_i = 1 \; W \\ L_i = 0 \; \mu H \\ C_i = 6 \; nF \end{array}$	
Option C	4-20mA HART		
	4-20mA analog		
Option E	FOUNDATION Fieldbus	$\begin{array}{llllllllllllllllllllllllllllllllllll$	
	Pulse/frequency/switch output		

Order code for "Output"	Output type	Intrinsically safe	values
Option G	PROFIBUS PA	STANDARD $U_i = 32 V$ $l_i = 300 mA$ $P_i = n.a.$ $L_i = 10 \mu H$ $C_i = 5 nF$	$\begin{array}{l} FISCO \\ U_i = 17.5 \ V \\ l_i = n.a. \\ P_i = n.a. \\ L_i = 10 \ \mu H \\ C_i = 5 \ nF \end{array}$
	Pulse/frequency/switch output	$\begin{array}{l} U_i = 35 \ V \\ l_i = 300 \ mA \\ P_i = 1 \ W \\ L_i = 0 \ \mu H \\ C_i = 6 \ nF \end{array}$	

Type of protection IS

Order code for "Output"	Output type	Intrinsically safe	values
Option A	4-20mA HART	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $	
Option B	4-20mA HART	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 5 \; nF \end{array} $	
	Pulse/frequency/switch output	$ \begin{array}{l} U_i = DC \; 30 \; V \\ I_i = \; 300 \; mA \\ P_i = \; 1 \; W \\ L_i = \; 0 \; \mu H \\ C_i = \; 6 \; nF \end{array} $	
Option C	4-20mA HART	$U_i = DC 30 V$	
	4-20mA analog	$ \begin{array}{l} I_i = 300 \mbox{ mA} \\ P_i = 1 \mbox{ W} \\ L_i = 0 \mu H \\ C_i = 30 \mbox{ nF} \end{array} $	
Option E	FOUNDATION Fieldbus		$ FISCO \\ U_i = 17.5 V \\ l_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \mu H \\ C_i = 5 nF $
	Pulse/frequency/switch output	$ \begin{array}{l} U_{i} = 30 \ V \\ l_{i} = 300 \ mA \\ P_{i} = 1 \ W \\ L_{i} = 0 \ \mu H \\ C_{i} = 6 \ nF \end{array} $	
Option G	PROFIBUS PA		$FISCO \\ U_i = 17.5 V \\ l_i = 550 mA \\ P_i = 5.5 W \\ L_i = 10 \mu H \\ C_i = 5 nF$
	Pulse/frequency/switch output	$U_{i} = 30 V$ $l_{i} = 300 mA$ $P_{i} = 1 W$ $L_{i} = 0 \mu H$ $C_{i} = 6 nF$	

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

All outputs are galvanically isolated from one another.

Protocol-specific data

Manufacturer ID	0x11
Device type ID	0x54
HART protocol revision	7
Device description files (DTM, DD)	Information and files under: www.endress.com
HART load	 Min. 250 Ω Max. 500 Ω
System integration	For information on system integration, see Operating Instructions.Measured variables via HART protocolBurst Mode functionality

FOUNDATION Fieldbus

HART

Manufacturer ID	0x452B48
Ident number	0x1054
Device revision	1
DD revision	Information and files under:
CFF revision	www.endress.comwww.fieldbus.org
Device Tester Version (ITK version)	6.1.1
ITK Test Campaign Number	IT094200
Link Master capability (LAS)	Yes
Choice of "Link Master" and "Basic Device"	Yes Factory setting: Basic Device
Node address	Factory setting: 247 (0xF7)
Supported functions	The following methods are supported: • Restart • ENP Restart • Diagnostic
Virtual Communication Relationships (VCRs)	
Number of VCRs	44
Number of link objects in VFD	50
Permanent entries	1
Client VCRs	0
Server VCRs	10
Source VCRs	43
Sink VCRs	0
Subscriber VCRs	43
Publisher VCRs	43
Device Link Capabilities	
Slot time	4
Min. delay between PDU	8

Max. response delay	Min. 5
System integration	 For information on system integration, see Operating Instructions. Cyclic data transmission Description of the modules Execution times Methods

PROFIBUS PA

Manufacturer ID	0x11
Ident number	0x155F
Profile version	3.02
Device description files (GSD, DTM, DD)	Information and files under: • www.endress.com • www.profibus.org
Supported functions	 Identification & Maintenance Simple device identification via control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur
Configuration of the device address	 DIP switches on the I/O electronics module Local display Via operating tools (e. g. FieldCare)
System integration	 For information on system integration, see Operating Instructions. Cyclic data transmission Block model Description of the modules

Power supply

Terminal assignment

Transmitter

Connection versions



Order code for "Output"	Terminal numbers			
	Output 1		Output 2	
	1 (+) 2 (-)		3 (+)	4 (-)
Option A	4-20 mA HART (passive)		-	
Option $\mathbf{B}^{(1)}$	4-20 mA HART (passive)		Pulse/frequency/switch output (passive)	
Option $C^{1)}$	4-20 mA HART (passive)		4-20 mA ana	alog (passive)
Option $\mathbf{E}^{(1)(2)}$	FOUNDATION Fieldbus		Pulse/frequenc (pas	y/switch output sive)
Option $\mathbf{G}^{(1)(3)}$	PROFIBUS PA		Pulse/frequenc (pas	y/switch output sive)

1)

Output 1 must always be used; output 2 is optional. FOUNDATION Fieldbus with integrated reverse polarity protection. PROFIBUS PA with integrated reverse polarity protection. 2)

3)

Pin assignment, device plug **PROFIBUS PA**



FOUNDATION Fieldbus

Pin		Assignment	Coding	Plug/socket
1	+	Signal +	А	Plug
2	-	Signal –		
3		Grounding		
4		Not assigned		

Supply voltage

Transmitter

An external power supply is required for each output.

Order code for "Output"	Minimum terminal voltage	Maximum terminal voltage
Option A ^{1) 2)} : 4-20 mA HART	 For 4 mA: ≥ DC 17.9 V For 20 mA: ≥ DC 13.5 V 	DC 35 V
Option B ^{1) 2)} : 4-20 mA HART, pulse/frequency/ switch output	 For 4 mA: ≥ DC 17.9 V For 20 mA: ≥ DC 13.5 V 	DC 35 V
Option C ^{1) 2)} : 4-20 mA HART + 4-20 mA analog	 For 4 mA: ≥ DC 17.9 V For 20 mA: ≥ DC 13.5 V 	DC 30 V

Order code for "Output"	Minimum terminal voltage	Maximum terminal voltage
Option E ³ : FOUNDATION Fieldbus, pulse/ frequency/switch output	≥ DC 9 V	DC 32 V
Option G ³ : PROFIBUS PA, pulse/frequency/switch output	≥ DC 9 V	DC 32 V

1) External supply voltage of the power supply unit with load.

2) For device versions with SD03 local display: The terminal voltage must be increased by DC 2 V if backlighting is used.

3) For device version with SD03 local display: The terminal voltage must be increased by DC 0.5 V if backlighting is used.



For information about the load see $\rightarrow \square 13$

Various power supply units can be ordered from Endress+Hauser: $\rightarrow \square 75$



For information on the Ex connection values \rightarrow 🗎 14

Power consumption

Transmitter

Order code for "Output; input"	Maximum power consumption
Option A: 4-20 mA HART	770 mW
Option B: 4-20 mA HART, pulse/ frequency/switch output	Operation with output 1: 770 mWOperation with output 1 and 2: 2 770 mW
Option C: 4-20 mA HART + 4-20 mA analog	Operation with output 1: 660 mWOperation with output 1 and 2: 1320 mW
Option E: FOUNDATION Fieldbus, pulse/ frequency/switch output	Operation with output 1: 576 mWOperation with output 1 and 2: 2576 mW
Option G: PROFIBUS PA, pulse/frequency/ switch output	Operation with output 1: 512 mWOperation with output 1 and 2: 2512 mW

For information on the Ex connection values $\rightarrow \cong 14$

Current consumption	Current output
	For every 4-20 mA or 4-20 mA HART current output: 3.6 to 22.5 mA
	If the option Defined value is selected in the Failure mode parameter : 3.59 to 22.5 mA
	FOUNDATION Fieldbus
	18 mA
	PROFIBUS PA
	16 mA
Power supply failure	Depending on the device version, the configuration is retained in the device memoryor in the pluggable data memory (HistoROM DAT).

Electrical connection

Connecting the transmitter



1 Cable entry for output 1

2 Cable entry for output 2

Connection examples

Current output 4-20 mA HART



■ 1 Connection example for 4 to 20 mA HART current output (passive)

- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load
- 5 Transmitter

Pulse/frequency output



☑ 2 Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values

Switch output



■ 3 Connection example for switch output (passive)

- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values

FOUNDATION Fieldbus



Connection example for FOUNDATION Fieldbus

- 1 Control system (e.g. PLC)
- 2 Power Conditioner (FOUNDATION Fieldbus)
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line

PROFIBUS PA



🛃 5 Connection example for PROFIBUS PA

- Control system (e.g. PLC) 1
- PROFIBUS PA segment coupler 2
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- Measuring device Local grounding 5
- 6
- Bus terminator 7
- Potential matching line 8

HART input



- ፼ 6 Connection example for HART input with a common negative (passive)
- 1 Automation system with HART output (e.g. PLC)
- Active barrier for power supply (e.g. RN221N) 2
- Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable 3 specifications
- 4 Analog display unit: observe maximum load
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): see requirements
- 6 Transmitter

Electrical connection

Connecting the transmitter



- 1 Cable entry for output 1
- 2 Cable entry for output 2

Connection examples

Current output 4-20 mA HART



- ☑ 7 Connection example for 4 to 20 mA HART current output (passive)
- 1 Automation system with current input (e.g. PLC)
- 2 Power supply
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 Analog display unit: observe maximum load
- 5 Transmitter

Pulse/frequency output



Connection example for pulse/frequency output (passive)

- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values

Switch output



Connection example for switch output (passive)

- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: Observe input values

FOUNDATION Fieldbus



■ 10 Connection example for FOUNDATION Fieldbus

- 1 Control system (e.g. PLC)
- 2 Power Conditioner (FOUNDATION Fieldbus)
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box
- 5 Measuring device
- 6 Local grounding
- 7 Bus terminator
- 8 Potential matching line

PROFIBUS PA



- *11* Connection example for PROFIBUS PA
 - Control system (e.g. PLC)
- PROFIBUS PA segment coupler 2
- 3 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications
- 4 T-box

1

- Measuring device Local grounding 5
- 6
- Bus terminator 7
- 8 Potential matching line

HART input



🖻 12 Connection example for HART input with a common negative (passive)

- 1 Automation system with HART output (e.g. PLC)
- 2 Active barrier for power supply (e.g. RN221N)
- Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable 3 specifications
 - 4 Analog display unit: observe maximum load
- 5 Pressure measuring device (e.g. Cerabar M, Cerabar S): see requirements
- 6 Transmitter

Potential equalization	Requirements				
	No special measures for potential equalization are required.				
	For devices intended for use in hazardous locations, please observe the guidelines in the Ex documentation (XA).				
Terminals	 For device version without int cross-sections 0.5 to 2.5 mm² For device version with integr 0.2 to 2.5 mm² (24 to 14 AW 	egrated overvoltage protection: plug-in spring terminals for wire (20 to 14 AWG) ated overvoltage protection: screw terminals for wire cross-sections G)			
Cable entries	 Cable gland (not for Ex d): M2 Thread for cable entry: For non-hazardous and haz For non-hazardous and haz For Ex d: M20 × 1.5 	 Cable gland (not for Ex d): M20 × 1.5 with cable Ø 6 to 12 mm (0.24 to 0.47 in) Thread for cable entry: For non-hazardous and hazardous areas: NPT ½" For non-hazardous and hazardous areas (not for XP): G ½" For Ex d: M20 × 1.5 			
Cable specification	Permitted temperature range				
	The installation guidelines thatThe cables must be suitable for	at apply in the country of installation must be observed. or the minimum and maximum temperatures to be expected.			
	Signal cable				
	Current output 4 to 20 mA HART				
	A shielded cable is recommende	A shielded cable is recommended. Observe grounding concept of the plant.			
	Current output 4 to 20 mA				
	Standard installation cable is sufficient.				
	Pulse/frequency/switch output				
	Standard installation cable is sufficient.				
	FOUNDATION Fieldbus				
	Twisted, shielded two-wire cable.				
	 Operating Instructions for "FOUNDATION Fieldbus Overview" (BA00013S) FOUNDATION Fieldbus Guideline IEC 61158-2 (MBP) 				
	PROFIBUS PA				
	Twisted, shielded two-wire cable. Cable type A is recommended .				
	For further information on planning and installing PROFIBUS networks see:				
	 Operating Instructions "PROFIBUS DP/PA: Guidelines for planning and commissioning" (BA00034S) PNO Directive 2.092 "PROFIBUS PA User and Installation Guideline" IEC 61158-2 (MBP) 				
Overvoltage protection	The device can be ordered with i Order code for "Accessory mount	integrated overvoltage protection for diverse approvals: ed", option NA "Overvoltage protection"			
	Input voltage range	Values correspond to supply voltage specifications $\rightarrow $ \cong 20 $^{1)}$			
	Resistance per channel	2 · 0.5 Ω max.			
	DC sparkover voltage	400 to 700 V			
	Trip surge voltage	< 800 V			
	Capacitance at 1 MHz	< 1.5 pF			

Nominal discharge current (8/20 µs)	10 kA
Temperature range	-40 to +85 °C (-40 to +185 °F)

1) The voltage is reduced by the amount of the internal resistance $I_{\text{min}} \cdot R_i$



For detailed information on the temperature tables, see the "Safety Instructions" (XA) for the device.

Performance characteristics

-

Reference operating conditions	 Error limits based on ISO 11631 Water with +15 to +45 °C (+59 to +113 °F) at2 to 6 bar (29 to 87 psi) Specifications as per calibration protocol Accuracy based on accredited calibration rigs that are traced to ISO 17025. To obtain measured errors, use the <i>Applicator</i> sizing tool → 75 				
Maximum measured error	o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature			
	Base accuracy	Base accuracy			
	Design fundamentals $\rightarrow \square 32$				
	Mass flow and volume flow (liquids)				
	±0.10 % o.r.				
	Mass flow (gases)				
	±0.35 % o.r.				
	Density (liquids)				
	Under reference operating conditions	Standard density calibration ¹⁾	Wide-range Density specification ^{2) 3)}		
	[g/cm ³]	[g/cm ³]	[g/cm³]		
	+0 0005	+0.02	+0.002		

Valid over the entire temperature and density range 1) 2)

Valid range for special density calibration: 0 to 2 g/cm³, +5 to +80 °C (+41 to +176 °F)

3) Order code for "Application package", option EE "Special density" only in combination with the order code for "Measuring tube mat., wetted surface", option BB, BF, HA, SA

Temperature

±0.5 °C ± 0.005 · T °C (±0.9 °F ± 0.003 · (T – 32) °F)

Zero point stability

Standard version: order code for "Measuring tube mat., wetted surface", option BB, BF, HA, SA

DN		Zero point stability		
[mm]	[in]	[kg/h]	[lb/min]	
1	1/ ₂₄	0.0010	0.000036	
2	1/ ₁₂	0.0050	0.00018	
4	1/8	0.0200	0.00072	

High-pressure version: order code for "Measuring tube mat., wetted surface", option HB

DN		Zero point stability		
[mm]	[in]	[kg/h]	[lb/min]	
1	1/24	0.0016	0.0000576	
2	1/12	0.0080	0.000288	
4	1/8	0.0320	0.001152	

Flow values

Flow values as turndown parameter depending on nominal diameter.

SI units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[mm]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]	[kg/h]
1	20	2	1	0.4	0.2	0.04
2	100	10	5	2	1	0.2
4	450	45	22.5	9	4.5	0.9

US units

DN	1:1	1:10	1:20	1:50	1:100	1:500
[inch]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]	[lb/min]
1/24	0.735	0.074	0.037	0.015	0.007	0.001
1/12	3.675	0.368	0.184	0.074	0.037	0.007
1/8	16.54	1.654	0.827	0.331	0.165	0.033

Accuracy of outputs

The outputs have the following base accuracy specifications.

Current output

Accuracy	±10 µA
----------	--------

Pulse/frequency output

o.r. = of reading

Accuracy	Max. ±100 ppm o.r.

Repeatability

o.r. = of reading; $1 \text{ g/cm}^3 = 1 \text{ kg/l}$; T = medium temperature

	Base repeatability				
	Design fundamentals	→ 🗎 32			
	Mass flow and volume flow	r (liquids)			
	±0.05 % o.r.				
	Mass flow (gases)	Mass flow (gases)			
	±0.15 % o.r.				
	Density (liquids)				
	$\pm 0.00025 \text{ g/cm}^3$				
	Temperature				
	± 0.25 °C $\pm 0.0025 \cdot$ T °C (\pm	0.45 °F ± 0.0015 · (T-32) °F)			
Response time	 The response time deper Response time in the even full scale value 	nds on the configuration (damping). Pent of erratic changes in the measured variable: After 500 ms \rightarrow 95 % of			
Influence of ambient	Current output				
temperature	o.r. = of reading				
	Additional error, in relation	n to the span of 16 mA:			
	Temperature coefficient at zero point (4 mA)	0.02 %/10 K			
	Temperature coefficient with span (20 mA)	0.05 %/10 K			
	Pulse/frequency output o.r. = of reading				
	Max. ±100 ppm o.r.				
Influence of medium	Mass flow and volume flo)W			
temperature	o.f.s. = of full scale value				
	When there is a difference between the temperature for zero point adjustment and the protection temperature, the additional measured error of the sensor is typically $\pm 0.0002 \%$ o.f.s./°C ($\pm 0. f.s./$ °F).				
The effect is reduced if zero point adjustment is performed at process temperature.					
	Density When there is a difference between the density calibration temperature and the process temperature, the typical measured error of the sensor is $\pm 0.00005 \text{ g/cm}^3$ /°C ($\pm 0.000025 \text{ g/cm}^3$ /°F). Field density calibration is possible.				
	Wide-range density specification (special density calibration) If the process temperature is outside the valid range ($\rightarrow \cong 29$) the measured error is ±0.00005 g/cm ³ /°C (±0.000025 g/cm ³ /°F)				



A0021342

Example for maximum measured error

<

BaseAccu



MeasValue

Ε Maximum measured error in % o.r. (example)

Flow rate in % of maximum full scale value Q

A0021344

Installation

No special measures such as supports etc. are necessary. External forces are absorbed by the construction of the device.



Use a sensor holder for additional stability in the process pipe and for non-flanged process connections. $\rightarrow \square 35$

Mounting location



To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

Installation in down pipes

However, the following installation suggestion allows for installation in an open vertical pipeline. Pipe restrictions or the use of an orifice with a smaller cross-section than the nominal diameter prevent the sensor running empty while measurement is in progress.



- 🖻 13 Installation in a down pipe (e.g. for batching applications)
- Supply tank 1
- 2 Sensor
- Orifice plate, pipe restriction 3
- 4 Valve
- 5 Batching tank

DN		Ø orifice plate, pipe restriction	
[mm]	[in]	[mm]	[in]
1	1/24	0.8	0.03
2	1/12	1.5	0.06
4	1⁄8	3.0	0.12

Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

		Orientation				
	A	Vertical orientation	A0015591	√ √ ¹⁾		
	В	Horizontal orientation, transmitter at top	E	✓ ²⁾		
	С	Horizontal orientation, transmitter at bottom	A0015590	⊠ ³⁾		
	D	Horizontal orientation, transmitter at side	A0015592			
	1) Thi 2) Ap min 3) Ap ma	s orientation is recommended to ensure plications with low process temperature nimum ambient temperature for the tra plications with high process temperatur ximum ambient temperature for the tra	e self-draining. s may decrease the ambient temperatur nsmitter, this orientation is recommend es may increase the ambient temperatu nsmitter, this orientation is recommend	re. To maintain the ed. re. To maintain the led.		
Inlet and outlet runs	No specia or T-piec	al precautions need to be taken for res, as long as no cavitation occurs -	fittings which create turbulence, su → 🗎 42.	ch as valves, elbows		
Special mounting instructions	Drainability When the device is installed in a vertical position, the measuring tube can be drained completely and protected against deposit buildup if the properties of the measured liquid allow this. Furthermore, as only one measuring tube is used the flow is not impeded and the risk of product being retained in the measuring device is reduced to a minimum. The larger internal diameter of the measuring tube ¹⁾ also reduces the risk of particles getting trapped in the measuring system. Due to the larger cross-section of the individual measuring tube, the tube is also generally less susceptible to clogging.					
	Rupture disk					
	Information that is relevant to the process: $\rightarrow \cong 42$.					
	 WAR Danger f Medium Take Obse Make insta Do no 	NING from medium escaping! escaping under pressure can cause precautions to prevent danger to p rve information on the rupture disk e sure that the function and operati llation of the device. ot remove or damage the rupture di	injury or material damage. ersons and damage if the rupture di sticker. on of the rupture disk is not impede sk.	isk is actuated. ed through the		
	The position of the rupture disk is indicated on a sticker applied over it. If the rupture disk is triggered, the sticker is destroyed. The disk can therefore be visually monitored.					
	If the sensor holder is used with a measuring device fitted with a rupture disk, it is important to ensure that the opening in the neck is not covered over and that the cover of the rupture disk is not					

damaged.

¹⁾ Compared with the double-tube design with a similar flow capacity with measuring tubes and a smaller internal diameter



1 Rupture disk label

For information on the dimensions: see the "Mechanical construction" section (accessories)

Sensor holder

The sensor holder is used to secure the device to a wall, tabletop or pipe (order code for "Enclosed accessories", option PR).



- 2 x Allen screw M8 x 50, washer and spring washer A4
- 2 1 x clamp (measuring device neck)
- *4 x securing screw for wall, tabletop or pipe mounting (not supplied)*
- 4 1 x base profile

1

- 5 2 x clamp (pipe mounting)
- A Measuring device central line

If the holder is used with a measuring device fitted with a rupture disk, it is important to ensure that the rupture disk in the neck is not covered over and that the cover of the rupture disk is not damaged.

Lubricate all threaded joints prior to mounting. The screws for wall, tabletop or pipe mounting are not supplied with the device and must be chosen to suit the individual installation position.

WARNING

Strain on pipes!

Excessive strain on unsupported pipes can cause the pipe to break.Install the sensor in a pipe that is adequately supported.

The following mounting versions are recommended for the installation:

Using the sensor holder.



1 Sensor holder (order code for "Enclosed accessories", option PR)

Mounting on a wall

Screw the sensor holder to the wall with four screws. Two of the four holes to secure the holder are designed to hook into the screws.

Mounting on a table

Screw the sensor holder onto the tabletop with four screws.

Mounting on a pipe

Secure the sensor holder to the pipe with two clamps.

Zero point adjustment

All measuring devices are calibrated in accordance with state-of-the-art technology. Calibration takes place under reference conditions $\rightarrow \square$ 29. Therefore, a zero point adjustment in the field is generally not required.

Experience shows that zero point adjustment is advisable only in special cases:

- To achieve maximum measuring accuracy even with low flow rates.
- Under extreme process or operating conditions (e.g. very high process temperatures or very high-viscosity fluids).

Environment

Ambient temperature range	Measuring device	-40 to +60 °C (-40 to +140 °F) -20 to +60 °C (-4 to +140 °F) The readability of the display may be impaired at temperatures outside the temperature range.		
	Readability of the local display			
	 If operating outdoors: Avoid direct sunlight, particularly in warm climatic regions. You can order a weather protection cover from Endress+Hauser. → ■ 73. 			
Climate class DIN EN 60068-2-38 (test Z/AD)		AD)		
	m			
----------------------	---			
Degree of protection	Transmitter			
	• As standard: IP66/6/, type 4X enclosure			
	 When housing is open: IP20, type 1 enclosure 			
	 Display module: IP20, type 1 enclosure 			
	Sensor			
	IP66/67, type 4X enclosure			
	Connector			
	IP67, only in screwed situation			
Vibration resistance	 Oscillation, sinusoidal, following IEC 60068-2-6 			
	– 2 to 8.4 Hz, 3.5 mm peak			
	– 8.4 to 2 000 Hz, 1 g peak			
	 Oscillation, broadband noise following IEC 60068-2-64 			
	– 10 to 200 Hz, 0.003 g ² /Hz			
	– 200 to 2 000 Hz, 0.001 g²/Hz			
	– Total: 1.54 g rms			
Shock resistance	Shock, half-sine according to IEC 60068-2-27			
	6 ms 30 g			
Shock resistance	Shock due to rough handling following IEC 60068-2-31			
Interior cleaning	 Cleaning in place (CIP) 			
	 Sterilization in place (SIP) 			
	Options			
	Oil- and grease-free version for wetted parts, without declaration			
	Order code for "Service", option HA			
Electromagnetic	As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)			
compatibility (EMC)	Details are provided in the Declaration of Conformity.			

Process

Medium temperature range	-50 to +205 °C (-58 to +401 °F)
Density	0 to 2 000 kg/m ³ (0 to 125 lb/cf)
Pressure-temperature ratings	The following pressure/temperature diagrams apply to all pressure-bearing parts of the device and not just the process connection. The diagrams show the maximum permissible medium pressure depending on the specific medium temperature.



Flange connection according to EN 1092-1 (DIN 2501)





■ 15 With flange material: Alloy C22, 2.4602 (UNS N06022)





Flange connection according to ASME B16.5



🖻 17 With flange material: 1.4404 (316/316L)



🖻 18 With flange material: Alloy C22, 2.4602 (UNS N06022)



■ 19 Lap joint flange with flange material: 1.4301 (F304), wetted parts Alloy C22: 2.4602 (UNS N06022)

Flange connection according to JIS B2220



20 With flange material: 1.4404 (316/316L) or Alloy C22, 2.4602 (UNS N06022)



■ 21 Lap joint flange with flange material: 1.4301 (F304), wetted parts Alloy C22: 2.4602 (UNS N06022)

Tri-Clamp process connection

The clamp connections are suitable up to a maximum pressure of 40 bar (580 psi). Please observe the operating limits of the clamp and seal used as they could be under 40 bar (580 psi). The clamp and seal are not included in the scope of supply.

Process connection 4-VCO-4, NPT ¼", G ¼"







■ 23 With flange material: Alloy C22, 2.4602 (UNS N06022)

Order code for "Measuring tube mat., wetted surface", option HB



24 With flange material: Alloy C22, 2.4602 (UNS N06022)

Sensor housing

The sensor housing is filled with dry nitrogen gas and protects the electronics and mechanics inside.

If a measuring tube fails (e.g. due to process characteristics like corrosive or abrasive fluids), the fluid will initially be contained by the sensor housing.

In the event of a tube failure, the pressure level inside the sensor housing will rise according to the operating process pressure. If the user judges that the sensor housing pressure rating/burst pressure does not provide an adequate safety margin, the device can be fitted with a rupture disk. This prevents excessively high pressure from forming inside the sensor housing. Therefore, the use of a rupture disk is strongly recommended in applications involving high gas pressures, and particularly in applications in which the process pressure is greater than 2/3 of the sensor housing burst pressure.



High-pressure devices are always fitted with a rupture disk: order code for "Measuring tube mat., wetted surface", option HB

Sensor housing nominal pressure rating and burst pressure

If the device is fitted with a rupture disk (order code for "Sensor option", option CA "Rupture disk"), the rupture disk trigger pressure is decisive for the maximum nominal pressure .

The sensor housing burst pressure refers to a typical internal pressure which is reached prior to mechanical failure of the sensor housing and which was determined during type testing. The corresponding type test declaration can be ordered with the device (order code for "Additional approval", option LN "Sensor housing burst pressure, type test").

DN		Sensor housing nominal pressure (designed with a safety factor ≥ 4)		Sensor housing burst pressure				
[mm]	[in]	[bar]	[psi]	[bar]	[psi]			
1	¹ / ₂₄	25	362	100	1450			
2	1/12	25	362	100	1450			
4	1/8	25	362	100	1450			
 To increase the level of safety, a device version with a rupture disk with a trigger pressure of 10 to 15 bar (145 to 217.5 psi)can be used (order code for "Sensor option", option CA "rupture disk"). If High-pressure devices are always fitted with a rupture disk: order code for "Measuring tube mat., wetted surface", option HB								
Select the nominal diameter by optimizing between the required flow range and permissible pressure loss.								
For an over section \rightarrow	erview of the ful 9	l scale values fo	r the measuring	range, see the "Mea	asuring range"			
 The minimum In most appli	n recommended cations, 20 to 5	l full scale value 0 % of the maxi	is approx. 1/20 mum full scale v	of the maximum fu value can be conside	ıll scale value ered ideal			

- A low full scale value must be selected for abrasive media (such as liquids with entrained solids): flow velocity < 1 m/s (< 3 ft/s).
- For gas measurement the following rules apply:
 - The flow velocity in the measuring tubes should not exceed half the sound velocity (0.5 Mach).
- The maximum mass flow depends on the density of the gas: formula \rightarrow 🗎 9

To calculate the pressure loss, use the Applicator sizing tool \rightarrow 🗎 75

To calculate the flow limit, use the Applicator sizing tool $\rightarrow \square 75$

Pressure loss

System pressure

Rupture disk

Flow limit

-

It is important that cavitation does not occur, or that gases entrained in the liquids do not outgas. This is prevented by means of a sufficiently high system pressure.

For this reason, the following mounting locations are recommended:

• At the lowest point in a vertical pipe

Downstream from pumps (no danger of vacuum)



Thermal insulation

In the case of some fluids, it is important to keep the heat radiated from the sensor to the transmitter to a low level. A wide range of materials can be used for the required insulation.

NOTICE

Electronics overheating on account of thermal insulation!

- Recommended orientation: horizontal orientation, transmitter housing pointing downwards.
- ▶ Do not insulate the transmitter housing .
- ▶ Maximum permissible temperature at the lower end of the transmitter housing: 80 °C (176 °F)
- Thermal insulation with extended neck free: the insulation is omitted around the extended neck. We recommend that you do not insulate the extended neck in order to ensure optimum dissipation of heat.



25 Thermal insulation with extended neck free

Heating

Some fluids require suitable measures to avoid loss of heat at the sensor.

Heating options

- Electrical heating, e.g. with electric band heaters
- Via pipes carrying hot water or steam
- Via heating jackets



NOTICE

Danger of overheating when heating

- ► Ensure that the temperature at the lower end of the transmitter housing does not exceed 80 °C (176 °F).
- Ensure that sufficient convection takes place at the transmitter neck.
- Ensure that a sufficiently large area of the transmitted neck remains exposed. The uncovered part serves as a radiator and protects the electronics from overheating and excessive cooling.

Vibrations

The high oscillation frequency of the measuring tubes ensures that the correct operation of the measuring system is not influenced by plant vibrations.

Mechanical construction



Compact version



Dimensions for version without overvoltage protection

Order code for "Housing", options B "GT18 dual compartment, 316L", C "GT20 dual compartment aluminum coated"

DN [mm]	A ¹⁾ [mm]	B [mm]	C ¹⁾ [mm]	D [mm]	E ²⁾ [mm]	F ²⁾ [mm]	G ³⁾ [mm]	H ³⁾ [mm]	I [mm]	K [mm]	L [mm]	M [mm]
1	165	75	90	54	279	333	162	102	60	9.1	4)	34
2	165	75	90	74	301	375	162	102	60	9.1	4)	48
4	165	75	90	90	316	406	162	102	60	9.1	4)	51

For versions with overvoltage protection (OVP): values + 8 mm 1)

1) 2) 3) 4) For version without local display: values - 3 mm

For version without local display: values - 7 mm Dependent on the respective process connection

Threaded glands

VCO coupling



Length tolerance for dimension L in mm: +1.5 / -2.0

4-VCO-4

Order code for "Process connection", option HAW

1.4435 (316/316L): order code for "Measuring tube mat., wetted surface", option BB, BF, SA Alloy C22: order code for "Measuring tube mat., wetted surface", option HA

Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [mm]	A [in]	E [m	L [mm]	
		Option BB, BF, HA, SA	Option HB	
1	AF 11/16	1.1	1	187
2	AF 11/16	2.5	2.1	264
4	AF 11/16	3.9	3.2	310



G ¼ "

Order code for "Process connection", option G06

1.4404 (316L): order code for "Measuring tube mat., wetted surface", option SA

Alloy C22: order code for "Measuring tube mat., wetted surface", option HA

Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [mm]	A [mm]		B [in]	C [mm]	L [mm]
	Option HA, SA	Option HB			
1	22.5	25	G ¼ "	AF 21	257
2	22.5	25	G ¼ "	AF 21	334
4	22.5	25	G ¼ "	AF 21	380

NPT 1/4 "

Order code for "Process connection", option P06 1.4404 (316L): order code for "Measuring tube mat., wetted surface", option SA Alloy C22: order code for "Measuring tube mat., wetted surface", option HA Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [mm]	A [mm]		B [in]	C [mm]	L [mm]
	Option HA, SA	Option HB	-		
1	22.5	25	NPT ¼ "	AF 19	257
2	22.5	25	NPT ¼ "	AF 19	334
4	22.5	25	NPT 1⁄4 "	AF 19	380

Clamp connections

Tri-Clamp



Length tolerance for dimension L in mm: +1.5 / -2.0i

½" Tri-Clamp Order code for "Process connection", option FBW 1.4435 (316L): order code for "Measuring tube mat., wetted surface", option BB, BF, SA									
DN [mm]	A [mm]	B [mm]	L [mm]						
1	25	9.5	193						
2	25	9.5	270						
4	25	9.5	316						

3-A version (Ra \leq 0.76 μ m/30 μ in, Ra \leq 0.38 μ m/15 μ in) available: Order code for "Measuring tube mat., wetted surface", option BB, BF in conjunction with order code for "Additional approval" , option LP

Flange connections

Fixed flange EN 1092-1, ASME B16.5, JIS B2220



Length tolerance for dimension L in mm: +1.5 / -2.0

Flange according to EN 1092-1 (DIN 2501 / DIN 2512N), PN 40 1.4404 (F316/F316L): order code for "Process connection", option D2S Alloy C22: order code for "Process connection", option D2C

Flange with groove according to EN 1092-1 Form D (DIN 2512N), PN 40 1.4404 (F316/F316L): order code for "Process connection", option D6S Alloy C22: order code for "Process connection", option D6C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
1	95	65	4 × Ø14	16	17.3	262
2	95	65	4 × Ø14	16	17.3	339
4	95	65	4 × Ø14	16	17.3	385
Surface rough	ess (flange): EN	[1092-1 Form F	31 (DIN 2526 Form	n C) Ra 3 2 to 1	2.5 µm	

Flange according to EN 1092-1 (DIN 2501 / DIN 2512N), PN 100 1.4404 (F316/F316L): order code for "Process connection", option D4S Alloy C22: order code for "Process connection", option D4C

Flange with groove according to EN 1092-1 Form D (DIN 2512N), PN 100 1.4404 (F316/F316L): order code for "Process connection", option D8S Alloy C22: order code for "Process connection", option D8C

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
1	105	75	$4 \times Ø14$	20	17.3	292
2	105	75	$4 \times Ø14$	20	17.3	369
4	105	75	$4 \times Ø14$	20	17.3	415
Surface roughn	iess (flange): EN	1092-1 Form E	31 (DIN 2526 Form	n C), Ra 3.2 to 1	2.5 µm	

Flange according to EN 1092-1 (DIN 2501 / DIN 2512N), PN 400 1.4404 (F316/F316L): order code for "Process connection", option DNS Alloy C22: order code for "Process connection", option DNC

Flange with groove according to EN 1092-1 Form D (DIN 2512N), PN 400 1.4404 (F316/F316L): order code for "Process connection", option DPS Alloy C22: order code for "Process connection", option DPC

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]
1	145	100	4 × Ø22	30	17.3	336
2	145	100	4 × Ø22	30	17.3	413
4	145	100	4 × Ø22	30	17.3	459
	(6)) =>					

Surface roughness (flange): EN 1092-1 Form B1 (DIN 2526 Form C), Ra 3.2 to 12.5 μm

Flange according to ASME B16.5, Class 150 RF, Schedule 40 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
1	90	60.3	4 × Ø15.9	11.6	15.7	262			
2	90	60.3	4 × Ø15.9	11.6	15.7	339			
4	90	60.3	4 × Ø15.9	11.6	15.7	385			
Surface rough	(flange), D								

Surface roughness (flange): Ra 3.2 to 6.3 µm

Flange according to ASME B16.5, Class 300 RF, Schedule 40 1.4404 (F316/F316L): order code for "Process connection", option ABS Alloy C22: order code for "Process connection", option ABC									
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]			
1	95	66.7	4 × Ø15.9	14.7	15.7	262			
2	95	66.7	4 × Ø15.9	14.7	15.7	339			
4	95 66.7 4 × Ø15.9 14.7 15.7 385								

Surface roughness (flange): Ra 3.2 to 6.3 μ m

Flange according to ASME B16.5, Class 600 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ACS Alloy C22: order code for "Process connection", option ACC

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
1	95	66.7	4 × Ø15.9	21.3	13.9	292				
2	95	66.7	4 × Ø15.9	21.3	13.9	369				
4	95	66.7	4 × Ø15.9	21.3	13.9	415				
Surface rough	Surface roughness (flange): Ra 3.2 to 6.3 μm									

Flange according to ASME B16.5, Class 900/1500 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ARS Alloy C22: order code for "Process connection", option ARC Flange according to ASME B16.5, Class 900/1500 RTJ, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ASS Alloy C22: order code for "Process connection", option ASC DN А в С D Ε L. [mm] [mm] [mm] [mm] [mm] [mm] [mm] $4 \times Ø22^{1}$ 1 120 82.6 29.3 14 324 $4 \times Ø22^{1)}$ 120 2 82.6 29.3 14 401 120 82.6 $4 \times Ø22^{1}$ 29.3 447 4 14 Surface roughness (flange): Ra 3.2 to 6.3 μ m

1) option ARC/ARS: 4 × Ø22.2

Flange according to ASME B16.5, Class 2500 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ATS Alloy C22: order code for "Process connection", option ATC

Flange according to ASME B16.5, Class 2500 RTJ, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option AUS Alloy C22: order code for "Process connection", option AUC

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
1	135	88.9	4ר22.2	37.2	14	351				
2	135	88.9	4ר22.2	37.2	14	428				
4	135	88.9	4 × Ø22.2	37.2	14	474				
Surface rough										

Surface roughness (flange): Ra 3.2 to 6.3 µm

Flange JIS B2220, 20K 1.4404 (F316/F316L): order code for "Process connection", option NES Alloy C22: order code for "Process connection", option NEC

DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
1	95	70	4 × Ø15	14	15	262				
2	95	70	4 × Ø15	14	15	339				
4	95	70	4 × Ø15	14	15	385				
Surface rough										

Surface roughness (flange): Ra 3.2 to 6.3 µm

Flange JIS B22 1.4404 (F316) Alloy C22: ord	Flange JIS B2220, 40K 1.4404 (F316/F316L): order code for "Process connection", option NGS Alloy C22: order code for "Process connection", option NGC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]					
1	115	80	4 × Ø19	20	15	292					
2	115	80	4 × Ø19	20	15	369					
4	115	80	4ר19	20	15	415					
Surface roughr	Surface roughness (flange): Ra 3.2 to 6.3 µm										

Flange JIS B2220, 63K 1.4404 (F316/F316L): order code for "Process connection", option NHS Alloy C22: order code for "Process connection", option NHC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	L [mm]				
1	120	85	4 × Ø19	23	12	312				
2	120 85 4ר19 23 12 389									
4	120	85	4 × Ø19	23	12	435				
Surface roughr	Surface roughness (flange): Ra 3.2 to 6.3 µm									

Lap joint flange EN 1092-1, ASME B16.5, JIS B2220





Length tolerance for dimension L in mm: +1.5 / -2.0

Lap joint fla 1.4301 (F30	Lap joint flange according to EN 1092-1 Form D: PN 40 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option DAC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]				
1	95	65	4 × Ø14	14.5	45	17.3	262				
2	95	65	4 × Ø14	14.5	45	17.3	339				
4	95	65	4 × Ø14	14.5	45	17.3	385				
Surface roug	Surface roughness (flange): Ra 3.2 to 12.5 µm										

Lap joint flange according to ASME B16.5: Class 150, Schedule 40 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option ADC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]			
1	90	60.3	4 × Ø15.9	15	35.1	15.7	262			
2	90	60.3	4 × Ø15.9	15	35.1	15.7	339			
4	90	60.3	4 × Ø15.9	15	35.1	15.7	385			
Surface roug	hnose (flange	$\mathbf{V} \mathbf{P}_2 2 2 \mathbf{t}_2 1^{\dagger}$	2 5 um							

Surface roughness (flange): Ra 3.2 to 12.5 μm

Lap joint f 1.4301 (F3	Lap joint flange according to ASME B16.5: Class 300, Schedule 40 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option AEC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]	L _{diff} ¹⁾ [mm]			
1	95	66.7	4 × Ø15.9	16.5	35.1	15.7	268	+6			
2	95	66.7	4 × Ø15.9	16.5	35.1	15.7	245	+6			
4	95	66.7	4 × Ø15.9	16.5	35.1	15.7	391	+6			
Surface rou	ıghness (fla	nge): Ra 3.2	to 12.5 µm								

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

Lap joint fla 1.4301 (F30	Lap joint flange according to ASME B16.5: Class 600, Schedule 80 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option AFC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]				
1	95	66.7	4 × Ø15.9	17	35.1	13.9	292				
2	95	66.7	4 × Ø15.9	17	35.1	13.9	369				
4	95	66.7	4 × Ø15.9	17	35.1	13.9	415				
Surface roug	hness (flange	$\mathbf{h} \cdot \mathbf{R} = 3 2 \mathbf{t} 0 1$	2 5 um								

Surface roughness (flange): Ra 3.2 to 12.5 μ m

Lap joint fla 1.4301 (F30	Lap joint flange JIS B2220: 20K 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option NIC										
DN [mm]	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	L [mm]				
1	95	70	4 × Ø15	14	51	15	262				
2	95	70	4 × Ø15	14	51	15	339				
4	95	70	4 × Ø15	14	51	15	385				
Surface roug	Surface roughness (flange): Ra 3.2 to 12.5 µm										

Accessories

Sensor holder



A	B	C	D	E	F	G
[mm]						
106	117	18	70	23.5	21	23

H	I	K	L	M	N	0
[mm]						
62	12	90	120	92	9	15

Dimensions in US units

Compact version



Dimensions for version without overvoltage protection

Order code for "Housing", options B "GT18 dual compartment, 316L", C "GT20 dual compartment aluminum coated"

DN [in]	A ¹⁾ [in]	B [in]	C ¹⁾ [in]	D [in]	E ²⁾ [in]	F ²⁾ [mm]	G ³⁾ [in]	H ³⁾ [in]	I [in]	K [in]	L [in]	M [in]
1/24	6.5	2.95	3.54	2.13	10.98	13.11	6.38	4.02	2.36	0.36	4)	1.34
1/12	6.5	2.95	3.54	2.91	11.85	14.76	6.38	4.02	2.36	0.36	4)	1.89
1/8	6.5	2.95	3.54	3.54	12.44	15.98	6.38	4.02	2.36	0.36	4)	2.01

For versions with overvoltage protection (OVP): values + 0.31 in For version without local display: values - 0.11 in 1)

2)

3) 4)

For version without local display: values - 0.28 in Dependent on the respective process connection

Threaded glands

VCO coupling



Length tolerance for dimension L in inch: +0.06 / -0.08 $\,$

4-VCO-4

-

Order code for "Process connection", option HAW

1.4435 (316/316L): order code for "Measuring tube mat., wetted surface", option BB, BF, SA Alloy C22: order code for "Measuring tube mat., wetted surface", option HA

Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [in]	A [in]	B [in]		L [in]
		Option BB, BF, HA, SA	Option HB	
1/ ₂₄	AF 11/16	0.04	0.04	7.36
1/ ₁₂	AF 11/16	0.1	0.08	10.39
1/8	AF 11/16	0.15	0.13	12.2



G ¼ "

Order code for "Process connection", option G06

1.4404 (316L): order code for "Measuring tube mat., wetted surface", option SA

Alloy C22: order code for "Measuring tube mat., wetted surface", option HA

Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [in]	A [in]		B [in]	C [in]	L [in]
	Option HA, SA	Option HB			
1/24	0.89	0.98	G ¼ "	AF ¹³ / ₁₆ "	10.12
1/12	0.89	0.98	G ¼ "	AF ¹³ / ₁₆ "	13.15
1/8	0.89	0.98	G ¼ "	AF ¹³ / ₁₆ "	14.96

NPT 1/4 "

Order code for "Process connection", option P06 1.4404 (316L): order code for "Measuring tube mat., wetted surface", option SA Alloy C22: order code for "Measuring tube mat., wetted surface", option HA Alloy C22, high pressure: order code for "Measuring tube mat., wetted surface", option HB

DN [in]	A [in]		B [in]	C [in]	L [in]
	Option HA, SA	Option HB			
1/24	0.89	0.98	NPT ¼ "	AF 3/4 "	10.12
1/12	0.89	0.98	NPT ¼ "	AF 3/4 "	13.15
1/8	0.89	0.98	NPT 1⁄4 "	AF 3⁄4 "	14.96

Clamp connections

Tri-Clamp





Length tolerance for dimension L in inch: +0.06 / -0.08 $\,$

¹ / ₂ " Tri-Clamp Order code for "Process connection", option FBW 1.4435 (316L): order code for "Measuring tube mat., wetted surface", option BB, BF, SA							
DN [in]	A [in]	B [in]	L [in]				
1/24	0.98	0.37	7.6				
1/12	0.98	0.37	10.63				
1/8	0.98	0.37	12.44				

3-A version (Ra \leq 0.76 μ m/30 μ in, Ra \leq 0.38 μ m/15 μ in) available: Order code for "Measuring tube mat., wetted surface", option BB, BF in conjunction with order code for "Additional approval" , option LP

Flange connections

i

Fixed flange ASME B16.5



Length tolerance for dimension L in inch: +0.06 / -0.08

Flange according to ASME B16.5, Class 150 RF, Schedule 40 1.4404 (F316/F316L): order code for "Process connection", option AAS Alloy C22: order code for "Process connection", option AAC

DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1/24	3.54	2.37	4 × Ø0.63	0.46	0.62	10.31
1/12	3.54	2.37	4 × Ø0.63	0.46	0.62	13.35
1/8	3.54	2.37	4 × Ø0.63	0.46	0.62	15.16
Surface rough	anoss (flango):	Po 2 2 to 6 2 u	m			

Surface roughness (flange): Ra 3.2 to 6.3 μm

 Flange according to ASME B16.5, Class 300 RF, Schedule 40

 1.4404 (F316/F316L): order code for "Process connection", option ABS

 Alloy C22: order code for "Process connection", option ABC

 DN
 A

 B
 C
 D

 E
 D

[in]	[in]	[in]	[in]	[in]	[in]	[in]		
1/24	3.74	2.63	4 × Ø0.63	0.58	0.62	10.31		
1/12	3.74	2.63	4 × Ø0.63	0.58	0.62	13.35		
1/8	3.74	2.63	4 × Ø0.63	0.58	0.62	15.16		
Surface roughness (flange): Ra 3.2 to 6.3 µm								

Flange according to ASME B16.5, Class 600 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ACS Alloy C22: order code for "Process connection", option ACC							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]	
1/24	3.74	2.63	4 × Ø0.63	0.84	0.55	11.5	
1/12	3.74	2.63	4 × Ø0.63	0.84	0.55	14.53	
1/8	3.74	2.63	4 × Ø0.63	0.84	0.55	16.34	
Surface roug	nness (flange):	Ra 3.2 to 6.3 µ	m				

Flange according to ASME B16.5, Class 900/1500 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ARS Alloy C22: order code for "Process connection", option ARC

Flange according to ASME B16.5, Class 900/1500 RTJ, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ASS Alloy C22: order code for "Process connection", option ASC

DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1/24	4.72	3.25	4 × Ø0.87	1.15	0.55	12.76
1/12	4.72	3.25	4 × Ø0.87	1.15	0.55	15.79
1/8	4.72	3.25	4 × Ø0.87	1.15	0.55	17.6

Surface roughness (flange): Ra 3.2 to 6.3 μ m

Flange according to ASME B16.5, Class 2500 RF, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option ATS Alloy C22: order code for "Process connection", option ATC

Flange according to ASME B16.5, Class 2500 RTJ, Schedule 80 1.4404 (F316/F316L): order code for "Process connection", option AUS Alloy C22: order code for "Process connection", option AUC

DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	L [in]
1/24	5.31	3.5	4 × Ø0.87	1.46	0.55	13.82
1/12	5.31	3.5	4 × Ø0.87	1.46	0.55	16.85
1⁄8	5.31	3.5	4ר0.87	1.46	0.55	18.66

Surface roughness (flange): Ra 3.2 to 6.3 µm

Lap joint flange ASME B16.5



i

Length tolerance for dimension L in mm: +1.5 / -2.0

Lap joint flange according to ASME B16.5: Class 150, Schedule 40 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option ADC									
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]		
1/24	3.54	2.37	4 × Ø0.63	0.59	1.65	0.62	10.31		
1/ ₁₂	3.54	2.37	4 × Ø0.63	0.59	1.65	0.62	13.35		
1/8	3.54	2.37	4 × Ø0.63	0.59	1.65	0.62	15.16		
Surface roug	hness (flange	e): Ra 3.2 to 1	2.5 µm						

Lap joint flange according to ASME B16.5: Class 300, Schedule 40 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option AEC								
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]	L _{diff} ¹⁾ [in]
1/ ₂₄	3.74	2.63	4 × Ø0.63	0.65	1.77	0.62	10.55	0.24
1/12	3.74	2.63	4 × Ø0.63	0.65	1.77	0.62	9.65	0.24
1/8	3.74	2.63	4 × Ø0.63	0.65	1.77	0.62	15.39	0.24
Surface rou								

Surface roughness (flange): Ra 3.2 to 12.5 μm

1) Difference to installation length of the welding neck flange (order code for "Process connection", option AAC)

Lap joint flange according to ASME B16.5: Class 600, Schedule 80 1.4301 (F304), wetted parts Alloy C22: order code for "Process connection", option AFC							
DN [in]	A [in]	B [in]	C [in]	D [in]	E [in]	F [in]	L [in]
1/24	3.74	2.63	4 × Ø15.9	0.67	1.89	0.55	11.5
1/12	3.74	2.63	4 × Ø15.9	0.67	1.89	0.55	14.53
1/8	3.74	2.63	4 × Ø15.9	0.67	1.89	0.55	16.34
Surface roug	Surface roughness (flange): Ra 3.2 to 12.5 µm						

Accessories

Sensor holder



A	B	C	D	E	F	G
[in]						
4.17	4.6	0.7	2.4	0.9	0.83	0.9

H	I	K	L	M	N	0
[in]						
2.4	0.5	3.54	4.7	3.6	0.35	0.6

Weight

All values (weight exclusive of packaging material) refer to devices with EN/DIN PN 40 flanges.

Weight in SI units

DN	Weight [kg]				
[mm]	Order code for "Housing", option C "GT20 dual compartment, aluminum, coated, compact"	Order code for "Housing", option B "GT18 dual compartment, 316L, compact"			
1	5.5	8.2			
2	7.1	9.8			
4	9	11.7			

Weight in US units

DN	Weight [lbs]				
[in]	Order code for "Housing", option C "GT20 dual compartment, aluminum, coated, compact"	Order code for "Housing", option B "GT18 dual compartment, 316L, compact"			
1/24	12	18			
1/12	16	22			
1/8	20	26			

Materials

Transmitter housing

- Order code for "Housing", option B "Compact, stainless":
 - Stainless steel CF-3M (316L, 1.4404)
- Order code for "Housing", option C "Compact, aluminum coated": Aluminum, AlSi10Mg, coated
- Window material: glass

Cable entries/cable glands



■ 26 Possible cable entries/cable glands

- 1 Female thread M20 × 1.5
- 2 Cable gland M20 × 1.5
- 3 Adapter for cable entry with internal thread G $\frac{1}{2}$ or NPT $\frac{1}{2}$
- 4 Device plugs

Order code for "Housing", option B "GT18 dual compartment, 316L"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	 Non-Ex Ex ia Ex ic Ex nA Ex tb 	Stainless steel ,1.4404
Adapter for cable entry with internal thread G ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Stainless steel, 1.4404 (316L)
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex	

Order code for "Housing", option C "GT20 dual compartment, aluminum coated"

Cable entry/cable gland	Type of protection	Material
Cable gland M20 × 1.5	Non-ExEx iaEx ic	Plastic
	Adapter for cable entry with internal thread G ½"	Nickel-plated brass
Adapter for cable entry with internal thread NPT ½"	For non-Ex and Ex (except for CSA Ex d/XP)	Nickel-plated brass
Thread NPT ½" via adapter	For non-Ex and Ex	

Device plug

Electrical connection	Material
Plug M12x1	 Socket: stainless steel, 1.4401/316 Contact housing: plastic, PUR, black Contacts: metal, CuZn, gold-plated Threaded connection seal: NBR

Sensor housing

- Acid and alkali-resistant outer surface
- Stainless steel, 1.4404 (316L)

Measuring tubes

Order code for "Measuring tube mat., wetted surface", option BB, BF, SA

Stainless steel, 1.4435 (316/316L)

Order code for "Measuring tube mat., wetted surface", option HA, HB

Alloy C22, 2.4602 (UNS N06022)

Process connections

Order code for "Measuring tube mat., wetted surface", option SA

VCO coupling	Stainless steel, 1.4404 (316/316L)
G¼" internal thread	Stainless steel, 1.4404 (316/316L)
NPT¼" internal thread	Stainless steel, 1.4404 (316/316L)
Tri-Clamp ¹ /2"	Stainless steel, 1.4435 (316L)
Fixed flange EN 1092-1, ASME B16.5, JIS B2220	Stainless steel, 1.4404 (316/316L)

Order code for "Measuring tube mat., wetted surface", option BB, BF

Order code for "Measuring tube mat., wetted surface", option HA

VCO coupling	Alloy C22, 2.4602 (UNS N06022)
G¼" internal thread	Alloy C22, 2.4602 (UNS N06022)
NPT¼" internal thread	Alloy C22, 2.4602 (UNS N06022)
Fixed flange EN 1092-1, ASME B16.5, JIS B2220	Alloy C22, 2.4602 (UNS N06022)
Lap joint flange EN 1092-1, ASME B16.5, JIS B2220	Stainless steel, 1.4301 (F304), wetted parts Alloy C22, 2.4602 (UNS N06022)

Order code for "Measuring tube mat., wetted surface", option HB (high-pressure option)

VCO coupling	Alloy C22, 2.4602 (UNS N06022)
G¼" internal thread	Alloy C22, 2.4602 (UNS N06022)
NPT¼" internal thread	Alloy C22, 2.4602 (UNS N06022)
Fixed flange EN 1092-1, ASME B16.5, JIS B2220	Stainless steel, 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)



Available process connections \rightarrow 🗎 64

Seals

Welded process connections without internal seals

	Accessories
	Sensor holder
	Stainless steel, 1.4404 (316L)
	Heating jacket
	 Heating jacket housing: stainless steel, 1.4571 (316Ti) NPT adapter ½": stainless steel, 1.4404 (316) G½" adapter: stainless steel, 1.4404
	Protective cover
	Stainless steel, 1.4404 (316L)
	Remote display FHX50
	Housing material: • Plastic PBT • Stainless steel CF-3M (316L, 1.4404)
Process connections	 Fixed flange connections: EN 1092-1 (DIN 2501) flange EN 1092-1 (DIN 2512N) flange ASME B16.5 flange JIS B2220 flange Clamp connections: Tri-Clamp (OD tubes), DIN 11866 series C VCO connections: 4-VCO-4 Internal thread: Cylindrical internal thread BSPP (G) in accordance with ISO 228-1 with sealing surfaces in accordance with DIN 3852-2/ISO 1179-1 NPT Process connection materials → 63
Surface roughness	All data relate to parts in contact with fluid. The following surface roughness quality can be ordered. • Not polished • $Ra_{max} = 0.76 \ \mu m \ (30 \ \mu in)$ mechanically polished • $Ra_{max} = 0.38 \ \mu m \ (15 \ \mu in)$ mechanically polished
	Operability

Operating concept	Operator-oriented menu structure for user-specific tasks
	Commissioning
	 Operation
	 Diagnostics
	 Expert level
	Quick and safe commissioning
	 Guided menus ("Make-it-run" wizards) for applications
	Menu guidance with brief explanations of the individual parameter functions

	 Reliable operation Operation in the following languages: Via local display: English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese Uniform operating philosophy applied to device and operating tools If replacing the electronic module, transfer the device configuration via the integrated memory (integrated HistoROM) which contains the process and measuring device data and the event logbook. No need to reconfigure.
	 Efficient diagnostics increase measurement availability Troubleshooting measures can be called up via the device and in the operating tools Diverse simulation options, logbook for events that occur and optional line recorder functions
Languages	 Can be operated in the following languages: Via local display: English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Swedish, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech Via "FieldCare" operating tool: English, German, French, Spanish, Italian, Chinese, Japanese
Local operation	Via display module

Two display modules are available:

Ore	der code for "Display; Operation", option C "SD02"	Oı	rder code for "Display; Operation", option E "SDO	03"
				10032221
1	Operation with pushbuttons	1	Operation with touch control	

Display elements

- 4-line, illuminated, graphic display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +60 °C (-4 to +140 °F)
- The readability of the display may be impaired at temperatures outside the temperature range.

Operating elements

- Operation with 3 push buttons with open housing: \boxdot , \Box , \Box
- or
- External operation via touch control (3 optical keys) without opening the housing: \pm , \Box , \blacksquare
- Operating elements also accessible in the various zones of the hazardous area

Additional functionality

- Data backup function
 The device configuration can be saved in the display module.
- Data comparison function The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function The transmitter configuration can be transmitted to another device using the display module.

Via remote display FHX50

The remote display FHX50 can be ordered as an optional extra \rightarrow \square 73.



■ 27 FHX50 operating options

1 SD02 display and operating module, push buttons: cover must be opened for operation

2 SD03 display and operating module, optical buttons: operation possible through cover glass

Display and operating elements

The display and operating elements correspond to those of the display module .

Via HART protocol

This communication interface is available in device versions with a HART output.

Remote operation



28 Options for remote operation via HART protocol (passive)

- 1 Control system (e.g. PLC)
- 2 Transmitter power supply unit, e.g. RN221N (with communication resistor)
- 3 Connection for Commubox FXA195 and Field Communicator 475
- 4 Field Communicator 475
- 5 Computer with web browser (e.g. Internet Explorer) for accessing computers with operating tool (e.g. FieldCare, DeviceCare, AMS Device Manager, SIMATIC PDM) with COM DTM "CDI Communication TCP/IP"
- 6 Commubox FXA195 (USB)
- 7 Field Xpert SFX350 or SFX370
- 8 VIATOR Bluetooth modem with connecting cable
- 9 Transmitter

Via PROFIBUS PA network

This communication interface is available in device versions with PROFIBUS PA.



29 Options for remote operation via PROFIBUS PA network

- 1 Automation system
- 2 Computer with PROFIBUS network card
- 3 PROFIBUS DP network
- 4 Segment coupler PROFIBUS DP/PA
- 5 PROFIBUS PA network
- 6 T-box
- 7 Measuring device

Via FOUNDATION Fieldbus network

This communication interface is available in device versions with FOUNDATION Fieldbus.



■ 30 Options for remote operation via FOUNDATION Fieldbus network

- 1 Automation system
- 2 Computer with FOUNDATION Fieldbus network card
- 3 Industry network
- 4 High Speed Ethernet FF-HSE network
- 5 Segment coupler FF-HSE/FF-H1
- 6 FOUNDATION Fieldbus FF-H1 network
- 7 Power supply FF-H1 network
- 8 T-box
- 9 Measuring device



Via service interface (CDI)



1 Service interface (CDI = Endress+Hauser Common Data Interface) of the measuring device

- 2 Commubox FXA291
- 3 Computer with FieldCare operating tool with COM DTM CDI Communication FXA291

Certificates and approvals

Currently available certificates and approvals can be called up via the product configurator.

CE mark	The device meets the legal requirements of the applicable EU Directives. These are listed in the corresponding EU Declaration of Conformity along with the standards applied.
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.
C-Tick symbol	The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".
Functional safety	The measuring device can be used for flow monitoring systems (min., max., range) up to SIL 2 (single-channel architecture; order code for "Additional approval", option LA) and SIL 3 (multichannel architecture with homogeneous redundancy) and is independently evaluated and certified by the TÜV in accordance with IEC 61508.
	The following types of monitoring in safety equipment are possible: Mass flow Volume flow Density
	Functional Safety Manual with information on the SIL device $\rightarrow \equiv 76$

Ex approval

The measuring device is certified for use in hazardous areas and the relevant safety instructions are provided in the separate "Safety Instructions" (XA) document. Reference is made to this document on the nameplate.



ATEX/IECEx

Currently, the following versions for use in hazardous areas are available:

Ex d

Category (ATEX)	Type of protection
II2G	Ex d[ia] IIC T6T1 Gb
II1/2G	Ex d[ia] IIC T6T1 Ga/Gb ¹⁾
II1/2G, II2D	Ex d[ia] IIC T6T1 Ga/Gb ¹⁾ Ex tb IIIC Txx °C Db

1) The following applies for sensors with nominal diameter DN 01: Ex db eb ia IIC T6...T1 Gb

Ex ia

Category (ATEX)	Type of protection
II2G	Ex ia IIC T6T1 Gb
II1/2G	Ex ia IIC T6T1 Ga/Gb ¹⁾
II1/2G, II2D	Ex ia IIC T6T1 Ga/Gb ¹⁾ Ex tb IIIC Txx °C Db

1) The following applies for sensors with nominal diameter DN 01: Ex db eb ia IIC T6...T1 Gb

Ex nA

Category (ATEX)	Type of protection
II3G	Ex nA IIC T6T1 Gc

	Ex ic	
	Category (ATEX)	Type of protection
	II3G	Ex ic IIC T6T1 Gc
	II1/3G	Ex ic[ia] IIC T6T1 Ga/Gc
	_C CSA _{US}	
	Currently, the following versions for u	se in hazardous areas are available:
	IS (Ex i) and XP (Ex d) Class I, II, III Division 1 Groups ABCDE	FG
	 NI (Ex nA, Ex nL) Class I Division 2 Groups ABCD Class II, III Division 1 Groups EFG 	
Sanitary compatibility	 3-A approval Only devices with the order code for FDA Food Contact Materials Regulation 	"Additional approval", option LP "3A" have 3-A approval. (EC) 1935/2004
Pharmaceutical compatibility	 FDA USP Class VI TSE/BSE Certificate of Suitability 	
Functional safety	The measuring device can be used for (single-channel architecture; order cod (multichannel architecture with homo certified by the TÜV in accordance wit	flow monitoring systems (min., max., range) up to SIL 2 de for "Additional approval", option LA) and SIL 3 geneous redundancy) and is independently evaluated and h IEC 61508.
	The following types of monitoring in s Mass flow Volume flow Density 	afety equipment are possible:
	Functional Safety Manual with ir	formation on the SIL device $\rightarrow \square 76$
HART certification	HART interface	
	The measuring device is certified and a meets all the requirements of the follo	registered by the FieldComm Group. The measuring system owing specifications:
	 The device can also be operated with 	h certified devices of other manufacturers (interoperability)
FOUNDATION Fieldbus	FOUNDATION Fieldbus interface	
certification	The measuring device is certified and i meets all the requirements of the follo • Certified in accordance with FOUND • Interoperability Test Kit (ITK), revisi • Physical Layer Conformance Test • The device can also be operated with	registered by the FieldComm Group. The measuring system owing specifications: DATION Fieldbus H1 ion version 6.1.1 (certificate available on request) h certified devices of other manufacturers (interoperability)
Certification PROFIBUS	PROFIBUS interface	
	The measuring device is certified and a Organization). The measuring system • Certified in accordance with PROFIE • The device can also be operated with	registered by the PNO (PROFIBUS User Organization meets all the requirements of the following specifications: BUS PA Profile 3.02 h certified devices of other manufacturers (interoperability)
Additional certification	CRN approval	
	Some device versions have CRN appro- must be ordered for a CRN-approved c	val. A CRN-approved process connection with a CSA approval levice.

Tests and certificates

- Pressure test, internal procedure, inspection certificate
- EN10204-3.1 material certificate, wetted parts and sensor housing
 PMI test (XRF), internal procedure, wetted parts, test report
- NACE MR0175 / ISO 15156
- NACE MR0103 / ISO 17945

Testing of welded connections

	Option		Test sta	Test standard		
		ISO 10675-1 AL1	ASME B31.3 NFS	ASME VIII Div.1	NORSOK M-601	connection
	KE	x				RT
	KI		х			RT
	KN			x		RT
	KS				Х	RT
	К5	x				DR
	К6		х			DR
	K7			x		DR
	К8				х	DR
		RT = R	adiographic testing All options wi	, DR = Digital radiog th test report	raphy	
Other standards and guidelines	 EN 60529 Degrees of p. IEC/EN 6006 Environment IEC/EN 6006 Environment devices. EN 61010-1 Safety requir general requ IEC/EN 6132 Emission in a requirement. IEC 61508 Functional sa NAMUR NE Electromagn NAMUR NE Data retention microprocess NAMUR NE Standardizat analog outpu NAMUR NE Software of find NAMUR NE Specification NAMUR NE Self-monitor NAMUR NE Requirement NAMUR NE Coriolis mass 	rotection provided 58-2-6 cal influences: Test 58-2-31 cal influences: Test ements for electric irements 26 accordance with Cl. 5). afety of electrical/6 21 etic compatibility (32 on in the event of a cors 43 ion of the signal le tt signal. 53 ield devices and sig 105 s for integrating fit 107 ing and diagnosis of 131 s for field devices fit 132 s meter	by enclosures (IP procedure - Test procedure - Test cal equipment for ass A requiremen electronic/program EMC) of industria power failure in t vel for the breakd gnal-processing d eldbus devices in o of field devices for standard appli	code) Fc: vibrate (sinus Ec: shocks due to measurement, co ts. Electromagnet mmable electronic al process and lab field and control i lown information evices with digita engineering tools cations	oidal). rough handling, ntrol and laborat ic compatibility (c safety-related sy oratory control ed nstruments with of digital transm l electronics for field devices	primarily for ory use - EMC ystems quipment itters with

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com -> Click "Corporate"
 -> Select your country -> Click "Products" -> Select the product using the filters and search field ->
 Open product page -> The "Configure" button to the right of the product image opens the Product
 Configurator.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
 - Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
 - Automatic verification of exclusion criteria
 - Automatic creation of the order code and its breakdown in PDF or Excel output format
 - Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered with the device or subsequently from Endress+Hauser. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Detailed information on the application packages: Special Documentation for the device $\rightarrow \square 76$

Diagnostics functions	Package	Description
	Extended HistoROM	Comprises extended functions concerning the event log and the activation of the measured value memory.
		Event log: Memory volume is extended from 20 message entries (standard version) to up to 100 entries.
		 Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Measured value logs can be accessed via the local display or operating tool e.g. FieldCare, DeviceCare or Web server.
Heartbeat Technology	Package	Description
Heartbeat Technology	Package Heartbeat Verification	Description Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". • Functional testing in the installed state without interrupting the process. • Traceable verification results on request, including a report. • Simple testing process via local operation or other operating interfaces. • Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. • Extension of calibration intervals according to operator's risk assessment.
Heartbeat Technology Special density	Package Heartbeat Verification	Description Heartbeat Verification Meets the requirement for traceable verification to DIN ISO 9001:2008 Chapter 7.6 a) "Control of monitoring and measuring equipment". • Functional testing in the installed state without interrupting the process. • Traceable verification results on request, including a report. • Simple testing process via local operation or other operating interfaces. • Clear measuring point assessment (pass/fail) with high test coverage within the framework of manufacturer specifications. • Extension of calibration intervals according to operator's risk assessment.

Special density	Many applications use density as a key measured value for monitoring quality or controlling processes. The device measures the density of the fluid as standard and
	makes this value available to the control system.
	The "Special Density" application package offers high-precision density
	measurement over a wide density and temperature range particularly for
	applications subject to varying process conditions.
Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Accessories	Description
Promass 200 transmitter	Transmitter for replacement or storage. Use the order code to define the following specifications: Approvals Output Display/operation Housing Software Installation Instructions EA00104D (Order number: 8X2CXX)
Remote display	EHX50 housing for accommodating a display module
FHX50	 FHX50 housing for accountrolating a display module ? FHX50 housing suitable for: SD02 display module (push buttons) SD03 display module (touch control) Length of connecting cable: up to max. 60 m (196 ft) (cable lengths available for order: 5 m (16 ft), 10 m (32 ft), 20 m (65 ft), 30 m (98 ft))
	 The measuring device can be ordered with the FHX50 housing and a display module. The following options must be selected in the separate order codes: Order code for measuring device, feature 030: Option L or M "Prepared for FHX50 display" Order code for FHX50 housing, feature 050 (device version): Option A "Prepared for FHX50 display" Order code for FHX50 housing, depends on the desired display module in feature 020 (display, operation): Option C: for an SD02 display module (push buttons) Option E: for an SD03 display module (touch control)
	 The FHX50 housing can also be ordered as a retrofit kit. The measuring device display module is used in the FHX50 housing. The following options must be selected in the order code for the FHX50 housing: Feature 050 (measuring device version): option B "Not prepared for FHX50 display" Feature 020 (display, operation): option A "None, existing displayed used"
	Special Documentation SD01007F
	(Order number: FHX50)
Overvoltage protection for 2-wire devices	Ideally, the overvoltage protection module should be ordered directly with the device. See product structure, feature 610 "Accessory mounted", option NA "Overvoltage protection". Separate order necessary only if retrofitting.
	 OVP10: For 1-channel devices (feature 020, option A): OVP20: For 2-channel devices (feature 020, options B, C, E or G)
	Special Documentation SD01090F
	(Order number OVP10: 71128617) (Order number OVP20: 71128619)
Protective cover	Is used to protect the measuring device from the effects of the weather: e.g. rainwater, excess heating from direct sunlight or extreme cold in winter. Special Documentation SD00333F
	(Order number: 71162242)
	1

Device-specific accessories For the transmitter

For the sensor

Accessories	Description		
Heating jacket	Is used to stabilize the temperature of the fluids in the sensor. Water, water vapor and other non-corrosive liquids are permitted for use as fluids.		
	If using oil as a heating medium, please consult with Endress+Hauser.		
	 If ordered together with the measuring device: 		
	order code for "Enclosed accessories"		
	 Option RB "heating jacket, G 1/2" internal thread" 		
	 Option RD "Heating jacket, NPT 1/2" internal thread" 		
	 If ordered subsequently: 		
	Use the order code with the product root DK8003.		
	Special Documentation SD02173D		
Sensor holder	For wall, tabletop and pipe mounting.		
	Order number: 71392563		

Communication-specific	Accessories	Description
	Commubox FXA195 HART	For intrinsically safe HART communication with FieldCare via the USB interface.
	Commubox FXA291	Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. Technical Information TI405C/07
	HART Loop Converter HMX50	Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values.
	Wireless HART adapter SWA70	Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. Operating Instructions BA00061S
	Fieldgate FXA320	Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. Technical Information TI00025S Operating Instructions BA00053S
	Fieldgate FXA520	Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. Technical Information TI00025S Operating Instructions BA00051S
	Field Xpert SFX350	Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in non-hazardous areas. Operating Instructions BA01202S
	Field Xpert SFX370	Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices and can be used in the non-hazardous area and in the hazardous area. Operating Instructions BA01202S

Service-specific accessories	Accessories	Description		
	Applicator	 Software for selecting and sizing Endress+Hauser measuring devices: Choice of measuring devices for industrial requirements Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, flow velocity and accuracy. Graphic illustration of the calculation results Determination of the partial order code, administration, documentation and access to all project-related data and parameters over the entire life cycle of a project. Applicator is available: Via the Internet: https://portal.endress.com/webapp/applicator As a downloadable DVD for local PC installation. 		
	W@M	W@M Life Cycle Management Improved productivity with information at your fingertips. Data relevant to a plant and its components is generated from the first stages of planning and during the asset's complete life cycle. W@M Life Cycle Management is an open and flexible information platform with online and on-site tools. Instant access for your staff to current, in-depth data shortens your plant's engineering time, speeds up procurement processes and increases plant uptime. Combined with the right services, W@M Life Cycle Management boosts productivity in every phase. For more information, visit www.endress.com/lifecyclemanagement		
	FieldCare	FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them. By using the status information, it is also a simple but effective way of checking their status and condition.		
	DeviceCare	Tool to connect and configure Endress+Hauser field devices. Innovation brochure IN01047S		

System components	Accessories	Description
	Memograph M graphic data manager	The Memograph M graphic data manager provides information on all the relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick. The Technical Information TI00133R Operating Instructions PA00247P
		• Operating instructions BA00247R
	RN221N	Active barrier with power supply for safe separation of 4-20 mA standard signal circuits. Offers bidirectional HART transmission.
		 Technical Information TI00073R Operating Instructions BA00202R
	RNS221	Supply unit for powering two 2-wire measuring devices solely in the non- hazardous area. Bidirectional communication is possible via the HART communication jacks.
		 Technical Information TI00081R Brief Operating Instructions KA00110R
	Cerabar M	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.
		 Technical Information TI00426P and TI00436P Operating Instructions BA00200P and BA00382P
	Cerabar S	The pressure transmitter for measuring the absolute and gauge pressure of gases, steam and liquids. It can be used to read in the operating pressure value.
		 Technical Information TI00383P Operating Instructions BA00271P

Documentation

- For an overview of the scope of the associated Technical Documentation, refer to the following:
 - The W@M Device Viewer (www.endress.com/deviceviewer): Enter serial number from nameplate
 - The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation Brief Operating Instructions

Brief Operating Instructions for the sensor

Measuring device	Documentation code
Proline Promass A	KA01282D

Brief Operating Instructions for transmitter

	Documentation code		
Measuring device	HART	FOUNDATION Fieldbus	PROFIBUS PA
Proline Promass 200	KA012268	KA01267D	KA01269D

Operating Instructions

	Documentation code		
Measuring device	HART	FOUNDATION Fieldbus	PROFIBUS PA
Proline Promass A 200	BA01821D	BA01827D	BA01828D

Description of Device Parameters

	Documentation code		
Measuring device	HART	FOUNDATION Fieldbus	PROFIBUS PA
Proline Promass 200	GP01010D	GP01030D	GP01029D

Supplementary device- Safety instructions dependent documentation	
Contents	Documentation code
ATEX/IECEx Ex i	XA00144D
ATEX/IECEx Ex d	XA00143D
ATEX/IECEx Ex nA	XA00145D
cCSAus IS	XA00151D
cCSAus XP	XA00152D
INMETRO Ex i	XA01300D
INMETRO Ex d	XA01305D
INMETRO Ex nA	XA01306D
NEPSI Ex i	XA00156D
NEPSI Ex d	XA00155D
NEPSI Ex nA	XA00157D

Special Documentation

Contents	Documentation code
Information on the Pressure Equipment Directive	SD01614D
Functional Safety Manual	SD00147D
Display and operating module FHX50	SD01007F

Contents	Documentation		
	HART	FOUNDATION Fieldbus	PROFIBUS PA
Heartbeat Technology	SD01849D	SD01848D	SD01850D

Installation Instructions

Contents	Comment
Installation instructions for spare part sets and accessories	Documentation code: specified for each individual accessory .

Registered trademarks

HART®

Registered trademark of the FieldComm Group, Austin, Texas, USA

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

FOUNDATION™ Fieldbus

Registration-pending trademark of the FieldComm Group, Austin, Texas, USA

TRI-CLAMP®

Registered trademark of Ladish & Co., Inc., Kenosha, USA

SWAGELOK[®]

Registered trademark of Swagelok & Co., Solon, USA

www.addresses.endress.com

