# Technical Information **Nivotester FTL325N**

Vibronic



## Level detector with NAMUR input for connecting any NAMUR sensor

#### **Application**

- Point level detection in liquid tanks and bulk solids silos, also in hazardous areas
- For sensors in Zone 0 or Zone 20
- Liquid detection in pipes for dry-run protection of pumps
- Overfill prevention in tanks with flammable or non-flammable water-polluting liquids
- Two-point control and point level detection in one switching unit
- Application in safety systems with functional safety requirements up to SIL 2 in accordance in IEC 61508 when using the Liquiphant M/S with electronic insert FEL56 and FEL58, Liquiphant FTL41 with electronic insert FEL48, Liquiphant FTL51B with electronic insert FEL68 or Soliphant M with electronic insert FEM58

#### Your benefits

- Intrinsically safe signal circuits [Ex ia] for use of sensors in hazardous areas
- Compact housing for simple side-by-side installation on standard DIN rails in cabinet
- Easy connection with plug-in terminal blocks
- NAMUR interface according to IEC/EN 60947-5-6 for connecting NAMUR sensors or electronic inserts



## Table of contents

Document information3Document conventions3
Function and system design3Measuring principle3NAMUR interface3Measuring system5
Input9Measured variable9Measuring range9Input signal9
Output9Output signal9Overvoltage category according to EN 610109Protection class9Signal on alarm9Galvanic isolation9
Power supply10Electrical connection10Supply voltage10Power consumption10
Performance characteristics10Switch-on behavior10
Installation11Mounting location11Orientation11
Environment12Ambient temperature range12Climate and mechanical application class12Degree of protection12Electromagnetic compatibility (EMC)12
Mechanical construction13Design, dimensions13Weight13Materials13Terminals13
Operability15Operating concept15Display elements15Operating elements15
Certificates and approvals16CE mark16RCM-Tick mark16Ex approval16Type of protection16Overfill prevention16

Other standards and guidelines	
Ordering information	16
Accessories	
Supplementary documentation	17

#### **Document information**

#### **Document conventions**

#### Symbols for certain types of information

Symbol	Meaning	
i	<b>Tip</b> Indicates additional information.	
1 1—1	Reference to page Refers to the corresponding page number.	

#### Symbols for graphics

Symbol	Meaning
1, 2, 3	Item numbers
A, B, C,	Views

## Function and system design

#### Measuring principle

#### Signal transmission

The intrinsically safe signal inputs of the Nivotester are galvanically isolated from the mains and the output.

The Nivotester supplies a DC current to the sensors or to sensors specified to IEC/EN 60947-5-6 via a two-wire loop. Sensors include, e.g., Liquiphant M/S with electronic insert FEL56 or FEL58, Liquiphant FTL51B with electronic insert FEL68, Liquiphant FTL41 with electronic insert FEL48 or Soliphant M with electronic insert FEM58. At the same time, a control current is transferred along this power supply line. Depending on the switch status, the control current range is between < 1.2 mA and 1.2 mA.

#### Signal evaluation

The Nivotester measures the control current which is transferred along the sensor power supply line and evaluates it. The relay for the level alarm switches when the sensor is covered or not covered. A yellow LED on the front panel of the Nivotester signals the relay switch status. A red LED signals faults, e.g., a short circuit or cable open circuit.

#### Fail-safe mode

By selecting the correct fail-safe mode, you ensure that the relays always operate with quiescent current safety.

The failure current signal of the connected sensor ( $<1.2\,$  mA and  $>2.1\,$  mA) can be set for each channel with the DIL switches on the Nivotester. This means that the Nivotester can be used for any application at the required level of operational safety. Combined with a sensor, quiescent current safety is defined as follows:

- MAX = maximum safety: the relay drops out when the switch point is exceeded (sensor is covered), a fault occurs or the power supply fails.
- MIN = minimum safety: the relay drops out when the switch point is undershot (sensor is not covered), a fault occurs or the power supply fails.

#### NAMUR interface

The Nivotester FTL325N has a NAMUR interface in accordance with IEC/EN 60947-5-6. The control current is evaluated, displayed and output by the Nivotester FTL325N according to the NAMUR standard.


The following Endress+Hauser sensors can be connected in accordance with IEC/EN 60947-5-6:

- Liquiphant FTL41 with FEL48, Liquiphant FTL51B with FEL68
- Liquiphant M, Liquiphant S with FEL56, FEL58
- Soliphant M with FEM58
- Liquicap M with FEI58
- Solicap M, Solicap S with FEI58

In addition, it is also possible to connect all sensors specified to IEC/EN 60947-5-6 and contact switches with an appropriate external resistance circuit for cable open circuit and short-circuit monitoring. When contact switches without a resistance circuit are used, alarm detection for short-circuiting and signal cable disconnection must be switched off at the appropriate channel.

#### Point level detection and current signal as a function of the level and fail-safe mode


The MIN or MAX setting is made on the electronic insert of the sensor.



- A Tuning fork not covered
- B Tuning fork covered
- C MAX fail-safe mode
- D MIN fail-safe mode
- 1 Control current 0.4 to 1.2 mA (FEL56)/2.1 to 5.5 mA (FEL48, FEL58, FEL68)
- 2 Control current 2.1 to 5.5 mA (FEL56)/0.4 to 1.2 mA (FEL48, FEL58, FEL68)
- 3 Control current 2.1 to 5.5 mA (FEL56)/0.4 to 1.2 mA (FEL48, FEL58, FEL68)
- 4 Control current 0.4 to 1.2 mA (FEL56)/2.1 to 5.5 mA (FEL48, FEL58, FEL68)

#### Switch position as a function of the electronic inserts

The relays only switch correctly if the failure current signal is set on the Nivotester as a function of the electronic inserts. Example: Nivotester with electronic insert FEL56 and FEL58 or FEL48 and FEL68:



- Electronic insert FEL56: failure current signal > 2.1 mA
- Electronic insert FEL48, FEL68, FEL58, FEM58, FEI58: failure current signal < 1.2 mA



For applications requiring functional safety in accordance with IEC 61508 (SIL), see the "Supplementary documentation" section of the Functional Safety Manual. If several tanks are in use, a separate Nivotester must be used for each level.

#### **Function monitoring**

To increase operational safety, the Nivotester is equipped with a function monitoring system. As there is a test button for every channel, function monitoring can be performed separately. The power supply to the sensor is interrupted during this process.

The red LED on the front panel indicates that a fault has occurred that causes the relays for the level alarm and fault signaling system to drop out.

A fault is reported if the control current leaves the valid range, for example in the event of:

- A short-circuit, or if the signal line to the sensor is disconnected
- Sensor corrosion
- Defective electronics in the sensor
- The input circuit of the Nivotester is defective

#### Two-point control ( $\Delta s$ )

Two-point control in a tank is possible with the 3-channel Nivotester (e.g., for pump control). The installation location of the sensors defines the switching hysteresis.


#### Measuring system

The measuring system can consist of the following components:

- ullet 1 to 3 sensors, e.g., Liquiphant M/S or Liquiphant
- 1-channel or 3-channel Nivotester
- Control or signal devices

Alternatively, sensors specified to IEC/EN 60947-5-6 or contact switches with an appropriate resistance circuit can be used. See also the "NAMUR interface" section  $\rightarrow \blacksquare 3$ .


#### Contact switch with resistance circuit



A0026113

#### 1-channel Nivotester


- 1 sensor
- 1-channel Nivotester
- Control or signal devices



A002607


#### 3-channel Nivotester

- 1. The 3 individual channels are used for point level measurement
- 3 sensors
- 3-channel Nivotester
- Control or signal devices




A0026079

- 2. Channels CH2 and CH3 are used for two-point control  $\Delta s$
- 2 sensors
- 3-channel Nivotester
- Control or signal devices
- If channel CH1 is not used, the alarm must be switched "off".




.....

- 3. Channels CH2 and CH3 are used for two-point control  $\Delta s$  and channel CH1 is used for overfill prevention
- 3 sensors
- 3-channel Nivotester
- Control or signal devices




A002608

- 4. Channel CH2 is used for point level measurement with two level relays and channel CH1 is used for additional point level measurement
- 2 sensors
- 3-channel Nivotester
- Control or signal devices



- 5. Channel CH2 is used for point level measurement with two level relays
- 1 sensor
- 3-channel Nivotester
- Control or signal devices
- If channel CH1 is not used, the alarm must be switched "off".



For more detailed information on the WHG or SIL wiring scheme, see the WHG documents and SIL manual.

#### Input Measured variable The point level signal is triggered at MIN level or MAX level, depending on the setting. Measuring range The measuring range depends on the installation location of the sensors. Galvanically isolated from power supply and output Input signal • Type of protection: intrinsic safety [Ex ia] IIC / [Ex ia] IIIC • Suitable sensors for connection: ■ Liquiphant M FTL50/51/50H/51H, FTL51C with electronic insert FEL56 or FEL58 Liquiphant S FTL70/71 with electronic insert FEL56 or FEL58 • Soliphant M FTM50/51/52 with FEM58 Solicap M FTI55, FTI56, Solicap S FTI77, Liquicap M FTI51, FTI52 with FEI58 Sensors certified to IEC/EN 60947-5-6 • Contact switch with appropriate resistance circuit Sensors powered by Nivotester • Connection cable: twin-core, shield not required • Cable length/cable resistance: 1 000 m (3 281 ft)/max. 25 $\Omega$ per wire • Signal transmission: current signal over power supply line • Control current: < 1.2 mA / > 2.1 mA; cable open circuit monitoring $< 200 \mu\text{A}$ , short-circuit monitoring > 6.1 mA (can be switched off for unused channels) See the relevant certificates for more information on using the sensors in hazardous areas, "Supplementary documentation" section. Output Output signal • Relay output per channel: a potential-free changeover contact for the level alarm • Quiescent current fail-safe mode: MIN/MAX safety can be selected with DIL switch • 1 fault-signaling relay for channels 1, 2 and 3 (1 potential-free changeover contact, but it is only possible to connect to two contacts) • Switching delay: approx. 0.5 s • Operating life: at least 10<sup>5</sup> switching operations with maximum contact load • Function indicator: LEDs for operation, level alarm and fault Relay contact switching capacity: Alternating voltage (AC) U ~ maximum 250 V

I ~ maximum 2 A

P ~ maximum 500 VA with cos  $\phi \ge 0.7$ 

Direct current (DC)

U = maximum 40 V

I = maximum 2 A

P = maximum 80 W

## Overvoltage category according to EN 61010

II

#### **Protection class**

II (double or reinforced insulation)

#### Signal on alarm

Level relay per channel dropped out; fault signaled by red LEDs, fault-signaling relay dropped out

#### Galvanic isolation

All input and output channels and relay contacts are galvanically isolated from each other. If simultaneously functional low voltage is connected to the power supply circuit or to the relay contacts, safe galvanic isolation is guaranteed up to a voltage of  $150~V_{AC}$ .

## Power supply

#### **Electrical connection**

#### Sensor operation in the hazardous area

Observe all national explosion protection regulations concerning the type and installation of intrinsically safe signal cabling.

Refer to the safety instructions for the maximum admissible values for capacitance and inductance, "Supplementary documentation" section.

#### Connecting the sensors

The removable terminal blocks are color-coded into intrinsically safe and non-intrinsically safe terminals. This difference helps to ensure safe wiring.

Blue terminal blocks at top for hazardous area

Twin-core connection cable between the Nivotester and sensor, e.g. commercially available instrument cable or cores in a multi-core cable for measurement purposes.

Use a shielded cable in the event of strong electromagnetic interference, e.g. from machines or radio equipment. Only connect the shield to the grounding terminal in the sensor. Do not connect it to the Nivotester.

#### Connecting the signal and control units

Gray terminal blocks at bottom for the non-hazardous area

The relay function depends on the level and fail-safe mode. If a device is connected at high inductance (e.g. contactor, solenoid valve etc.), a spark arrester must be installed to protect the relay contact.

#### Connecting the supply voltage

Green terminal block at bottom

A fuse is integrated into the power supply circuit. An additional fine-wire fuse is not necessary. The Nivotester has reverse polarity protection.

#### Supply voltage

#### Alternating current version (AC)

Voltage range: 85 to 253 V AC, 50/60 Hz

#### Direct current range (DC)

- Voltage range: 20 to 30 V AC / 20 to 60 V DC
- D/C power supply:
  - 1-channel: maximum 60 mA
  - 3-channel: maximum 113 mA
- ullet Permitted residual ripple within tolerance:  $U_{ss}$  = maximum 2 V

#### Power consumption

#### AC

- 1-channel: maximum 1.75 W
- 3-channel: maximum 2.75 W

#### DC

1-channel: 1.2 W (for U<sub>min</sub> 20 V)
 3-channel: 2.25 W (for U<sub>min</sub> 20 V)

#### **Performance characteristics**

#### Switch-on behavior

Correct switch state after switching on the power supply: 10 to 20 s, depending on the connected sensor.

### Installation

#### Mounting location


- The Nivotester must be housed in a cabinet outside the hazardous area.
- The devices must be mounted in such a way that they are protected from impact and weather conditions. Where possible, mount the device in a location where it is not exposed to direct sunlight, particularly in warm climates.

#### Orientation

#### Horizontal orientation




Horizontal installation ensures better dissipation of heat and is therefore the preferred orientation.



A002630

- Dimensions mm (in)
- A Connection of another device type
- B DIN rail in accordance with EN 60715 TH35-7.5/15

#### Vertical orientation



A0026420

Dimensions mm (in)

A Connection of another device type

#### **Environment**

#### Ambient temperature range

- For single installation: -20 to +60 °C (-4 to 140 °F)
- For side-by-side installation without lateral spacing: -20 to +50 °C (-4 to +122 °F)
- For installation in protective housing: -20 to +40 °C (-4 to +104 °F)
  Up to four 1-channel or two 3-channel Nivotesters or a maximum of two 1-channel Nivotesters plus one 3-channel Nivotester fit in a protective housing.
- Storage temperature: -20 to +85 °C (-4 to 185), preferably at 20 °C (68 °F)

## Climate and mechanical application class

3K3 and 3M2 in accordance with IEC/EN 60721-3-3

#### Degree of protection

- IP20 (as per IEC/EN 60529)
- IK06 (as per IEC/EN 62262)

## Electromagnetic compatibility (EMC)


- Interference emission according to EN 61326, Class A equipment
- Interference immunity according to EN 61326; Annex A (Industrial) and NAMUR Recommendation NE21 (EMC)

12

### Mechanical construction

#### Design, dimensions

#### **Dimensions**



Dimensions mm (in)

- 1 1-channel Nivotester
- 2 3-channel Nivotester

#### Weight

- 1-channel: approx. 148 g (5.22 oz)
- 3-channel: approx. 250 g (8.81 oz)

#### Materials

- Housing: polycarbonate
- Front cover: PP polypropylene
- Fixing slide to secure to DIN rail: polyamide PA6

#### **Terminals**

#### 1-channel

- 2 screw terminals: sensor power supply
- 3 screw terminals: level relay
- 2 screw terminals: fault-signaling relay
- 2 screw terminals: power supply


#### 3-channel

- 3x2 screw terminals: sensor power supply, channel 1 to 3
- 3x3 screw terminals: level relay, channel 1 to 3
- 2 screw terminals: fault-signaling relay
- 2 screw terminals: power supply

#### Connection cross-section

Maximum 1 x 2.5 mm<sup>2</sup> (14 AWG) or 2 x 1.5 mm<sup>2</sup> (16 AWG)

#### Terminal assignment



- 1-channel Nivotester 3-channel Nivotester Α
- В
- 1
- 2
- Sensor 1 (Ex ia)
  Level relay 1
  Power supply / fault-signaling relay
  Sensor 3 (Ex ia)
  Sensor 2 (Ex ia) 3
- 5
- Level relay 2 Level relay 3 6 7

## Operability

#### Operating concept

Onsite configuration with DIL switches behind fold-down front panel


#### Display elements

#### Light emitting diodes (LEDs)

- Green light emitting diode: operational
- One red LED per channel: fault signal
- One yellow LED per channel: level relay picked up


#### Operating elements

#### 1-channel Nivotester



- DIL switch: failure current signal 2.1 mA / 1.2 mA (1), fault on/off position (2)
- Light emitting diodes (LEDs)

#### 3-channel Nivotester



- DIL switch for channel 1: failure current signal 2.1 mA / 1.2 mA (1), fault on/off position (2)
- Light emitting diodes (LEDs)
- DIL switch for channel 2 and 3: fault on/off position (1/3), failure current signal 2.1 mA / 1.2 mA (2/4)
- Switch for functions:  $\Delta s$ , e.g. pump control (1), two level relays (2), individual channels (3)
- Light emitting diodes (LEDs)

## Certificates and approvals

CE mark	The measuring device is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.				
	Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.				
RCM-Tick mark	The measuring device complies with the EMC requirements of the "Australian Communications and Media Authority (ACMA)".				
Ex approval	The Endress+Hauser sales center can provide information on the hazardous area versions currently available. All data relevant to explosion protection are provided in separate documents which can be supplied on request, "Supplementary documentation" section.				
Type of protection	II(1)G [Ex ia Ga] IIC				
	II(1)D [Ex ia Da] IIIC				
Overfill prevention	■ WHG				
	■ Leak approval				
Other standards and guidelines	The applicable European guidelines and standards can be found in the relevant EU Declarations of Conformity.				
	<ul> <li>IEC/EN 60947-5-6: Low-voltage switchgear and control gear - DC interface for proximity sensors and switching amplifiers (NAMUR)</li> </ul>				
	■ IEC/EN 60721-3-3: Classification of environmental conditions				
	<ul> <li>IEC/EN 60529: Degrees of protection provided by enclosures (IP code)</li> <li>IEC/EN 61010: Safety requirements for electrical equipment for measurement, control and laboratory use</li> </ul>				
	<ul> <li>IEC/EN 61326: Interference emission (class A equipment), interference immunity (Appendix A - Industrial)</li> </ul>				
	<ul> <li>IEC 61508: Functional safety of safety-related electric/electronic/programmable electronic systems (E/E/PES)</li> </ul>				

#### **Functional safety**

SIL 1, SIL 2 for protection functions as

- Overfill prevention in conjunction with Liquiphant + electronic insert FEL56/58 or Soliphant + FFM58
- Minimum detection in conjunction with Liquiphant + electronic insert FEL56/58

Refer to the Functional Safety Manual, "Supplementary documentation" section!

## Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser website: www.endress.com → Select your country → Products → Select measuring technology, software or components → Select the product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product opens.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

## Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

## Accessories

#### **Protective housing**

The protective housing with IP66 ingress protection is equipped with an integrated DIN rail and is closed by a transparent cover which can also be lead-sealed.

- Dimensions in mm (in) B/H/D: 180/182/165 (7.1/7.2/6.5)
- Part number: 52010132

## Supplementary documentation



Please see www.endress.com  $\Rightarrow$  download for the available documentation





www.addresses.endress.com