Technical Information Proline Promag D 400

Electromagnetic flowmeter

Products



The flowmeter designed as a compact wafer version and with integrated web server

Application

- The measuring principle is virtually independent of pressure, density, temperature and viscosity
- For basic water applications; optimized for limited space and plastic pipe installations

Device properties

- Short installation length and low weight
- Integrated ground disks made of stainless steel
- International drinking water approvals
- Transmitter housing made of durable polycarbonate
- Same housing concept for compact/remote version
- Integrated data logger: measured values monitoring

Your benefits

- Easy, fast centering of the sensor innovative housing construction
- Energy-saving flow measurement no pressure loss due to cross-section constriction
- Maintenance-free no moving parts
- Safe operation no need to open the device due to display with touch control, background lighting
- Time-saving local operation without additional software and hardware - integrated web server
- Integrated verification Heartbeat Technology™



Table of contents

| Document information | | Vibration resistance | 35 |
|--------------------------------|-----|--|----|
| Function and system design | | Process | |
| Measuring system | | Medium temperature range | |
| Device architecture | 5 | J | |
| Safety | 6 | Pressure tightness | |
| | | | 35 |
| Input | 6 | Pressure loss | |
| Measured variable | | | |
| Measuring range | | Vibrations | 36 |
| Operable flow range | 7 | | |
| Input signal | 7 | Mechanical construction | |
| | | Design, dimensions | |
| Output | 7 | Weight | |
| Output signal | | Measuring tube specification | |
| Signal on alarm | | Materials | |
| Low flow cut off | | Mounting bolts | |
| Galvanic isolation | 10 | Fitted electrodes | |
| Protocol-specific data | 10 | Frocess connections | 40 |
| Power supply | L5 | Operability | |
| Terminal assignment | | Operating concept | |
| Pin assignment, device plug | | Local operation | |
| | 19 | Remote operation | |
| Power consumption | | Service interface | 48 |
| Current consumption | | | |
| - | 20 | Certificates and approvals | 50 |
| | 20 | CE mark | |
| | 24 | C-Tick symbol | |
| | 25 | Drinking water approval | |
| Cable entries | 26 | Certification PROFIBUS | 51 |
| Cable specification | 26 | | 51 |
| | | EtherNet/IP certification | |
| Performance characteristics 2 | 28 | Other standards and guidelines | 51 |
| Reference operating conditions | | | |
| Maximum measured error | | Ordering information | 51 |
| Repeatability | | , | |
| | 29 | Application packages | 52 |
| | | Diagnostics functions | |
| Installation | o l | | |
| Mounting location | | real total recimiology | 2 |
| 3 | 30 | Assessments | |
| | 31 | | |
| | 31 | | 53 |
| | 31 | Communication-specific accessories | |
| | 32 | Service-specific accessories | |
| | 33 | System components | Э4 |
| • | 33 | | |
| - | | | 54 |
| Environment | 84 | Standard documentation | |
| | 34 | Supplementary device-dependent documentation | 55 |
| | 34 | | |
| · - | 34 | Registered trademarks | 55 |
| | 34 | - | |
| | 34 | | |
| | | | |

Document information

Symbols used

Electrical symbols

| Symbol | Meaning | Symbol | Meaning |
|--------|--|--------------|--|
| | Direct current | ~ | Alternating current |
| ≂ | Direct current and alternating current | - | Ground connection A grounded terminal which, as far as the operator is concerned, is grounded via a grounding system. |
| | Protective ground connection A terminal which must be connected to ground prior to establishing any other connections. | ♦ | Equipotential connection A connection that has to be connected to the plant grounding system: This may be a potential equalization line or a star grounding system depending on national or company codes of practice. |

Symbols for certain types of information

| Symbol | Meaning |
|----------|--|
| ✓ | Permitted Procedures, processes or actions that are permitted. |
| | Preferred Procedures, processes or actions that are preferred. |
| X | Forbidden Procedures, processes or actions that are forbidden. |
| i | Tip Indicates additional information. |
| [i] | Reference to documentation |
| A | Reference to page |
| | Reference to graphic |
| | Visual inspection |


Symbols in graphics

| Symbol | Meaning | Symbol | Meaning |
|------------|----------------|----------------|--------------------------------|
| 1, 2, 3, | Item numbers | 1. , 2. , 3 | Series of steps |
| A, B, C, | Views | A-A, B-B, C-C, | Sections |
| EX | Hazardous area | × | Safe area (non-hazardous area) |
| ≋ → | Flow direction | | |

Function and system design

Measuring principle

Following *Faraday's law of magnetic induction*, a voltage is induced in a conductor moving through a magnetic field.



A0017035

- Ue Induced voltage
- B Magnetic induction (magnetic field)
- L Electrode spacing
- I Current
- v Flow velocity

In the electromagnetic measuring principle, the flowing medium is the moving conductor. The voltage induced (U_e) is proportional to the flow velocity (v) and is supplied to the amplifier by means of two measuring electrodes. The flow volume (Q) is calculated via the pipe cross-section (A). The DC magnetic field is created through a switched direct current of alternating polarity.

Formulae for calculation

- Induced voltage $U_e = B \cdot L \cdot v$
- Volume flow $Q = A \cdot v$


Measuring system

The device consists of a transmitter and a sensor.

Two device versions are available:

- Compact version the transmitter and sensor form a mechanical unit.
- Remote version the transmitter and sensor are mounted separately from one another.

Transmitter




Device versions and materials

- Compact version: compact housing
 - Polycarbonate plastic
 - Aluminum, AlSi10Mg, coated
- Remote version: wall-mount housing
 - Polycarbonate plastic
 - Aluminum, AlSi10Mg, coated

Configuration:

- External operation via four-line, illuminated local display with touch control and guided menus ("Make-it-run" wizards) for applications
- Via operating tools (e.g. FieldCare)
- Via Web browser (e.g. Microsoft Internet Explorer)
- Also for device version with EtherNet/IP output:
 - Via Add-on Profile Level 3 for automation system from Rockwell Automation
 - Via Electronic Data Sheet (EDS)
- Also for device version with PROFIBUS DP output:
 Via PDM driver for Siemens automation system


Sensor



Wafer version

- Nominal diameter range: DN 25 to 100 (1 to 4")
- Materials
- Sensor housing: aluminum, AlSi10Mg, coated
- Sensor connection housing: aluminum, AlSi10Mg, coated
- Liner: polyamide
- O-rings: EPDM
- Electrodes: stainless steel, 1.4435 (316L)
- Ground disks: stainless steel, 1.4301 (304)

Device architecture



A002314

- $\ensuremath{\,\blacksquare}\xspace\,1$ Possibilities for integrating measuring devices into a system
- 1 Control system (e.g. PLC)
- 2 EtherNet/IP
- 3 PROFIBUS DP
- 4 4-20 mA HART, pulse/frequency/switch output
- 5 Non-hazardous area
- 6 Non-hazardous area and Zone 2/Div. 2

Safety

IT security

We only provide a warranty if the device is installed and used as described in the Operating Instructions. The device is equipped with security mechanisms to protect it against any inadvertent changes to the device settings.

IT security measures in line with operators' security standards and designed to provide additional protection for the device and device data transfer must be implemented by the operators themselves.

Input

Measured variable

Direct measured variables

Volume flow (proportional to induced voltage)

Calculated measured variables

Mass flow

Measuring range

Typically v = 0.01 to 10 m/s (0.03 to 33 ft/s) with the specified accuracy

Electrical conductivity: 5 to 10000 $\mu S/cm$

Flow characteristic values in SI units

| | ninal neter | Recommended flow | Factory settings | | |
|------|----------------|--|---|------------------------------|---------------------------------|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | Full scale value current output (v ~ 2.5 m/s) | Pulse value (~ 2 pulse/s) | Low flow cut off (v ~ 0.04 m/s) |
| [mm] | [in] | [dm³/min] | [dm³/min] | [dm³] | [dm³/min] |
| 25 | 1 | 9 to 300 | 75 | 0.5 | 1 |
| 40 | 1 ½ | 25 to 700 | 200 | 1.5 | 3 |
| 50 | 2 | 35 to 1100 | 300 | 2.5 | 5 |
| 65 | - | 60 to 2 000 | 500 | 5 | 8 |
| 80 | 3 | 90 to 3 000 | 750 | 5 | 12 |
| 100 | 4 | 145 to 4700 | 1200 | 10 | 20 |

Flow characteristic values in US units

| | inal ieter | Recommended flow | Factory settings | | |
|-------|---------------|--|---|------------------------------|---------------------------------|
| | | min./max. full scale value (v ~ 0.3/10 m/s) | Full scale value current output (v ~ 2.5 m/s) | Pulse value (~ 2 pulse/s) | Low flow cut off (v ~ 0.04 m/s) |
| [in] | [mm] | [gal/min] | [gal/min] | [gal] | [gal/min] |
| 1 | 25 | 2.5 to 80 | 18 | 0.2 | 0.25 |
| 1 1/2 | 40 | 7 to 190 | 50 | 0.5 | 0.75 |
| 2 | 50 | 10 to 300 | 75 | 0.5 | 1.25 |
| - | 65 | 16 to 500 | 130 | 1 | 2 |
| 3 | 80 | 24 to 800 | 200 | 2 | 2.5 |
| 4 | 100 | 40 to 1250 | 300 | 2 | 4 |



Recommended measuring range

"Flow limit" section ($\rightarrow \triangleq 35$)

Operable flow range

Over 1000:1

Input signal

External measured values



Various pressure transmitters and temperature measuring devices can be ordered from Endress +Hauser: see "Accessories" section (\rightarrow $\stackrel{\triangle}{=}$ 54)

It is recommended to read in external measured values to calculate the following measured variables: Corrected volume flow ${\bf v}$

HART protocol

The measured values are written from the automation system to the measuring device via the HART protocol. The pressure transmitter must support the following protocol-specific functions:

- HART protocol
- Burst mode

Fieldbuses

The measured values can be written from the automation system to the measuring via:

- PROFIBUS DP
- Modbus RS485
- EtherNet/IP

Status input

| Maximum input values | ■ DC 30 V ■ 6 mA | |
|----------------------|---|--|
| Response time | ljustable: 5 to 200 ms | |
| Input signal level | Low signal: DC -3 to +5 V High signal: DC 12 to 30 V | |
| Assignable functions | Off Reset totalizers 1-3 separately Reset all totalizers Flow override | |

Output

Output signal

Current output

| Current output | Can be set as: 4-20 mA NAMUR 4-20 mA US 4-20 mA HART 0-20 mA |
|-------------------------------|---|
| Maximum output values | DC 24 V (no flow)22.5 mA |
| Load | 0 to 700Ω |
| Resolution | 0.5 μΑ |
| Damping | Adjustable: 0.07 to 999 s |
| Assignable measured variables | Volume flow Mass flow Flow velocity Electronic temperature |

Pulse/frequency/switch output

| Function | With the order code for "Output; Input", option H: output 2 can be set as a pulse or frequency output With the order code for "Output; Input", option I: output 2 and 3 can be set as a pulse, frequency or switch output | |
|-------------------------------|--|--|
| Version | Passive, open collector | |
| Maximum input values | ■ DC 30 V ■ 250 mA | |
| Voltage drop | For 25 mA: ≤ DC 2 V | |
| Pulse output | | |
| Pulse width | Adjustable: 0.05 to 2 000 ms | |
| Maximum pulse rate | 10 000 Impulse/s | |
| Pulse value | Adjustable | |
| Assignable measured variables | Volume flowMass flow | |
| Frequency output | | |
| Output frequency | Adjustable: 0 to 12 500 Hz | |
| Damping | Adjustable: 0 to 999 s | |
| Pulse/pause ratio | 1:1 | |
| Assignable measured variables | Volume flow Mass flow Flow velocity Electronic temperature | |
| Switch output | | |
| Switching behavior | Binary, conductive or non-conductive | |
| Switching delay | Adjustable: 0 to 100 s | |
| Number of switching cycles | Unlimited | |
| Assignable functions | Off On Diagnostic behavior Limit value: Off Volume flow Mass flow Flow velocity Totalizer 1-3 Electronic temperature Flow direction monitoring Status Empty pipe detection Low flow cut off | |

PROFIBUS DP

| Signal encoding | NRZ code |
|-----------------|-------------------|
| Data transfer | 9.6 kBaud12 MBaud |

Modbus RS485

| Physical interface | In accordance with EIA/TIA-485-A standard |
|----------------------|---|
| Terminating resistor | Integrated, can be activated via DIP switch on the transmitter electronics module |

EtherNet/IP

| Standards | In accordance with IEEE 802.3 |
|-----------|-------------------------------|
|-----------|-------------------------------|

Signal on alarm

Depending on the interface, failure information is displayed as follows:

Current output

4-20 mA

| Failure mode | Selectable (as per NAMUR recommendation NE 43): |
|--------------|---|
| | ■ Minimum value: 3.6 mA |
| | ■ Maximum value: 22 mA |
| | ■ Defined value: 3.59 to 22.5 mA |
| | Actual value |
| | ■ Last valid value |

0-20 mA

| Failure mode | Choose from: |
|--------------|-------------------------------|
| | ■ Maximum alarm: 22 mA |
| | ■ Defined value: 0 to 22.5 mA |

HART

Pulse/frequency/switch output

| Pulse output | | |
|------------------|---|--|
| Failure mode | Choose from: Actual value No pulses | |
| Frequency output | Frequency output | |
| Failure mode | Choose from: Actual value Defined value: 0 to 12 500 Hz O Hz | |
| Switch output | | |
| Failure mode | Choose from: Current status Open Closed | |

PROFIBUS DP

| Status and alarm | Diagnostics in accordance with PROFIBUS PA Profile 3.02 |
|------------------|---|
| messages | |

Modbus RS485

| Failure mode | Choose from: |
|--------------|--|
| | NaN value instead of current value |
| | ■ Last valid value |

EtherNet/IP

| Device diagnostics | Device condition can be read out in Input Assembly |
|--------------------|--|
|--------------------|--|

Local display

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
| Backlight | Red backlighting indicates a device error. |



Status signal as per NAMUR recommendation NE 107

Operating tool

- Via digital communication:
 - HART protocol
 - PROFIBUS DP
 - Modbus RS485
 - EtherNet/IP
- Via service interface

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
|--------------------|---|



Additional information on remote operation ($\rightarrow \triangleq 47$)

Web browser

| Plain text display | With information on cause and remedial measures |
|--------------------|---|
|--------------------|---|

Light emitting diodes (LED)

| Status information | Status indicated by various light emitting diodes |
|--------------------|--|
| | The following information is displayed depending on the device version: Supply voltage active Data transmission active Device alarm/error has occurred EtherNet/IP network available EtherNet/IP connection established |

Low flow cut off

The switch points for low flow cut off are user-selectable.

Galvanic isolation

The following connections are galvanically isolated from each other:

- Inputs
- Outputs
- Power supply

Protocol-specific data

HART

| Manufacturer ID | 0x11 |
|------------------------------------|---|
| Device type ID | 0x67 |
| HART protocol revision | 7 |
| Device description files (DTM, DD) | Information and files under: www.endress.com |
| HART load | Min. 250 Ω |

10

| Dynamic variables | Read out the dynamic variables: HART command 3 The measured variables can be freely assigned to the dynamic variables. |
|-------------------|--|
| | Measured variables for PV (primary dynamic variable) Off Volume flow Mass flow Flow velocity Electronic temperature Measured variables for SV, TV, QV (secondary, tertiary and quaternary) |
| | dynamic variable) Volume flow Mass flow Flow velocity Electronic temperature Totalizer 1 Totalizer 2 Totalizer 3 |
| Device variables | Read out the device variables: HART command 9 The device variables are permanently assigned. A maximum of 8 device variables can be transmitted: 0 = volume flow 1 = mass flow 2 = conductivity 3 = flow velocity 4 = electronic temperature 5 = totalizer 1 6 = totalizer 2 7 = totalizer 3 |

PROFIBUS DP

| Manufacturer ID | 0x11 |
|--|---|
| Ident number | 0x1562 |
| Profile version | 3.02 |
| Device description files (GSD, DTM, DD) | Information and files under: www.endress.com www.profibus.org |
| Output values (from measuring device to automation system) | Analog input 1 to 4 Mass flow Volume flow Flow velocity Electronic temperature Digital input 1 to 2 Empty pipe detection Low flow cut off Verification status |
| | Totalizer 1 to 3 ■ Mass flow ■ Volume flow |

| Input values (from automation system to measuring device) | Analog output 1 (fixed assignment) External density Digital output 1 to 2 (fixed assignment) Digital output 1: switch positive zero return on/off Digital output 2: start verification Totalizer 1 to 3 Totalize Reset and hold Preset and hold Stop Operating mode configuration: Net flow total Forward flow total |
|---|--|
| Supported functions | Reverse flow total Identification & Maintenance Simplest device identification on the part of the control system and nameplate PROFIBUS upload/download Reading and writing parameters is up to ten times faster with PROFIBUS upload/download Condensed status Simplest and self-explanatory diagnostic information by categorizing diagnostic messages that occur |
| Configuration of the device address | DIP switches on the I/O electronics module Via operating tools (e.g. FieldCare) |

Modbus RS485

| Protocol | Modbus Applications Protocol Specification V1.1 | | |
|-------------------------|--|--|--|
| Device type | Slave | | |
| Slave address range | 1 to 247 | | |
| Broadcast address range | 0 | | |
| Function codes | 03: Read holding register 04: Read input register 06: Write single registers 08: Diagnostics 16: Write multiple registers 23: Read/write multiple registers | | |
| Broadcast messages | Supported by the following function codes: O6: Write single registers 16: Write multiple registers 23: Read/write multiple registers | | |
| Supported baud rate | ■ 1200 BAUD ■ 2400 BAUD ■ 4800 BAUD ■ 9600 BAUD ■ 19200 BAUD ■ 38400 BAUD ■ 57600 BAUD ■ 115200 BAUD | | |
| Data transfer mode | ASCII RTU | | |
| Data access | Each device parameter can be accessed via Modbus RS485. For Modbus register information | | |

EtherNet/IP

| Protocol | The CIP Networks Library Volume 1: Common Industrial Protocol The CIP Networks Library Volume 2: EtherNet/IP Adaptation of CIP | | | | |
|--|--|---|---------------|--|--|
| Communication type | ■ 10Base-T ■ 100Base-TX | | | | |
| Device profile | Generic device (product type | Generic device (product type: 0x2B) | | | |
| Manufacturer ID | 0x49E | | | | |
| Device type ID | 0x1067 | | | | |
| Baud rates | Automatic ¹⁰ / ₁₀₀ Mbit with h | alf-duplex and full-duple | x detection | | |
| Polarity | Auto-polarity for automatic | correction of crossed TxI | and RxD pairs | | |
| Supported CIP connections | Max. 3 connections | | | | |
| Explicit connections | Max. 6 connections | | | | |
| I/O connections | Max. 6 connections (scanne | r) | | | |
| Configuration options for measuring device | Manufacturer-specific sofAdd-on Profile Level 3 forWeb browser | DIP switches on the electronics module for IP addressing Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser Electronic Data Sheet (EDS) integrated in the measuring device | | | |
| Configuration of the EtherNet interface | Speed: 10 MBit, 100 MBiDuplex: half-duplex, full-o | | ing) | | |
| Configuration of the device address | DIP switches on the electronics module for IP addressing (last octet) DHCP Manufacturer-specific software (FieldCare) Add-on Profile Level 3 for Rockwell Automation control systems Web browser EtherNet/IP tools, e.g. RSLinx (Rockwell Automation) | | | | |
| Device Level Ring (DLR) | No | | | | |
| Fix Input | | | | | |
| RPI | 5 ms to 10 s (factory setting | : 20 ms) | | | |
| Exclusive Owner Multicast | | Instance | Size [byte] | | |
| | Instance configuration: | 0x68 | 398 | | |
| | $O \rightarrow T$ configuration: | 0x66 | 56 | | |
| | $T \rightarrow O$ configuration: | 0x64 | 32 | | |
| Exclusive Owner Multicast | | Instance | Size [byte] | | |
| | Instance configuration: | 0x69 | - | | |
| | $O \rightarrow T$ configuration: | 0x66 | 56 | | |
| | $T \rightarrow O$ configuration: | 0x64 | 32 | | |
| Input only Multicast | | Instance | Size [byte] | | |
| | Instance configuration: | 0x68 | 398 | | |
| | $O \rightarrow T$ configuration: | 0xC7 | - | | |
| | $T \rightarrow O$ configuration: | 0x64 | 32 | | |
| Input only Multicast | | Instance | Size [byte] | | |
| | Instance configuration: | 0x69 | - | | |
| | O → T configuration: | 0xC7 | - | | |
| | $T \rightarrow O$ configuration: | 0x64 | 32 | | |

| Input Assembly | Current device diagnostics Volume flow Mass flow Totalizer 1 Totalizer 2 Totalizer 3 | | |
|-----------------------------|---|----------|---------------------|
| Configurable Input | <u>'</u> | | |
| RPI | 5 ms to 10 s (factory setting: | 20 ms) | |
| Exclusive Owner Multicast | | Instance | Size [byte] |
| | Instance configuration: | 0x68 | 398 |
| | $O \rightarrow T$ configuration: | 0x66 | 56 |
| | $T \rightarrow O$ configuration: | 0x65 | 88 |
| Exclusive Owner Multicast | | Instance | Size [byte] |
| | Instance configuration: | 0x69 | - |
| | $O \rightarrow T$ configuration: | 0x66 | 56 |
| | $T \rightarrow 0$ configuration: | 0x65 | 88 |
| Input only Multicast | | Instance | Size [byte] |
| | Instance configuration: | 0x68 | 398 |
| | O → T configuration: | 0xC7 | - |
| | $T \rightarrow 0$ configuration: | 0x65 | 88 |
| Input only Multicast | | Instance | Size [byte] |
| | Instance configuration: | 0x69 | - |
| | $O \rightarrow T$ configuration: | 0xC7 | - |
| | $T \rightarrow O$ configuration: | 0x65 | 88 |
| Configurable Input Assembly | Volume flow Mass flow Electronic temperature Totalizer 1 to 3 Flow velocity Volume flow unit Mass flow unit Temperature unit Unit totalizer 1-3 Flow velocity unit Verification result Verification status | | g device has one or |
| Fix Output | more application packa | yes. | |
| Output Assembly | Activation of reset totalize Activation of reference der Reset totalizers 1-3 External density Density unit Activation verification Start verification | | |

| Configuration | | | | |
|---------------------------------------|--|--|--|--|
| Configuration Configuration Assembly | Only the most common configurations are listed below. Software write protection Mass flow unit Mass unit Volume flow unit Volume unit Density unit Temperature unit Totalizer 1-3: Assignment Unit | | | |
| | Unit Measuring mode Failure mode Alarm delay | | | |

Power supply


Terminal assignment

Transmitter

 $0-20\ mA/4-20\ mA$ HART connection version with additional outputs and inputs

The sensor can be ordered with terminals.

| Connection me | thods available | Possible options for order code |
|---------------|-----------------|--|
| Outputs | Power supply | "Electrical connection" |
| Terminals | Terminals | Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½" |



- Supply voltage
- Output 1 (26/27) and output 2 (24/25)
- Output 3 (22/23) and input 1 (20/21)

Supply voltage

| Order code for "Power supply" | Terminal numbers | | |
|-------------------------------|------------------|----------|--|
| | 1 (L+/L) | 2 (L-/N) | |
| Option L | AC100 | to 240 V | |
| (wide range power unit) | AC/D | C24 V | |


Signal transmission 0-20 mA/4-20 mA HART with additional outputs and inputs

| Order code for | Terminal numbers | | | | | | | |
|-------------------------|------------------|--------------------------------------|-------------------------|-----------------------------|------------------------------|--------|--------|--------|
| "Output" and "Input" | Outp | Output 1 Output 2 Output | | Output 1 | | out 3 | Inp | out |
| | 26 (+) | 27 (-) | 24 (+) | 25 (-) | 22 (+) | 23 (-) | 20 (+) | 21 (-) |
| Option H | (a) | mA HART ctive) 20 mA ctive) | Pulse/fr out (pas | . , | Switch (pass | | - | - |
| Option I | (a) | nA HART ctive) 20 mA ctive) | switch | equency/ output sive) | Pulse/fre switch (pass | output | Status | input |

PROFIBUS DP connection version

The sensor can be ordered with terminals.

| Connection me | thods available | Possible options for order code | |
|---------------|-----------------|--|--|
| Outputs | Power supply | "Electrical connection" | |
| Terminals | Terminals | Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½" | |



- Supply voltage (wide range power unit) PROFIBUS DP
- 2

Supply voltage

| Order code for "Power supply" | Terminal numbers | | |
|-------------------------------|------------------|----------|--|
| | 1 (L+/L) | 2 (L-/N) | |
| Option L | AC100 | to 240 V | |
| (wide range power unit) | AC/DC24 V | | |

16


PROFIBUS DP signal transmission

| Order code for "Output" and "Input" | Terminal numbers | |
|---|------------------|----------------|
| | 26 (RxD/TxD-P) | 27 (RxD/TxD-N) |
| Option L | В | A |
| Order code for "Output": Option L: PROFIBUS DP, for use in non-hazardous areas and Zone 2/div. 2 | | |

Modbus RS485 connection version

The sensor can be ordered with terminals.

| Connection methods available | | Descible entions for order sade | |
|------------------------------|-----------------|--|--|
| Outputs | Power supply | Possible options for order code "Electrical connection" | |
| Terminals | Terminals | Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½" | |



- Supply voltage (wide range power unit) Modbus RS485

Supply voltage

| Order code for "Power supply" | Terminal numbers | |
|-------------------------------|------------------|----------|
| | 1 (L+/L) | 2 (L-/N) |
| Option L | AC100 | to 240 V |
| (wide range power unit) | AC/DC24 V | |


Signal transmission Modbus RS485

| Order code for "Output" and "Input" | Terminal numbers | | |
|-------------------------------------|------------------|--------|--|
| | 26 (+) | 27 (-) | |
| Option M | A | В | |

EtherNet/IP connection version

The sensor can be ordered with terminals or a device plug.

| Connection methods available | | Descible entions for order sede | |
|------------------------------|--------------|--|--|
| Outputs | Power supply | Possible options for order code "Electrical connection" | |
| Terminals | Terminals | Option A: coupling M20x1 Option B: thread M20x1 Option C: thread G ½" Option D: thread NPT ½" | |
| Device plug | Terminals | Option L: plug M12x1 + thread NPT ½" Option N: plug M12x1 + coupling M20 Option P: plug M12x1 + thread G ½" Option U: plug M12x1 + thread M20 | |



- Supply voltage (wide range power unit) EtherNet/IP


Supply voltage

| Order code for "Power supply" | Terminal numbers | | |
|-------------------------------|------------------|----------|--|
| | 1 (L+/L) | 2 (L-/N) | |
| Option L | AC100 t | to 240 V | |
| (wide range power unit) | AC/DC24 V | | |

EtherNet/IP signal transmission

| Order code for "Output" | Connection via |
|-------------------------|-----------------------|
| Option N | EtherNet/IP connector |

Remote version



- **₽** 2 Remote version terminal assignment
- Transmitter wall-mount housing
- В Sensor connection housing
- Electrode cable
- 2 Coil current cable
- n.c. Not connected, insulated cable shields

Terminal No. and cable colors: 6/5 = brown; 7/8 = white; 4 = green

Pin assignment, device plug



Order codes for the M12x1 connectors, see the "Order code for electrical connection" column: EtherNet/IP (→ 🖺 18)

EtherNet/IP

Device plug for signal transmission (device side)

| 2 | Pin | | Assignment | Coding | Plug/socket |
|---------------|-----|---|------------|--------|-------------|
| | 1 | + | Tx | D | Socket |
| 1 3 | 2 | + | Rx | | |
| | 3 | - | Tx | | |
| | 4 | - | Rx | | |
| 4 A0016812 | | | | | |



- Recommended plug:
 Binder, series 763, part no. 99 3729 810 04
 - Phoenix, part no. 1543223 SACC-M12MSD-4Q
 - When using the device in a hazardous location, use a suitably certified plug.

Supply voltage

Transmitter

| Order code for "Power supply" | Terminal voltage | Frequency range |
|-------------------------------|------------------|------------------|
| Option L | AC100 to 240 V | 50/ 60 Hz, ±4 Hz |
| Option L | AC/DC24 V | 50/ 60 Hz, ±4 Hz |

Power consumption

| Order code for "Output" | Maximum power consumption |
|---|---------------------------|
| Option H : 0/4-20mA HART, pulse/frequency/switch output, switch output | 30 VA/8 W |
| Option I: 0/4-20mA HART, 2 x pulse/frequency/switch output, status input | 30 VA/8 W |
| Option L: PROFIBUS DP | 30 VA/8 W |
| Option M : Modbus RS485 | 30 VA/8 W |
| Option N : EtherNet/IP | 30 VA/8 W |

Current consumption

Transmitter


| Order code for "Power supply" | Maximum Current consumption | Maximum switch-on current |
|-----------------------------------|--------------------------------|------------------------------|
| Option L : AC 100 to 240 V | 145 mA | 25 A (< 5 ms) |
| Option L: AC/DC 24 V | 350 mA | 27 A (< 5 ms) |

Power supply failure

- Totalizers stop at the last value measured.
- Configuration is retained in the plug-in memory (HistoROM DAT).
- Error messages (incl. total operated hours) are stored.

Electrical connection

Connecting the transmitter




₩ 3 Supply voltage and signal transmission connection

- Compact version Α
- В Remote version wall-mount housing
- Cable entry for supply voltage
- Cable entry for signal transmission

Remote version connection

Connecting cable




€ 4 Connecting cable connection: electrode and coil current cable

- Transmitter wall-mount housing Α
- В Sensor connection housing
- Electrode cable 1
- 2 Coil current cable

- Fix the cable run or route it in an armored conduit.
 Cable movements can influence the measuring signal especially in the case of low fluid conductivities.
- Route the cable well clear of electrical machines and switching elements.
- Ensure potential equalization between sensor and transmitter .

Connection examples


Current output 4-20 mA HART



A0016800

- **■** 5 Connection example for 4-20 mA HART current output (active)
- 1 Automation system with current input (e.g. PLC)
- *2* Cable shield, observe cable specifications ($\rightarrow \stackrel{\triangle}{=} 26$)
- *3* Connection for HART operating devices (→ 🖺 47)
- 4 Resistor for HART communication (\geq 250 Ω): observe maximum load (\rightarrow \cong 7)
- 5 Analog display unit: observe maximum load ($\rightarrow \square 7$)
- 6 Transmitter


Current output 4-20 mA



A0017162

- 6 Connection example for 0-20 mA current output (active) and 4-20 mA current output (active)
- 1 Automation system with current input (e.g. PLC)
- 2 Analog display unit: observe maximum load ($\rightarrow \square 7$)
- 3 Transmitter


Pulse/frequency output



 \blacksquare 7 Connection example for pulse/frequency output (passive)


- 1 Automation system with pulse/frequency input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values ($\Rightarrow \triangleq 8$)

Switch output



- 8 Connection example for switch output (passive)
- 1 Automation system with switch input (e.g. PLC)
- 2 Power supply
- 3 Transmitter: observe input values ($\rightarrow \triangleq 8$)

PROFIBUS DP




■ 9 Connection example for PROFIBUS DP, non-hazardous area and Zone 2/Div. 2

- 1 Control system (e.g. PLC)
- 3 Transmitter

22


If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.

Modbus RS485



- 10 Connection example for Modbus RS485, non-hazardous area and Zone 2/Div. 2
- 1 Control system (e.g. PLC)
- 2 Cable shield: the cable shield must be grounded at both ends to comply with EMC requirements; observe cable specifications $(\rightarrow \ \ \ \ \ \ \ \ \ \ \)$
- 3 Distribution box
- 4 Transmitter


EtherNet/IP



A001680

- 11 Connection example for EtherNet/IP
- 1 Control system (e.g. PLC)
- 2 Ethernet switch
- 3 Observe cable specifications ($\rightarrow \stackrel{\triangle}{=} 27$)
- 4 Device plug
- 5 Transmitter

Status input



■ 12 Connection example for status input

- Automation system with status output (e.g. PLC)
- Power supply 2
- *Transmitter: observe input values*

Potential equalization

Requirements

Please consider the following to ensure correct measurement:


- Same electrical potential for the fluid and sensor
- Remote version: same electrical potential for the sensor and transmitter
- Company-internal grounding concepts
- Pipe material and grounding

Connection examples for standard situations

Metal, grounded pipe

This connection method also applies:

- For plastic pipes
- For pipes with insulating liner



Connection example in special situations


Unlined and ungrounded metal pipe

This connection method also applies in situations where:

- The customary potential equalization is not used
- Equalizing currents are present

Ground cable Copper wire, at least6 mm² (0.0093 in²)

24



Note the following when installing:


- Connect both pipe flanges to one another via a ground cable and ground them.
- Connect the connection housing of the transmitter or sensor to ground potential by means of the ground terminal provided for the purpose. Mount the ground cable directly on the conductive flange coating of the pipe with the flange screws.
- For remote device versions, the ground terminal in the example always refers to the sensor and **not** to the transmitter.
- The necessary ground cable can be ordered from Endress+Hauser .

Pipe with a cathodic protection unit

This connection method is only used if the following two conditions are met:

- Metal pipe without liner or pipe with electrically conductive liner
- Cathodic protection is integrated in the personal protection equipment

Ground cable Copper wire, at least6 mm² (0.0093 in²)



A0017518

Prerequisite: The sensor is installed in the pipe in a way that provides electrical insulation.

- 1. Connect the two flanges of the pipe to one another via a ground cable.
- 2. Guide the shield of the signal lines through a capacitor.
- 3. Connect the measuring device to the power supply such that it is floating in relation to the protective ground (isolation transformer).
- For remote device versions, the ground terminal in the example always refers to the sensor and **not** to the transmitter.
- The necessary ground cable can be ordered from Endress+Hauser .

Terminals

Transmitter

- Supply voltage cable: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)
- Signal cable: plug-in spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)
- Electrode cable: spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)
- Coil current cable: spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)

Sensor connection housing

Spring terminals for wire cross-sections 0.5 to 2.5 mm² (20 to 14 AWG)

Cable entries

Cable entry thread

- M20 x 1.5
- Via adapter:
 - NPT ½"
 - G ½"

Cable gland

- For standard cable: M20 × 1.5 with cable ϕ 6 to 12 mm (0.24 to 0.47 in)
- For reinforced cable: M20 × 1.5 with cable ϕ 9.5 to 16 mm (0.37 to 0.63 in)



If metal cable entries are used, use a grounding plate.

Cable specification

Permitted temperature range

- -40 °C (-40 °F) to +80 °C (+176 °F)
- Minimum requirement: cable temperature range ≥ ambient temperature +20 K

Power supply cable

Standard installation cable is sufficient.

Signal cable

Current output

- For 0-20 mA and 4-20 mA: standard installation cable is sufficient.
- For 4-20 mA HART: Shielded cable recommended. Observe grounding concept of the plant.

Pulse/frequency/switch output

Standard installation cable is sufficient.

Status input

Standard installation cable is sufficient.

PROFIBUS DP

The IEC 61158 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

| Cable type | A |
|--------------------------|--|
| Characteristic impedance | 135 to 165 Ω at a measuring frequency of 3 to 20 MHz |
| Cable capacitance | <30 pF/m |
| Wire cross-section | >0.34 mm ² (22 AWG) |
| Cable type | Twisted pairs |
| Loop resistance | ≤110 Ω/km |
| Signal damping | Max. 9 dB over the entire length of the cable cross-section |
| Shielding | Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant. |

Modbus RS485

The EIA/TIA-485 standard specifies two types of cable (A and B) for the bus line which can be used for every transmission rate. Cable type A is recommended.

| Cable type | A |
|--------------------------|---|
| Characteristic impedance | 135 to 165 Ω at a measuring frequency of 3 to 20 MHz |
| Cable capacitance | <30 pF/m |

| Wire cross-section | >0.34 mm ² (22 AWG) |
|--------------------|--|
| Cable type | Twisted pairs |
| Loop resistance | ≤110 Ω/km |
| Signal damping | Max. 9 dB over the entire length of the cable cross-section |
| Shielding | Copper braided shielding or braided shielding with foil shield. When grounding the cable shield, observe the grounding concept of the plant. |

EtherNet/IP

The standard ANSI/TIA/EIA-568-B.2 Annex specifies CAT 5 as the minimum category for a cable used for EtherNet/IP. CAT 5e and CAT 6 are recommended.

For more information on planning and installing EtherNet/IP networks, please refer to the "Media Planning and Installation Manual. EtherNet/IP" of ODVA Organization.


Connecting cable for remote version

Electrode cable

| Standard cable | $3\times0.38~mm^2$ (20 AWG) with common, braided copper shield (4 $\sim\!\!7$ mm (0.28 in) and individual shielded cores |
|--------------------------|--|
| Conductor resistance | ≤50 Ω/km (0.015 Ω/ft) |
| Capacitance: core/shield | <420 pF/m (128 pF/ft) |
| Operating temperature | −20 to +80 °C (−68 to +176 °F) |

Coil current cable

| Standard cable | $2\times0.75~mm^2$ (18 AWG) with common, braided copper shield (4 $\sim7~mm$ (0.28")) and individually shielded cores |
|---|---|
| Conductor resistance | ≤37 Ω/km (0.011 Ω/ft) |
| Capacitance: core/core, shield grounded | ≤120 pF/m (37 pF/ft) |
| Operating temperature | −20 to +80 °C (−68 to +176 °F) |
| Test voltage for cable insulation | ≤ AC 1433 V r.m.s. 50/60 Hz or ≥ DC 2026 V |



A0003194

■ 13 Cable cross-section

- a Electrode cable
- b Coil current cable
- Core
- 2 Core insulation
- 3 Core shield
- 4 Core jacket
- 5 Core reinforcement
- 6 Cable shield
- 7 Outer jacket

Operation in zones of severe electrical interference

The measuring system meets the general safety requirements (→ 🖺 51) and EMC specifications (→ 🖺 35).

Grounding is by means of the ground terminal provided for the purpose inside the connection housing. The stripped and twisted lengths of cable shield to the ground terminal must be as short as

Performance characteristics

Reference operating conditions

In accordance with DIN EN 29104

- Fluid temperature: +28±2 °C (+82±4 °F)
- Ambient temperature range: +22±2 °C (+72±4 °F)
- Warm-up period:30 min

Installation

- Inlet run > 10 × DN
- Outlet run > 5 × DN
- Sensor and transmitter grounded.
- The sensor is centered in the pipe.



To calculate the measuring range, use the *Applicator* sizing tool ($\rightarrow \triangleq 54$)

Maximum measured error

Error limits under reference operating conditions


o.r. = of reading

Volume flow

 ± 0.5 % o.r. ± 1 mm/s (0.04 in/s)



Fluctuations in the supply voltage do not have any effect within the specified range.



Maximum measured error in % o.r.

Accuracy of outputs

o.r. = of reading

The outputs have the following base accuracy specifications.

Current output

| Accuracy | Max. ±5 μA |
|----------|------------|
| _ | · · |

Pulse/frequency output

| Accuracy | Max. ±50 ppm o.r. (across the complete ambient temperature range) |
|----------|---|
| _ | |

Repeatability

o.r. = of reading

Volume flow

Max. ± 0.1 % o.r. ± 0.5 mm/s (0.02 in/s)

Influence of ambient temperature

o.r. = of reading; o.f.s. = of full scale value

Current output

| Temperature coefficient | Typically ± 50 ppm/°C o.r. or ± 1 μ A/°C |
|-------------------------|--|


Pulse/frequency output

| Temperature coefficient | Max.±0.5 ppm v.M./°C |
|-------------------------|----------------------|
| Temperature coefficient | Max.±0.5 ppm v.M./ C |

Installation

No special measures such as supports are necessary. External forces are absorbed by the construction of the device.

Mounting location



Preferably install the sensor in an ascending pipe, and ensure a sufficient distance to the next pipe elbow: $h \ge 2 \times DN$


To prevent measuring errors arising from accumulation of gas bubbles in the measuring tube, avoid the following mounting locations in the pipe:

- Highest point of a pipeline.
- Directly upstream of a free pipe outlet in a down pipe.

Installation in down pipes

Install a siphon with a vent valve downstream of the sensor in down pipes whose length $h \ge 1$ 5 m (16.4 ft). This precaution is to avoid low pressure and the consequent risk of damage to the measuring tube. This measure also prevents the system losing prime.

For information on the liner's resistance to partial vacuum ($\rightarrow \implies 35$)




 \blacksquare 15 Installation in a down pipe

- 1 Vent valve
- 2 Pipe siphon
- h Length of down pipe

Installation in partially filled pipes

A partially filled pipe with a gradient necessitates a drain-type configuration. The empty pipe detection (EPD) function offers additional protection by detecting empty or partially filled pipes.




A0017063

Orientation

The direction of the arrow on the sensor nameplate helps you to install the sensor according to the flow direction (direction of medium flow through the piping).

An optimum orientation position helps avoid gas and air accumulations and deposits in the measuring tube.


Vertical



A001559

Optimum for self-emptying pipe systems.

Horizontal



A0017195


1 Measuring electrodes for signal detection

i

The measuring electrode plane must be horizontal. This prevents brief insulation of the two measuring electrodes by entrained air bubbles.

Inlet and outlet runs

If possible, install the sensor upstream from fittings such as valves, T-pieces or elbows. Observe the following inlet and outlet runs to comply with accuracy specifications:




Δ0016275

Adapters

Suitable adapters to DIN EN 545 (double-flange reducers) can be used to install the sensor in larger-diameter pipes. The resultant increase in the rate of flow improves measuring accuracy with very slow-moving fluids.

The nomogram shown here can be used to calculate the pressure loss caused by reducers and expanders:

- Calculate the ratio of the diameters d/D.
- From the nomogram read off the pressure loss as a function of flow velocity (downstream from the reduction) and the d/D ratio.
- The nomogram only applies to liquids with a viscosity similar to that of water.




A0016359

Mounting kit

The sensor is installed between the pipe flanges using a mounting kit. The device is centered using the recesses on the sensor. Centering sleeves are also provided depending on the flange standard or the diameter of the pitch circle.

i



■ 16 Mounting the sensor


- 1 Nut
- 2 Washer
- 3 Mounting bolts
- 4 Centering sleeve
- 5 Seal

Length of connecting cable

To ensure correct measuring results when using the remote version,

observe the maximum permitted cable length L_{max} . This length is determined by the conductivity of the fluid.

If measuring liquids in general: $5 \mu S/cm$




Permitted length of connecting cable for remote version

Area shaded gray = permitted range L_{max} =length of connecting cable in [m] ([ft]) [μ S/cm] = fluid conductivity


Installing the wall-mount housing

Wall mounting



■ 18 Engineering unit mm (in)

Post mounting



🖪 19 Engineering unit mm (in)

Special mounting instructions

Display protection

To ensure that the optional display protection can be easily opened, maintain the following minimum head clearance: 350 mm (13.8 in)

Environment

Ambient temperature range

| Transmitter | -40 to +60 °C (-40 to +140 °F) |
|---------------|---|
| Local display | -20 to $+60$ °C (-4 to $+140$ °F), the readability of the display may be impaired at temperatures outside the temperature range. |
| Sensor | -20 to +60 °C (-4 to +140 °F) |
| | Mount the transmitter separately from the sensor if both the ambient and fluid temperatures are high. |
| Liner | Do not exceed or fall below the permitted temperature range of the liner ($\rightarrow \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ $ |

If operating outdoors:

- Install the measuring device in a shady location.
- Avoid direct sunlight, particularly in warm climatic regions.
- Avoid direct exposure to weather conditions.
- Protect the display against impact.
- Protect the display from abrasion by sand in desert areas.



Storage temperature

The storage temperature corresponds to the operating temperature range of the measuring transmitter and the appropriate measuring sensors.

- Protect the measuring device against direct sunlight during storage in order to avoid unacceptably high surface temperatures.
- Select a storage location where moisture cannot collect in the measuring device as fungus or bacteria infestation can damage the liner.
- If protection caps or protective covers are mounted these should never be removed before installing the measuring device.

Atmosphere

If a plastic transmitter housing is permanently exposed to certain steam and air mixtures, this can damage the housing.



If you are unsure, please contact your Endress+Hauser Sales Center for clarification.

Degree of protection

Transmitter

- As standard: IP66/67, type 4X enclosure
- When housing is open: IP20, type 1 enclosure

Sensor

As standard: IP66/67, type 4X enclosure

Shock resistance

Compact version

6 ms 30 g, according to IEC 60068-2-27

Remote version

- Transmitter: 6 ms 30 g, according to IEC 60068-2-27
- Sensor: 6 ms 50 g, according to IEC 60068-2-27

Vibration resistance

Compact version

- Vibration sinusoidal, 1 g peak, according to IEC 60068-2-6
- Vibration broad-band random, 1.54 g rms, according to IEC 60068-2-64

Remote version

- Transmitter
 - Vibration sinusoidal, 1 g peak, according to IEC 60068-2-6
 - Vibration broad-band random, 1.54 g rms, according to IEC 60068-2-64
- Sensor:
 - Vibration sinusoidal, 2 g peak, according to IEC 60068-2-6
 - Vibration broad-band random, 2.70 g rms, according to IEC 60068-2-64

Mechanical load

- Protect the transmitter housing against mechanical effects, such as shock or impact; the use of the remote version is sometimes preferable.
- Never use the transmitter housing as a ladder or climbing aid.

Electromagnetic compatibility (EMC)

- As per IEC/EN 61326 and NAMUR Recommendation 21 (NE 21)
- Complies with emission limits for industry as per EN 55011 (Class A)
- Device version with PROFIBUS DP: Complies with emission limits for industry as per EN 50170 Volume 2, IEC 61784
- The following applies for PROFIBUS DP: If baud rates > 1.5 MBaud an EMC cable entry must be used and the cable shield must continue as far as the terminal wherever possible.
- For details refer to the Declaration of Conformity.


Process

Medium temperature range

0 to +60 °C (+32 to +140 °F) for polyamide

Pressure-temperature ratings

Permitted process pressure



Pressure tightness

Measuring tube: 0 mbar abs. (0 psi abs.) at a medium temperature of \leq +60 °C (+140 °F)

Flow limit


The diameter of the pipe and the flow rate determine the nominal diameter of the sensor. The optimum velocity of flow is between 2 to 3 m/s (6.56 to 9.84 ft/s). Also match the velocity of flow (v) to the physical properties of the fluid:

- v < 2 m/s (6.56 ft/s): for abrasive fluids (e.g. potter's clay, lime milk, ore slurry)
- v > 2 m/s (6.56 ft/s): for fluids producing buildup (e.g. wastewater sludges)
- A necessary increase in the flow velocity can be achieved by reducing the sensor nominal diameter.
- For an overview of the measuring range full scale values, see the "Measuring range" section

Pressure loss

- No pressure loss occurs if the sensor is installed in a pipe with the same nominal diameter.

System pressure



Never install the sensor on the pump suction side in order to avoid the risk of low pressure, and thus damage to the liner.


- Furthermore, install pulse dampers if reciprocating, diaphragm or peristaltic pumps are used.
- For information on the liner's resistance to partial vacuum (→ 🖺 35)
 - Information on the shock resistance of the measuring system ($\rightarrow \triangleq 34$)
 - Information on the vibration resistance of the measuring system ($\rightarrow \implies 34$)

Vibrations

In the event of very strong vibrations, the pipe and sensor must be supported and fixed.

It is also advisable to mount the sensor and transmitter separately.

Information on the shock resistance of the measuring system ($\rightarrow \cong 34$)
Information on the vibration resistance of the measuring system ($\rightarrow \cong 34$)



■ 20 Measures to avoid device vibrations (L > 10 m (33 ft))


36

Mechanical construction

Design, dimensions

Compact version

 $Order\ code\ for\ "Housing",\ option\ M\ "Compact,\ Polycarbonate"\ or\ option\ A\ "Compact,\ alu,\ coated"$



21 € 21 Engineering unit mm (in)

Dimensions in SI units

| DN 1) | Α | В | С | D | E | F | G | Н | d1 | d2 | e1 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|------------------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 25 | 193 | 103 | 90 | 167 | 190 | 43 | 233 | 55 | 86 | 24 | 68 |
| 40 | 193 | 103 | 90 | 167 | 201 | 52 | 253 | 69 | 104 | 38 | 87 |
| 50 | 193 | 103 | 90 | 167 | 212 | 62 | 274 | 83 | 124 | 50 | 106 |
| 65 | 193 | 103 | 90 | 167 | 222 | 70 | 292 | 93 | 139 | 60 | 125 |
| 80 | 193 | 103 | 90 | 167 | 226 | 75 | 301 | 117 | 151 | 76 | 135 |
| 100 | 193 | 103 | 90 | 167 | 240 | 89 | 329 | 148 | 179 | 97 | 160 |

EN (DIN), JIS


max. Ø seals

Dimensions in US units

| DN 1) | Α | В | С | D | E | F | G | Н | d1 | d2 | e1 ²⁾ | e2 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|------------------|------------------|
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| 1 | 7.60 | 4.06 | 3.54 | 6.57 | 7.48 | 1.69 | 9.17 | 2.17 | 3.39 | 0.94 | 2.68 | - |
| 1 ½ | 7.60 | 4.06 | 3.54 | 6.57 | 7.91 | 2.05 | 9.96 | 2.72 | 4.11 | 1.50 | 3.43 | - |
| 2 | 7.60 | 4.06 | 3.54 | 6.57 | 8.35 | 2.44 | 10.8 | 3.27 | 4.88 | 1.97 | 4.17 | - |
| 3 | 7.60 | 4.06 | 3.54 | 6.57 | 8.90 | 2.95 | 11.9 | 4.61 | 5.94 | 2.99 | - | 5.43 |
| 4 | 7.60 | 4.06 | 3.54 | 6.57 | 9.45 | 3.50 | 13.0 | 5.83 | 7.05 | 3.82 | 6.30 | - |

- 1) 2) ASME
- max. Ø seals

Order code for "Housing", option Q "Compact, Polycarbonate, tilted" or option R "Compact, alu, coated, tilted"



№ 22 Engineering unit mm (in)

Dimensions in SI units

| DN 1) | Α | В | С | D | Е | F | G | Н | d1 | d2 | e1 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|------------------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 25 | 199 | 119 | 80 | 167 | 235 | 43 | 278 | 55 | 86 | 24 | 68 |
| 40 | 199 | 119 | 80 | 167 | 246 | 52 | 298 | 69 | 104 | 38 | 87 |
| 50 | 199 | 119 | 80 | 167 | 257 | 62 | 319 | 83 | 124 | 50 | 106 |

| DN 1) | Α | В | С | D | E | F | G | Н | d1 | d2 | e1 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|------------------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 65 | 199 | 119 | 80 | 167 | 267 | 70 | 337 | 93 | 139 | 60 | 125 |
| 80 | 199 | 119 | 80 | 167 | 271 | 75 | 346 | 117 | 151 | 76 | 135 |
| 100 | 199 | 119 | 80 | 167 | 285 | 89 | 374 | 148 | 179 | 97 | 160 |

- EN (DIN), JIS max. Ø seals
- 1) 2)


Dimensions in US units

| DN 1) | Α | В | С | D | E | F | G | Н | d1 | d2 | e1 ²⁾ | e2 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|------------------|------------------|
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| 1 | 7.83 | 4.69 | 3.15 | 6.57 | 9.25 | 1.69 | 10.9 | 2.17 | 3.39 | 0.94 | 2.68 | - |
| 1 ½ | 7.83 | 4.69 | 3.15 | 6.57 | 9.69 | 2.05 | 11.7 | 2.72 | 4.11 | 1.50 | 3.43 | - |
| 2 | 7.83 | 4.69 | 3.15 | 6.57 | 10.1 | 2.44 | 12.6 | 3.27 | 4.88 | 1.97 | 4.17 | - |
| 3 | 7.83 | 4.69 | 3.15 | 6.57 | 10.7 | 2.95 | 13.6 | 4.61 | 5.94 | 2.99 | - | 5.43 |
| 4 | 7.83 | 4.69 | 3.15 | 6.57 | 11.2 | 3.50 | 14.7 | 5.83 | 7.05 | 3.82 | 6.30 | - |

- ASME 1)
- 2) max. Ø seals

Transmitter remote version

 ${\it Order\ code\ for\ "Housing"}, option\ N\ "Remote,\ polycarbonate"\ or\ option\ P\ "Remote,\ aluminum\ coated"$




Dimensions in SI units

| A | B | C | D | E | F | G | H |
|------|------|------|------|------|------|------|------|
| [mm] |
| 167 | 24 | 187 | 21 | 232 | 80 | 50 | |

Dimensions in US units

| A | B | C | D | E | F | G | H |
|------|------|------|------|------|------|------|------|
| [in] |
| 6.57 | 0.94 | 7.36 | 0.83 | 9.13 | 3.15 | 1.97 | |

Sensor remote version



■ 23 Engineering unit mm (in)

Dimensions in SI units

| DN 1) | Α | В | С | D | Е | F | G | Н | d 1 | d 2 | e 1 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|-------------------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 25 | 129 | 163 | 143 | 55 | 102 | 192 | 43 | 235 | 86 | 24 | 68 |
| 40 | 129 | 163 | 143 | 69 | 102 | 203 | 52 | 255 | 104 | 38 | 87 |
| 50 | 129 | 163 | 143 | 83 | 102 | 214 | 62 | 276 | 124 | 50 | 106 |
| 65 | 129 | 163 | 143 | 93 | 102 | 224 | 70 | 294 | 139 | 60 | 125 |

| DN 1) | Α | В | С | D | E | F | G | Н | d 1 | d 2 | e 1 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|-------------------|
| [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] |
| 80 | 129 | 163 | 143 | 117 | 102 | 228 | 75 | 303 | 151 | 76 | 135 |
| 100 | 129 | 163 | 143 | 148 | 102 | 242 | 89 | 331 | 179 | 97 | 160 |

- EN (DIN), JIS 1)
- max. Ø seals 2)

Dimensions in US units

| DN 1) | Α | В | С | D | E | F | G | Н | d 1 | d 2 | e 1 ²⁾ | e 2 ²⁾ |
|-------|------|------|------|------|------|------|------|------|------|------|-------------------|-------------------|
| [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] | [in] |
| 1 | 5.08 | 6.42 | 5.63 | 2.17 | 4.02 | 7.56 | 1.69 | 9.25 | 3.39 | 0.94 | 2.68 | - |
| 1 ½ | 5.08 | 6.42 | 5.63 | 2.72 | 4.02 | 7.99 | 2.05 | 10.0 | 4.11 | 1.50 | 3.43 | - |
| 2 | 5.08 | 6.42 | 5.63 | 3.27 | 4.02 | 8.43 | 2.44 | 10.9 | 4.88 | 1.97 | 4.17 | - |
| 3 | 5.08 | 6.42 | 5.63 | 4.61 | 4.02 | 8.98 | 2.95 | 11.9 | 5.94 | 2.99 | - | 5.43 |
| 4 | 5.08 | 6.42 | 5.63 | 5.83 | 4.02 | 9.53 | 3.50 | 13.0 | 7.05 | 3.82 | 6.30 | - |

- ASME
- 2) max. Ø seals

Weight

Compact version

Weight data:

- Including the transmitter

 - Order code for "Housing", option M, Q: 1.3 kg (2.9 lbs)
 Order code for "Housing", option A, R: 2.0 kg (4.4 lbs)
- Excluding packaging material

Weight in SI units

| EN 1092-1 (DIN 2501), JIS B2220 | | | | | | | | |
|---------------------------------|---|--|--|--|--|--|--|--|
| DN | Weigh | t [kg] | | | | | | |
| [mm] | Order code for "Housing", option M, Q: Polycarbonate plastic | Order code for "Housing", option A, R: Aluminum, AlSi10Mg, coated | | | | | | |
| 25 | 2.50 | 3.20 | | | | | | |
| 40 | 3.10 | 3.80 | | | | | | |
| 50 | 3.90 | 4.60 | | | | | | |
| 65 | 4.70 | 5.40 | | | | | | |
| 80 | 5.70 | 6.40 | | | | | | |
| 100 | 8.40 | 9.10 | | | | | | |

Weight in US units

| ASME | ASME B16.5 | | | | | | | | | |
|-----------------|---|--|--|--|--|--|--|--|--|--|
| DN Weight [lbs] | | | | | | | | | | |
| [in] | Order code for "Housing", option M, Q: Polycarbonate plastic | Order code for "Housing", option A, R: Aluminum, AlSi10Mg, coated | | | | | | | | |
| 1 | 5.51 | 7.06 | | | | | | | | |
| 1½ | 6.84 | 8.40 | | | | | | | | |
| 2 | 8.60 | 10.1 | | | | | | | | |

| ASME B16.5 | | | | | |
|------------|---|--|--|--|--|
| DN | Weight [lbs] | | | | |
| [in] | Order code for "Housing", option M, Q: Polycarbonate plastic | Order code for "Housing", option A, R: Aluminum, AlSi10Mg, coated | | | |
| 3 | 12.6 | 14.1 | | | |
| 4 | 18.5 | 20.1 | | | |

Transmitter remote version

Wall-mount housing

Depends on the material of the wall-mount housing:
Polycarbonate plastic: 1.3 kg (2.9 lb)Aluminum, AlSi10Mg, coated: 2.0 kg (4.4 lb)

Sensor remote version

Weight data:

- Including sensor connection housing
- Excluding the connecting cable
- Excluding packaging material

Weight in SI units

| EN 1092-1 (DIN 2501), JIS B2220 | | |
|---------------------------------|----------------|--|
| DN [mm] | Weight [kg] | |
| 25 | 2.5 | |
| 40 | 3.1 | |
| 50 | 3.9 | |
| 65 | 4.7 | |
| 80 | 5.7 | |
| 100 | 8.4 | |

Weight in US units

| ASME B16.5 | | |
|------------|-----------------|--|
| DN [in] | Weight [lbs] | |
| 1 | 5.5 | |
| 1½ | 6.8 | |
| 2 | 8.6 | |
| 3 | 12.6 | |
| 4 | 18.5 | |

Measuring tube specification

Pressure rating EN (DIN)

| Pressure rating PN 16 | | | | | | | | |
|-----------------------|------|-----------|------------|-------|-----------|---------|-------------------|------|
| DN | | Moun | ting bolts | | Length | | internal diameter | |
| | | | | | Centering | sleeves | Measuring tube | |
| [mm] | [in] | | [mm] | [in] | [mm] | [in] | [mm] | [in] |
| 25 | 1 | 4 × M12 × | 145 | 5.71 | 54 | 2.13 | 24 | 0.94 |
| 40 | 1 ½ | 4 × M16 × | 170 | 6.69 | 68 | 2.68 | 38 | 1.50 |
| 50 | 2 | 4 × M16 × | 185 | 7.28 | 82 | 3.23 | 50 | 1.97 |
| 65 ¹⁾ | - | 4 × M16 × | 200 | 7.87 | 92 | 3.62 | 60 | 2.36 |
| 65 ²⁾ | - | 8 × M16 × | 200 | 7.87 | _ 3) | _ | 60 | 2.36 |
| 80 | 3 | 8 × M16 × | 225 | 8.86 | 116 | 4.57 | 76 | 2.99 |
| 100 | 4 | 8 × M16 × | 260 | 10.24 | 147 | 5.79 | 97 | 3.82 |

- 1) EN (DIN) flange: 4-hole \rightarrow with centering sleeves
- 2) EN (DIN) flange: 8-hole \rightarrow without centering sleeves
- 3) A centering sleeve is not required. The device is centered directly via the sensor housing.

ASME pressure rating

| Pressure rating Class 150 | | | | | | | | |
|---------------------------|------|----------------|---------|------|-----------|---------|-------------------|---------|
| DN | | Mounting | j bolts | | Length | | internal diameter | |
| | | | | | Centering | sleeves | Measurii | ng tube |
| [mm] | [in] | | [mm] | [in] | [mm] | [in] | [mm] | [in] |
| 25 | 1 | 4 × UNC ½" × | 145 | 5.70 | _ 1) | - | 24 | 0.94 |
| 40 | 1 ½ | 4 × UNC ½" × | 165 | 6.50 | - | _ | 38 | 1.50 |
| 50 | 2 | 4 × UNC 5/8" × | 190.5 | 7.50 | - | - | 50 | 1.97 |
| 80 | 3 | 8 × UNC 5/8" × | 235 | 9.25 | - | _ | 76 | 2.99 |
| 100 | 4 | 8 × UNC 5/8" × | 264 | 10.4 | 147 | 5.79 | 97 | 3.82 |

1) A centering sleeve is not required. The device is centered directly via the sensor housing.

Pressure rating JIS

| Pressure | Pressure rating 10K | | | | | | | |
|----------|---------------------|-----------|-------------|-------|-----------|---------|-------------------|---------|
| DN | | Mour | iting bolts | | Length | | internal diameter | |
| | | | | | Centering | sleeves | Measurii | ng tube |
| [mm] | [in] | | [mm] | [in] | [mm] | [in] | [mm] | [in] |
| 25 | 1 | 4 × M16 × | 170 | 6.69 | 54 | 2.13 | 24 | 0.94 |
| 40 | 1 ½ | 4 × M16 × | 170 | 6.69 | 68 | 2.68 | 38 | 1.50 |
| 50 | 2 | 4 × M16 × | 185 | 7.28 | _ 1) | _ | 50 | 1.97 |
| 65 | - | 4 × M16 × | 200 | 7.87 | _ | _ | 60 | 2.36 |
| 80 | 3 | 8 × M16 × | 225 | 8.86 | - | - | 76 | 2.99 |
| 100 | 4 | 8 × M16 × | 260 | 10.24 | - | - | 97 | 3.82 |

1) A centering sleeve is not required. The device is centered directly via the sensor housing.

Materials

Transmitter housing


Order Code for "Housing"

- Compact version, standard:
 - Option A: aluminum, AlSi10Mg, coated
 - Option **M**: polycarbonate plastic
- Compact version, inclined:
 - Option **Q**: polycarbonate plastic
 - Option R: aluminum, AlSi10Mg, coated
- Remote version (wall-mount housing):
 - Option **N**: polycarbonate plastic
 - Option **P**: aluminum, AlSi10Mg, coated

Window material

| Transmitter housing material | Window material |
|------------------------------|-----------------|
| Polycarbonate plastic | Plastic |
| Aluminum, AlSi10Mg, coated | Glass |

Cable entries/cable glands



A002064

■ 24 Possible cable entries/cable glands

- 1 Cable entry in transmitter housing, wall-mount housing or connection housing with internal thread M20 x 1.5
- 2 Cable gland M20 x 1.5
- 3 Adapter for cable entry with internal thread G ½" or NPT ½"

Compact and remote versions and sensor connection housing

| Cable entry/cable gland | Material |
|--|---|
| Cable gland M20 × 1.5 | Plastic |
| Remote version: cable gland M20 \times 1.5 Option of reinforced connecting cable | Sensor connection housing: Nickel-plated brass Transmitter wall-mount housing: Plastic |
| Adapter for cable entry with internal thread G ½" or NPT ½" | Nickel-plated brass |

Device plug

| Electrical connection | Material |
|-----------------------|---|
| Plug M12x1 | Socket: Stainless steel, 1.4404 (316L) Contact housing: Polyamide Contacts: Gold-plated brass |

Connecting cable for remote version

Electrode and coil current cable

- Standard cable: PVC cable with copper shield
- Reinforced cable: PVC cable with copper shield and additional steel wire braided jacket

Sensor housing

Aluminum, AlSi10Mg, coated

Sensor connection housing

Aluminum, AlSi10Mg, coated

Sensor cable entries

Order code for "Housing", option N "Remote, polycarbonate" or option P "Remote, coated aluminum". The various cable entries are suitable for hazardous and non-hazardous areas.

| Electrical connection | Material |
|------------------------------|---------------------|
| Cable gland M20 × 1.5 | Nickel-plated brass |
| Thread G ½" via adapter | Nickel-plated brass |
| Thread NPT ½" via adapter | Nickel-plated brass |

Liner


Polyamide

Electrodes

Stainless steel, 1.4435/F316L

Process connections

- EN 1092-1 (DIN 2501)
- ASME B16.5
- JIS B2220



Seals

O-rings made from EPDM

Accessories

Display protection

Stainless steel, 1.4301 (304L)

Ground disks

Stainless steel ,1.4301/304

Mounting bolts

Tensile strength

- Galvanized steel mounting bolts: strength category 5.6 or 5.8
- Stainless steel mounting bolts: strength category A2-70

Fitted electrodes

2 measuring electrodes made of 1.4435 (316L)

Process connections

- EN 1092-1 (DIN 2501)
- ASME B16.5
- JIS B2220

For information on the materials of the process connections ($\rightarrow \implies 45$)

Operability

Operating concept

Operator-oriented menu structure for user-specific tasks

- Commissioning
- Operation
- Diagnostics
- Expert level

Quick and safe commissioning

- Guided menus ("Make-it-run" wizards) for applications
- Menu quidance with brief explanations of the individual parameter functions

Reliable operation


- Operation in the following languages:
 - Via local display:
 - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech
 - Via "FieldCare" operating tool:
 - English, German, French, Spanish, Italian, Chinese, Japanese
 - Via Web browser:
 - English, German, French, Spanish, Italian, Dutch, Portuguese, Polish, Russian, Turkish, Chinese, Japanese, Bahasa (Indonesian), Vietnamese, Czech
- Uniform operating philosophy applied to device, operating tools and Web browser
- If replacing the electronic module, transfer the device configuration via the plug-in memory (HistoROM DAT) which contains the process and measuring device data and the event logbook. No need to reconfigure.

Efficient diagnostics increase measurement availability

- Troubleshooting measures can be called up via the device, operating tools and Web browser
- Diverse simulation options, logbook for events that occur and optional line recorder functions

Local operation

Via display module



A0020538

Display elements

- 4-line display
- White background lighting; switches to red in event of device errors
- Format for displaying measured variables and status variables can be individually configured
- Permitted ambient temperature for the display: -20 to +50 °C (-4 to +122 °F) The readability of the display may be impaired at temperatures outside the temperature range.

Operating elements


External operation via touch control; 3 optical keys: 🕞, 🗐, 📵

Additional functionality

- Data backup function
 - The device configuration can be saved in the display module.
- Data comparison function
 - The device configuration saved in the display module can be compared to the current device configuration.
- Data transfer function
 - The transmitter configuration can be transmitted to another device using the display module.

Remote operation

Via HART protocol




A0017124

25 Options for remote operation via HART protocol

- Control system (e.g. PLC)
- 2 Field Communicator 475
- Computer with operating tool (e.g. FieldCare, AMS Device Manager, SIMATIC PDM)
- Commubox FXA195 (USB)
- Field Xpert SFX350 or SFX370
- VIATOR Bluetooth modem with connecting cable
- Transmitter

Via PROFIBUS DP network


This communication interface is present in the following device version: Order code for "Output", option \mathbf{L} : PROFIBUS DP



- 1 Automation system
- Computer with PROFIBUS network card 2
- PROFIBUS DP network 3
- Measuring device

Via Ethernet-based fieldbus

This communication interface is present in the following device version: Order code for "Output", option **N**: EtherNet/IP



- 1 Ethernet network
- Automation system, e.g. "RSLogix" (Rockwell Automation) 2
- 3 Workstation for measuring device operation: with Add-on Profile Level 3 for "RSLogix 5000" (Rockwell Automation) or with Electronic Data Sheet (EDS)
- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- Ethernet switch
- Measuring device

Service interface


Service interface (CDI-RJ45)

This communication interface is present in the following device version:

- Order code for "Output", option **H**: 4-20/0-20 mA HART, pulse/frequency/switch output
- Order code for "Output", option I: 4-20/0-20 mA HART, pulse/frequency/switch output, status
- Order code for "Output", option **L**: PROFIBUS DP
- Order code for "Output", option M: Modbus RS485

48


HART



- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server


PROFIBUS DP

1




- A0023114
- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- 2 Standard Ethernet connecting cable with RJ45 plug
- 3 Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server

EtherNet/IP



- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- Standard Ethernet connecting cable with RJ45 plug
- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server

Modbus RS485



- Computer with Web browser (e.g. Internet Explorer) for accessing the integrated device Web server or with "FieldCare" operating tool with COM DTM "CDI Communication TCP/IP"
- Standard Ethernet connecting cable with RJ45 plug
- Service interface (CDI -RJ45) of the measuring device with access to the integrated Web server

Certificates and approvals

CE mark

The measuring system is in conformity with the statutory requirements of the applicable EC Directives. These are listed in the corresponding EC Declaration of Conformity along with the standards applied.

Endress+Hauser confirms successful testing of the device by affixing to it the CE mark.

C-Tick symbol

The measuring system meets the EMC requirements of the "Australian Communications and Media Authority (ACMA)".

Drinking water approval

- ACS
- KTW/W270
- NSF 61
- WRAS BS 6920

Certification PROFIBUS

PROFIBUS interface

The measuring device is certified and registered by the PROFIBUS User Organization (PNO). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with PROFIBUS PA Profile 3.02
- The device can also be operated with certified devices of other manufacturers (interoperability)

Modbus RS485 certification

The measuring device meets all the requirements of the MODBUS/TCP conformity test and has the "MODBUS/TCP Conformance Test Policy, Version 2.0". The measuring device has successfully passed all the test procedures carried out and is certified by the "MODBUS/TCP Conformance Test Laboratory" of the University of Michigan.

EtherNet/IP certification

The measuring device is certified and registered by the ODVA (Open Device Vendor Association). The measuring system meets all the requirements of the following specifications:

- Certified in accordance with the ODVA Conformance Test
- EtherNet/IP Performance Test
- EtherNet/IP PlugFest compliance
- The device can also be operated with certified devices of other manufacturers (interoperability)

Other standards and guidelines

■ EN 60529

Degrees of protection provided by enclosures (IP code)

■ EN 61010-1

Safety requirements for electrical equipment for measurement, control and laboratory use

■ IEC/EN 61326

Emission in accordance with Class A requirements. Electromagnetic compatibility (EMC requirements).

■ ANSI/ISA-61010-1 (82.02.01): 2004

Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements

CAN/CSA-C22.2 No. 61010-1-04

Safety Requirements for Electrical Equipment for Measurement, Control and Laboratory Use - Part 1 General Requirements

■ NAMUR NE 21

Electromagnetic compatibility (EMC) of industrial process and laboratory control equipment

■ NAMUR NE 32

Data retention in the event of a power failure in field and control instruments with microprocessors

■ NAMUR NE 43

Standardization of the signal level for the breakdown information of digital transmitters with analog output signal.

■ NAMUR NE 53

Software of field devices and signal-processing devices with digital electronics

■ NAMUR NE 105

Specifications for integrating fieldbus devices in engineering tools for field devices

■ NAMUR NE 107

Self-monitoring and diagnosis of field devices

■ NAMUR NE 131

Requirements for field devices for standard applications

Ordering information

Detailed ordering information is available from the following sources:

- In the Product Configurator on the Endress+Hauser web site: www.endress.com → Choose your country → Products → Select measuring technology, software or components → Select product (picklists: measurement method, product family etc.) → Device support (right-hand column): Configure the selected product → The Product Configurator for the selected product is opened.
- From your Endress+Hauser Sales Center: www.addresses.endress.com

Product Configurator - the tool for individual product configuration

- Up-to-the-minute configuration data
- Depending on the device: Direct input of measuring point-specific information such as measuring range or operating language
- Automatic verification of exclusion criteria
- Automatic creation of the order code and its breakdown in PDF or Excel output format
- Ability to order directly in the Endress+Hauser Online Shop

Application packages

Many different application packages are available to enhance the functionality of the device. Such packages might be needed to address safety aspects or specific application requirements.

The application packages can be ordered from Endress+Hauser either directly with the device or subsequently. Detailed information on the order code in question is available from your local Endress +Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Diagnostics functions

| Package | Description |
|----------------------------|---|
| HistoROM extended function | Comprises extended functions concerning the event log and the activation of the measured value memory. |
| | Event log: Memory volume is extended from 20 message entries (basic version) to up to 100 entries. |
| | Data logging (line recorder): Memory capacity for up to 1000 measured values is activated. 250 measured values can be output via each of the 4 memory channels. The recording interval can be defined and configured by the user. Data logging is visualized via the local display or FieldCare. |

Heartbeat Technology

| Package | Description |
|---------------------------------------|---|
| Heartbeat Verification +Monitoring | Heartbeat Monitoring: Continuously supplies monitoring data, which are characteristic of the measuring principle, for an external condition monitoring system. This makes it possible to: Draw conclusions - using these data and other information - about the impact the measuring application has on the measuring performance over time. Schedule servicing in time. Monitor the product quality, e.g. gas pockets. |
| | Heartbeat Verification: Makes it possible to check the device functionality on demand when the device is installed, without having to interrupt the process. Access via onsite operation or other operating interfaces, such as FieldCare for instance. End-to-end, traceable documentation of the verification results, including report. Makes it possible to extend calibration intervals in accordance with operator's risk assessment. |

Accessories

Various accessories, which can be ordered with the device or subsequently from Endress+Hauser, are available for the device. Detailed information on the order code in question is available from your local Endress+Hauser sales center or on the product page of the Endress+Hauser website: www.endress.com.

Device-specific accessories

For the transmitter

| Accessories | Description |
|-------------------------------------|--|
| Display protection | Is used to protect the display against impact or scoring from sand in desert areas. For details, see Special Documentation SD00333F |
| Connecting cable for remote version | Coil current and electrode cables, various lengths, reinforced cables available on request. |
| Post mounting kit | Post mounting kit for transmitter. |
| Compact → remote conversion kit | For converting a compact device version to a remote device version. |

For the sensor

| Accessories | Description |
|--------------|--|
| Mounting kit | Consists of: 2 process connections Threaded fasteners Seals |

Communication-specific accessories

| Accessories | Description | |
|--------------------------------|--|--|
| Commubox FXA195 HART | For intrinsically safe HART communication with FieldCare via the USB interface. For details, see "Technical Information" TI00404F | |
| HART Loop Converter HMX50 | Is used to evaluate and convert dynamic HART process variables to analog current signals or limit values. For details, see "Technical Information" TI00429F and Operating Instructions BA00371F | |
| Wireless HART adapter SWA70 | Is used for the wireless connection of field devices. The WirelessHART adapter can be easily integrated into field devices and existing infrastructures, offers data protection and transmission safety and can be operated in parallel with other wireless networks with minimum cabling complexity. For details, see Operating Instructions BA00061S | |
| Fieldgate FXA320 | Gateway for the remote monitoring of connected 4-20 mA measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00053S | |
| Fieldgate FXA520 | Gateway for the remote diagnostics and remote configuration of connected HART measuring devices via a Web browser. For details, see "Technical Information" TI00025S and Operating Instructions BA00051S | |
| Field Xpert SFX350 | Field Xpert SFX350 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area . For details, see Operating Instructions BA01202S | |
| Field Xpert SFX370 | Field Xpert SFX370 is a mobile computer for commissioning and maintenance. It enables efficient device configuration and diagnostics for HART and FOUNDATION Fieldbus devices in the non-Ex area and the Ex area . For details, see Operating Instructions BA01202S | |

Service-specific accessories

| Accessories | Description | |
|-----------------|--|--|
| Applicator | Software for selecting and sizing Endress+Hauser measuring devices: Calculation of all the necessary data for identifying the optimum flowmeter: e.g. nominal diameter, pressure loss, accuracy or process connections. Graphic illustration of the calculation results | |
| | Administration, documentation and access to all project-related data and parameters throughout the entire life cycle of a project. | |
| | Applicator is available: Via the Internet: https://wapps.endress.com/applicator On CD-ROM for local PC installation. | |
| W@M | Life cycle management for your plant W@M supports you with a wide range of software applications over the entire process: from planning and procurement, to the installation, commissioning and operation of the measuring devices. All the relevant device information, such as the device status, spare parts and device-specific documentation, is available for every device over the entire life cycle. The application already contains the data of your Endress+Hauser device. Endress +Hauser also takes care of maintaining and updating the data records. | |
| | W@M is available: Via the Internet: www.endress.com/lifecyclemanagement On CD-ROM for local PC installation. | |
| FieldCare | FDT-based plant asset management tool from Endress+Hauser. It can configure all smart field units in your system and helps you manage them using the status information, it is also a simple but effective way of checking th status and condition. | |
| | For details, see Operating Instructions BA00027S and BA00059S | |
| Commubox FXA291 | Connects Endress+Hauser field devices with a CDI interface (= Endress+Hauser Common Data Interface) and the USB port of a computer or laptop. | |
| | For details, see "Technical Information" TI00405C | |

System components

| Accessories | Description |
|---|---|
| Memograph M graphic display recorder | The Memograph M graphic display recorder provides information on all relevant measured variables. Measured values are recorded correctly, limit values are monitored and measuring points analyzed. The data are stored in the 256 MB internal memory and also on a SD card or USB stick. |
| | For details, see "Technical Information" TI00133R and Operating Instructions BA00247R |

Supplementary documentation



For an overview of the scope of the associated Technical Documentation, refer to the following:

- The CD-ROM provided for the device (depending on the device version, the CD-ROM might not be part of the delivery!)
- The W@M Device Viewer: Enter the serial number from the nameplate (www.endress.com/deviceviewer)
- The *Endress+Hauser Operations App*: Enter the serial number from the nameplate or scan the 2-D matrix code (QR code) on the nameplate.

Standard documentation

Brief Operating Instructions

| Measuring device | Documentation code |
|------------------|--------------------|
| Promag D 400 | KA01112D |

54

Operating Instructions

| Measuring device | Documentation code | | | |
|------------------|--------------------|-------------|--------------|-------------|
| | HART | PROFIBUS DP | Modbus RS485 | EtherNet/IP |
| Promag D 400 | BA01061D | BA01232D | BA01229D | BA01212D |

Supplementary devicedependent documentation

Special Documentation

| Contents | Documentation code |
|-----------------------------------|--------------------|
| Modbus RS485 Register Information | SD01379D |
| Heartbeat Technology | SD01183D |

Installation Instructions

| Contents | Documentation code |
|---|--|
| Installation Instructions for spare part sets | Specified for each individual accessory (→ 🖺 52) |

Registered trademarks

HART®

Registered trademark of the HART Communication Foundation, Austin, USA

PROFIBUS®

Registered trademark of the PROFIBUS User Organization, Karlsruhe, Germany

Modbus®

Registered trademark of SCHNEIDER AUTOMATION, INC.

EtherNet/IPTM

Trademark of ODVA, Inc.

Microsoft®

Registered trademark of the Microsoft Corporation, Redmond, Washington, USA

Applicator®, FieldCare®, Field XpertTM, HistoROM®, Heartbeat TechnologyTM Registered or registration-pending trademarks of the Endress+Hauser Group

www.addresses.endress.com

